

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010700

Luminaire Tested: S123DIP-B775D1025UB2750-4F0-XX-W2A-D_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010700
REPORT IS A COMBINATION OF REPORTS P990234 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B775D1025UB2750-4F0-XX-W2A-D_3000K
Description: Define 3 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7304.0 lumens
Efficiency: N/A
Efficacy: 113.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.25 / 1.37
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 64.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010700

CATALOG NUMBER: S123DIP-B775D1025UB2750-4F0-XX-W2A-D_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010700

CATALOG NUMBER: S123DIP-B775D1025UB2750-4F0-XX-W2A-D_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48			41
1	95	90	86	82	86	82	79	75	67	65	62	53	52	50	41	40	38			33
2	86	78	72	66	78	71	66	61	58	54	51	46	44	41	35	33	32			27
3	78	68	61	55	71	62	56	51	51	46	42	41	37	34	31	29	27			22
4	71	60	52	46	65	55	48	43	45	40	36	36	32	29	28	25	23			19
5	65	54	45	39	59	49	42	36	40	35	31	32	28	25	25	22	20			16
6	60	48	40	34	54	44	37	31	36	31	27	29	25	22	22	19	17			14
7	56	43	35	30	50	40	32	27	33	27	23	26	22	19	20	17	15			12
8	51	39	31	26	47	36	29	24	30	24	21	24	20	17	19	16	14			11
9	48	36	28	23	43	33	26	21	27	22	18	22	18	15	17	14	12			10
10	45	33	25	21	41	30	24	19	25	20	16	20	16	14	16	13	11			9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10399	10399	10399
5°	10428	10094	10086
10°	10330	9820	9746
15°	10194	9519	9385
20°	9999	9182	8997
25°	9760	8803	8596
30°	9516	8460	8193
35°	9243	8101	7865
40°	8980	7771	7518
45°	8691	7453	7232
50°	8404	7136	6922
55°	8085	6814	6637
60°	7775	6482	6345
65°	7455	6129	6002
70°	6973	5733	5650
75°	6364	5281	5285
80°	5657	4825	4870
85°	4956	4456	4573

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 8691 cd/sqm

TEST NUMBER: P1010700

CATALOG NUMBER: S123DIP-B775D1025UB2750-4F0-XX-W2A-D_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.6	1.3
10°-20°	261.3	3.6
20°-30°	390.7	5.3
30°-40°	466.5	6.4
40°-50°	488.1	6.7
50°-60°	458.0	6.3
60°-70°	382.6	5.2
70°-80°	273.6	3.7
80°-90°	165.5	2.3
90°-100°	149.2	2.0
100°-110°	301.9	4.1
110°-120°	605.8	8.3
120°-130°	734.0	10.0
130°-140°	766.4	10.5
140°-150°	707.3	9.7
150°-160°	568.4	7.8
160°-170°	366.8	5.0
170°-180°	126.4	1.7
0°-30°	743.6	10.2
0°-40°	1210.1	16.6
0°-60°	2156.2	29.5
0°-90°	2977.8	40.8
90°-120°	1056.9	14.5
90°-150°	3264.7	44.7
90°-180°	4326.0	59.2
0°-180°	7304.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	966	966	966	966	966	
5°	967	965	959	967	966	92
15°	921	924	923	934	932	259
25°	831	842	845	859	859	383
35°	716	732	746	762	766	448
45°	585	610	637	657	665	451
55°	446	481	519	547	556	400
65°	308	349	396	427	438	305
75°	167	217	269	304	317	179
85°	52	104	160	196	206	53
90°	15	76	143	182	195	13
95°	72	72	135	174	185	81
105°	303	339	295	150	161	321
115°	558	576	623	658	670	551
125°	782	790	824	848	858	699
135°	971	976	992	1014	1016	748
145°	1120	1125	1127	1138	1142	701
155°	1232	1230	1231	1236	1230	568
165°	1299	1296	1295	1303	1296	367
175°	1330	1325	1326	1333	1325	127
180°	1330	1330	1330	1330	1330	

TEST NUMBER: P1010700

CATALOG NUMBER: S123DIP-B775D1025UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	966.1	966.1	966.1	966.1	966.1
2.5°	971.4	968.2	959.8	968.2	967.2
5°	967.2	965.1	958.8	967.2	966.1
7.5°	959.8	959.8	953.5	964.0	963.0
10°	949.3	951.4	946.1	956.7	954.6
12.5°	936.7	939.8	936.7	946.1	944.0
15°	920.9	924.0	923.0	933.5	932.5
17.5°	901.9	908.3	907.2	916.7	914.6
20°	880.9	887.2	889.3	898.8	899.8
22.5°	858.8	865.1	868.3	880.9	879.8
25°	831.4	842.0	845.1	858.8	858.8
27.5°	805.1	816.7	823.0	834.6	835.6
30°	776.7	790.4	798.8	811.4	811.4
32.5°	745.1	760.9	772.5	786.2	789.3
35°	715.7	732.5	746.2	762.0	766.2
37.5°	684.1	703.0	718.8	736.7	739.9
40°	652.5	671.5	692.5	710.4	714.6
42.5°	617.8	642.0	664.1	684.1	690.4
45°	585.2	610.4	636.7	656.7	665.1
47.5°	550.4	578.8	608.3	630.4	636.7
50°	516.8	546.2	578.8	603.1	610.4
52.5°	481.0	512.5	549.4	574.6	584.1
55°	446.2	481.0	518.9	547.3	555.7
57.5°	412.6	448.3	489.4	517.8	527.3
60°	376.8	414.7	457.8	487.3	498.9
62.5°	343.1	382.0	428.3	457.8	468.3
65°	308.4	349.4	395.7	427.3	437.8
67.5°	273.6	316.8	363.1	397.8	406.2
70°	236.8	282.1	332.6	366.3	376.8
72.5°	203.1	248.4	301.0	335.7	346.3
75°	167.3	216.8	269.4	304.2	316.8
77.5°	136.8	186.3	238.9	275.7	285.2
80°	104.2	155.8	210.5	246.3	256.8
82.5°	75.8	128.4	184.2	220.0	230.5
85°	51.6	104.2	160.0	195.8	206.3
87.5°	31.6	84.2	137.9	173.7	184.2
90°	14.7	76.2	142.6	182.4	194.8
92.5°	35.3	74.7	136.2	177.8	188.3
95°	71.9	72.4	134.8	174.3	184.8
97.5°	120.2	130.4	129.5	169.0	180.5
100°	176.5	229.9	124.2	162.6	174.1
102.5°	240.6	282.9	158.3	155.2	167.7
105°	302.8	339.0	295.3	149.9	161.4
107.5°	368.0	399.0	456.9	333.2	213.3
110°	433.1	460.0	513.0	507.7	374.8

TEST NUMBER: P1010700

CATALOG NUMBER: S123DIP-B775D1025UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	496.4	518.0	568.9	604.1	611.6
115°	557.6	576.1	622.9	658.0	670.5
117.5°	618.9	634.2	674.9	708.0	717.4
120°	674.1	688.3	726.0	758.1	765.5
122.5°	731.4	740.4	777.0	805.1	813.5
125°	781.8	789.7	824.1	848.2	857.5
127.5°	833.2	840.0	871.2	895.3	900.6
130°	880.6	887.4	912.4	936.4	940.7
132.5°	924.9	932.8	951.6	974.5	978.9
135°	971.4	976.3	991.8	1013.7	1016.0
137.5°	1010.9	1017.8	1027.1	1048.9	1052.1
140°	1049.4	1055.3	1061.4	1081.2	1084.5
142.5°	1086.0	1090.8	1093.8	1110.4	1112.7
145°	1119.6	1125.4	1127.4	1137.7	1141.9
147.5°	1151.1	1156.0	1158.0	1163.2	1162.4
150°	1180.7	1183.7	1185.7	1187.6	1186.8
152.5°	1207.4	1208.4	1209.4	1213.3	1208.4
155°	1232.1	1230.1	1231.1	1236.0	1230.1
157.5°	1251.9	1251.9	1250.9	1256.8	1248.9
160°	1269.6	1268.7	1267.7	1273.6	1266.7
162.5°	1286.4	1283.5	1282.5	1289.4	1283.5
165°	1299.3	1296.3	1295.3	1303.2	1296.3
167.5°	1310.1	1306.2	1306.2	1314.1	1306.2
170°	1319.0	1315.1	1315.1	1323.0	1315.1
172.5°	1325.0	1320.0	1321.0	1328.9	1320.0
175°	1329.9	1325.0	1326.0	1332.9	1325.0
177.5°	1331.9	1326.9	1327.9	1335.8	1326.0
180°	1329.9	1329.9	1329.9	1329.9	1329.9

(END OF REPORT)