

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010423

Luminaire Tested: S123DIP-B1000D1195UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010423
REPORT IS A COMBINATION OF REPORTS P989102 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B1000D1195UB2750-4F0-XX-W2A-F_5000K
Description: Define 3 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8521.0 lumens
Efficiency: N/A
Efficacy: 104.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 81.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010423

CATALOG NUMBER: S123DIP-B1000D1195UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010423

CATALOG NUMBER: S123DIP-B1000D1195UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	98	98	98	98	81	81	81	66	66	66	53	53	53
1	97	93	89	85	89	85	82	79	71	69	67	58	57	55	46	45	44
2	88	81	75	70	81	74	69	65	62	58	55	51	48	46	41	39	37
3	80	71	64	58	74	65	59	54	55	50	46	45	42	39	36	34	32
4	74	63	55	49	67	58	51	46	49	44	39	40	36	33	32	30	27
5	67	56	48	42	62	52	44	39	44	38	34	36	32	29	29	26	24
6	62	50	42	36	57	46	39	34	39	34	30	33	28	25	26	23	21
7	57	45	37	32	53	42	35	30	36	30	26	30	25	22	24	21	19
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	17
9	50	37	30	25	45	35	28	23	30	24	21	25	21	18	20	17	15
10	46	34	27	22	43	32	25	21	27	22	19	23	19	16	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16283	16283	16283
5°	16323	15721	15697
10°	16178	15189	15033
15°	15953	14635	14309
20°	15696	14022	13592
25°	15362	13373	12824
30°	14997	12702	12018
35°	14614	12016	11216
40°	14214	11298	10428
45°	13773	10596	9603
50°	13326	9815	8776
55°	12751	9001	7939
60°	12158	8103	7047
65°	11603	7132	6116
70°	10802	6054	5032
75°	9647	4793	3906
80°	8333	3369	2763
85°	6493	1810	1383

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13773 cd/sqm

TEST NUMBER: P1010423

CATALOG NUMBER: S123DIP-B1000D1195UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	142.6	1.7
10°-20°	402.7	4.7
20°-30°	594.7	7.0
30°-40°	694.6	8.2
40°-50°	698.3	8.2
50°-60°	613.4	7.2
60°-70°	456.8	5.4
70°-80°	260.0	3.1
80°-90°	76.9	0.9
90°-100°	53.0	0.6
100°-110°	256.2	3.0
110°-120°	627.8	7.4
120°-130°	797.0	9.4
130°-140°	851.4	10.0
140°-150°	796.2	9.3
150°-160°	642.2	7.5
160°-170°	414.4	4.9
170°-180°	142.8	1.7
0°-30°	1140.0	13.4
0°-40°	1834.6	21.5
0°-60°	3146.3	36.9
0°-90°	3940.0	46.2
90°-120°	937.0	11.0
90°-150°	3381.6	39.7
90°-180°	4581.0	53.8
0°-180°	8521.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1513	1513	1513	1513	1513	
5°	1514	1508	1493	1506	1504	144
15°	1441	1436	1419	1430	1422	406
25°	1308	1301	1284	1285	1281	603
35°	1132	1124	1107	1099	1093	708
45°	927	922	905	890	883	716
55°	704	702	686	671	665	630
65°	480	474	460	450	446	474
75°	254	248	244	238	234	271
85°	68	65	65	62	62	73
90°	1	12	27	31	34	8
95°	68	22	35	42	42	81
105°	333	345	244	47	49	353
115°	624	631	641	652	656	616
125°	880	889	893	895	898	786
135°	1095	1102	1106	1110	1106	843
145°	1264	1272	1274	1276	1276	791
155°	1392	1390	1391	1397	1390	641
165°	1468	1465	1464	1472	1465	415
175°	1503	1497	1498	1506	1497	143
180°	1503	1503	1503	1503	1503	

TEST NUMBER: P1010423

CATALOG NUMBER: S123DIP-B1000D1195UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1512.7	1512.7	1512.7	1512.7	1512.7
2.5°	1519.2	1514.0	1499.7	1512.7	1511.4
5°	1514.0	1507.5	1493.2	1506.2	1503.6
7.5°	1502.3	1495.8	1481.5	1493.2	1491.9
10°	1486.7	1480.2	1463.3	1475.0	1472.4
12.5°	1465.9	1460.7	1445.1	1452.9	1451.6
15°	1441.2	1436.0	1419.1	1429.5	1421.7
17.5°	1413.9	1407.4	1390.5	1398.3	1395.7
20°	1382.7	1374.9	1358.0	1363.2	1359.3
22.5°	1347.6	1339.7	1322.8	1326.7	1321.5
25°	1308.5	1300.7	1283.8	1285.1	1281.2
27.5°	1268.2	1260.4	1242.2	1243.5	1239.6
30°	1224.0	1217.5	1199.3	1199.3	1190.2
32.5°	1179.8	1170.7	1157.6	1148.5	1144.6
35°	1131.6	1123.8	1106.9	1099.1	1092.6
37.5°	1083.5	1073.1	1056.2	1047.1	1043.2
40°	1032.8	1025.0	1006.8	996.4	991.2
42.5°	982.0	972.9	954.7	944.3	939.1
45°	927.4	922.2	905.3	889.7	883.2
47.5°	874.1	866.3	850.7	835.1	829.9
50°	819.5	813.0	796.0	781.7	773.9
52.5°	762.2	758.3	740.1	728.4	720.6
55°	703.7	702.4	685.5	671.2	664.7
57.5°	649.1	643.9	630.9	617.8	610.0
60°	589.2	587.9	572.3	560.6	554.1
62.5°	535.9	532.0	516.4	504.7	500.8
65°	480.0	473.5	460.5	450.1	446.1
67.5°	420.1	414.9	404.5	395.4	390.2
70°	366.8	359.0	351.2	342.1	335.6
72.5°	310.9	305.7	296.6	288.8	286.2
75°	253.6	248.4	244.5	238.0	234.1
77.5°	202.9	200.3	195.1	189.9	189.9
80°	153.5	149.6	147.0	145.7	145.7
82.5°	105.4	105.4	105.4	102.8	101.5
85°	67.6	65.0	65.0	62.4	62.4
87.5°	33.8	29.9	28.6	27.3	27.3
90°	1.1	12.3	26.8	31.3	33.5
92.5°	25.7	19.0	29.0	36.8	38.0
95°	68.1	22.3	34.6	42.4	42.4
97.5°	123.9	92.7	35.7	44.7	45.8
100°	188.7	211.0	36.8	45.8	46.9
102.5°	262.4	276.9	82.6	45.8	48.0
105°	332.7	345.0	244.5	46.9	49.1
107.5°	407.5	417.5	434.3	262.4	116.1
110°	482.3	491.2	503.5	466.7	307.0



TEST NUMBER: P1010423

CATALOG NUMBER: S123DIP-B1000D1195UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	553.7	561.5	573.8	583.9	581.6
115°	624.1	630.8	640.8	652.0	656.4
117.5°	693.3	701.1	706.7	715.6	716.7
120°	756.9	767.0	770.3	779.2	779.2
122.5°	821.7	829.5	833.9	839.5	840.6
125°	879.7	888.6	893.1	895.3	897.6
127.5°	937.8	946.7	952.3	955.6	953.4
130°	991.4	1000.3	1004.8	1009.2	1007.0
132.5°	1042.7	1051.6	1055.0	1059.5	1056.1
135°	1095.2	1101.9	1106.3	1109.7	1106.3
137.5°	1139.8	1148.8	1151.0	1156.6	1154.3
140°	1184.5	1191.2	1194.5	1199.0	1196.8
142.5°	1225.8	1232.5	1235.8	1239.2	1235.8
145°	1263.8	1271.6	1273.8	1276.0	1276.0
147.5°	1300.6	1306.2	1308.4	1310.6	1305.1
150°	1334.1	1337.4	1339.7	1341.9	1338.6
152.5°	1364.2	1365.3	1366.5	1370.9	1365.3
155°	1392.1	1389.9	1391.0	1396.6	1389.9
157.5°	1414.5	1414.5	1413.4	1420.1	1411.1
160°	1434.6	1433.4	1432.3	1439.0	1431.2
162.5°	1453.5	1450.2	1449.1	1456.9	1450.2
165°	1468.1	1464.7	1463.6	1472.5	1464.7
167.5°	1480.3	1475.9	1475.9	1484.8	1475.9
170°	1490.4	1485.9	1485.9	1494.8	1485.9
172.5°	1497.1	1491.5	1492.6	1501.5	1491.5
175°	1502.7	1497.1	1498.2	1506.0	1497.1
177.5°	1504.9	1499.3	1500.4	1509.4	1498.2
180°	1502.7	1502.7	1502.7	1502.7	1502.7

(END OF REPORT)