

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010702

Luminaire Tested: S123DIP-B775D1025UB2750-4F0-XX-W2A-D_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010702
REPORT IS A COMBINATION OF REPORTS P990236 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B775D1025UB2750-4F0-XX-W2A-D_4000K
Description: Define 3 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7263.0 lumens
Efficiency: N/A
Efficacy: 112.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.25 / 1.37
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 64.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010702

CATALOG NUMBER: S123DIP-B775D1025UB2750-4F0-XX-W2A-D_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010702

CATALOG NUMBER: S123DIP-B775D1025UB2750-4F0-XX-W2A-D_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48
1	95	90	86	82	86	82	79	75	67	65	62	53	52	50	41	40	38
2	86	78	72	66	78	71	66	61	58	54	51	46	44	41	35	33	32
3	78	68	61	55	71	62	56	51	51	46	42	41	37	34	31	29	27
4	71	60	52	46	65	55	48	43	45	40	36	36	32	29	28	25	23
5	65	54	45	39	59	49	42	36	40	35	31	32	28	25	25	22	20
6	60	48	40	34	54	44	37	31	36	31	27	29	25	22	22	19	17
7	56	43	35	30	50	40	32	27	33	27	23	26	22	19	20	17	15
8	51	39	31	26	47	36	29	24	30	24	21	24	20	17	19	16	14
9	48	36	28	23	43	33	26	21	27	22	18	22	18	15	17	14	12
10	45	33	25	21	41	30	24	19	25	20	16	20	16	14	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10342	10342	10342
5°	10370	10039	10030
10°	10273	9766	9692
15°	10137	9466	9333
20°	9944	9132	8948
25°	9706	8754	8548
30°	9464	8414	8147
35°	9191	8055	7821
40°	8931	7728	7476
45°	8642	7412	7193
50°	8357	7097	6883
55°	8041	6775	6600
60°	7732	6446	6309
65°	7414	6095	5969
70°	6935	5701	5618
75°	6330	5252	5255
80°	5624	4797	4844
85°	4928	4431	4546

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8642 cd/sqm

TEST NUMBER: P1010702

CATALOG NUMBER: S123DIP-B775D1025UB2750-4F0-XX-W2A-D_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.1	1.3
10°-20°	259.8	3.6
20°-30°	388.5	5.3
30°-40°	463.9	6.4
40°-50°	485.4	6.7
50°-60°	455.5	6.3
60°-70°	380.5	5.2
70°-80°	272.0	3.7
80°-90°	164.5	2.3
90°-100°	148.3	2.0
100°-110°	300.2	4.1
110°-120°	602.4	8.3
120°-130°	729.9	10.0
130°-140°	762.0	10.5
140°-150°	703.3	9.7
150°-160°	565.1	7.8
160°-170°	364.7	5.0
170°-180°	125.7	1.7
0°-30°	739.5	10.2
0°-40°	1203.4	16.6
0°-60°	2144.3	29.5
0°-90°	2961.3	40.8
90°-120°	1051.0	14.5
90°-150°	3246.2	44.7
90°-180°	4302.0	59.2
0°-180°	7263.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	961	961	961	961	961	
5°	962	960	954	962	961	91
15°	916	919	918	928	927	258
25°	827	837	840	854	854	381
35°	712	728	742	758	762	445
45°	582	607	633	653	662	449
55°	444	478	516	544	553	397
65°	307	348	394	425	435	303
75°	166	216	268	302	315	178
85°	51	104	159	195	205	53
90°	15	76	142	181	194	13
95°	71	72	134	173	184	81
105°	301	337	294	149	160	319
115°	554	573	619	654	667	548
125°	777	785	820	843	853	695
135°	966	971	986	1008	1010	744
145°	1113	1119	1121	1131	1136	697
155°	1225	1223	1224	1229	1223	564
165°	1292	1289	1288	1296	1289	365
175°	1322	1318	1318	1325	1318	126
180°	1322	1322	1322	1322	1322	

TEST NUMBER: P1010702

CATALOG NUMBER: S123DIP-B775D1025UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	960.8	960.8	960.8	960.8	960.8
2.5°	966.0	962.9	954.5	962.9	961.8
5°	961.8	959.7	953.5	961.8	960.8
7.5°	954.5	954.5	948.2	958.7	957.6
10°	944.0	946.1	940.9	951.4	949.3
12.5°	931.5	934.6	931.5	940.9	938.8
15°	915.8	918.9	917.9	928.3	927.3
17.5°	896.9	903.2	902.2	911.6	909.5
20°	876.0	882.3	884.4	893.8	894.9
22.5°	854.0	860.3	863.5	876.0	875.0
25°	826.8	837.3	840.4	854.0	854.0
27.5°	800.7	812.2	818.4	830.0	831.0
30°	772.4	786.0	794.4	806.9	806.9
32.5°	741.0	756.7	768.2	781.8	785.0
35°	711.7	728.4	742.0	757.7	761.9
37.5°	680.3	699.1	714.8	732.6	735.8
40°	648.9	667.7	688.7	706.5	710.6
42.5°	614.4	638.4	660.4	680.3	686.6
45°	581.9	607.0	633.2	653.1	661.5
47.5°	547.4	575.6	604.9	626.9	633.2
50°	513.9	543.2	575.6	599.7	607.0
52.5°	478.3	509.7	546.3	571.4	580.9
55°	443.8	478.3	516.0	544.2	552.6
57.5°	410.3	445.9	486.7	514.9	524.4
60°	374.7	412.4	455.3	484.6	496.1
62.5°	341.2	379.9	426.0	455.3	465.7
65°	306.7	347.5	393.5	424.9	435.4
67.5°	272.1	315.0	361.1	395.6	404.0
70°	235.5	280.5	330.7	364.2	374.7
72.5°	202.0	247.0	299.3	333.9	344.3
75°	166.4	215.6	267.9	302.5	315.0
77.5°	136.1	185.2	237.6	274.2	283.6
80°	103.6	154.9	209.3	244.9	255.4
82.5°	75.4	127.7	183.2	218.7	229.2
85°	51.3	103.6	159.1	194.7	205.1
87.5°	31.4	83.7	137.1	172.7	183.2
90°	14.6	75.7	141.9	181.4	193.8
92.5°	35.2	74.3	135.4	176.8	187.3
95°	71.4	71.9	134.1	173.4	183.8
97.5°	119.6	129.6	128.7	168.0	179.5
100°	175.4	228.6	123.5	161.7	173.2
102.5°	239.3	281.3	157.5	154.4	166.7
105°	301.2	337.1	293.7	149.1	160.4
107.5°	365.9	396.7	454.4	331.4	212.1
110°	430.7	457.4	510.1	504.9	372.8

TEST NUMBER: P1010702

CATALOG NUMBER: S123DIP-B775D1025UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	493.6	515.1	565.7	600.7	608.2
115°	554.4	572.9	619.4	654.3	666.7
117.5°	615.3	630.6	671.1	704.0	713.4
120°	670.3	684.3	721.9	753.7	761.1
122.5°	727.3	736.3	772.6	800.5	808.9
125°	777.3	785.1	819.5	843.4	852.7
127.5°	828.4	835.2	866.3	890.2	895.5
130°	875.5	882.4	907.2	931.0	935.4
132.5°	919.7	927.6	946.2	968.9	973.4
135°	965.9	970.7	986.2	1008.0	1010.2
137.5°	1005.2	1011.9	1021.3	1042.9	1046.2
140°	1043.4	1049.3	1055.4	1075.0	1078.3
142.5°	1079.7	1084.6	1087.6	1104.1	1106.4
145°	1113.1	1119.0	1121.0	1131.3	1135.5
147.5°	1144.5	1149.5	1151.4	1156.5	1155.8
150°	1174.0	1177.0	1178.9	1180.9	1180.1
152.5°	1200.5	1201.5	1202.5	1206.4	1201.5
155°	1225.1	1223.1	1224.1	1229.0	1223.1
157.5°	1244.8	1244.8	1243.8	1249.7	1241.8
160°	1262.4	1261.5	1260.5	1266.4	1259.5
162.5°	1279.1	1276.2	1275.2	1282.1	1276.2
165°	1291.9	1289.0	1288.0	1295.8	1289.0
167.5°	1302.7	1298.8	1298.8	1306.7	1298.8
170°	1311.6	1307.6	1307.6	1315.5	1307.6
172.5°	1317.5	1312.5	1313.5	1321.4	1312.5
175°	1322.4	1317.5	1318.4	1325.3	1317.5
177.5°	1324.3	1319.4	1320.4	1328.3	1318.4
180°	1322.4	1322.4	1322.4	1322.4	1322.4

(END OF REPORT)