

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010703

Luminaire Tested: S123DIP-B775D1025UB2750-4F0-XX-W2A-D_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010703
REPORT IS A COMBINATION OF REPORTS P990237 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B775D1025UB2750-4F0-XX-W2A-D_5000K
Description: Define 3 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7024.0 lumens
Efficiency: N/A
Efficacy: 109.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.25 / 1.37
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 64.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010703

CATALOG NUMBER: S123DIP-B775D1025UB2750-4F0-XX-W2A-D_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010703

CATALOG NUMBER: S123DIP-B775D1025UB2750-4F0-XX-W2A-D_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48
1	95	90	86	82	86	82	79	75	67	65	62	53	52	50	41	40	38
2	86	78	72	66	78	71	66	61	58	54	51	46	44	41	35	33	32
3	78	68	61	55	71	62	56	51	51	46	42	41	37	34	31	29	27
4	71	60	52	46	65	55	48	43	45	40	36	36	32	29	28	25	23
5	65	54	45	39	59	49	42	36	40	35	31	32	28	25	25	22	20
6	60	48	40	34	54	44	37	31	36	31	27	29	25	22	22	19	17
7	56	43	35	30	50	40	32	27	33	27	23	26	22	19	20	17	15
8	51	39	31	26	47	36	29	24	30	24	21	24	20	17	19	16	14
9	48	36	28	23	43	33	26	21	27	22	18	22	18	15	17	14	12
10	45	33	25	21	41	30	24	19	25	20	16	20	16	14	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10002	10002	10002
5°	10030	9709	9701
10°	9936	9446	9374
15°	9804	9155	9027
20°	9618	8832	8654
25°	9388	8467	8268
30°	9152	8137	7880
35°	8889	7791	7564
40°	8637	7475	7231
45°	8358	7168	6956
50°	8082	6864	6658
55°	7777	6552	6384
60°	7478	6234	6102
65°	7170	5895	5773
70°	6708	5515	5434
75°	6121	5079	5083
80°	5440	4642	4684
85°	4764	4286	4397

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 8358 cd/sqm

TEST NUMBER: P1010703

CATALOG NUMBER: S123DIP-B775D1025UB2750-4F0-XX-W2A-D_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.2	1.3
10°-20°	251.3	3.6
20°-30°	375.8	5.4
30°-40°	448.7	6.4
40°-50°	469.4	6.7
50°-60°	440.5	6.3
60°-70°	368.0	5.2
70°-80°	263.1	3.7
80°-90°	159.1	2.3
90°-100°	143.5	2.0
100°-110°	290.4	4.1
110°-120°	582.5	8.3
120°-130°	705.8	10.0
130°-140°	736.9	10.5
140°-150°	680.1	9.7
150°-160°	546.5	7.8
160°-170°	352.7	5.0
170°-180°	121.5	1.7
0°-30°	715.2	10.2
0°-40°	1163.9	16.6
0°-60°	2073.9	29.5
0°-90°	2864.1	40.8
90°-120°	1016.4	14.5
90°-150°	3139.2	44.7
90°-180°	4160.0	59.2
0°-180°	7024.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	929	929	929	929	929	
5°	930	928	922	930	929	88
15°	886	889	888	898	897	250
25°	800	810	813	826	826	369
35°	688	704	718	733	737	430
45°	563	587	612	632	640	434
55°	429	463	499	526	534	384
65°	297	336	381	411	421	293
75°	161	208	259	292	305	172
85°	50	100	154	188	198	51
90°	14	73	137	175	187	13
95°	69	70	130	168	178	78
105°	291	326	284	144	155	308
115°	536	554	599	633	645	530
125°	752	759	792	816	824	672
135°	934	939	954	975	977	719
145°	1076	1082	1084	1094	1098	674
155°	1185	1183	1184	1188	1183	546
165°	1249	1246	1246	1253	1246	353
175°	1279	1274	1275	1282	1274	122
180°	1279	1279	1279	1279	1279	

TEST NUMBER: P1010703

CATALOG NUMBER: S123DIP-B775D1025UB2750-4F0-XX-W2A-D_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	929.2	929.2	929.2	929.2	929.2
2.5°	934.3	931.3	923.2	931.3	930.3
5°	930.3	928.2	922.2	930.3	929.2
7.5°	923.2	923.2	917.1	927.2	926.2
10°	913.1	915.1	910.0	920.1	918.1
12.5°	900.9	903.9	900.9	910.0	908.0
15°	885.7	888.8	887.7	897.9	896.9
17.5°	867.5	873.6	872.6	881.7	879.6
20°	847.3	853.3	855.4	864.5	865.5
22.5°	826.0	832.1	835.1	847.3	846.2
25°	799.7	809.8	812.8	826.0	826.0
27.5°	774.4	785.5	791.6	802.7	803.7
30°	747.0	760.2	768.3	780.4	780.4
32.5°	716.7	731.9	743.0	756.2	759.2
35°	688.3	704.5	717.7	732.9	736.9
37.5°	658.0	676.2	691.4	708.6	711.6
40°	627.6	645.8	666.1	683.3	687.3
42.5°	594.2	617.5	638.7	658.0	664.0
45°	562.8	587.1	612.4	631.6	639.7
47.5°	529.4	556.7	585.1	606.3	612.4
50°	497.0	525.4	556.7	580.0	587.1
52.5°	462.6	493.0	528.4	552.7	561.8
55°	429.2	462.6	499.0	526.4	534.5
57.5°	396.8	431.2	470.7	498.0	507.1
60°	362.4	398.8	440.3	468.7	479.8
62.5°	330.0	367.4	412.0	440.3	450.5
65°	296.6	336.1	380.6	411.0	421.1
67.5°	263.2	304.7	349.2	382.6	390.7
70°	227.8	271.3	319.9	352.3	362.4
72.5°	195.4	238.9	289.5	322.9	333.0
75°	160.9	208.5	259.1	292.5	304.7
77.5°	131.6	179.2	229.8	265.2	274.3
80°	100.2	149.8	202.5	236.9	247.0
82.5°	72.9	123.5	177.1	211.6	221.7
85°	49.6	100.2	153.9	188.3	198.4
87.5°	30.4	81.0	132.6	167.0	177.1
90°	14.2	73.3	137.2	175.4	187.4
92.5°	34.0	71.9	131.0	171.1	181.1
95°	69.1	69.6	129.7	167.7	177.8
97.5°	115.6	125.5	124.5	162.5	173.6
100°	169.7	221.1	119.5	156.4	167.4
102.5°	231.4	272.0	152.3	149.3	161.4
105°	291.2	326.0	284.0	144.2	155.2
107.5°	353.9	383.6	439.4	320.5	205.1
110°	416.5	442.3	493.3	488.2	360.5

TEST NUMBER: P1010703

CATALOG NUMBER: S123DIP-B775D1025UB2750-4F0-XX-W2A-D_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	477.3	498.1	547.0	580.9	588.1
115°	536.2	554.0	598.9	632.7	644.6
117.5°	595.1	609.8	649.0	680.9	689.9
120°	648.1	661.8	698.0	728.9	736.0
122.5°	703.2	712.0	747.2	774.1	782.2
125°	751.6	759.2	792.4	815.5	824.5
127.5°	801.0	807.6	837.7	860.8	866.0
130°	846.6	853.2	877.3	900.3	904.5
132.5°	889.4	897.0	915.0	937.0	941.3
135°	934.0	938.7	953.6	974.8	976.9
137.5°	972.0	978.6	987.6	1008.6	1011.8
140°	1009.0	1014.7	1020.6	1039.6	1042.8
142.5°	1044.2	1048.9	1051.7	1067.8	1069.9
145°	1076.5	1082.1	1084.0	1094.0	1098.0
147.5°	1106.8	1111.6	1113.5	1118.4	1117.7
150°	1135.3	1138.2	1140.1	1142.0	1141.1
152.5°	1161.0	1161.9	1162.9	1166.7	1161.9
155°	1184.7	1182.8	1183.8	1188.5	1182.8
157.5°	1203.7	1203.7	1202.8	1208.5	1200.9
160°	1220.8	1219.9	1218.9	1224.6	1218.0
162.5°	1237.0	1234.1	1233.2	1239.8	1234.1
165°	1249.3	1246.5	1245.5	1253.1	1246.5
167.5°	1259.8	1256.0	1256.0	1263.6	1256.0
170°	1268.3	1264.5	1264.5	1272.1	1264.5
172.5°	1274.0	1269.3	1270.2	1277.8	1269.3
175°	1278.8	1274.0	1275.0	1281.6	1274.0
177.5°	1280.7	1275.9	1276.9	1284.5	1275.0
180°	1278.8	1278.8	1278.8	1278.8	1278.8

(END OF REPORT)