

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010705

Luminaire Tested: S123DIP-B775D1025UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010705
REPORT IS A COMBINATION OF REPORTS P990239 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B775D1025UB2750-4F0-XX-W2A-F_3000K
Description: Define 3 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7243.0 lumens
Efficiency: N/A
Efficacy: 112.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 64.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010705

CATALOG NUMBER: S123DIP-B775D1025UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010705

CATALOG NUMBER: S123DIP-B775D1025UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51
1	96	92	88	85	88	84	81	78	70	68	66	57	55	54	45	44	43
2	88	80	74	69	80	74	68	64	61	57	54	50	47	45	39	37	36
3	80	71	63	58	73	65	59	53	54	49	46	44	41	38	35	32	30
4	73	62	55	49	67	57	51	45	48	43	39	39	35	32	31	28	26
5	67	56	48	42	61	51	44	39	43	37	33	35	31	28	28	25	23
6	62	50	42	36	56	46	39	34	39	33	29	32	28	25	25	22	20
7	57	45	37	31	52	41	34	29	35	30	26	29	25	22	23	20	18
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	20	17	14
10	46	34	27	22	42	32	25	21	27	22	18	22	18	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13177	13177	13177
5°	13209	12722	12703
10°	13092	12292	12165
15°	12910	11844	11580
20°	12701	11347	10999
25°	12431	10822	10378
30°	12136	10279	9725
35°	11827	9725	9076
40°	11503	9142	8438
45°	11146	8575	7771
50°	10783	7943	7102
55°	10319	7284	6424
60°	9838	6557	5702
65°	9389	5771	4949
70°	8740	4899	4072
75°	7809	3879	3161
80°	6743	2725	2236
85°	5254	1465	1119

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11146 cd/sqm

TEST NUMBER: P1010705

CATALOG NUMBER: S123DIP-B775D1025UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.4	1.6
10°-20°	325.9	4.5
20°-30°	481.3	6.6
30°-40°	562.1	7.8
40°-50°	565.1	7.8
50°-60°	496.4	6.9
60°-70°	369.7	5.1
70°-80°	210.4	2.9
80°-90°	62.5	0.9
90°-100°	46.9	0.6
100°-110°	226.7	3.1
110°-120°	555.6	7.7
120°-130°	705.4	9.7
130°-140°	753.5	10.4
140°-150°	704.6	9.7
150°-160°	568.4	7.8
160°-170°	366.8	5.1
170°-180°	126.4	1.7
0°-30°	922.6	12.7
0°-40°	1484.6	20.5
0°-60°	2546.1	35.2
0°-90°	3188.7	44.0
90°-120°	829.3	11.4
90°-150°	2992.8	41.3
90°-180°	4054.0	56.0
0°-180°	7243.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1224	1224	1224	1224	1224	
5°	1225	1220	1208	1219	1217	116
15°	1166	1162	1148	1157	1150	329
25°	1059	1053	1039	1040	1037	488
35°	916	910	896	890	884	573
45°	750	746	733	720	715	579
55°	570	568	555	543	538	510
65°	388	383	373	364	361	383
75°	205	201	198	193	190	219
85°	55	53	53	50	50	59
90°	1	11	24	28	30	7
95°	60	20	31	38	38	72
105°	294	305	216	42	44	312
115°	552	558	567	577	581	545
125°	779	786	790	792	794	696
135°	969	975	979	982	979	746
145°	1118	1125	1127	1129	1129	700
155°	1232	1230	1231	1236	1230	568
165°	1299	1296	1295	1303	1296	367
175°	1330	1325	1326	1333	1325	127
180°	1330	1330	1330	1330	1330	

TEST NUMBER: P1010705

CATALOG NUMBER: S123DIP-B775D1025UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1224.2	1224.2	1224.2	1224.2	1224.2
2.5°	1229.4	1225.2	1213.7	1224.2	1223.1
5°	1225.2	1220.0	1208.4	1218.9	1216.8
7.5°	1215.8	1210.5	1198.9	1208.4	1207.3
10°	1203.1	1197.9	1184.2	1193.7	1191.5
12.5°	1186.3	1182.1	1169.4	1175.8	1174.7
15°	1166.3	1162.1	1148.4	1156.8	1150.5
17.5°	1144.2	1138.9	1125.2	1131.6	1129.4
20°	1118.9	1112.6	1098.9	1103.1	1100.0
22.5°	1090.5	1084.2	1070.5	1073.7	1069.4
25°	1058.9	1052.6	1038.9	1040.0	1036.8
27.5°	1026.3	1020.0	1005.2	1006.3	1003.1
30°	990.5	985.2	970.5	970.5	963.1
32.5°	954.7	947.3	936.8	929.5	926.3
35°	915.8	909.5	895.8	889.5	884.2
37.5°	876.8	868.4	854.7	847.3	844.2
40°	835.8	829.5	814.7	806.3	802.1
42.5°	794.7	787.3	772.6	764.2	760.0
45°	750.5	746.3	732.6	720.0	714.7
47.5°	707.4	701.0	688.4	675.8	671.6
50°	663.1	657.9	644.2	632.6	626.3
52.5°	616.8	613.7	598.9	589.5	583.1
55°	569.5	568.4	554.7	543.1	537.9
57.5°	525.3	521.0	510.5	500.0	493.7
60°	476.8	475.8	463.1	453.7	448.4
62.5°	433.7	430.5	417.9	408.4	405.3
65°	388.4	383.1	372.6	364.2	361.0
67.5°	340.0	335.8	327.4	320.0	315.8
70°	296.8	290.5	284.2	276.8	271.6
72.5°	251.6	247.4	240.0	233.7	231.6
75°	205.3	201.0	197.9	192.6	189.5
77.5°	164.2	162.1	157.9	153.7	153.7
80°	124.2	121.0	118.9	117.9	117.9
82.5°	85.3	85.3	85.3	83.2	82.1
85°	54.7	52.6	52.6	50.5	50.5
87.5°	27.4	24.2	23.2	22.1	22.1
90°	1.0	10.9	23.7	27.7	29.6
92.5°	22.7	16.8	25.7	32.6	33.6
95°	60.3	19.8	30.6	37.5	37.5
97.5°	109.7	82.0	31.6	39.5	40.5
100°	167.0	186.7	32.6	40.5	41.5
102.5°	232.2	245.0	73.1	40.5	42.5
105°	294.4	305.3	216.4	41.5	43.5
107.5°	360.6	369.5	384.3	232.2	102.8
110°	426.8	434.7	445.6	413.0	271.7

TEST NUMBER: P1010705

CATALOG NUMBER: S123DIP-B775D1025UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	490.1	497.0	507.9	516.7	514.8
115°	552.3	558.2	567.1	577.0	581.0
117.5°	613.6	620.5	625.4	633.3	634.3
120°	669.9	678.8	681.8	689.7	689.7
122.5°	727.2	734.1	738.1	743.0	744.0
125°	778.6	786.5	790.4	792.4	794.4
127.5°	830.0	837.9	842.8	845.8	843.8
130°	877.4	885.3	889.2	893.2	891.2
132.5°	922.8	930.7	933.7	937.7	934.7
135°	969.3	975.2	979.2	982.1	979.2
137.5°	1008.8	1016.7	1018.7	1023.6	1021.6
140°	1048.3	1054.2	1057.2	1061.2	1059.2
142.5°	1084.9	1090.8	1093.8	1096.7	1093.8
145°	1118.5	1125.4	1127.4	1129.3	1129.3
147.5°	1151.1	1156.0	1158.0	1160.0	1155.0
150°	1180.7	1183.7	1185.7	1187.6	1184.7
152.5°	1207.4	1208.4	1209.4	1213.3	1208.4
155°	1232.1	1230.1	1231.1	1236.0	1230.1
157.5°	1251.9	1251.9	1250.9	1256.8	1248.9
160°	1269.6	1268.7	1267.7	1273.6	1266.7
162.5°	1286.4	1283.5	1282.5	1289.4	1283.5
165°	1299.3	1296.3	1295.3	1303.2	1296.3
167.5°	1310.1	1306.2	1306.2	1314.1	1306.2
170°	1319.0	1315.1	1315.1	1323.0	1315.1
172.5°	1325.0	1320.0	1321.0	1328.9	1320.0
175°	1329.9	1325.0	1326.0	1332.9	1325.0
177.5°	1331.9	1326.9	1327.9	1335.8	1326.0
180°	1329.9	1329.9	1329.9	1329.9	1329.9

(END OF REPORT)