

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010435

Luminaire Tested: S123DIP-B1000D365UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010435
REPORT IS A COMBINATION OF REPORTS P989159 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B1000D365UB2750-4F0-XX-W2A-F_3000K
Description: Define 3 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5555.0 lumens
Efficiency: N/A
Efficacy: 99.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 56.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010435

CATALOG NUMBER: S123DIP-B1000D365UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010435

CATALOG NUMBER: S123DIP-B1000D365UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	113	113	113	113	107	107	107	107	97	97	97	87	87	87	78	78	78
1	103	98	94	91	98	94	90	87	85	82	79	76	74	72	69	67	66
2	94	86	80	74	89	82	76	71	74	70	66	67	64	60	61	58	55
3	86	76	68	62	81	72	65	60	65	60	55	59	55	51	54	50	47
4	78	67	59	52	74	64	56	51	58	52	47	53	48	44	48	44	41
5	72	60	51	45	68	57	49	44	52	46	41	48	42	38	43	39	35
6	66	54	45	39	63	52	44	38	47	41	36	43	38	33	39	35	31
7	62	49	40	35	58	47	39	34	43	36	32	39	34	30	36	31	28
8	57	44	36	31	54	43	35	30	39	33	28	36	30	27	33	28	25
9	53	41	33	28	51	39	32	27	36	30	25	33	28	24	30	26	22
10	50	37	30	25	48	36	29	24	33	27	23	31	25	22	28	24	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16937	16937	16937
5°	16979	16352	16328
10°	16828	15798	15636
15°	16593	15222	14883
20°	16326	14585	14137
25°	15978	13910	13339
30°	15598	13212	12499
35°	15200	12498	11666
40°	14784	11751	10845
45°	14325	11021	9988
50°	13859	10209	9129
55°	13262	9362	8257
60°	12647	8428	7329
65°	12067	7417	6363
70°	11235	6297	5234
75°	10035	4987	4062
80°	8665	3505	2873
85°	6762	1882	1438

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14325 cd/sqm

TEST NUMBER: P1010435

CATALOG NUMBER: S123DIP-B1000D365UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.3	2.7
10°-20°	418.8	7.5
20°-30°	618.6	11.1
30°-40°	722.5	13.0
40°-50°	726.3	13.1
50°-60°	638.0	11.5
60°-70°	475.2	8.6
70°-80°	270.4	4.9
80°-90°	77.8	1.4
90°-100°	16.9	0.3
100°-110°	81.6	1.5
110°-120°	200.0	3.6
120°-130°	253.8	4.6
130°-140°	271.2	4.9
140°-150°	253.6	4.6
150°-160°	204.5	3.7
160°-170°	132.0	2.4
170°-180°	45.5	0.8
0°-30°	1185.8	21.3
0°-40°	1908.2	34.4
0°-60°	3272.5	58.9
0°-90°	4095.9	73.7
90°-120°	298.5	5.4
90°-150°	1077.0	19.4
90°-180°	1459.0	26.3
0°-180°	5555.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1574	1574	1574	1574	1574	
5°	1575	1568	1553	1567	1564	149
15°	1499	1494	1476	1487	1479	423
25°	1361	1353	1335	1337	1333	627
35°	1177	1169	1151	1143	1136	736
45°	965	959	942	925	919	745
55°	732	731	713	698	691	656
65°	499	492	479	468	464	493
75°	264	258	254	248	244	282
85°	70	68	68	65	65	75
90°	0	4	8	10	11	6
95°	22	7	11	14	14	26
105°	106	110	78	15	16	112
115°	199	201	204	208	209	196
125°	280	283	284	285	286	250
135°	349	351	352	353	352	269
145°	402	405	406	406	406	252
155°	443	443	443	445	443	204
165°	468	466	466	469	466	132
175°	479	477	477	480	477	46
180°	479	479	479	479	479	

TEST NUMBER: P1010435

CATALOG NUMBER: S123DIP-B1000D365UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1573.5	1573.5	1573.5	1573.5	1573.5
2.5°	1580.2	1574.8	1559.9	1573.5	1572.1
5°	1574.8	1568.0	1553.2	1566.7	1564.0
7.5°	1562.6	1555.9	1541.0	1553.2	1551.8
10°	1546.4	1539.6	1522.0	1534.2	1531.5
12.5°	1524.7	1519.3	1503.1	1511.2	1509.9
15°	1499.0	1493.6	1476.0	1486.9	1478.7
17.5°	1470.6	1463.9	1446.3	1454.4	1451.7
20°	1438.2	1430.0	1412.5	1417.9	1413.8
22.5°	1401.6	1393.5	1375.9	1380.0	1374.6
25°	1361.0	1352.9	1335.3	1336.7	1332.6
27.5°	1319.1	1311.0	1292.0	1293.4	1289.3
30°	1273.1	1266.3	1247.4	1247.4	1237.9
32.5°	1227.1	1217.6	1204.1	1194.6	1190.6
35°	1177.0	1168.9	1151.3	1143.2	1136.5
37.5°	1127.0	1116.2	1098.6	1089.1	1085.0
40°	1074.2	1066.1	1047.2	1036.3	1030.9
42.5°	1021.5	1012.0	993.0	982.2	976.8
45°	964.6	959.2	941.6	925.4	918.6
47.5°	909.2	901.0	884.8	868.6	863.2
50°	852.3	845.6	828.0	813.1	805.0
52.5°	792.8	788.8	769.8	757.6	749.5
55°	731.9	730.6	713.0	698.1	691.3
57.5°	675.1	669.7	656.2	642.6	634.5
60°	612.9	611.5	595.3	583.1	576.3
62.5°	557.4	553.3	537.1	524.9	520.9
65°	499.2	492.5	478.9	468.1	464.1
67.5°	437.0	431.6	420.8	411.3	405.9
70°	381.5	373.4	365.3	355.8	349.1
72.5°	323.3	317.9	308.5	300.3	297.6
75°	263.8	258.4	254.4	247.6	243.5
77.5°	211.1	208.4	202.9	197.5	197.5
80°	159.6	155.6	152.9	151.5	151.5
82.5°	109.6	109.6	109.6	106.9	105.5
85°	70.4	67.6	67.6	64.9	64.9
87.5°	35.2	31.1	29.8	28.4	28.4
90°	0.4	3.9	8.5	10.0	10.7
92.5°	8.2	6.0	9.2	11.7	12.1
95°	21.7	7.1	11.0	13.5	13.5
97.5°	39.5	29.5	11.4	14.2	14.6
100°	60.1	67.2	11.7	14.6	14.9
102.5°	83.6	88.2	26.3	14.6	15.3
105°	106.0	109.9	77.9	14.9	15.6
107.5°	129.8	133.0	138.3	83.6	37.0
110°	153.6	156.5	160.4	148.6	97.8



TEST NUMBER: P1010435

CATALOG NUMBER: S123DIP-B1000D365UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	176.4	178.9	182.8	186.0	185.3
115°	198.8	200.9	204.1	207.7	209.1
117.5°	220.8	223.3	225.1	227.9	228.3
120°	241.1	244.3	245.3	248.2	248.2
122.5°	261.7	264.2	265.6	267.4	267.7
125°	280.2	283.0	284.5	285.2	285.9
127.5°	298.7	301.5	303.3	304.4	303.7
130°	315.7	318.6	320.0	321.4	320.7
132.5°	332.1	334.9	336.0	337.4	336.4
135°	348.8	350.9	352.4	353.4	352.4
137.5°	363.0	365.9	366.6	368.4	367.7
140°	377.3	379.4	380.5	381.9	381.2
142.5°	390.4	392.5	393.6	394.7	393.6
145°	402.5	405.0	405.7	406.4	406.4
147.5°	414.2	416.0	416.7	417.4	415.7
150°	424.9	426.0	426.7	427.4	426.3
152.5°	434.5	434.9	435.2	436.6	434.9
155°	443.4	442.7	443.0	444.8	442.7
157.5°	450.5	450.5	450.2	452.3	449.4
160°	456.9	456.6	456.2	458.3	455.8
162.5°	463.0	461.9	461.5	464.0	461.9
165°	467.6	466.5	466.2	469.0	466.5
167.5°	471.5	470.1	470.1	472.9	470.1
170°	474.7	473.3	473.3	476.1	473.3
172.5°	476.8	475.0	475.4	478.2	475.0
175°	478.6	476.8	477.2	479.7	476.8
177.5°	479.3	477.5	477.9	480.7	477.2
180°	478.6	478.6	478.6	478.6	478.6

(END OF REPORT)