

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010436

Luminaire Tested: S123DIP-B1000D365UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010436
REPORT IS A COMBINATION OF REPORTS P989160 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B1000D365UB2750-4F0-XX-W2A-F_3500K
Description: Define 3 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5579.0 lumens
Efficiency: N/A
Efficacy: 99.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 56.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010436

CATALOG NUMBER: S123DIP-B1000D365UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1010436

CATALOG NUMBER: S123DIP-B1000D365UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	113	113	113	113	107	107	107	107	97	97	97	87	87	87	78	78	78			74
1	103	98	94	91	98	94	90	87	85	82	79	76	74	72	69	67	66			62
2	94	86	80	74	89	82	76	71	74	70	66	67	64	60	61	58	55			52
3	86	76	68	62	81	72	65	60	65	60	55	59	55	51	54	50	47			44
4	78	67	59	52	74	64	56	51	58	52	47	53	48	44	48	44	41			38
5	72	60	51	45	68	57	49	44	52	46	41	48	42	38	43	39	35			33
6	66	54	45	39	63	52	44	38	47	41	36	43	38	33	39	35	31			29
7	62	49	40	35	58	47	39	34	43	36	32	39	34	30	36	31	28			25
8	57	44	36	31	54	43	35	30	39	33	28	36	30	27	33	28	25			23
9	53	41	33	28	51	39	32	27	36	30	25	33	28	24	30	26	22			20
10	50	37	30	25	48	36	29	24	33	27	23	31	25	22	28	24	20			19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17011	17011	17011
5°	17053	16424	16400
10°	16902	15868	15705
15°	16666	15289	14948
20°	16397	14649	14199
25°	16048	13971	13398
30°	15667	13270	12555
35°	15267	12554	11718
40°	14848	11803	10894
45°	14389	11071	10033
50°	13921	10253	9168
55°	13321	9403	8294
60°	12702	8465	7362
65°	12121	7450	6390
70°	11285	6325	5257
75°	10080	5009	4081
80°	8703	3521	2886
85°	6791	1891	1445

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14389 cd/sqm

TEST NUMBER: P1010436

CATALOG NUMBER: S123DIP-B1000D365UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.0	2.7
10°-20°	420.7	7.5
20°-30°	621.3	11.1
30°-40°	725.6	13.0
40°-50°	729.5	13.1
50°-60°	640.8	11.5
60°-70°	477.3	8.6
70°-80°	271.6	4.9
80°-90°	78.2	1.4
90°-100°	16.9	0.3
100°-110°	81.9	1.5
110°-120°	200.8	3.6
120°-130°	254.9	4.6
130°-140°	272.3	4.9
140°-150°	254.6	4.6
150°-160°	205.4	3.7
160°-170°	132.5	2.4
170°-180°	45.7	0.8
0°-30°	1191.0	21.3
0°-40°	1916.6	34.4
0°-60°	3286.9	58.9
0°-90°	4114.0	73.7
90°-120°	299.6	5.4
90°-150°	1081.4	19.4
90°-180°	1465.0	26.3
0°-180°	5579.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1580	1580	1580	1580	1580	
5°	1582	1575	1560	1574	1571	150
15°	1506	1500	1482	1493	1485	425
25°	1367	1359	1341	1343	1338	630
35°	1182	1174	1156	1148	1142	740
45°	969	963	946	930	923	748
55°	735	734	716	701	694	659
65°	501	495	481	470	466	495
75°	265	260	256	249	245	283
85°	71	68	68	65	65	76
90°	0	4	9	10	11	6
95°	22	7	11	14	14	26
105°	106	110	78	15	16	113
115°	200	202	205	208	210	197
125°	281	284	286	286	287	251
135°	350	352	354	355	354	270
145°	404	407	407	408	408	253
155°	445	444	445	447	444	205
165°	470	468	468	471	468	133
175°	481	479	479	482	479	46
180°	481	481	481	481	481	

TEST NUMBER: P1010436

CATALOG NUMBER: S123DIP-B1000D365UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1580.4	1580.4	1580.4	1580.4	1580.4
2.5°	1587.2	1581.7	1566.8	1580.4	1579.0
5°	1581.7	1574.9	1560.0	1573.6	1570.9
7.5°	1569.5	1562.7	1547.8	1560.0	1558.6
10°	1553.2	1546.4	1528.7	1541.0	1538.2
12.5°	1531.4	1526.0	1509.7	1517.9	1516.5
15°	1505.6	1500.2	1482.5	1493.4	1485.2
17.5°	1477.1	1470.3	1452.6	1460.8	1458.1
20°	1444.5	1436.3	1418.7	1424.1	1420.0
22.5°	1407.8	1399.6	1382.0	1386.1	1380.6
25°	1367.0	1358.9	1341.2	1342.6	1338.5
27.5°	1324.9	1316.7	1297.7	1299.1	1295.0
30°	1278.7	1271.9	1252.9	1252.9	1243.4
32.5°	1232.5	1223.0	1209.4	1199.9	1195.8
35°	1182.2	1174.1	1156.4	1148.2	1141.5
37.5°	1131.9	1121.1	1103.4	1093.9	1089.8
40°	1078.9	1070.8	1051.8	1040.9	1035.5
42.5°	1025.9	1016.4	997.4	986.5	981.1
45°	968.9	963.4	945.8	929.5	922.7
47.5°	913.2	905.0	888.7	872.4	867.0
50°	856.1	849.3	831.6	816.7	808.5
52.5°	796.3	792.2	773.2	761.0	752.8
55°	735.2	733.8	716.1	701.2	694.4
57.5°	678.1	672.6	659.1	645.5	637.3
60°	615.6	614.2	597.9	585.7	578.9
62.5°	559.9	555.8	539.5	527.2	523.2
65°	501.4	494.6	481.0	470.2	466.1
67.5°	438.9	433.5	422.6	413.1	407.7
70°	383.2	375.0	366.9	357.4	350.6
72.5°	324.8	319.3	309.8	301.7	299.0
75°	265.0	259.5	255.5	248.7	244.6
77.5°	212.0	209.3	203.8	198.4	198.4
80°	160.3	156.3	153.6	152.2	152.2
82.5°	110.1	110.1	110.1	107.4	106.0
85°	70.7	67.9	67.9	65.2	65.2
87.5°	35.3	31.3	29.9	28.5	28.5
90°	0.4	3.9	8.6	10.0	10.7
92.5°	8.2	6.1	9.3	11.8	12.1
95°	21.8	7.1	11.1	13.6	13.6
97.5°	39.6	29.6	11.4	14.3	14.6
100°	60.3	67.5	11.8	14.6	15.0
102.5°	83.9	88.5	26.4	14.6	15.4
105°	106.4	110.3	78.2	15.0	15.7
107.5°	130.3	133.5	138.9	83.9	37.1
110°	154.2	157.1	161.0	149.2	98.2

TEST NUMBER: P1010436

CATALOG NUMBER: S123DIP-B1000D365UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	177.1	179.6	183.5	186.7	186.0
115°	199.6	201.7	204.9	208.5	209.9
117.5°	221.7	224.2	226.0	228.9	229.2
120°	242.1	245.3	246.4	249.2	249.2
122.5°	262.8	265.3	266.7	268.5	268.8
125°	281.3	284.2	285.6	286.3	287.1
127.5°	299.9	302.8	304.5	305.6	304.9
130°	317.0	319.9	321.3	322.8	322.0
132.5°	333.5	336.3	337.4	338.8	337.8
135°	350.2	352.4	353.8	354.9	353.8
137.5°	364.5	367.4	368.1	369.9	369.2
140°	378.8	381.0	382.0	383.5	382.7
142.5°	392.0	394.2	395.2	396.3	395.2
145°	404.2	406.7	407.4	408.1	408.1
147.5°	415.9	417.7	418.4	419.2	417.4
150°	426.7	427.7	428.4	429.2	428.1
152.5°	436.3	436.6	437.0	438.4	436.6
155°	445.2	444.5	444.9	446.6	444.5
157.5°	452.4	452.4	452.0	454.1	451.3
160°	458.8	458.4	458.1	460.2	457.7
162.5°	464.9	463.8	463.4	465.9	463.8
165°	469.5	468.4	468.1	470.9	468.4
167.5°	473.4	472.0	472.0	474.9	472.0
170°	476.6	475.2	475.2	478.1	475.2
172.5°	478.8	477.0	477.4	480.2	477.0
175°	480.6	478.8	479.1	481.6	478.8
177.5°	481.3	479.5	479.8	482.7	479.1
180°	480.6	480.6	480.6	480.6	480.6

(END OF REPORT)