

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010712

Luminaire Tested: S123DIP-B775D1195UB2750-4F0-XX-W2A-A_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010712
REPORT IS A COMBINATION OF REPORTS P990291 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B775D1195UB2750-4F0-XX-W2A-A_4000K
Description: Define 3 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8000.0 lumens
Efficiency: N/A
Efficacy: 112.8 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.37 / 1.5
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 70.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010712

CATALOG NUMBER: S123DIP-B775D1195UB2750-4F0-XX-W2A-A_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010712

CATALOG NUMBER: S123DIP-B775D1195UB2750-4F0-XX-W2A-A_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48
1	96	92	88	85	87	84	81	78	69	67	65	55	54	52	42	42	41
2	88	80	74	69	80	73	68	64	61	57	54	49	46	44	38	36	35
3	80	71	64	58	73	65	59	54	54	49	45	43	40	37	33	31	30
4	73	63	55	49	66	57	51	46	48	43	39	39	35	32	30	28	26
5	67	56	48	42	61	51	44	39	43	37	33	35	31	28	27	25	22
6	62	50	42	37	56	46	39	34	38	33	29	31	27	24	25	22	20
7	57	45	37	32	52	42	35	30	35	30	26	28	25	22	22	20	18
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14
10	46	34	27	22	42	32	25	21	27	22	18	22	18	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11626	11626	11626	11626
5°	11634	13396	11668	9998
10°	11560	16210	11572	8730
15°	11400	19225	11493	7859
20°	11263	22134	11287	7231
25°	11059	22692	11084	6904
30°	10913	18748	10913	6689
35°	10732	12538	10665	6500
40°	10515	9051	10385	6210
45°	10243	7170	9947	5850
50°	9583	6088	9241	5495
55°	8857	5351	8496	5100
60°	8120	4658	7688	4685
65°	7313	3989	6957	4132
70°	6473	3311	6040	3485
75°	5535	2497	5177	2689
80°	4376	1667	4034	1768
85°	3016	765	2411	696

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 18751 cd/sqm

TEST NUMBER: P1010712

CATALOG NUMBER: S123DIP-B775D1195UB2750-4F0-XX-W2A-A_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	106.2	1.3
10°-20°	341.2	4.3
20°-30°	574.1	7.2
30°-40°	648.8	8.1
40°-50°	581.1	7.3
50°-60°	469.1	5.9
60°-70°	326.9	4.1
70°-80°	171.6	2.1
80°-90°	44.2	0.6
90°-100°	54.8	0.7
100°-110°	264.9	3.3
110°-120°	649.2	8.1
120°-130°	824.1	10.3
130°-140°	880.4	11.0
140°-150°	823.3	10.3
150°-160°	664.0	8.3
160°-170°	428.5	5.4
170°-180°	147.7	1.8
0°-30°	1021.5	12.8
0°-40°	1670.3	20.9
0°-60°	2720.4	34.0
0°-90°	3263.1	40.8
90°-120°	968.9	12.1
90°-150°	3496.7	43.7
90°-180°	4737.0	59.2
0°-180°	8000.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1080	1080	1080	1080	1080	
5°	1079	1283	1082	958	1079	102
15°	1030	1910	1038	781	1030	291
25°	942	2267	944	690	942	435
35°	831	1221	826	633	831	520
45°	690	659	670	538	690	528
55°	489	448	469	427	489	438
65°	302	291	288	301	302	301
75°	146	150	136	161	146	156
85°	31	34	25	31	31	36
90°	1	35	1	35	1	6
95°	70	44	70	44	70	84
105°	344	51	344	51	344	365
115°	645	679	645	679	645	637
125°	910	928	910	928	910	813
135°	1132	1144	1132	1144	1132	872
145°	1307	1320	1307	1320	1307	818
155°	1440	1437	1440	1437	1440	663
165°	1518	1515	1518	1515	1518	429
175°	1554	1548	1554	1548	1554	148
180°	1554	1554	1554	1554	1554	

TEST NUMBER: P1010712

CATALOG NUMBER: S123DIP-B775D1195UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1
2.5°	1083.3	1091.6	1095.8	1102.1	1108.4	1117.8	1120.9	1126.2	1124.1	1128.3	1130.4
5°	1079.1	1093.7	1106.3	1122.0	1136.6	1147.1	1157.6	1174.3	1186.9	1189.0	1198.4
7.5°	1071.8	1092.7	1114.7	1136.6	1164.9	1181.7	1200.5	1223.5	1242.4	1272.7	1284.2
10°	1062.3	1091.6	1123.0	1153.4	1192.1	1218.3	1241.3	1280.0	1318.8	1350.2	1379.5
12.5°	1047.7	1084.3	1125.1	1170.1	1220.4	1250.7	1282.1	1333.4	1392.0	1440.2	1471.6
15°	1029.9	1075.9	1128.3	1176.4	1231.9	1288.4	1321.9	1379.5	1463.2	1508.2	1588.8
17.5°	1015.2	1062.3	1114.7	1190.0	1265.4	1321.9	1346.0	1451.7	1509.2	1584.6	1675.7
20°	992.2	1051.9	1118.9	1194.2	1291.5	1326.1	1375.3	1482.0	1553.2	1651.6	1763.6
22.5°	968.1	1032.0	1112.6	1191.1	1299.9	1336.6	1403.5	1488.3	1601.4	1698.7	1822.2
25°	942.0	1011.1	1092.7	1185.8	1292.6	1346.0	1408.8	1513.4	1635.9	1758.3	1872.4
27.5°	915.8	991.2	1075.9	1169.1	1272.7	1335.5	1398.3	1507.2	1664.2	1797.1	1942.6
30°	890.7	966.0	1050.8	1146.1	1254.9	1315.6	1375.3	1511.3	1686.1	1835.8	1982.3
32.5°	863.5	940.9	1029.9	1109.4	1219.3	1284.2	1351.2	1511.3	1699.7	1858.8	1992.8
35°	831.0	910.6	987.0	1066.5	1175.4	1247.6	1322.9	1500.9	1712.3	1866.2	1948.8
37.5°	799.6	869.8	935.7	1013.1	1127.2	1204.7	1291.5	1488.3	1706.0	1834.8	1857.8
40°	764.0	834.2	887.5	959.8	1080.1	1170.1	1258.1	1471.6	1678.8	1760.4	1693.5
42.5°	729.5	785.0	831.0	901.2	1032.0	1119.9	1215.1	1441.2	1625.4	1642.2	1491.5
45°	689.7	729.5	770.3	849.9	979.7	1069.7	1175.4	1397.3	1539.6	1491.5	1301.0
47.5°	638.4	674.0	719.0	792.3	924.2	1017.3	1117.8	1340.7	1415.1	1314.6	1106.3
50°	589.3	619.6	661.5	732.6	865.6	956.6	1063.4	1251.8	1288.4	1130.4	953.5
52.5°	540.1	563.1	603.9	675.1	808.0	895.9	993.3	1160.7	1139.8	970.2	813.2
55°	488.8	508.7	547.4	617.5	741.0	824.7	917.9	1048.7	994.3	833.1	707.5
57.5°	438.5	459.5	499.2	557.9	674.0	755.7	830.0	932.6	850.9	722.2	611.2
60°	393.5	411.3	441.7	499.2	605.0	670.9	738.9	809.0	741.0	616.5	531.7
62.5°	346.4	363.2	391.4	443.8	534.8	593.4	647.9	705.4	630.1	539.0	463.7
65°	302.5	316.1	342.2	390.4	464.7	512.9	556.8	596.6	535.9	452.1	395.6
67.5°	262.7	274.2	296.2	339.1	401.9	436.4	472.0	505.5	454.2	387.3	339.1
70°	219.8	229.2	249.1	280.5	330.7	366.3	392.5	417.6	371.6	318.2	285.7
72.5°	182.1	191.5	204.1	236.5	271.1	293.1	321.3	334.9	308.8	264.8	232.4
75°	145.5	152.8	164.3	185.3	217.7	232.4	250.1	260.6	236.5	207.2	187.3
77.5°	114.1	117.2	125.6	140.2	162.2	179.0	192.6	198.9	182.1	163.3	146.5
80°	80.6	84.8	91.1	103.6	120.4	125.6	134.0	141.3	130.8	114.1	103.6
82.5°	53.4	58.6	61.8	67.0	77.5	83.7	85.8	92.1	82.7	76.4	72.2
85°	31.4	33.5	34.5	37.7	42.9	46.1	49.2	50.2	48.1	47.1	42.9
87.5°	15.7	15.7	15.7	17.8	18.8	20.9	22.0	22.0	22.0	20.9	19.9
90°	1.2	3.8	6.3	8.9	11.4	12.7	14.4	17.7	21.0	24.4	27.7
92.5°	26.6	25.0	23.5	21.9	20.4	19.6	20.8	23.1	25.4	27.7	30.0
95°	70.4	59.9	49.4	38.9	28.4	23.1	24.5	27.3	30.2	33.0	35.8
97.5°	128.1	120.9	113.7	106.6	99.4	95.8	89.3	76.2	63.1	50.0	36.9
100°	195.1	200.2	205.4	210.5	215.6	218.2	198.2	158.2	118.1	78.1	38.1
102.5°	271.3	274.6	278.0	281.3	284.6	286.3	264.0	219.3	174.7	130.0	85.4
105°	344.0	346.8	349.6	352.5	355.3	356.7	345.2	322.1	299.0	275.9	252.8
107.5°	421.4	423.7	426.0	428.3	430.6	431.7	433.6	437.5	441.4	445.2	449.1
110°	498.7	500.7	502.8	504.8	506.9	507.9	509.3	512.1	515.0	517.8	520.6

TEST NUMBER: P1010712

CATALOG NUMBER: S123DIP-B775D1195UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	572.6	574.4	576.2	578.0	579.8	580.7	582.1	584.9	587.8	590.6	593.4
115°	645.3	646.8	648.4	649.9	651.4	652.2	653.4	655.7	658.0	660.3	662.6
117.5°	716.9	718.7	720.5	722.3	724.1	725.0	725.6	726.9	728.2	729.4	730.7
120°	782.7	785.0	787.3	789.6	791.9	793.1	793.5	794.2	795.0	795.7	796.5
122.5°	849.6	851.4	853.2	855.0	856.8	857.7	858.2	859.2	860.3	861.3	862.3
125°	909.7	911.7	913.8	915.8	917.9	918.9	919.4	920.4	921.5	922.5	923.5
127.5°	969.7	971.7	973.8	975.8	977.9	978.9	979.5	980.8	982.1	983.4	984.7
130°	1025.1	1027.1	1029.2	1031.2	1033.3	1034.3	1034.8	1035.8	1036.9	1037.9	1038.9
132.5°	1078.2	1080.2	1082.3	1084.3	1086.4	1087.4	1087.8	1088.6	1089.3	1090.1	1090.9
135°	1132.5	1134.0	1135.6	1137.1	1138.6	1139.4	1139.9	1140.9	1142.0	1143.0	1144.0
137.5°	1178.6	1180.7	1182.7	1184.8	1186.9	1187.9	1188.2	1188.7	1189.2	1189.7	1190.2
140°	1224.8	1226.3	1227.9	1229.4	1230.9	1231.7	1232.1	1232.9	1233.6	1234.4	1235.2
142.5°	1267.5	1269.0	1270.6	1272.1	1273.6	1274.4	1274.8	1275.6	1276.3	1277.1	1277.9
145°	1306.8	1308.6	1310.4	1312.1	1313.9	1314.8	1315.1	1315.6	1316.1	1316.7	1317.2
147.5°	1344.9	1346.2	1347.4	1348.7	1350.0	1350.6	1350.9	1351.4	1351.9	1352.4	1352.9
150°	1379.5	1380.3	1381.1	1381.8	1382.6	1383.0	1383.3	1383.8	1384.3	1384.8	1385.3
152.5°	1410.7	1410.9	1411.2	1411.4	1411.7	1411.8	1411.9	1412.2	1412.5	1412.7	1413.0
155°	1439.5	1439.0	1438.5	1438.0	1437.5	1437.2	1437.3	1437.6	1437.9	1438.1	1438.4
157.5°	1462.6	1462.6	1462.6	1462.6	1462.6	1462.6	1462.5	1462.2	1462.0	1461.7	1461.5
160°	1483.4	1483.1	1482.9	1482.6	1482.3	1482.2	1482.1	1481.8	1481.6	1481.3	1481.1
162.5°	1503.0	1502.2	1501.4	1500.7	1499.9	1499.5	1499.4	1499.1	1498.9	1498.6	1498.4
165°	1518.0	1517.2	1516.5	1515.7	1515.0	1514.6	1514.5	1514.2	1513.9	1513.7	1513.4
167.5°	1530.7	1529.7	1528.7	1527.6	1526.6	1526.1	1526.1	1526.1	1526.1	1526.1	1526.1
170°	1541.1	1540.1	1539.1	1538.0	1537.0	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5
172.5°	1548.0	1546.7	1545.5	1544.2	1542.9	1542.3	1542.4	1542.7	1542.9	1543.2	1543.4
175°	1553.8	1552.5	1551.2	1549.9	1548.6	1548.0	1548.1	1548.4	1548.7	1548.9	1549.2
177.5°	1556.1	1554.8	1553.5	1552.2	1550.9	1550.3	1550.4	1550.7	1551.0	1551.2	1551.5
180°	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8

TEST NUMBER: P1010712

CATALOG NUMBER: S123DIP-B775D1195UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1
2.5°	1137.7	1139.8	1147.1	1152.3	1162.8	1161.8	1161.8	1160.7	1157.6	1162.8	1166.0
5°	1217.2	1235.0	1237.1	1260.1	1261.2	1270.6	1276.9	1271.7	1284.2	1283.2	1273.8
7.5°	1315.6	1339.7	1351.2	1373.2	1398.3	1392.0	1416.1	1420.3	1418.2	1428.7	1436.0
10°	1423.4	1465.3	1494.6	1535.4	1545.9	1552.2	1567.9	1581.5	1608.7	1587.7	1601.4
12.5°	1546.9	1577.3	1616.0	1680.9	1713.3	1734.3	1741.6	1751.0	1769.9	1758.3	1759.4
15°	1650.5	1691.4	1757.3	1837.9	1847.3	1873.5	1867.2	1923.7	1950.9	1910.1	1933.1
17.5°	1758.3	1812.8	1891.3	1961.4	2001.2	2019.0	2035.7	2090.1	2088.0	2081.8	2087.0
20°	1827.4	1916.4	2013.7	2106.9	2118.4	2132.0	2177.0	2200.0	2195.8	2213.6	2225.1
22.5°	1924.8	2019.0	2122.6	2184.3	2210.5	2226.2	2261.8	2276.4	2282.7	2286.9	2279.6
25°	2006.4	2106.9	2183.3	2237.7	2253.4	2261.8	2273.3	2277.5	2274.3	2267.0	2273.3
27.5°	2061.9	2142.5	2194.8	2219.9	2211.5	2197.9	2176.0	2161.3	2128.9	2113.2	2132.0
30°	2084.9	2120.5	2136.2	2094.3	2052.5	2019.0	1977.1	1899.6	1838.9	1856.7	1832.7
32.5°	2048.3	2025.2	1949.9	1842.1	1809.6	1755.2	1636.9	1545.9	1549.0	1500.9	1520.8
35°	1940.5	1835.8	1693.5	1530.2	1487.3	1458.0	1328.2	1308.3	1266.4	1221.4	1234.0
37.5°	1750.0	1597.2	1424.5	1304.1	1240.3	1176.4	1103.2	1059.2	1034.1	1015.2	1029.9
40°	1517.6	1331.3	1189.0	1081.2	1026.7	985.9	935.7	891.7	863.5	860.3	865.6
42.5°	1289.5	1132.5	1001.6	899.1	881.3	833.1	800.7	766.1	757.8	744.2	751.5
45°	1091.6	964.0	856.1	772.4	751.5	738.9	699.2	677.2	667.8	659.4	671.9
47.5°	948.3	814.3	735.8	685.5	664.6	643.7	621.7	607.0	599.7	600.8	599.7
50°	810.1	711.7	642.6	603.9	591.3	576.7	558.9	549.5	546.3	536.9	544.3
52.5°	697.1	625.9	577.7	541.1	531.7	521.2	506.6	501.3	494.0	491.9	491.9
55°	606.0	550.5	511.8	487.7	476.2	467.8	459.5	453.2	448.0	448.0	448.0
57.5°	534.8	486.7	458.4	437.5	433.3	424.9	415.5	415.5	408.2	407.1	410.3
60°	474.1	431.2	409.2	391.4	385.2	383.1	373.6	373.6	371.6	366.3	370.5
62.5°	412.4	381.0	362.1	348.5	342.2	342.2	334.9	329.7	329.7	330.7	328.6
65°	355.9	332.8	316.1	305.6	302.5	298.3	297.2	293.1	289.9	291.0	289.9
67.5°	305.6	287.8	276.3	267.9	262.7	260.6	257.5	257.5	255.4	256.4	251.2
70°	260.6	242.8	233.4	225.0	222.9	222.9	218.7	219.8	217.7	220.8	218.7
72.5°	214.6	201.0	193.6	190.5	188.4	187.3	185.3	183.2	182.1	184.2	183.2
75°	173.7	162.2	157.0	154.9	152.8	152.8	151.8	150.7	149.7	149.7	149.7
77.5°	135.0	127.7	121.4	123.5	120.4	121.4	118.3	118.3	119.3	118.3	118.3
80°	99.4	94.2	94.2	92.1	87.9	90.0	90.0	86.9	85.8	87.9	84.8
82.5°	65.9	64.9	62.8	61.8	59.7	60.7	59.7	58.6	57.6	59.7	57.6
85°	38.7	38.7	37.7	35.6	37.7	36.6	35.6	35.6	34.5	34.5	34.5
87.5°	19.9	17.8	17.8	16.7	17.8	15.7	16.7	15.7	14.7	15.7	14.7
90°	28.7	29.7	30.8	31.8	32.3	32.6	33.1	33.6	34.1	34.6	34.1
92.5°	31.8	33.6	35.4	37.2	38.1	38.2	38.5	38.7	39.0	39.2	39.0
95°	37.6	39.4	41.2	43.0	43.9	43.9	43.9	43.9	43.9	43.9	43.9
97.5°	39.0	41.0	43.1	45.2	46.2	46.3	46.6	46.8	47.1	47.3	47.1
100°	40.1	42.2	44.2	46.3	47.3	47.4	47.7	48.0	48.2	48.5	48.2
102.5°	76.9	68.5	60.0	51.5	47.3	47.6	48.1	48.6	49.1	49.6	49.1
105°	207.4	162.0	116.6	71.2	48.5	48.8	49.3	49.8	50.3	50.8	50.3
107.5°	409.6	370.1	330.6	291.1	271.3	254.5	220.9	187.3	153.7	120.1	153.7
110°	512.1	503.7	495.2	486.7	482.5	464.2	427.5	390.8	354.2	317.5	354.2



TEST NUMBER: P1010712

CATALOG NUMBER: S123DIP-B775D1195UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	595.7	598.0	600.3	602.6	603.7	603.4	602.9	602.4	601.9	601.4	601.9
115°	665.2	667.8	670.3	672.9	674.2	674.7	675.7	676.8	677.8	678.8	677.8
117.5°	732.8	734.8	736.9	739.0	740.0	740.1	740.4	740.6	740.9	741.1	740.9
120°	798.6	800.6	802.7	804.8	805.8	805.8	805.8	805.8	805.8	805.8	805.8
122.5°	863.6	864.9	866.2	867.5	868.1	868.2	868.5	868.8	869.0	869.3	869.0
125°	924.0	924.5	925.0	925.5	925.8	926.1	926.6	927.1	927.6	928.1	927.6
127.5°	985.5	986.3	987.0	987.8	988.2	987.9	987.4	986.9	986.3	985.8	986.3
130°	1039.9	1041.0	1042.0	1043.1	1043.6	1043.3	1042.8	1042.3	1041.8	1041.3	1041.8
132.5°	1091.9	1092.9	1094.0	1095.0	1095.5	1095.1	1094.3	1093.6	1092.8	1092.0	1092.8
135°	1144.8	1145.6	1146.3	1147.1	1147.5	1147.1	1146.3	1145.6	1144.8	1144.0	1144.8
137.5°	1191.5	1192.7	1194.0	1195.3	1195.9	1195.6	1195.1	1194.6	1194.1	1193.6	1194.1
140°	1236.2	1237.2	1238.3	1239.3	1239.8	1239.5	1239.0	1238.5	1238.0	1237.5	1238.0
142.5°	1278.7	1279.5	1280.2	1281.0	1281.4	1281.0	1280.2	1279.5	1278.7	1277.9	1278.7
145°	1317.7	1318.2	1318.7	1319.2	1319.5	1319.5	1319.5	1319.5	1319.5	1319.5	1319.5
147.5°	1353.4	1353.9	1354.4	1354.9	1355.2	1354.6	1353.3	1352.0	1350.8	1349.5	1350.8
150°	1385.8	1386.3	1386.8	1387.3	1387.6	1387.2	1386.4	1385.7	1384.9	1384.1	1384.9
152.5°	1414.0	1415.0	1416.1	1417.1	1417.6	1417.0	1415.7	1414.4	1413.1	1411.8	1413.1
155°	1439.7	1440.9	1442.2	1443.5	1444.1	1443.3	1441.8	1440.3	1438.7	1437.2	1438.7
157.5°	1463.0	1464.6	1466.1	1467.6	1468.4	1467.4	1465.3	1463.2	1461.2	1459.1	1461.2
160°	1482.6	1484.2	1485.7	1487.2	1488.0	1487.1	1485.3	1483.5	1481.7	1479.9	1481.7
162.5°	1500.2	1502.0	1503.8	1505.6	1506.5	1505.7	1504.2	1502.6	1501.1	1499.5	1501.1
165°	1515.4	1517.5	1519.5	1521.6	1522.6	1521.7	1519.9	1518.2	1516.4	1514.6	1516.4
167.5°	1528.1	1530.2	1532.2	1534.3	1535.3	1534.3	1532.2	1530.2	1528.1	1526.1	1528.1
170°	1538.5	1540.6	1542.6	1544.7	1545.7	1544.7	1542.6	1540.6	1538.5	1536.5	1538.5
172.5°	1545.4	1547.5	1549.5	1551.6	1552.6	1551.5	1549.2	1546.9	1544.6	1542.3	1544.6
175°	1551.0	1552.8	1554.6	1556.4	1557.3	1556.3	1554.2	1552.1	1550.1	1548.0	1550.1
177.5°	1553.5	1555.6	1557.6	1559.7	1560.7	1559.4	1556.9	1554.3	1551.8	1549.2	1551.8
180°	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8

TEST NUMBER: P1010712

CATALOG NUMBER: S123DIP-B775D1195UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1
2.5°	1157.6	1160.7	1152.3	1150.3	1150.3	1154.4	1151.3	1123.0	1128.3	1122.0	1119.9
5°	1285.3	1279.0	1270.6	1266.4	1261.2	1246.5	1245.5	1213.1	1206.8	1185.8	1176.4
7.5°	1425.5	1420.3	1395.2	1392.0	1389.9	1376.3	1341.8	1307.2	1282.1	1258.1	1235.0
10°	1585.7	1570.0	1558.4	1535.4	1523.9	1505.1	1460.1	1427.6	1384.7	1348.1	1299.9
12.5°	1778.2	1760.4	1721.7	1705.0	1690.3	1638.0	1593.0	1556.3	1472.6	1447.5	1387.8
15°	1919.5	1881.9	1877.7	1841.0	1838.9	1781.4	1695.5	1655.8	1590.9	1498.8	1437.0
17.5°	2072.3	2038.8	2012.7	1968.7	1962.4	1908.0	1845.2	1747.9	1676.7	1588.8	1510.3
20°	2184.3	2166.5	2121.5	2103.7	2067.1	2021.1	1956.2	1835.8	1748.9	1661.0	1564.7
22.5°	2273.3	2255.5	2219.9	2195.8	2174.9	2115.3	2037.8	1935.2	1815.9	1700.8	1601.4
25°	2272.2	2267.0	2252.4	2240.8	2225.1	2181.2	2116.3	2017.9	1885.0	1758.3	1620.2
27.5°	2143.5	2158.2	2183.3	2195.8	2192.7	2186.4	2149.8	2067.1	1947.8	1797.1	1642.2
30°	1875.6	1928.9	1976.0	2038.8	2057.7	2103.7	2124.7	2077.6	1982.3	1842.1	1670.4
32.5°	1555.3	1632.8	1735.3	1769.9	1829.5	1918.5	2017.9	2035.7	1976.0	1868.2	1688.2
35°	1275.8	1339.7	1419.2	1473.7	1527.0	1671.5	1797.1	1905.9	1925.8	1854.6	1684.0
37.5°	1056.1	1101.1	1171.2	1217.2	1266.4	1389.9	1565.8	1707.1	1806.5	1808.6	1672.5
40°	897.0	916.9	977.6	1011.1	1058.1	1164.9	1321.9	1506.1	1651.6	1718.6	1642.2
42.5°	759.9	786.0	836.3	861.4	891.7	984.9	1088.5	1263.3	1443.3	1586.7	1585.7
45°	678.2	697.1	720.1	741.0	775.6	831.0	949.3	1080.1	1252.8	1415.1	1478.9
47.5°	606.0	623.8	646.8	653.1	676.1	728.5	800.7	914.8	1075.9	1237.1	1357.5
50°	545.3	560.0	575.6	587.2	597.6	640.5	695.0	791.3	920.0	1075.9	1225.6
52.5°	498.2	508.7	522.3	528.6	538.0	569.4	611.2	682.4	788.1	930.5	1075.9
55°	454.2	461.6	469.9	480.4	484.6	507.6	540.1	600.8	679.3	807.0	945.1
57.5°	413.4	416.6	421.8	428.1	433.3	453.2	481.5	522.3	591.3	689.7	820.6
60°	367.4	375.7	378.9	385.2	388.3	404.0	426.0	460.5	513.9	598.7	697.1
62.5°	328.6	333.9	339.1	342.2	349.6	354.8	372.6	404.0	448.0	510.8	599.7
65°	294.1	296.2	299.3	302.5	304.6	310.9	327.6	348.5	382.0	437.5	506.6
67.5°	254.3	256.4	260.6	261.7	263.8	272.1	281.5	299.3	327.6	369.5	426.0
70°	215.6	218.7	220.8	222.9	226.1	229.2	239.7	254.3	276.3	305.6	349.6
72.5°	182.1	185.3	185.3	187.3	186.3	190.5	201.0	211.4	226.1	250.1	288.9
75°	148.6	148.6	150.7	151.8	152.8	157.0	161.2	169.6	181.1	199.9	224.0
77.5°	117.2	116.2	118.3	118.3	118.3	121.4	125.6	129.8	137.1	150.7	169.6
80°	85.8	85.8	87.9	89.0	86.9	87.9	90.0	94.2	99.4	108.9	119.3
82.5°	56.5	60.7	59.7	60.7	59.7	61.8	62.8	63.8	65.9	70.1	77.5
85°	34.5	34.5	34.5	35.6	34.5	35.6	35.6	35.6	36.6	38.7	41.9
87.5°	14.7	14.7	14.7	15.7	14.7	14.7	15.7	14.7	15.7	15.7	16.7
90°	33.6	33.1	32.6	32.3	31.8	30.8	29.7	28.7	27.7	24.4	21.0
92.5°	38.7	38.5	38.2	38.1	37.2	35.4	33.6	31.8	30.0	27.7	25.4
95°	43.9	43.9	43.9	43.9	43.0	41.2	39.4	37.6	35.8	33.0	30.2
97.5°	46.8	46.6	46.3	46.2	45.2	43.1	41.0	39.0	36.9	50.0	63.1
100°	48.0	47.7	47.4	47.3	46.3	44.2	42.2	40.1	38.1	78.1	118.1
102.5°	48.6	48.1	47.6	47.3	51.5	60.0	68.5	76.9	85.4	130.0	174.7
105°	49.8	49.3	48.8	48.5	71.2	116.6	162.0	207.4	252.8	275.9	299.0
107.5°	187.3	220.9	254.5	271.3	291.1	330.6	370.1	409.6	449.1	445.2	441.4
110°	390.8	427.5	464.2	482.5	486.7	495.2	503.7	512.1	520.6	517.8	515.0

TEST NUMBER: P1010712

CATALOG NUMBER: S123DIP-B775D1195UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	602.4	602.9	603.4	603.7	602.6	600.3	598.0	595.7	593.4	590.6	587.8
115°	676.8	675.7	674.7	674.2	672.9	670.3	667.8	665.2	662.6	660.3	658.0
117.5°	740.6	740.4	740.1	740.0	739.0	736.9	734.8	732.8	730.7	729.4	728.2
120°	805.8	805.8	805.8	805.8	804.8	802.7	800.6	798.6	796.5	795.7	795.0
122.5°	868.8	868.5	868.2	868.1	867.5	866.2	864.9	863.6	862.3	861.3	860.3
125°	927.1	926.6	926.1	925.8	925.5	925.0	924.5	924.0	923.5	922.5	921.5
127.5°	986.9	987.4	987.9	988.2	987.8	987.0	986.3	985.5	984.7	983.4	982.1
130°	1042.3	1042.8	1043.3	1043.6	1043.1	1042.0	1041.0	1039.9	1038.9	1037.9	1036.9
132.5°	1093.6	1094.3	1095.1	1095.5	1095.0	1094.0	1092.9	1091.9	1090.9	1090.1	1089.3
135°	1145.6	1146.3	1147.1	1147.5	1147.1	1146.3	1145.6	1144.8	1144.0	1143.0	1142.0
137.5°	1194.6	1195.1	1195.6	1195.9	1195.3	1194.0	1192.7	1191.5	1190.2	1189.7	1189.2
140°	1238.5	1239.0	1239.5	1239.8	1239.3	1238.3	1237.2	1236.2	1235.2	1234.4	1233.6
142.5°	1279.5	1280.2	1281.0	1281.4	1281.0	1280.2	1279.5	1278.7	1277.9	1277.1	1276.3
145°	1319.5	1319.5	1319.5	1319.5	1319.2	1318.7	1318.2	1317.7	1317.2	1316.7	1316.1
147.5°	1352.0	1353.3	1354.6	1355.2	1354.9	1354.4	1353.9	1353.4	1352.9	1352.4	1351.9
150°	1385.7	1386.4	1387.2	1387.6	1387.3	1386.8	1386.3	1385.8	1385.3	1384.8	1384.3
152.5°	1414.4	1415.7	1417.0	1417.6	1417.1	1416.1	1415.0	1414.0	1413.0	1412.7	1412.5
155°	1440.3	1441.8	1443.3	1444.1	1443.5	1442.2	1440.9	1439.7	1438.4	1438.1	1437.9
157.5°	1463.2	1465.3	1467.4	1468.4	1467.6	1466.1	1464.6	1463.0	1461.5	1461.7	1462.0
160°	1483.5	1485.3	1487.1	1488.0	1487.2	1485.7	1484.2	1482.6	1481.1	1481.3	1481.6
162.5°	1502.6	1504.2	1505.7	1506.5	1505.6	1503.8	1502.0	1500.2	1498.4	1498.6	1498.9
165°	1518.2	1519.9	1521.7	1522.6	1521.6	1519.5	1517.5	1515.4	1513.4	1513.7	1513.9
167.5°	1530.2	1532.2	1534.3	1535.3	1534.3	1532.2	1530.2	1528.1	1526.1	1526.1	1526.1
170°	1540.6	1542.6	1544.7	1545.7	1544.7	1542.6	1540.6	1538.5	1536.5	1536.5	1536.5
172.5°	1546.9	1549.2	1551.5	1552.6	1551.6	1549.5	1547.5	1545.4	1543.4	1543.2	1542.9
175°	1552.1	1554.2	1556.3	1557.3	1556.4	1554.6	1552.8	1551.0	1549.2	1548.9	1548.7
177.5°	1554.3	1556.9	1559.4	1560.7	1559.7	1557.6	1555.6	1553.5	1551.5	1551.2	1551.0
180°	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8

TEST NUMBER: P1010712

CATALOG NUMBER: S123DIP-B775D1195UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1
2.5°	1109.4	1106.3	1106.3	1104.2	1097.9	1086.4	1085.4	1087.5	1081.2	1074.9	1065.5
5°	1163.9	1144.0	1137.7	1131.4	1118.9	1097.9	1089.5	1082.2	1070.7	1057.1	1042.4
7.5°	1209.9	1181.7	1173.3	1161.8	1136.6	1107.3	1088.5	1072.8	1057.1	1038.3	1020.5
10°	1267.5	1226.7	1206.8	1190.0	1155.5	1114.7	1086.4	1063.4	1038.3	1015.2	992.2
12.5°	1332.4	1266.4	1260.1	1219.3	1179.6	1118.9	1084.3	1050.8	1017.3	989.1	965.0
15°	1386.8	1314.6	1288.4	1261.2	1184.8	1109.4	1075.9	1038.3	999.5	969.2	933.6
17.5°	1421.3	1361.7	1306.2	1269.6	1190.0	1123.0	1058.1	1015.2	974.4	932.6	903.2
20°	1463.2	1376.3	1328.2	1279.0	1200.5	1112.6	1047.7	994.3	944.1	906.4	870.8
22.5°	1505.1	1387.8	1348.1	1294.7	1202.6	1102.1	1028.8	975.5	917.9	880.2	841.5
25°	1500.9	1404.6	1338.6	1293.6	1181.7	1092.7	1006.9	944.1	890.7	842.5	803.8
27.5°	1504.0	1385.7	1318.8	1266.4	1167.0	1079.1	983.8	917.9	862.4	812.2	771.4
30°	1505.1	1357.5	1298.9	1236.1	1139.8	1046.6	957.7	890.7	832.1	777.7	741.0
32.5°	1501.9	1334.5	1261.2	1204.7	1096.9	1015.2	927.3	856.1	796.5	746.3	711.7
35°	1494.6	1307.2	1222.5	1151.3	1052.9	970.2	899.1	825.8	762.0	715.9	676.1
37.5°	1474.7	1277.9	1181.7	1111.5	1001.6	917.9	855.1	794.4	732.6	678.2	644.7
40°	1460.1	1238.2	1140.8	1064.4	946.2	864.5	812.2	754.6	693.9	644.7	612.3
42.5°	1426.6	1200.5	1099.0	1007.9	891.7	808.0	758.8	712.8	660.4	612.3	583.0
45°	1372.1	1159.7	1047.7	955.6	832.1	752.5	707.5	669.8	623.8	577.7	548.4
47.5°	1295.7	1101.1	993.3	901.2	773.5	692.9	647.9	619.6	583.0	544.3	519.1
50°	1213.1	1037.2	937.8	846.7	716.9	638.4	594.5	568.3	544.3	508.7	484.6
52.5°	1105.2	969.2	873.9	787.1	656.2	580.9	542.2	523.3	498.2	473.1	452.1
55°	1000.6	881.3	802.8	720.1	596.6	526.5	488.8	468.9	454.2	433.3	416.6
57.5°	879.2	799.6	727.4	652.1	541.1	477.3	441.7	417.6	408.2	398.8	383.1
60°	767.2	706.5	647.9	585.1	483.5	426.0	391.4	372.6	363.2	356.9	346.4
62.5°	664.6	617.5	567.3	517.0	424.9	372.6	346.4	327.6	319.2	318.2	308.8
65°	566.2	532.7	491.9	442.7	370.5	324.5	299.3	287.8	278.4	278.4	271.1
67.5°	467.8	444.8	412.4	377.8	321.3	278.4	255.4	244.9	239.7	239.7	234.4
70°	389.3	373.6	344.3	314.0	264.8	232.4	214.6	205.1	202.0	203.0	198.9
72.5°	316.1	299.3	275.3	253.3	216.7	192.6	180.0	169.6	164.3	165.4	164.3
75°	244.9	236.5	215.6	198.9	169.6	152.8	141.3	136.1	131.9	132.9	130.8
77.5°	184.2	171.6	160.1	148.6	130.8	117.2	107.8	102.6	99.4	99.4	99.4
80°	125.6	123.5	114.1	107.8	93.2	82.7	75.4	74.3	71.2	71.2	71.2
82.5°	81.6	76.4	71.2	67.0	58.6	52.3	49.2	47.1	46.1	45.0	47.1
85°	45.0	41.9	39.8	35.6	32.4	29.3	26.2	25.1	24.1	25.1	24.1
87.5°	17.8	14.7	14.7	13.6	12.6	11.5	11.5	9.4	9.4	8.4	8.4
90°	17.7	14.4	12.7	11.4	8.9	6.3	3.8	1.2	3.8	6.3	8.9
92.5°	23.1	20.8	19.6	20.4	21.9	23.5	25.0	26.6	25.0	23.5	21.9
95°	27.3	24.5	23.1	28.4	38.9	49.4	59.9	70.4	59.9	49.4	38.9
97.5°	76.2	89.3	95.8	99.4	106.6	113.7	120.9	128.1	120.9	113.7	106.6
100°	158.2	198.2	218.2	215.6	210.5	205.4	200.2	195.1	200.2	205.4	210.5
102.5°	219.3	264.0	286.3	284.6	281.3	278.0	274.6	271.3	274.6	278.0	281.3
105°	322.1	345.2	356.7	355.3	352.5	349.6	346.8	344.0	346.8	349.6	352.5
107.5°	437.5	433.6	431.7	430.6	428.3	426.0	423.7	421.4	423.7	426.0	428.3
110°	512.1	509.3	507.9	506.9	504.8	502.8	500.7	498.7	500.7	502.8	504.8

TEST NUMBER: P1010712

CATALOG NUMBER: S123DIP-B775D1195UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	584.9	582.1	580.7	579.8	578.0	576.2	574.4	572.6	574.4	576.2	578.0
115°	655.7	653.4	652.2	651.4	649.9	648.4	646.8	645.3	646.8	648.4	649.9
117.5°	726.9	725.6	725.0	724.1	722.3	720.5	718.7	716.9	718.7	720.5	722.3
120°	794.2	793.5	793.1	791.9	789.6	787.3	785.0	782.7	785.0	787.3	789.6
122.5°	859.2	858.2	857.7	856.8	855.0	853.2	851.4	849.6	851.4	853.2	855.0
125°	920.4	919.4	918.9	917.9	915.8	913.8	911.7	909.7	911.7	913.8	915.8
127.5°	980.8	979.5	978.9	977.9	975.8	973.8	971.7	969.7	971.7	973.8	975.8
130°	1035.8	1034.8	1034.3	1033.3	1031.2	1029.2	1027.1	1025.1	1027.1	1029.2	1031.2
132.5°	1088.6	1087.8	1087.4	1086.4	1084.3	1082.3	1080.2	1078.2	1080.2	1082.3	1084.3
135°	1140.9	1139.9	1139.4	1138.6	1137.1	1135.6	1134.0	1132.5	1134.0	1135.6	1137.1
137.5°	1188.7	1188.2	1187.9	1186.9	1184.8	1182.7	1180.7	1178.6	1180.7	1182.7	1184.8
140°	1232.9	1232.1	1231.7	1230.9	1229.4	1227.9	1226.3	1224.8	1226.3	1227.9	1229.4
142.5°	1275.6	1274.8	1274.4	1273.6	1272.1	1270.6	1269.0	1267.5	1269.0	1270.6	1272.1
145°	1315.6	1315.1	1314.8	1313.9	1312.1	1310.4	1308.6	1306.8	1308.6	1310.4	1312.1
147.5°	1351.4	1350.9	1350.6	1350.0	1348.7	1347.4	1346.2	1344.9	1346.2	1347.4	1348.7
150°	1383.8	1383.3	1383.0	1382.6	1381.8	1381.1	1380.3	1379.5	1380.3	1381.1	1381.8
152.5°	1412.2	1411.9	1411.8	1411.7	1411.4	1411.2	1410.9	1410.7	1410.9	1411.2	1411.4
155°	1437.6	1437.3	1437.2	1437.5	1438.0	1438.5	1439.0	1439.5	1439.0	1438.5	1438.0
157.5°	1462.2	1462.5	1462.6	1462.6	1462.6	1462.6	1462.6	1462.6	1462.6	1462.6	1462.6
160°	1481.8	1482.1	1482.2	1482.3	1482.6	1482.9	1483.1	1483.4	1483.1	1482.9	1482.6
162.5°	1499.1	1499.4	1499.5	1499.9	1500.7	1501.4	1502.2	1503.0	1502.2	1501.4	1500.7
165°	1514.2	1514.5	1514.6	1515.0	1515.7	1516.5	1517.2	1518.0	1517.2	1516.5	1515.7
167.5°	1526.1	1526.1	1526.1	1526.6	1527.6	1528.7	1529.7	1530.7	1529.7	1528.7	1527.6
170°	1536.5	1536.5	1536.5	1537.0	1538.0	1539.1	1540.1	1541.1	1540.1	1539.1	1538.0
172.5°	1542.7	1542.4	1542.3	1542.9	1544.2	1545.5	1546.7	1548.0	1546.7	1545.5	1544.2
175°	1548.4	1548.1	1548.0	1548.6	1549.9	1551.2	1552.5	1553.8	1552.5	1551.2	1549.9
177.5°	1550.7	1550.4	1550.3	1550.9	1552.2	1553.5	1554.8	1556.1	1554.8	1553.5	1552.2
180°	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8

TEST NUMBER: P1010712

CATALOG NUMBER: S123DIP-B775D1195UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1
2.5°	1063.4	1062.3	1064.4	1058.1	1047.7	1042.4	1027.8	1024.7	1023.6	1024.7	1025.7
5°	1034.1	1033.0	1029.9	1019.4	1006.9	997.4	979.7	978.6	972.3	966.0	969.2
7.5°	1005.8	1001.6	995.4	981.7	965.0	954.5	939.9	929.4	921.0	915.8	911.6
10°	977.6	971.3	965.0	947.2	926.3	910.6	892.8	884.4	875.0	870.8	866.6
12.5°	940.9	934.6	923.1	902.2	889.6	869.8	852.0	843.6	838.4	830.0	824.7
15°	911.6	899.1	892.8	870.8	844.6	842.5	810.1	808.0	797.5	797.5	789.2
17.5°	878.1	868.7	857.2	835.2	816.4	797.5	780.8	774.5	765.1	763.0	758.8
20°	845.7	833.1	828.9	807.0	787.1	764.0	746.3	740.0	735.8	731.6	734.7
22.5°	812.2	801.7	791.3	771.4	756.7	733.7	723.2	716.9	710.7	708.6	709.6
25°	779.7	770.3	759.9	740.0	724.3	705.4	696.0	692.9	689.7	689.7	688.7
27.5°	748.3	738.9	729.5	711.7	696.0	682.4	675.1	671.9	668.8	670.9	673.0
30°	715.9	707.5	699.2	683.5	670.9	658.3	654.1	652.1	651.0	656.2	656.2
32.5°	686.6	679.3	673.0	658.3	645.8	635.3	632.2	633.2	634.3	637.4	639.5
35°	656.2	651.0	644.7	632.2	621.7	612.3	613.3	613.3	615.4	620.7	624.8
37.5°	629.0	621.7	616.5	606.0	597.6	589.3	592.4	595.5	597.6	603.9	606.0
40°	596.6	593.4	589.3	578.8	571.5	570.4	571.5	573.6	577.7	580.9	584.0
42.5°	570.4	566.2	561.0	552.6	546.3	547.4	548.4	550.5	552.6	557.9	561.0
45°	541.1	538.0	533.8	526.5	521.2	522.3	523.3	523.3	525.4	531.7	533.8
47.5°	508.7	509.7	504.5	497.2	494.0	494.0	494.0	496.1	501.3	503.4	504.5
50°	477.3	475.2	474.1	466.8	464.7	463.7	464.7	465.8	473.1	472.0	475.2
52.5°	443.8	443.8	442.7	438.5	435.4	435.4	433.3	438.5	440.6	442.7	445.9
55°	411.3	408.2	407.1	405.0	400.9	399.8	401.9	408.2	410.3	412.4	415.5
57.5°	375.7	375.7	373.6	370.5	370.5	370.5	370.5	374.7	377.8	379.9	386.2
60°	343.3	339.1	336.0	336.0	336.0	334.9	341.2	341.2	347.5	348.5	350.6
62.5°	304.6	302.5	300.4	301.4	300.4	302.5	304.6	308.8	309.8	312.9	316.1
65°	267.9	267.9	265.8	272.1	267.9	267.9	273.2	273.2	275.3	278.4	282.6
67.5°	232.4	233.4	231.3	231.3	233.4	234.4	235.5	239.7	240.7	244.9	250.1
70°	195.7	197.8	198.9	196.8	198.9	201.0	203.0	204.1	208.3	210.4	213.5
72.5°	163.3	165.4	162.2	163.3	164.3	166.4	167.5	169.6	171.6	177.9	180.0
75°	130.8	129.8	128.7	132.9	130.8	135.0	136.1	136.1	138.2	143.4	145.5
77.5°	100.5	100.5	101.5	99.4	102.6	101.5	102.6	105.7	108.9	108.9	117.2
80°	70.1	72.2	72.2	72.2	73.3	74.3	72.2	77.5	78.5	78.5	81.6
82.5°	45.0	46.1	45.0	47.1	47.1	49.2	48.1	49.2	51.3	53.4	54.4
85°	24.1	24.1	26.2	26.2	25.1	26.2	25.1	26.2	28.3	28.3	29.3
87.5°	8.4	8.4	8.4	8.4	9.4	8.4	9.4	9.4	8.4	8.4	11.5
90°	11.4	12.7	14.4	17.7	21.0	24.4	27.7	28.7	29.7	30.8	31.8
92.5°	20.4	19.6	20.8	23.1	25.4	27.7	30.0	31.8	33.6	35.4	37.2
95°	28.4	23.1	24.5	27.3	30.2	33.0	35.8	37.6	39.4	41.2	43.0
97.5°	99.4	95.8	89.3	76.2	63.1	50.0	36.9	39.0	41.0	43.1	45.2
100°	215.6	218.2	198.2	158.2	118.1	78.1	38.1	40.1	42.2	44.2	46.3
102.5°	284.6	286.3	264.0	219.3	174.7	130.0	85.4	76.9	68.5	60.0	51.5
105°	355.3	356.7	345.2	322.1	299.0	275.9	252.8	207.4	162.0	116.6	71.2
107.5°	430.6	431.7	433.6	437.5	441.4	445.2	449.1	409.6	370.1	330.6	291.1
110°	506.9	507.9	509.3	512.1	515.0	517.8	520.6	512.1	503.7	495.2	486.7

TEST NUMBER: P1010712

CATALOG NUMBER: S123DIP-B775D1195UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	579.8	580.7	582.1	584.9	587.8	590.6	593.4	595.7	598.0	600.3	602.6
115°	651.4	652.2	653.4	655.7	658.0	660.3	662.6	665.2	667.8	670.3	672.9
117.5°	724.1	725.0	725.6	726.9	728.2	729.4	730.7	732.8	734.8	736.9	739.0
120°	791.9	793.1	793.5	794.2	795.0	795.7	796.5	798.6	800.6	802.7	804.8
122.5°	856.8	857.7	858.2	859.2	860.3	861.3	862.3	863.6	864.9	866.2	867.5
125°	917.9	918.9	919.4	920.4	921.5	922.5	923.5	924.0	924.5	925.0	925.5
127.5°	977.9	978.9	979.5	980.8	982.1	983.4	984.7	985.5	986.3	987.0	987.8
130°	1033.3	1034.3	1034.8	1035.8	1036.9	1037.9	1038.9	1039.9	1041.0	1042.0	1043.1
132.5°	1086.4	1087.4	1087.8	1088.6	1089.3	1090.1	1090.9	1091.9	1092.9	1094.0	1095.0
135°	1138.6	1139.4	1139.9	1140.9	1142.0	1143.0	1144.0	1144.8	1145.6	1146.3	1147.1
137.5°	1186.9	1187.9	1188.2	1188.7	1189.2	1189.7	1190.2	1191.5	1192.7	1194.0	1195.3
140°	1230.9	1231.7	1232.1	1232.9	1233.6	1234.4	1235.2	1236.2	1237.2	1238.3	1239.3
142.5°	1273.6	1274.4	1274.8	1275.6	1276.3	1277.1	1277.9	1278.7	1279.5	1280.2	1281.0
145°	1313.9	1314.8	1315.1	1315.6	1316.1	1316.7	1317.2	1317.7	1318.2	1318.7	1319.2
147.5°	1350.0	1350.6	1350.9	1351.4	1351.9	1352.4	1352.9	1353.4	1353.9	1354.4	1354.9
150°	1382.6	1383.0	1383.3	1383.8	1384.3	1384.8	1385.3	1385.8	1386.3	1386.8	1387.3
152.5°	1411.7	1411.8	1411.9	1412.2	1412.5	1412.7	1413.0	1414.0	1415.0	1416.1	1417.1
155°	1437.5	1437.2	1437.3	1437.6	1437.9	1438.1	1438.4	1439.7	1440.9	1442.2	1443.5
157.5°	1462.6	1462.6	1462.5	1462.2	1462.0	1461.7	1461.5	1463.0	1464.6	1466.1	1467.6
160°	1482.3	1482.2	1482.1	1481.8	1481.6	1481.3	1481.1	1482.6	1484.2	1485.7	1487.2
162.5°	1499.9	1499.5	1499.4	1499.1	1498.9	1498.6	1498.4	1500.2	1502.0	1503.8	1505.6
165°	1515.0	1514.6	1514.5	1514.2	1513.9	1513.7	1513.4	1515.4	1517.5	1519.5	1521.6
167.5°	1526.6	1526.1	1526.1	1526.1	1526.1	1526.1	1526.1	1528.1	1530.2	1532.2	1534.3
170°	1537.0	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1538.5	1540.6	1542.6	1544.7
172.5°	1542.9	1542.3	1542.4	1542.7	1542.9	1543.2	1543.4	1545.4	1547.5	1549.5	1551.6
175°	1548.6	1548.0	1548.1	1548.4	1548.7	1548.9	1549.2	1551.0	1552.8	1554.6	1556.4
177.5°	1550.9	1550.3	1550.4	1550.7	1551.0	1551.2	1551.5	1553.5	1555.6	1557.6	1559.7
180°	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8

TEST NUMBER: P1010712

CATALOG NUMBER: S123DIP-B775D1195UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1
2.5°	1024.7	1025.7	1021.5	1018.4	1026.7	1021.5	1021.5	1022.6	1020.5	1023.6	1022.6
5°	967.1	968.1	960.8	962.9	958.7	957.7	956.6	962.9	961.9	960.8	962.9
7.5°	910.6	910.6	907.4	905.3	905.3	902.2	906.4	905.3	907.4	907.4	910.6
10°	863.5	865.6	860.3	855.1	854.1	855.1	855.1	856.1	857.2	864.5	863.5
12.5°	824.7	821.6	820.6	817.4	812.2	810.1	808.0	819.5	816.4	816.4	816.4
15°	781.8	789.2	788.1	778.7	776.6	780.8	778.7	778.7	789.2	788.1	787.1
17.5°	758.8	756.7	754.6	749.4	750.4	749.4	750.4	750.4	756.7	756.7	756.7
20°	732.6	728.5	728.5	726.4	726.4	723.2	727.4	728.5	732.6	732.6	733.7
22.5°	709.6	706.5	706.5	705.4	707.5	703.3	707.5	708.6	708.6	711.7	711.7
25°	689.7	687.6	687.6	689.7	689.7	689.7	689.7	693.9	690.8	691.8	690.8
27.5°	671.9	673.0	674.0	675.1	674.0	675.1	676.1	678.2	679.3	678.2	676.1
30°	655.2	658.3	659.4	659.4	661.5	662.5	663.6	663.6	664.6	661.5	663.6
32.5°	642.6	642.6	644.7	645.8	647.9	648.9	648.9	651.0	650.0	646.8	647.9
35°	624.8	624.8	629.0	631.1	634.3	633.2	634.3	634.3	635.3	633.2	630.1
37.5°	607.0	609.1	609.1	613.3	614.4	615.4	614.4	616.5	615.4	613.3	612.3
40°	586.1	585.1	586.1	589.3	590.3	590.3	590.3	592.4	592.4	592.4	591.3
42.5°	560.0	563.1	562.0	565.2	564.1	564.1	566.2	568.3	569.4	566.2	567.3
45°	534.8	534.8	536.9	536.9	538.0	538.0	542.2	540.1	542.2	540.1	541.1
47.5°	507.6	508.7	508.7	509.7	511.8	513.9	511.8	512.9	512.9	513.9	511.8
50°	477.3	477.3	479.4	482.5	486.7	484.6	483.5	487.7	484.6	484.6	482.5
52.5°	445.9	449.0	450.1	453.2	456.3	457.4	458.4	456.3	457.4	454.2	455.3
55°	415.5	416.6	420.7	423.9	427.0	427.0	426.0	427.0	428.1	423.9	423.9
57.5°	385.2	388.3	392.5	392.5	396.7	396.7	395.6	395.6	396.7	393.5	392.5
60°	352.7	355.9	361.1	361.1	367.4	368.4	366.3	364.2	364.2	361.1	362.1
62.5°	318.2	321.3	324.5	329.7	333.9	331.8	336.0	331.8	332.8	326.6	326.6
65°	287.8	288.9	294.1	299.3	299.3	301.4	299.3	300.4	297.2	297.2	293.1
67.5°	252.2	252.2	257.5	262.7	267.9	267.9	267.9	264.8	264.8	261.7	261.7
70°	220.8	219.8	225.0	228.2	231.3	232.4	230.3	229.2	227.1	224.0	222.9
72.5°	182.1	184.2	189.4	191.5	196.8	195.7	201.0	194.7	194.7	189.4	188.4
75°	147.6	149.7	154.9	158.0	161.2	161.2	164.3	161.2	157.0	154.9	153.9
77.5°	117.2	116.2	120.4	125.6	126.6	125.6	127.7	126.6	122.5	122.5	120.4
80°	83.7	86.9	91.1	90.0	94.2	93.2	93.2	91.1	91.1	87.9	90.0
82.5°	55.5	58.6	59.7	58.6	59.7	61.8	62.8	61.8	61.8	59.7	60.7
85°	29.3	29.3	31.4	32.4	31.4	31.4	32.4	35.6	33.5	31.4	33.5
87.5°	9.4	8.4	8.4	9.4	8.4	8.4	9.4	9.4	10.5	10.5	10.5
90°	32.3	32.6	33.1	33.6	34.1	34.6	34.1	33.6	33.1	32.6	32.3
92.5°	38.1	38.2	38.5	38.7	39.0	39.2	39.0	38.7	38.5	38.2	38.1
95°	43.9	43.9	43.9	43.9	43.9	43.9	43.9	43.9	43.9	43.9	43.9
97.5°	46.2	46.3	46.6	46.8	47.1	47.3	47.1	46.8	46.6	46.3	46.2
100°	47.3	47.4	47.7	48.0	48.2	48.5	48.2	48.0	47.7	47.4	47.3
102.5°	47.3	47.6	48.1	48.6	49.1	49.6	49.1	48.6	48.1	47.6	47.3
105°	48.5	48.8	49.3	49.8	50.3	50.8	50.3	49.8	49.3	48.8	48.5
107.5°	271.3	254.5	220.9	187.3	153.7	120.1	153.7	187.3	220.9	254.5	271.3
110°	482.5	464.2	427.5	390.8	354.2	317.5	354.2	390.8	427.5	464.2	482.5

TEST NUMBER: P1010712

CATALOG NUMBER: S123DIP-B775D1195UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	603.7	603.4	602.9	602.4	601.9	601.4	601.9	602.4	602.9	603.4	603.7
115°	674.2	674.7	675.7	676.8	677.8	678.8	677.8	676.8	675.7	674.7	674.2
117.5°	740.0	740.1	740.4	740.6	740.9	741.1	740.9	740.6	740.4	740.1	740.0
120°	805.8	805.8	805.8	805.8	805.8	805.8	805.8	805.8	805.8	805.8	805.8
122.5°	868.1	868.2	868.5	868.8	869.0	869.3	869.0	868.8	868.5	868.2	868.1
125°	925.8	926.1	926.6	927.1	927.6	928.1	927.6	927.1	926.6	926.1	925.8
127.5°	988.2	987.9	987.4	986.9	986.3	985.8	986.3	986.9	987.4	987.9	988.2
130°	1043.6	1043.3	1042.8	1042.3	1041.8	1041.3	1041.8	1042.3	1042.8	1043.3	1043.6
132.5°	1095.5	1095.1	1094.3	1093.6	1092.8	1092.0	1092.8	1093.6	1094.3	1095.1	1095.5
135°	1147.5	1147.1	1146.3	1145.6	1144.8	1144.0	1144.8	1145.6	1146.3	1147.1	1147.5
137.5°	1195.9	1195.6	1195.1	1194.6	1194.1	1193.6	1194.1	1194.6	1195.1	1195.6	1195.9
140°	1239.8	1239.5	1239.0	1238.5	1238.0	1237.5	1238.0	1238.5	1239.0	1239.5	1239.8
142.5°	1281.4	1281.0	1280.2	1279.5	1278.7	1277.9	1278.7	1279.5	1280.2	1281.0	1281.4
145°	1319.5	1319.5	1319.5	1319.5	1319.5	1319.5	1319.5	1319.5	1319.5	1319.5	1319.5
147.5°	1355.2	1354.6	1353.3	1352.0	1350.8	1349.5	1350.8	1352.0	1353.3	1354.6	1355.2
150°	1387.6	1387.2	1386.4	1385.7	1384.9	1384.1	1384.9	1385.7	1386.4	1387.2	1387.6
152.5°	1417.6	1417.0	1415.7	1414.4	1413.1	1411.8	1413.1	1414.4	1415.7	1417.0	1417.6
155°	1444.1	1443.3	1441.8	1440.3	1438.7	1437.2	1438.7	1440.3	1441.8	1443.3	1444.1
157.5°	1468.4	1467.4	1465.3	1463.2	1461.2	1459.1	1461.2	1463.2	1465.3	1467.4	1468.4
160°	1488.0	1487.1	1485.3	1483.5	1481.7	1479.9	1481.7	1483.5	1485.3	1487.1	1488.0
162.5°	1506.5	1505.7	1504.2	1502.6	1501.1	1499.5	1501.1	1502.6	1504.2	1505.7	1506.5
165°	1522.6	1521.7	1519.9	1518.2	1516.4	1514.6	1516.4	1518.2	1519.9	1521.7	1522.6
167.5°	1535.3	1534.3	1532.2	1530.2	1528.1	1526.1	1528.1	1530.2	1532.2	1534.3	1535.3
170°	1545.7	1544.7	1542.6	1540.6	1538.5	1536.5	1538.5	1540.6	1542.6	1544.7	1545.7
172.5°	1552.6	1551.5	1549.2	1546.9	1544.6	1542.3	1544.6	1546.9	1549.2	1551.5	1552.6
175°	1557.3	1556.3	1554.2	1552.1	1550.1	1548.0	1550.1	1552.1	1554.2	1556.3	1557.3
177.5°	1560.7	1559.4	1556.9	1554.3	1551.8	1549.2	1551.8	1554.3	1556.9	1559.4	1560.7
180°	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8

TEST NUMBER: P1010712

CATALOG NUMBER: S123DIP-B775D1195UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1
2.5°	1025.7	1027.8	1028.8	1024.7	1021.5	1026.7	1034.1	1039.3	1043.5	1048.7	1051.9
5°	965.0	972.3	972.3	974.4	977.6	982.8	996.4	1005.8	1014.2	1020.5	1025.7
7.5°	913.7	918.9	922.1	927.3	932.6	939.9	955.6	969.2	981.7	989.1	997.4
10°	867.7	871.8	877.1	880.2	889.6	900.1	920.0	931.5	946.2	957.7	968.1
12.5°	823.7	838.4	841.5	840.4	848.8	860.3	880.2	898.0	913.7	925.2	936.7
15°	792.3	797.5	803.8	802.8	820.6	823.7	840.4	861.4	882.3	889.6	900.1
17.5°	757.8	766.1	772.4	775.6	780.8	792.3	808.0	823.7	850.9	852.0	879.2
20°	730.6	738.9	743.1	747.3	750.4	764.0	777.7	795.4	817.4	828.9	843.6
22.5°	712.8	716.9	720.1	723.2	727.4	734.7	751.5	771.4	786.0	798.6	808.0
25°	691.8	696.0	700.2	702.3	705.4	709.6	722.2	737.9	758.8	767.2	776.6
27.5°	677.2	677.2	679.3	679.3	683.5	687.6	697.1	711.7	728.5	738.9	751.5
30°	661.5	660.4	661.5	660.4	659.4	665.7	674.0	686.6	698.1	710.7	719.0
32.5°	645.8	644.7	644.7	645.8	641.6	644.7	648.9	660.4	673.0	679.3	688.7
35°	629.0	626.9	626.9	626.9	624.8	622.7	626.9	637.4	645.8	654.1	661.5
37.5°	612.3	609.1	609.1	607.0	605.0	601.8	601.8	610.2	621.7	624.8	634.3
40°	589.3	589.3	587.2	586.1	584.0	581.9	578.8	586.1	596.6	599.7	607.0
42.5°	566.2	563.1	562.0	562.0	562.0	558.9	556.8	562.0	568.3	573.6	577.7
45°	540.1	538.0	539.0	538.0	535.9	534.8	533.8	535.9	543.2	545.3	550.5
47.5°	511.8	510.8	510.8	509.7	508.7	509.7	505.5	510.8	512.9	514.9	519.1
50°	482.5	481.5	480.4	479.4	479.4	480.4	479.4	479.4	483.5	485.6	489.8
52.5°	453.2	450.1	450.1	449.0	449.0	446.9	449.0	450.1	452.1	454.2	456.3
55°	421.8	421.8	418.7	418.7	416.6	416.6	417.6	416.6	420.7	422.8	422.8
57.5°	391.4	387.3	388.3	386.2	384.1	383.1	383.1	385.2	387.3	387.3	389.3
60°	359.0	354.8	353.8	349.6	351.7	348.5	349.6	349.6	353.8	351.7	353.8
62.5°	326.6	321.3	318.2	316.1	316.1	317.1	315.0	314.0	316.1	318.2	322.4
65°	292.0	288.9	285.7	282.6	282.6	281.5	283.6	280.5	279.5	280.5	282.6
67.5°	256.4	253.3	250.1	247.0	248.1	244.9	242.8	246.0	243.9	244.9	247.0
70°	221.9	219.8	213.5	211.4	210.4	211.4	210.4	208.3	211.4	210.4	211.4
72.5°	187.3	185.3	182.1	176.9	176.9	175.8	174.8	174.8	173.7	173.7	173.7
75°	153.9	149.7	146.5	145.5	143.4	142.3	141.3	139.2	140.2	141.3	139.2
77.5°	119.3	114.1	113.0	113.0	109.9	109.9	110.9	109.9	108.9	108.9	108.9
80°	87.9	83.7	83.7	81.6	79.5	79.5	79.5	79.5	78.5	77.5	78.5
82.5°	56.5	55.5	54.4	54.4	56.5	52.3	54.4	53.4	52.3	52.3	51.3
85°	31.4	32.4	31.4	32.4	30.4	31.4	31.4	31.4	30.4	31.4	29.3
87.5°	11.5	11.5	11.5	12.6	12.6	12.6	12.6	12.6	13.6	12.6	12.6
90°	31.8	30.8	29.7	28.7	27.7	24.4	21.0	17.7	14.4	12.7	11.4
92.5°	37.2	35.4	33.6	31.8	30.0	27.7	25.4	23.1	20.8	19.6	20.4
95°	43.0	41.2	39.4	37.6	35.8	33.0	30.2	27.3	24.5	23.1	28.4
97.5°	45.2	43.1	41.0	39.0	36.9	50.0	63.1	76.2	89.3	95.8	99.4
100°	46.3	44.2	42.2	40.1	38.1	78.1	118.1	158.2	198.2	218.2	215.6
102.5°	51.5	60.0	68.5	76.9	85.4	130.0	174.7	219.3	264.0	286.3	284.6
105°	71.2	116.6	162.0	207.4	252.8	275.9	299.0	322.1	345.2	356.7	355.3
107.5°	291.1	330.6	370.1	409.6	449.1	445.2	441.4	437.5	433.6	431.7	430.6
110°	486.7	495.2	503.7	512.1	520.6	517.8	515.0	512.1	509.3	507.9	506.9

TEST NUMBER: P1010712

CATALOG NUMBER: S123DIP-B775D1195UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	602.6	600.3	598.0	595.7	593.4	590.6	587.8	584.9	582.1	580.7	579.8
115°	672.9	670.3	667.8	665.2	662.6	660.3	658.0	655.7	653.4	652.2	651.4
117.5°	739.0	736.9	734.8	732.8	730.7	729.4	728.2	726.9	725.6	725.0	724.1
120°	804.8	802.7	800.6	798.6	796.5	795.7	795.0	794.2	793.5	793.1	791.9
122.5°	867.5	866.2	864.9	863.6	862.3	861.3	860.3	859.2	858.2	857.7	856.8
125°	925.5	925.0	924.5	924.0	923.5	922.5	921.5	920.4	919.4	918.9	917.9
127.5°	987.8	987.0	986.3	985.5	984.7	983.4	982.1	980.8	979.5	978.9	977.9
130°	1043.1	1042.0	1041.0	1039.9	1038.9	1037.9	1036.9	1035.8	1034.8	1034.3	1033.3
132.5°	1095.0	1094.0	1092.9	1091.9	1090.9	1090.1	1089.3	1088.6	1087.8	1087.4	1086.4
135°	1147.1	1146.3	1145.6	1144.8	1144.0	1143.0	1142.0	1140.9	1139.9	1139.4	1138.6
137.5°	1195.3	1194.0	1192.7	1191.5	1190.2	1189.7	1189.2	1188.7	1188.2	1187.9	1186.9
140°	1239.3	1238.3	1237.2	1236.2	1235.2	1234.4	1233.6	1232.9	1232.1	1231.7	1230.9
142.5°	1281.0	1280.2	1279.5	1278.7	1277.9	1277.1	1276.3	1275.6	1274.8	1274.4	1273.6
145°	1319.2	1318.7	1318.2	1317.7	1317.2	1316.7	1316.1	1315.6	1315.1	1314.8	1313.9
147.5°	1354.9	1354.4	1353.9	1353.4	1352.9	1352.4	1351.9	1351.4	1350.9	1350.6	1350.0
150°	1387.3	1386.8	1386.3	1385.8	1385.3	1384.8	1384.3	1383.8	1383.3	1383.0	1382.6
152.5°	1417.1	1416.1	1415.0	1414.0	1413.0	1412.7	1412.5	1412.2	1411.9	1411.8	1411.7
155°	1443.5	1442.2	1440.9	1439.7	1438.4	1438.1	1437.9	1437.6	1437.3	1437.2	1437.5
157.5°	1467.6	1466.1	1464.6	1463.0	1461.5	1461.7	1462.0	1462.2	1462.5	1462.6	1462.6
160°	1487.2	1485.7	1484.2	1482.6	1481.1	1481.3	1481.6	1481.8	1482.1	1482.2	1482.3
162.5°	1505.6	1503.8	1502.0	1500.2	1498.4	1498.6	1498.9	1499.1	1499.4	1499.5	1499.9
165°	1521.6	1519.5	1517.5	1515.4	1513.4	1513.7	1513.9	1514.2	1514.5	1514.6	1515.0
167.5°	1534.3	1532.2	1530.2	1528.1	1526.1	1526.1	1526.1	1526.1	1526.1	1526.1	1526.6
170°	1544.7	1542.6	1540.6	1538.5	1536.5	1536.5	1536.5	1536.5	1536.5	1536.5	1537.0
172.5°	1551.6	1549.5	1547.5	1545.4	1543.4	1543.2	1542.9	1542.7	1542.4	1542.3	1542.9
175°	1556.4	1554.6	1552.8	1551.0	1549.2	1548.9	1548.7	1548.4	1548.1	1548.0	1548.6
177.5°	1559.7	1557.6	1555.6	1553.5	1551.5	1551.2	1551.0	1550.7	1550.4	1550.3	1550.9
180°	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8	1553.8

TEST NUMBER: P1010712

CATALOG NUMBER: S123DIP-B775D1195UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1080.1	1080.1	1080.1	1080.1
2.5°	1057.1	1060.2	1070.7	1083.3
5°	1036.2	1044.5	1059.2	1079.1
7.5°	1013.1	1025.7	1046.6	1071.8
10°	987.0	1004.8	1030.9	1062.3
12.5°	958.7	981.7	1015.2	1047.7
15°	940.9	964.0	994.3	1029.9
17.5°	906.4	933.6	965.0	1015.2
20°	870.8	901.2	942.0	992.2
22.5°	843.6	876.0	914.8	968.1
25°	811.1	844.6	886.5	942.0
27.5°	776.6	810.1	857.2	915.8
30°	750.4	782.9	827.9	890.7
32.5°	719.0	750.4	797.5	863.5
35°	683.5	719.0	764.0	831.0
37.5°	656.2	688.7	735.8	799.6
40°	626.9	655.2	701.2	764.0
42.5°	595.5	626.9	666.7	729.5
45°	566.2	589.3	630.1	689.7
47.5°	534.8	561.0	592.4	638.4
50°	501.3	523.3	557.9	589.3
52.5°	468.9	486.7	516.0	540.1
55°	434.4	452.1	474.1	488.8
57.5°	401.9	414.5	429.1	438.5
60°	362.1	374.7	384.1	393.5
62.5°	326.6	336.0	341.2	346.4
65°	289.9	295.2	298.3	302.5
67.5°	250.1	255.4	256.4	262.7
70°	213.5	214.6	216.7	219.8
72.5°	179.0	181.1	180.0	182.1
75°	143.4	145.5	143.4	145.5
77.5°	108.9	110.9	110.9	114.1
80°	78.5	79.5	80.6	80.6
82.5°	51.3	54.4	52.3	53.4
85°	29.3	30.4	30.4	31.4
87.5°	13.6	14.7	13.6	15.7
90°	8.9	6.3	3.8	1.2
92.5°	21.9	23.5	25.0	26.6
95°	38.9	49.4	59.9	70.4
97.5°	106.6	113.7	120.9	128.1
100°	210.5	205.4	200.2	195.1
102.5°	281.3	278.0	274.6	271.3
105°	352.5	349.6	346.8	344.0
107.5°	428.3	426.0	423.7	421.4
110°	504.8	502.8	500.7	498.7

TEST NUMBER: P1010712

CATALOG NUMBER: S123DIP-B775D1195UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	578.0	576.2	574.4	572.6
115°	649.9	648.4	646.8	645.3
117.5°	722.3	720.5	718.7	716.9
120°	789.6	787.3	785.0	782.7
122.5°	855.0	853.2	851.4	849.6
125°	915.8	913.8	911.7	909.7
127.5°	975.8	973.8	971.7	969.7
130°	1031.2	1029.2	1027.1	1025.1
132.5°	1084.3	1082.3	1080.2	1078.2
135°	1137.1	1135.6	1134.0	1132.5
137.5°	1184.8	1182.7	1180.7	1178.6
140°	1229.4	1227.9	1226.3	1224.8
142.5°	1272.1	1270.6	1269.0	1267.5
145°	1312.1	1310.4	1308.6	1306.8
147.5°	1348.7	1347.4	1346.2	1344.9
150°	1381.8	1381.1	1380.3	1379.5
152.5°	1411.4	1411.2	1410.9	1410.7
155°	1438.0	1438.5	1439.0	1439.5
157.5°	1462.6	1462.6	1462.6	1462.6
160°	1482.6	1482.9	1483.1	1483.4
162.5°	1500.7	1501.4	1502.2	1503.0
165°	1515.7	1516.5	1517.2	1518.0
167.5°	1527.6	1528.7	1529.7	1530.7
170°	1538.0	1539.1	1540.1	1541.1
172.5°	1544.2	1545.5	1546.7	1548.0
175°	1549.9	1551.2	1552.5	1553.8
177.5°	1552.2	1553.5	1554.8	1556.1
180°	1553.8	1553.8	1553.8	1553.8

(END OF REPORT)