

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010446

Luminaire Tested: S123DIP-B1000D585UB2750-4F0-XX-W2A-D_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010446
REPORT IS A COMBINATION OF REPORTS P989215 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B1000D585UB2750-4F0-XX-W2A-D_3500K
Description: Define 3 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6549.0 lumens
Efficiency: N/A
Efficacy: 105.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.25 / 1.37
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 62.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010446

CATALOG NUMBER: S123DIP-B1000D585UB2750-4F0-XX-W2A-D_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1010446

CATALOG NUMBER: S123DIP-B1000D585UB2750-4F0-XX-W2A-D_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64
1	98	94	89	85	92	87	83	80	75	73	70	65	63	61	55	53	52
2	89	81	74	69	83	76	70	65	65	61	57	56	53	50	47	45	43
3	81	71	63	57	75	66	59	53	57	52	47	49	45	41	42	38	36
4	74	62	54	48	69	58	51	45	51	45	40	44	39	35	37	33	30
5	68	56	47	41	63	52	44	39	45	39	34	39	34	30	33	29	26
6	62	50	41	35	58	47	39	33	41	35	30	35	30	26	30	26	23
7	58	45	37	31	54	42	35	29	37	31	26	32	27	23	27	23	20
8	54	41	33	27	50	38	31	26	34	28	23	29	24	21	25	21	18
9	50	37	29	24	46	35	28	23	31	25	21	27	22	19	23	19	16
10	47	34	27	22	43	32	25	21	28	23	19	25	20	17	22	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13426	13426	13426
5°	13463	13032	13021
10°	13337	12679	12583
15°	13160	12289	12116
20°	12910	11855	11616
25°	12602	11366	11098
30°	12287	10923	10578
35°	11931	10459	10154
40°	11594	10033	9706
45°	11220	9621	9337
50°	10848	9214	8937
55°	10439	8796	8568
60°	10037	8369	8190
65°	9624	7913	7749
70°	9003	7402	7293
75°	8217	6818	6823
80°	7302	6228	6287
85°	6397	5750	5902

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11220 cd/sqm

TEST NUMBER: P1010446

CATALOG NUMBER: S123DIP-B1000D585UB2750-4F0-XX-W2A-D_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	118.3	1.8
10°-20°	337.3	5.2
20°-30°	504.4	7.7
30°-40°	602.3	9.2
40°-50°	630.1	9.6
50°-60°	591.3	9.0
60°-70°	493.9	7.5
70°-80°	353.2	5.4
80°-90°	211.7	3.2
90°-100°	159.3	2.4
100°-110°	228.8	3.5
110°-120°	387.6	5.9
120°-130°	446.8	6.8
130°-140°	454.4	6.9
140°-150°	412.8	6.3
150°-160°	330.2	5.0
160°-170°	213.1	3.3
170°-180°	73.4	1.1
0°-30°	960.1	14.7
0°-40°	1562.3	23.9
0°-60°	2783.8	42.5
0°-90°	3842.5	58.7
90°-120°	775.7	11.8
90°-150°	2089.7	31.9
90°-180°	2706.0	41.3
0°-180°	6549.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1247	1247	1247	1247	1247	
5°	1249	1246	1238	1249	1247	118
15°	1189	1193	1192	1205	1204	335
25°	1073	1087	1091	1109	1109	495
35°	924	946	963	984	989	578
45°	756	788	822	848	859	583
55°	576	621	670	706	717	516
65°	398	451	511	552	565	394
75°	216	280	348	393	409	231
85°	67	134	206	253	266	69
90°	18	90	167	216	230	15
95°	50	79	152	198	212	53
105°	182	221	228	164	178	192
115°	328	347	402	440	453	324
125°	456	461	503	532	543	408
135°	566	568	585	611	616	436
145°	651	654	655	667	672	407
155°	716	715	715	718	715	330
165°	755	753	752	757	753	213
175°	773	770	770	774	770	74
180°	773	773	773	773	773	

TEST NUMBER: P1010446

CATALOG NUMBER: S123DIP-B1000D585UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1247.3	1247.3	1247.3	1247.3	1247.3
2.5°	1254.1	1250.0	1239.2	1250.0	1248.7
5°	1248.7	1246.0	1237.8	1248.7	1247.3
7.5°	1239.2	1239.2	1231.0	1244.6	1243.3
10°	1225.6	1228.3	1221.5	1235.1	1232.4
12.5°	1209.3	1213.4	1209.3	1221.5	1218.8
15°	1188.9	1193.0	1191.6	1205.2	1203.8
17.5°	1164.4	1172.6	1171.2	1183.5	1180.7
20°	1137.3	1145.4	1148.1	1160.4	1161.7
22.5°	1108.7	1116.9	1121.0	1137.3	1135.9
25°	1073.4	1087.0	1091.1	1108.7	1108.7
27.5°	1039.4	1054.4	1062.5	1077.5	1078.8
30°	1002.8	1020.4	1031.3	1047.6	1047.6
32.5°	962.0	982.4	997.3	1015.0	1019.1
35°	923.9	945.7	963.4	983.7	989.2
37.5°	883.2	907.6	928.0	951.1	955.2
40°	842.4	866.9	894.1	917.2	922.6
42.5°	797.6	828.8	857.4	883.2	891.3
45°	755.5	788.1	822.0	847.9	858.7
47.5°	710.6	747.3	785.4	813.9	822.0
50°	667.1	705.2	747.3	778.6	788.1
52.5°	620.9	661.7	709.3	741.9	754.1
55°	576.1	620.9	669.9	706.5	717.4
57.5°	532.6	578.8	631.8	668.5	680.7
60°	486.4	535.3	591.1	629.1	644.0
62.5°	443.0	493.2	553.0	591.1	604.6
65°	398.1	451.1	510.9	551.7	565.2
67.5°	353.3	409.0	468.8	513.6	524.5
70°	305.7	364.1	429.4	472.8	486.4
72.5°	262.2	320.7	388.6	433.4	447.0
75°	216.0	279.9	347.8	392.7	409.0
77.5°	176.6	240.5	308.4	356.0	368.2
80°	134.5	201.1	271.7	317.9	331.5
82.5°	97.8	165.8	237.8	284.0	297.6
85°	66.6	134.5	206.5	252.7	266.3
87.5°	40.8	108.7	178.0	224.2	237.8
90°	18.3	90.5	167.3	215.8	230.5
92.5°	29.5	84.5	157.6	206.4	219.2
95°	49.9	79.4	152.3	198.4	212.0
97.5°	77.3	110.1	144.8	190.1	204.2
100°	109.2	164.2	137.1	181.1	195.3
102.5°	145.8	191.3	152.6	171.6	186.4
105°	182.0	220.9	227.6	164.1	177.5
107.5°	219.0	252.7	317.1	265.3	202.4
110°	256.2	285.2	345.9	362.2	291.1



TEST NUMBER: P1010446

CATALOG NUMBER: S123DIP-B1000D585UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	292.9	315.9	373.8	413.0	424.1
115°	327.7	347.4	401.5	439.8	453.0
117.5°	363.3	378.2	427.3	464.5	475.8
120°	394.6	406.6	453.2	489.0	498.5
122.5°	427.9	434.7	479.1	511.9	521.9
125°	456.4	461.0	502.7	532.4	543.0
127.5°	486.3	489.5	526.3	555.3	563.6
130°	513.8	517.0	546.5	574.6	581.7
132.5°	538.8	543.4	565.6	592.4	600.1
135°	565.8	568.0	585.2	611.4	616.5
137.5°	588.8	592.1	602.7	627.3	632.9
140°	610.4	613.9	619.6	642.3	648.0
142.5°	631.7	633.7	635.4	654.9	659.9
145°	651.2	653.8	655.0	667.0	672.4
147.5°	668.7	671.6	672.8	678.0	680.5
150°	686.0	687.7	688.8	690.0	691.0
152.5°	701.5	702.0	702.6	704.9	702.0
155°	715.8	714.7	715.2	718.1	714.7
157.5°	727.3	727.3	726.7	730.2	725.6
160°	737.6	737.0	736.5	739.9	735.9
162.5°	747.4	745.7	745.1	749.1	745.7
165°	754.8	753.1	752.5	757.1	753.1
167.5°	761.2	758.9	758.9	763.5	758.9
170°	766.3	764.0	764.0	768.6	764.0
172.5°	769.8	766.9	767.5	772.1	766.9
175°	772.6	769.8	770.3	774.4	769.8
177.5°	773.8	770.9	771.5	776.1	770.3
180°	772.6	772.6	772.6	772.6	772.6

(END OF REPORT)