

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010736

Luminaire Tested: S123DIP-B775D365UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010736
REPORT IS A COMBINATION OF REPORTS P990360 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B775D365UB2750-4F0-XX-W2A-F_3500K
Description: Define 3 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4666.0 lumens
Efficiency: N/A
Efficacy: 103.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 45.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010736

CATALOG NUMBER: S123DIP-B775D365UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1010736

CATALOG NUMBER: S123DIP-B775D365UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	105	105	105	105	94	94	94	83	83	83	73	73	73
1	102	97	93	90	96	92	89	85	82	79	77	73	71	69	65	63	62
2	93	85	79	73	87	80	75	70	72	68	64	64	61	58	57	54	52
3	85	75	67	61	80	71	64	59	63	58	54	57	52	49	50	47	44
4	77	66	58	52	73	63	55	50	56	50	46	51	46	42	45	41	38
5	71	59	51	44	67	56	49	43	51	44	40	45	40	36	41	36	33
6	66	53	45	39	62	51	43	37	46	39	35	41	36	32	37	33	29
7	61	48	40	34	57	46	38	33	41	35	31	37	32	28	34	29	26
8	57	44	36	30	53	42	34	29	38	32	27	34	29	25	31	27	23
9	53	40	32	27	50	38	31	26	35	29	24	32	26	23	29	24	21
10	49	37	29	24	47	35	28	24	32	26	22	29	24	21	26	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13235	13235	13235
5°	13268	12778	12759
10°	13150	12346	12219
15°	12967	11895	11631
20°	12757	11396	11047
25°	12486	10870	10424
30°	12190	10325	9768
35°	11879	9767	9117
40°	11552	9183	8475
45°	11195	8612	7806
50°	10832	7977	7134
55°	10364	7316	6452
60°	9882	6586	5728
65°	9430	5797	4971
70°	8779	4922	4090
75°	7844	3897	3175
80°	6775	2739	2245
85°	5283	1473	1124

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11195 cd/sqm

TEST NUMBER: P1010736

CATALOG NUMBER: S123DIP-B775D365UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.9	2.5
10°-20°	327.3	7.0
20°-30°	483.4	10.4
30°-40°	564.6	12.1
40°-50°	567.5	12.2
50°-60°	498.6	10.7
60°-70°	371.3	8.0
70°-80°	211.3	4.5
80°-90°	61.0	1.3
90°-100°	16.9	0.4
100°-110°	81.9	1.8
110°-120°	200.8	4.3
120°-130°	254.9	5.5
130°-140°	272.3	5.8
140°-150°	254.6	5.5
150°-160°	205.4	4.4
160°-170°	132.5	2.8
170°-180°	45.7	1.0
0°-30°	926.6	19.9
0°-40°	1491.2	32.0
0°-60°	2557.3	54.8
0°-90°	3201.0	68.6
90°-120°	299.6	6.4
90°-150°	1081.4	23.2
90°-180°	1465.0	31.4
0°-180°	4666.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1230	1230	1230	1230	1230	
5°	1231	1225	1214	1224	1222	117
15°	1171	1167	1153	1162	1156	330
25°	1064	1057	1044	1044	1041	490
35°	920	913	900	893	888	575
45°	754	750	736	723	718	582
55°	572	571	557	546	540	512
65°	390	385	374	366	363	385
75°	206	202	199	194	190	220
85°	55	53	53	51	51	59
90°	0	4	9	10	11	5
95°	22	7	11	14	14	26
105°	106	110	78	15	16	113
115°	200	202	205	208	210	197
125°	281	284	286	286	287	251
135°	350	352	354	355	354	270
145°	404	407	407	408	408	253
155°	445	444	445	447	444	205
165°	470	468	468	471	468	133
175°	481	479	479	482	479	46
180°	481	481	481	481	481	

TEST NUMBER: P1010736

CATALOG NUMBER: S123DIP-B775D365UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1229.6	1229.6	1229.6	1229.6	1229.6
2.5°	1234.8	1230.6	1219.0	1229.6	1228.5
5°	1230.6	1225.3	1213.7	1224.3	1222.2
7.5°	1221.1	1215.8	1204.2	1213.7	1212.6
10°	1208.4	1203.1	1189.4	1198.9	1196.8
12.5°	1191.5	1187.3	1174.6	1180.9	1179.9
15°	1171.4	1167.2	1153.4	1161.9	1155.6
17.5°	1149.2	1143.9	1130.2	1136.5	1134.4
20°	1123.8	1117.5	1103.7	1108.0	1104.8
22.5°	1095.3	1088.9	1075.2	1078.4	1074.1
25°	1063.6	1057.2	1043.5	1044.5	1041.4
27.5°	1030.8	1024.5	1009.7	1010.7	1007.5
30°	994.9	989.6	974.8	974.8	967.4
32.5°	958.9	951.5	940.9	933.5	930.4
35°	919.8	913.4	899.7	893.4	888.1
37.5°	880.7	872.2	858.5	851.1	847.9
40°	839.4	833.1	818.3	809.8	805.6
42.5°	798.2	790.8	776.0	767.5	763.3
45°	753.8	749.6	735.8	723.1	717.9
47.5°	710.5	704.1	691.4	678.7	674.5
50°	666.1	660.8	647.0	635.4	629.1
52.5°	619.5	616.4	601.6	592.0	585.7
55°	572.0	570.9	557.2	545.5	540.2
57.5°	527.6	523.3	512.8	502.2	495.8
60°	478.9	477.9	465.2	455.7	450.4
62.5°	435.6	432.4	419.7	410.2	407.0
65°	390.1	384.8	374.3	365.8	362.6
67.5°	341.5	337.3	328.8	321.4	317.2
70°	298.1	291.8	285.5	278.1	272.8
72.5°	252.7	248.4	241.0	234.7	232.6
75°	206.2	201.9	198.8	193.5	190.3
77.5°	164.9	162.8	158.6	154.4	154.4
80°	124.8	121.6	119.5	118.4	118.4
82.5°	85.6	85.6	85.6	83.5	82.5
85°	55.0	52.9	52.9	50.7	50.7
87.5°	27.5	24.3	23.3	22.2	22.2
90°	0.4	3.9	8.6	10.0	10.7
92.5°	8.2	6.1	9.3	11.8	12.1
95°	21.8	7.1	11.1	13.6	13.6
97.5°	39.6	29.6	11.4	14.3	14.6
100°	60.3	67.5	11.8	14.6	15.0
102.5°	83.9	88.5	26.4	14.6	15.4
105°	106.4	110.3	78.2	15.0	15.7
107.5°	130.3	133.5	138.9	83.9	37.1
110°	154.2	157.1	161.0	149.2	98.2



TEST NUMBER: P1010736

CATALOG NUMBER: S123DIP-B775D365UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	177.1	179.6	183.5	186.7	186.0
115°	199.6	201.7	204.9	208.5	209.9
117.5°	221.7	224.2	226.0	228.9	229.2
120°	242.1	245.3	246.4	249.2	249.2
122.5°	262.8	265.3	266.7	268.5	268.8
125°	281.3	284.2	285.6	286.3	287.1
127.5°	299.9	302.8	304.5	305.6	304.9
130°	317.0	319.9	321.3	322.8	322.0
132.5°	333.5	336.3	337.4	338.8	337.8
135°	350.2	352.4	353.8	354.9	353.8
137.5°	364.5	367.4	368.1	369.9	369.2
140°	378.8	381.0	382.0	383.5	382.7
142.5°	392.0	394.2	395.2	396.3	395.2
145°	404.2	406.7	407.4	408.1	408.1
147.5°	415.9	417.7	418.4	419.2	417.4
150°	426.7	427.7	428.4	429.2	428.1
152.5°	436.3	436.6	437.0	438.4	436.6
155°	445.2	444.5	444.9	446.6	444.5
157.5°	452.4	452.4	452.0	454.1	451.3
160°	458.8	458.4	458.1	460.2	457.7
162.5°	464.9	463.8	463.4	465.9	463.8
165°	469.5	468.4	468.1	470.9	468.4
167.5°	473.4	472.0	472.0	474.9	472.0
170°	476.6	475.2	475.2	478.1	475.2
172.5°	478.8	477.0	477.4	480.2	477.0
175°	480.6	478.8	479.1	481.6	478.8
177.5°	481.3	479.5	479.8	482.7	479.1
180°	480.6	480.6	480.6	480.6	480.6

(END OF REPORT)