

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010750

Luminaire Tested: S123DIP-B775D585UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010750
REPORT IS A COMBINATION OF REPORTS P990419 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B775D585UB2750-4F0-XX-W2A-F_3000K
Description: Define 3 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5533.0 lumens
Efficiency: N/A
Efficacy: 107.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 51.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010750

CATALOG NUMBER: S123DIP-B775D585UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010750

CATALOG NUMBER: S123DIP-B775D585UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	88	88	88	75	75	75	63	63	63
1	99	95	91	87	92	89	85	82	77	74	72	66	64	62	56	54	53
2	91	83	77	71	84	77	72	67	67	63	59	58	55	52	49	47	45
3	83	73	65	59	77	68	62	56	59	54	50	51	47	44	43	41	38
4	76	65	56	50	70	60	53	48	53	47	43	45	41	38	39	35	33
5	69	58	49	43	64	54	47	41	47	41	37	41	36	33	35	31	29
6	64	52	43	37	59	48	41	36	42	37	32	37	32	29	32	28	25
7	59	47	39	33	55	44	37	31	39	33	28	34	29	25	29	25	22
8	55	42	35	29	51	40	33	28	35	29	25	31	26	23	27	23	20
9	51	39	31	26	48	37	30	25	32	27	23	28	24	20	25	21	18
10	48	36	28	23	45	34	27	22	30	24	20	26	22	18	23	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13177	13177	13177
5°	13209	12722	12703
10°	13092	12292	12165
15°	12910	11844	11580
20°	12701	11347	10999
25°	12431	10822	10378
30°	12136	10279	9725
35°	11827	9725	9076
40°	11503	9142	8438
45°	11146	8575	7771
50°	10783	7943	7102
55°	10319	7284	6424
60°	9838	6557	5702
65°	9389	5771	4949
70°	8740	4899	4072
75°	7809	3879	3161
80°	6743	2725	2236
85°	5254	1465	1119

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11146 cd/sqm

TEST NUMBER: P1010750

CATALOG NUMBER: S123DIP-B775D585UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.4	2.1
10°-20°	325.9	5.9
20°-30°	481.3	8.7
30°-40°	562.1	10.2
40°-50°	565.1	10.2
50°-60°	496.4	9.0
60°-70°	369.7	6.7
70°-80°	210.4	3.8
80°-90°	61.4	1.1
90°-100°	27.1	0.5
100°-110°	131.2	2.4
110°-120°	321.4	5.8
120°-130°	408.1	7.4
130°-140°	435.9	7.9
140°-150°	407.6	7.4
150°-160°	328.8	5.9
160°-170°	212.2	3.8
170°-180°	73.1	1.3
0°-30°	922.6	16.7
0°-40°	1484.6	26.8
0°-60°	2546.1	46.0
0°-90°	3187.5	57.6
90°-120°	479.7	8.7
90°-150°	1731.3	31.3
90°-180°	2345.0	42.4
0°-180°	5533.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1224	1224	1224	1224	1224	
5°	1225	1220	1208	1219	1217	116
15°	1166	1162	1148	1157	1150	329
25°	1059	1053	1039	1040	1037	488
35°	916	910	896	890	884	573
45°	750	746	733	720	715	579
55°	570	568	555	543	538	510
65°	388	383	373	364	361	383
75°	205	201	198	193	190	219
85°	55	53	53	50	50	59
90°	1	6	14	16	17	6
95°	35	11	18	22	22	42
105°	170	177	125	24	25	181
115°	320	323	328	334	336	316
125°	450	455	457	458	460	402
135°	561	564	566	568	566	432
145°	647	651	652	653	653	405
155°	713	712	712	715	712	328
165°	752	750	749	754	750	212
175°	769	766	767	771	766	73
180°	769	769	769	769	769	

TEST NUMBER: P1010750

CATALOG NUMBER: S123DIP-B775D585UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1224.2	1224.2	1224.2	1224.2	1224.2
2.5°	1229.4	1225.2	1213.7	1224.2	1223.1
5°	1225.2	1220.0	1208.4	1218.9	1216.8
7.5°	1215.8	1210.5	1198.9	1208.4	1207.3
10°	1203.1	1197.9	1184.2	1193.7	1191.5
12.5°	1186.3	1182.1	1169.4	1175.8	1174.7
15°	1166.3	1162.1	1148.4	1156.8	1150.5
17.5°	1144.2	1138.9	1125.2	1131.6	1129.4
20°	1118.9	1112.6	1098.9	1103.1	1100.0
22.5°	1090.5	1084.2	1070.5	1073.7	1069.4
25°	1058.9	1052.6	1038.9	1040.0	1036.8
27.5°	1026.3	1020.0	1005.2	1006.3	1003.1
30°	990.5	985.2	970.5	970.5	963.1
32.5°	954.7	947.3	936.8	929.5	926.3
35°	915.8	909.5	895.8	889.5	884.2
37.5°	876.8	868.4	854.7	847.3	844.2
40°	835.8	829.5	814.7	806.3	802.1
42.5°	794.7	787.3	772.6	764.2	760.0
45°	750.5	746.3	732.6	720.0	714.7
47.5°	707.4	701.0	688.4	675.8	671.6
50°	663.1	657.9	644.2	632.6	626.3
52.5°	616.8	613.7	598.9	589.5	583.1
55°	569.5	568.4	554.7	543.1	537.9
57.5°	525.3	521.0	510.5	500.0	493.7
60°	476.8	475.8	463.1	453.7	448.4
62.5°	433.7	430.5	417.9	408.4	405.3
65°	388.4	383.1	372.6	364.2	361.0
67.5°	340.0	335.8	327.4	320.0	315.8
70°	296.8	290.5	284.2	276.8	271.6
72.5°	251.6	247.4	240.0	233.7	231.6
75°	205.3	201.0	197.9	192.6	189.5
77.5°	164.2	162.1	157.9	153.7	153.7
80°	124.2	121.0	118.9	117.9	117.9
82.5°	85.3	85.3	85.3	83.2	82.1
85°	54.7	52.6	52.6	50.5	50.5
87.5°	27.4	24.2	23.2	22.1	22.1
90°	0.6	6.3	13.7	16.0	17.1
92.5°	13.1	9.7	14.9	18.9	19.4
95°	34.9	11.4	17.7	21.7	21.7
97.5°	63.4	47.4	18.3	22.9	23.4
100°	96.6	108.0	18.9	23.4	24.0
102.5°	134.3	141.8	42.3	23.4	24.6
105°	170.3	176.6	125.2	24.0	25.2
107.5°	208.6	213.8	222.3	134.3	59.4
110°	246.9	251.5	257.8	238.9	157.2



TEST NUMBER: P1010750

CATALOG NUMBER: S123DIP-B775D585UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	283.5	287.5	293.8	298.9	297.8
115°	319.5	322.9	328.1	333.8	336.1
117.5°	355.0	359.0	361.8	366.4	367.0
120°	387.5	392.7	394.4	399.0	399.0
122.5°	420.7	424.7	427.0	429.8	430.4
125°	450.4	455.0	457.3	458.4	459.6
127.5°	480.1	484.7	487.6	489.3	488.1
130°	507.6	512.1	514.4	516.7	515.6
132.5°	533.9	538.4	540.2	542.4	540.7
135°	560.7	564.2	566.4	568.2	566.4
137.5°	583.6	588.2	589.3	592.2	591.0
140°	606.5	609.9	611.6	613.9	612.7
142.5°	627.6	631.0	632.8	634.5	632.8
145°	647.0	651.0	652.2	653.3	653.3
147.5°	665.9	668.8	669.9	671.0	668.2
150°	683.1	684.8	685.9	687.1	685.3
152.5°	698.5	699.1	699.6	701.9	699.1
155°	712.8	711.6	712.2	715.1	711.6
157.5°	724.2	724.2	723.6	727.1	722.5
160°	734.5	733.9	733.4	736.8	732.8
162.5°	744.2	742.5	741.9	745.9	742.5
165°	751.6	749.9	749.4	753.9	749.9
167.5°	757.9	755.6	755.6	760.2	755.6
170°	763.1	760.8	760.8	765.4	760.8
172.5°	766.5	763.6	764.2	768.8	763.6
175°	769.4	766.5	767.1	771.1	766.5
177.5°	770.5	767.6	768.2	772.8	767.1
180°	769.4	769.4	769.4	769.4	769.4

(END OF REPORT)