

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010752

Luminaire Tested: S123DIP-B775D585UB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010752
REPORT IS A COMBINATION OF REPORTS P990421 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B775D585UB2750-4F0-XX-W2A-F_4000K
Description: Define 3 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5501.0 lumens
Efficiency: N/A
Efficacy: 107.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 51.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010752

CATALOG NUMBER: S123DIP-B775D585UB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010752

CATALOG NUMBER: S123DIP-B775D585UB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	88	88	88	75	75	75	63	63	63
1	99	95	91	87	92	89	85	82	77	74	72	66	64	62	56	54	53
2	91	83	77	71	84	77	72	67	67	63	59	58	55	52	49	47	45
3	83	73	65	59	77	68	62	56	59	54	50	51	47	44	43	41	38
4	76	65	56	50	70	60	53	48	53	47	43	45	41	38	39	35	33
5	69	58	49	43	64	54	47	41	47	41	37	41	36	33	35	31	29
6	64	52	43	37	59	48	41	36	43	37	32	37	32	29	32	28	25
7	59	47	39	33	55	44	37	31	39	33	28	34	29	25	29	25	22
8	55	42	35	29	51	40	33	28	35	29	25	31	26	23	27	23	20
9	51	39	31	26	48	37	30	25	32	27	23	28	24	20	25	21	18
10	48	36	28	23	45	34	27	22	30	24	20	26	22	18	23	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13103	13103	13103
5°	13135	12651	12631
10°	13018	12222	12097
15°	12837	11777	11514
20°	12630	11282	10937
25°	12361	10762	10320
30°	12067	10221	9670
35°	11760	9669	9025
40°	11437	9091	8391
45°	11083	8527	7728
50°	10723	7898	7063
55°	10259	7243	6387
60°	9783	6520	5671
65°	9336	5738	4922
70°	8693	4872	4048
75°	7764	3858	3143
80°	6705	2712	2223
85°	5225	1456	1113

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11083 cd/sqm

TEST NUMBER: P1010752

CATALOG NUMBER: S123DIP-B775D585UB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	114.8	2.1
10°-20°	324.0	5.9
20°-30°	478.6	8.7
30°-40°	558.9	10.2
40°-50°	561.9	10.2
50°-60°	493.6	9.0
60°-70°	367.6	6.7
70°-80°	209.2	3.8
80°-90°	61.0	1.1
90°-100°	27.0	0.5
100°-110°	130.4	2.4
110°-120°	319.5	5.8
120°-130°	405.6	7.4
130°-140°	433.3	7.9
140°-150°	405.2	7.4
150°-160°	326.8	5.9
160°-170°	210.9	3.8
170°-180°	72.7	1.3
0°-30°	917.4	16.7
0°-40°	1476.3	26.8
0°-60°	2531.7	46.0
0°-90°	3169.5	57.6
90°-120°	476.9	8.7
90°-150°	1721.0	31.3
90°-180°	2331.0	42.4
0°-180°	5501.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1217	1217	1217	1217	1217	
5°	1218	1213	1202	1212	1210	116
15°	1160	1156	1142	1150	1144	327
25°	1053	1047	1033	1034	1031	485
35°	911	904	891	884	879	570
45°	746	742	728	716	711	576
55°	566	565	552	540	535	507
65°	386	381	370	362	359	381
75°	204	200	197	192	188	218
85°	54	52	52	50	50	58
90°	1	6	14	16	17	6
95°	35	11	18	22	22	41
105°	169	176	124	24	25	180
115°	318	321	326	332	334	314
125°	448	452	454	456	457	400
135°	557	561	563	565	563	429
145°	643	647	648	649	649	403
155°	708	707	708	711	707	326
165°	747	746	745	749	746	211
175°	765	762	762	766	762	73
180°	765	765	765	765	765	

TEST NUMBER: P1010752

CATALOG NUMBER: S123DIP-B775D585UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1217.3	1217.3	1217.3	1217.3	1217.3
2.5°	1222.5	1218.3	1206.8	1217.3	1216.2
5°	1218.3	1213.1	1201.6	1212.0	1209.9
7.5°	1208.9	1203.7	1192.1	1201.6	1200.5
10°	1196.3	1191.1	1177.5	1186.9	1184.8
12.5°	1179.6	1175.4	1162.8	1169.1	1168.1
15°	1159.7	1155.5	1141.9	1150.3	1144.0
17.5°	1137.7	1132.5	1118.9	1125.2	1123.1
20°	1112.6	1106.3	1092.7	1096.9	1093.8
22.5°	1084.3	1078.1	1064.5	1067.6	1063.4
25°	1052.9	1046.7	1033.1	1034.1	1031.0
27.5°	1020.5	1014.2	999.6	1000.6	997.5
30°	984.9	979.7	965.0	965.0	957.7
32.5°	949.3	942.0	931.5	924.2	921.1
35°	910.6	904.3	890.7	884.4	879.2
37.5°	871.9	863.5	849.9	842.6	839.4
40°	831.0	824.8	810.1	801.7	797.6
42.5°	790.2	782.9	768.2	759.9	755.7
45°	746.3	742.1	728.5	715.9	710.7
47.5°	703.4	697.1	684.5	672.0	667.8
50°	659.4	654.2	640.6	629.0	622.8
52.5°	613.3	610.2	595.5	586.1	579.8
55°	566.2	565.2	551.6	540.1	534.8
57.5°	522.3	518.1	507.6	497.2	490.9
60°	474.1	473.1	460.5	451.1	445.9
62.5°	431.2	428.1	415.5	406.1	403.0
65°	386.2	381.0	370.5	362.1	359.0
67.5°	338.1	333.9	325.5	318.2	314.0
70°	295.2	288.9	282.6	275.3	270.0
72.5°	250.2	246.0	238.6	232.4	230.3
75°	204.1	199.9	196.8	191.5	188.4
77.5°	163.3	161.2	157.0	152.8	152.8
80°	123.5	120.4	118.3	117.2	117.2
82.5°	84.8	84.8	84.8	82.7	81.6
85°	54.4	52.3	52.3	50.2	50.2
87.5°	27.2	24.1	23.0	22.0	22.0
90°	0.6	6.2	13.6	15.9	17.0
92.5°	13.1	9.7	14.8	18.7	19.3
95°	34.7	11.4	17.6	21.6	21.6
97.5°	63.1	47.2	18.2	22.7	23.3
100°	96.0	107.4	18.7	23.3	23.9
102.5°	133.5	140.9	42.0	23.3	24.4
105°	169.3	175.6	124.4	23.9	25.0
107.5°	207.4	212.5	221.0	133.5	59.1
110°	245.5	250.0	256.2	237.5	156.2

TEST NUMBER: P1010752

CATALOG NUMBER: S123DIP-B775D585UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	281.8	285.8	292.0	297.2	296.0
115°	317.6	321.0	326.1	331.8	334.1
117.5°	352.8	356.8	359.7	364.2	364.8
120°	385.2	390.3	392.0	396.6	396.6
122.5°	418.2	422.2	424.4	427.3	427.8
125°	447.7	452.3	454.5	455.7	456.8
127.5°	477.3	481.8	484.7	486.4	485.2
130°	504.5	509.1	511.4	513.6	512.5
132.5°	530.7	535.2	536.9	539.2	537.5
135°	557.4	560.8	563.1	564.8	563.1
137.5°	580.1	584.7	585.8	588.6	587.5
140°	602.8	606.2	608.0	610.2	609.1
142.5°	623.9	627.3	629.0	630.7	629.0
145°	643.2	647.2	648.3	649.4	649.4
147.5°	661.9	664.8	665.9	667.0	664.2
150°	679.0	680.7	681.8	683.0	681.2
152.5°	694.3	694.9	695.5	697.7	694.9
155°	708.5	707.4	708.0	710.8	707.4
157.5°	719.9	719.9	719.3	722.7	718.2
160°	730.1	729.5	729.0	732.4	728.4
162.5°	739.8	738.1	737.5	741.5	738.1
165°	747.2	745.5	744.9	749.4	745.5
167.5°	753.4	751.1	751.1	755.7	751.1
170°	758.5	756.2	756.2	760.8	756.2
172.5°	761.9	759.1	759.7	764.2	759.1
175°	764.8	761.9	762.5	766.5	761.9
177.5°	765.9	763.1	763.6	768.2	762.5
180°	764.8	764.8	764.8	764.8	764.8

(END OF REPORT)