

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010480

Luminaire Tested: S123DIP-B1165D1025UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010480
REPORT IS A COMBINATION OF REPORTS P989339 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B1165D1025UB2750-4F0-XX-W2A-F_3000K
Description: Define 3 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8825.0 lumens
Efficiency: N/A
Efficacy: 98.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 89.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010480

CATALOG NUMBER: S123DIP-B1165D1025UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010480

CATALOG NUMBER: S123DIP-B1165D1025UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60
1	99	94	90	87	91	88	84	81	75	72	70	63	62	60	53	52	50
2	90	82	76	71	83	77	71	66	66	62	58	56	53	50	46	44	42
3	82	72	65	59	76	67	61	56	58	53	49	49	45	42	41	38	36
4	75	64	56	50	69	60	53	47	51	46	42	44	40	36	37	34	31
5	69	57	49	43	64	53	46	40	46	40	36	39	35	31	33	30	27
6	63	51	43	37	59	48	40	35	41	36	31	36	31	28	30	27	24
7	59	46	38	33	54	43	36	31	38	32	28	32	28	24	27	24	21
8	54	42	34	29	50	39	32	27	34	29	25	30	25	22	25	22	19
9	51	38	31	26	47	36	29	24	31	26	22	27	23	20	23	20	17
10	47	35	28	23	44	33	26	22	29	24	20	25	21	18	22	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19719	19719	19719
5°	19769	19039	19011
10°	19593	18395	18206
15°	19321	17724	17330
20°	19008	16981	16460
25°	18604	16196	15531
30°	18162	15383	14554
35°	17699	14553	13583
40°	17214	13682	12629
45°	16681	12833	11630
50°	16138	11887	10629
55°	15441	10901	9615
60°	14725	9813	8534
65°	14052	8636	7407
70°	13081	7331	6093
75°	11686	5806	4730
80°	10092	4080	3345
85°	7867	2194	1676

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 16681 cd/sqm

TEST NUMBER: P1010480

CATALOG NUMBER: S123DIP-B1165D1025UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	172.7	2.0
10°-20°	487.7	5.5
20°-30°	720.3	8.2
30°-40°	841.2	9.5
40°-50°	845.7	9.6
50°-60°	742.9	8.4
60°-70°	553.3	6.3
70°-80°	314.9	3.6
80°-90°	92.2	1.0
90°-100°	46.9	0.5
100°-110°	226.7	2.6
110°-120°	555.6	6.3
120°-130°	705.4	8.0
130°-140°	753.5	8.5
140°-150°	704.6	8.0
150°-160°	568.4	6.4
160°-170°	366.8	4.2
170°-180°	126.4	1.4
0°-30°	1380.7	15.6
0°-40°	2221.8	25.2
0°-60°	3810.4	43.2
0°-90°	4770.7	54.1
90°-120°	829.3	9.4
90°-150°	2992.8	33.9
90°-180°	4054.0	45.9
0°-180°	8825.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1832	1832	1832	1832	1832	
5°	1834	1826	1808	1824	1821	174
15°	1745	1739	1719	1731	1722	492
25°	1585	1575	1555	1556	1552	730
35°	1370	1361	1341	1331	1323	857
45°	1123	1117	1096	1078	1070	867
55°	852	851	830	813	805	763
65°	581	573	558	545	540	573
75°	307	301	296	288	284	328
85°	82	79	79	76	76	88
90°	1	11	24	28	30	9
95°	60	20	31	38	38	72
105°	294	305	216	42	44	312
115°	552	558	567	577	581	545
125°	779	786	790	792	794	696
135°	969	975	979	982	979	746
145°	1118	1125	1127	1129	1129	700
155°	1232	1230	1231	1236	1230	568
165°	1299	1296	1295	1303	1296	367
175°	1330	1325	1326	1333	1325	127
180°	1330	1330	1330	1330	1330	

TEST NUMBER: P1010480

CATALOG NUMBER: S123DIP-B1165D1025UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1832.0	1832.0	1832.0	1832.0	1832.0
2.5°	1839.9	1833.6	1816.3	1832.0	1830.5
5°	1833.6	1825.7	1808.4	1824.2	1821.0
7.5°	1819.4	1811.6	1794.2	1808.4	1806.8
10°	1800.5	1792.7	1772.2	1786.4	1783.2
12.5°	1775.3	1769.0	1750.1	1759.6	1758.0
15°	1745.4	1739.1	1718.6	1731.2	1721.8
17.5°	1712.3	1704.4	1684.0	1693.4	1690.3
20°	1674.5	1665.1	1644.6	1650.9	1646.2
22.5°	1632.0	1622.5	1602.1	1606.8	1600.5
25°	1584.7	1575.3	1554.8	1556.4	1551.6
27.5°	1535.9	1526.4	1504.4	1506.0	1501.2
30°	1482.3	1474.5	1452.4	1452.4	1441.4
32.5°	1428.8	1417.7	1402.0	1391.0	1386.2
35°	1370.5	1361.0	1340.6	1331.1	1323.2
37.5°	1312.2	1299.6	1279.1	1268.1	1263.4
40°	1250.8	1241.3	1219.3	1206.7	1200.4
42.5°	1189.3	1178.3	1156.3	1143.6	1137.3
45°	1123.2	1116.9	1096.4	1077.5	1069.6
47.5°	1058.6	1049.1	1030.2	1011.3	1005.0
50°	992.4	984.5	964.1	946.7	937.3
52.5°	923.1	918.4	896.3	882.2	872.7
55°	852.2	850.6	830.2	812.8	805.0
57.5°	786.1	779.8	764.0	748.3	738.8
60°	713.6	712.0	693.1	678.9	671.1
62.5°	649.0	644.3	625.4	611.2	606.5
65°	581.3	573.4	557.6	545.0	540.3
67.5°	508.8	502.5	489.9	478.9	472.6
70°	444.2	434.8	425.3	414.3	406.4
72.5°	376.5	370.2	359.2	349.7	346.6
75°	307.2	300.9	296.2	288.3	283.5
77.5°	245.7	242.6	236.3	230.0	230.0
80°	185.9	181.2	178.0	176.4	176.4
82.5°	127.6	127.6	127.6	124.4	122.9
85°	81.9	78.8	78.8	75.6	75.6
87.5°	41.0	36.2	34.7	33.1	33.1
90°	1.0	10.9	23.7	27.7	29.6
92.5°	22.7	16.8	25.7	32.6	33.6
95°	60.3	19.8	30.6	37.5	37.5
97.5°	109.7	82.0	31.6	39.5	40.5
100°	167.0	186.7	32.6	40.5	41.5
102.5°	232.2	245.0	73.1	40.5	42.5
105°	294.4	305.3	216.4	41.5	43.5
107.5°	360.6	369.5	384.3	232.2	102.8
110°	426.8	434.7	445.6	413.0	271.7

TEST NUMBER: P1010480

CATALOG NUMBER: S123DIP-B1165D1025UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	490.1	497.0	507.9	516.7	514.8
115°	552.3	558.2	567.1	577.0	581.0
117.5°	613.6	620.5	625.4	633.3	634.3
120°	669.9	678.8	681.8	689.7	689.7
122.5°	727.2	734.1	738.1	743.0	744.0
125°	778.6	786.5	790.4	792.4	794.4
127.5°	830.0	837.9	842.8	845.8	843.8
130°	877.4	885.3	889.2	893.2	891.2
132.5°	922.8	930.7	933.7	937.7	934.7
135°	969.3	975.2	979.2	982.1	979.2
137.5°	1008.8	1016.7	1018.7	1023.6	1021.6
140°	1048.3	1054.2	1057.2	1061.2	1059.2
142.5°	1084.9	1090.8	1093.8	1096.7	1093.8
145°	1118.5	1125.4	1127.4	1129.3	1129.3
147.5°	1151.1	1156.0	1158.0	1160.0	1155.0
150°	1180.7	1183.7	1185.7	1187.6	1184.7
152.5°	1207.4	1208.4	1209.4	1213.3	1208.4
155°	1232.1	1230.1	1231.1	1236.0	1230.1
157.5°	1251.9	1251.9	1250.9	1256.8	1248.9
160°	1269.6	1268.7	1267.7	1273.6	1266.7
162.5°	1286.4	1283.5	1282.5	1289.4	1283.5
165°	1299.3	1296.3	1295.3	1303.2	1296.3
167.5°	1310.1	1306.2	1306.2	1314.1	1306.2
170°	1319.0	1315.1	1315.1	1323.0	1315.1
172.5°	1325.0	1320.0	1321.0	1328.9	1320.0
175°	1329.9	1325.0	1326.0	1332.9	1325.0
177.5°	1331.9	1326.9	1327.9	1335.8	1326.0
180°	1329.9	1329.9	1329.9	1329.9	1329.9

(END OF REPORT)