

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010775

Luminaire Tested: S123RDIP-B1000D1025UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010775
REPORT IS A COMBINATION OF REPORTS P992731 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B1000D1025UB2750-4F0-XX-W2A-F_3000K
Description: Define 3 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7826.0 lumens
Efficiency: N/A
Efficacy: 103.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010775

CATALOG NUMBER: S123RDIP-B1000D1025UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010775

CATALOG NUMBER: S123RDIP-B1000D1025UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54
1	98	94	90	86	90	86	83	80	73	70	68	60	59	57	49	48	47
2	89	82	76	71	82	76	71	66	64	60	57	53	51	48	43	41	40
3	82	72	65	60	75	67	61	56	57	52	48	47	44	41	39	36	34
4	75	64	56	51	69	59	53	47	51	45	41	42	38	35	35	32	30
5	69	57	49	43	63	53	46	41	45	40	36	38	34	31	31	28	26
6	63	51	44	38	58	48	41	36	41	35	31	35	30	27	28	25	23
7	59	47	39	33	54	43	36	31	37	32	28	31	27	24	26	23	21
8	54	42	35	29	50	39	33	28	34	29	25	29	25	22	24	21	19
9	51	39	31	26	47	36	29	25	31	26	22	27	22	19	22	19	17
10	47	36	28	24	44	33	27	22	29	24	20	25	21	18	21	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17957	17957	17957
5°	17987	17322	17276
10°	17845	16671	16343
15°	17614	15866	15321
20°	17310	14990	14179
25°	16997	14081	13097
30°	16594	13112	11818
35°	16180	12162	10653
40°	15791	11130	9366
45°	15292	10120	8209
50°	14741	9043	7011
55°	14171	7889	5914
60°	13625	6705	4801
65°	12921	5491	3747
70°	12033	4151	2678
75°	10758	2811	2122
80°	9180	1953	1489
85°	6887	1055	780

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15292 cd/sqm

TEST NUMBER: P1010775

CATALOG NUMBER: S123RDIP-B1000D1025UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	156.8	2.0
10°-20°	436.3	5.6
20°-30°	628.2	8.0
30°-40°	707.4	9.0
40°-50°	676.7	8.6
50°-60°	553.9	7.1
60°-70°	373.5	4.8
70°-80°	187.3	2.4
80°-90°	51.6	0.7
90°-100°	46.9	0.6
100°-110°	226.7	2.9
110°-120°	555.6	7.1
120°-130°	705.4	9.0
130°-140°	753.5	9.6
140°-150°	704.6	9.0
150°-160°	568.4	7.3
160°-170°	366.8	4.7
170°-180°	126.4	1.6
0°-30°	1221.3	15.6
0°-40°	1928.7	24.6
0°-60°	3159.3	40.4
0°-90°	3771.7	48.2
90°-120°	829.3	10.6
90°-150°	2992.8	38.2
90°-180°	4054.0	51.8
0°-180°	7826.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1668	1668	1668	1668	1668	
5°	1668	1662	1645	1658	1655	158
15°	1591	1576	1538	1532	1522	448
25°	1448	1414	1352	1323	1308	666
35°	1253	1204	1120	1062	1038	784
45°	1030	969	865	788	755	795
55°	782	716	601	522	495	701
65°	534	460	354	288	273	529
75°	283	218	143	130	127	301
85°	72	42	38	35	35	79
90°	1	11	24	28	30	8
95°	60	20	31	38	38	72
105°	294	305	216	42	44	312
115°	552	558	567	577	581	545
125°	779	786	790	792	794	696
135°	969	975	979	982	979	746
145°	1118	1125	1127	1129	1129	700
155°	1232	1230	1231	1236	1230	568
165°	1299	1296	1295	1303	1296	367
175°	1330	1325	1326	1333	1325	127
180°	1330	1330	1330	1330	1330	

TEST NUMBER: P1010775

CATALOG NUMBER: S123RDIP-B1000D1025UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1668.3	1668.3	1668.3	1668.3	1668.3
2.5°	1675.1	1669.7	1653.4	1668.3	1665.6
5°	1668.3	1661.5	1645.3	1657.5	1654.8
7.5°	1656.1	1649.4	1629.1	1637.2	1633.1
10°	1639.9	1630.4	1606.1	1607.4	1600.7
12.5°	1616.9	1606.1	1574.9	1573.6	1565.5
15°	1591.2	1576.3	1538.4	1531.6	1522.2
17.5°	1560.1	1543.8	1496.5	1482.9	1469.4
20°	1524.9	1503.2	1451.8	1434.2	1418.0
22.5°	1485.6	1459.9	1404.5	1381.5	1366.6
25°	1447.8	1413.9	1351.7	1323.3	1308.4
27.5°	1401.8	1365.2	1297.6	1259.7	1236.7
30°	1354.4	1313.8	1238.0	1192.0	1170.4
32.5°	1307.0	1259.7	1178.5	1127.1	1104.1
35°	1252.9	1204.2	1120.3	1062.1	1037.8
37.5°	1198.8	1146.0	1058.1	993.1	963.4
40°	1147.4	1087.8	991.8	921.4	890.3
42.5°	1089.2	1029.7	929.5	851.1	824.0
45°	1029.7	968.8	864.6	787.5	755.0
47.5°	971.5	903.8	801.0	717.1	688.7
50°	906.5	842.9	733.4	649.5	618.3
52.5°	848.4	778.0	669.8	581.8	554.7
55°	782.1	715.8	600.8	522.3	495.2
57.5°	722.5	650.8	534.5	460.0	437.0
60°	660.3	585.9	473.6	400.5	377.5
62.5°	598.0	523.6	411.3	343.7	319.3
65°	534.5	460.0	354.5	288.2	273.3
67.5°	470.9	395.1	292.3	242.2	226.0
70°	408.6	335.6	240.8	193.5	178.6
72.5°	346.4	274.7	190.8	154.2	150.2
75°	282.8	217.8	143.4	129.9	127.2
77.5°	224.6	165.1	112.3	104.2	101.5
80°	169.1	113.7	85.2	81.2	78.5
82.5°	116.4	70.4	60.9	56.8	56.8
85°	71.7	41.9	37.9	35.2	35.2
87.5°	32.5	17.6	17.6	16.2	14.9
90°	1.0	10.9	23.7	27.7	29.6
92.5°	22.7	16.8	25.7	32.6	33.6
95°	60.3	19.8	30.6	37.5	37.5
97.5°	109.7	82.0	31.6	39.5	40.5
100°	167.0	186.7	32.6	40.5	41.5
102.5°	232.2	245.0	73.1	40.5	42.5
105°	294.4	305.3	216.4	41.5	43.5
107.5°	360.6	369.5	384.3	232.2	102.8
110°	426.8	434.7	445.6	413.0	271.7

TEST NUMBER: P1010775

CATALOG NUMBER: S123RDIP-B1000D1025UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	490.1	497.0	507.9	516.7	514.8
115°	552.3	558.2	567.1	577.0	581.0
117.5°	613.6	620.5	625.4	633.3	634.3
120°	669.9	678.8	681.8	689.7	689.7
122.5°	727.2	734.1	738.1	743.0	744.0
125°	778.6	786.5	790.4	792.4	794.4
127.5°	830.0	837.9	842.8	845.8	843.8
130°	877.4	885.3	889.2	893.2	891.2
132.5°	922.8	930.7	933.7	937.7	934.7
135°	969.3	975.2	979.2	982.1	979.2
137.5°	1008.8	1016.7	1018.7	1023.6	1021.6
140°	1048.3	1054.2	1057.2	1061.2	1059.2
142.5°	1084.9	1090.8	1093.8	1096.7	1093.8
145°	1118.5	1125.4	1127.4	1129.3	1129.3
147.5°	1151.1	1156.0	1158.0	1160.0	1155.0
150°	1180.7	1183.7	1185.7	1187.6	1184.7
152.5°	1207.4	1208.4	1209.4	1213.3	1208.4
155°	1232.1	1230.1	1231.1	1236.0	1230.1
157.5°	1251.9	1251.9	1250.9	1256.8	1248.9
160°	1269.6	1268.7	1267.7	1273.6	1266.7
162.5°	1286.4	1283.5	1282.5	1289.4	1283.5
165°	1299.3	1296.3	1295.3	1303.2	1296.3
167.5°	1310.1	1306.2	1306.2	1314.1	1306.2
170°	1319.0	1315.1	1315.1	1323.0	1315.1
172.5°	1325.0	1320.0	1321.0	1328.9	1320.0
175°	1329.9	1325.0	1326.0	1332.9	1325.0
177.5°	1331.9	1326.9	1327.9	1335.8	1326.0
180°	1329.9	1329.9	1329.9	1329.9	1329.9

(END OF REPORT)