

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010776

Luminaire Tested: S123RDIP-B1000D1025UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010776
REPORT IS A COMBINATION OF REPORTS P992732 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B1000D1025UB2750-4F0-XX-W2A-F_3500K
Description: Define 3 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7860.0 lumens
Efficiency: N/A
Efficacy: 104.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010776

CATALOG NUMBER: S123RDIP-B1000D1025UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1010776

CATALOG NUMBER: S123RDIP-B1000D1025UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54	41	41	41
1	98	94	90	86	90	86	83	80	73	70	68	60	59	57	49	48	47	39	38	37
2	89	82	76	71	82	76	71	66	64	60	57	53	51	48	43	41	40	35	34	33
3	82	72	65	60	75	67	61	56	57	52	48	47	44	41	39	36	34	30	29	28
4	75	64	56	51	69	59	53	47	51	45	41	42	38	35	35	32	30	26	25	24
5	69	57	49	43	63	53	46	41	45	40	36	38	34	31	31	28	26	23	22	21
6	63	51	44	38	58	48	41	36	41	35	31	35	30	27	28	25	23	20	19	18
7	59	47	39	33	54	43	36	31	37	32	28	31	27	24	26	23	21	18	17	16
8	54	42	35	29	50	39	33	28	34	29	25	29	25	22	24	21	19	16	15	14
9	51	39	31	26	47	36	29	25	31	26	22	27	22	19	22	19	17	15	14	13
10	47	36	28	24	44	33	27	22	29	24	20	25	21	18	21	18	15	13	12	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18034	18034	18034
5°	18063	17396	17349
10°	17922	16742	16411
15°	17688	15933	15385
20°	17384	15054	14239
25°	17069	14140	13153
30°	16664	13168	11868
35°	16249	12214	10698
40°	15859	11177	9406
45°	15356	10163	8244
50°	14804	9081	7042
55°	14231	7922	5939
60°	13683	6734	4821
65°	12974	5514	3763
70°	12086	4170	2690
75°	10803	2823	2130
80°	9218	1962	1494
85°	6916	1058	782

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15356 cd/sqm

TEST NUMBER: P1010776

CATALOG NUMBER: S123RDIP-B1000D1025UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.5	2.0
10°-20°	438.1	5.6
20°-30°	630.8	8.0
30°-40°	710.4	9.0
40°-50°	679.5	8.6
50°-60°	556.3	7.1
60°-70°	375.0	4.8
70°-80°	188.1	2.4
80°-90°	51.8	0.7
90°-100°	47.1	0.6
100°-110°	227.8	2.9
110°-120°	558.1	7.1
120°-130°	708.5	9.0
130°-140°	756.9	9.6
140°-150°	707.8	9.0
150°-160°	570.9	7.3
160°-170°	368.4	4.7
170°-180°	127.0	1.6
0°-30°	1226.5	15.6
0°-40°	1936.9	24.6
0°-60°	3172.7	40.4
0°-90°	3787.7	48.2
90°-120°	833.0	10.6
90°-150°	3006.1	38.2
90°-180°	4072.0	51.8
0°-180°	7860.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1675	1675	1675	1675	1675	
5°	1675	1669	1652	1664	1662	159
15°	1598	1583	1545	1538	1529	450
25°	1454	1420	1357	1329	1314	669
35°	1258	1209	1125	1067	1042	788
45°	1034	973	868	791	758	798
55°	785	719	603	524	497	704
65°	537	462	356	289	274	531
75°	284	219	144	130	128	303
85°	72	42	38	35	35	79
90°	1	11	24	28	30	8
95°	60	20	31	38	38	72
105°	296	307	217	42	44	314
115°	555	561	570	580	584	548
125°	782	790	794	796	798	699
135°	974	980	984	986	984	750
145°	1123	1130	1132	1134	1134	703
155°	1238	1236	1237	1242	1236	570
165°	1305	1302	1301	1309	1302	369
175°	1336	1331	1332	1339	1331	127
180°	1336	1336	1336	1336	1336	

TEST NUMBER: P1010776

CATALOG NUMBER: S123RDIP-B1000D1025UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1675.4	1675.4	1675.4	1675.4	1675.4
2.5°	1682.2	1676.7	1660.4	1675.4	1672.7
5°	1675.4	1668.6	1652.3	1664.5	1661.8
7.5°	1663.2	1656.4	1636.0	1644.1	1640.1
10°	1646.9	1637.3	1612.9	1614.2	1607.4
12.5°	1623.8	1612.9	1581.6	1580.3	1572.1
15°	1597.9	1583.0	1544.9	1538.2	1528.6
17.5°	1566.7	1550.4	1502.8	1489.2	1475.6
20°	1531.4	1509.6	1458.0	1440.3	1424.0
22.5°	1492.0	1466.1	1410.4	1387.3	1372.4
25°	1453.9	1419.9	1357.4	1328.9	1314.0
27.5°	1407.7	1371.0	1303.1	1265.0	1241.9
30°	1360.1	1319.4	1243.3	1197.1	1175.4
32.5°	1312.6	1265.0	1183.5	1131.9	1108.8
35°	1258.2	1209.3	1125.1	1066.7	1042.2
37.5°	1203.9	1150.9	1062.6	997.4	967.5
40°	1152.3	1092.5	996.0	925.3	894.1
42.5°	1093.8	1034.0	933.5	854.7	827.5
45°	1034.0	972.9	868.3	790.8	758.2
47.5°	975.6	907.7	804.4	720.2	691.6
50°	910.4	846.5	736.5	652.2	621.0
52.5°	852.0	781.3	672.6	584.3	557.1
55°	785.4	718.8	603.3	524.5	497.3
57.5°	725.6	653.6	536.7	462.0	438.9
60°	663.1	588.4	475.6	402.2	379.1
62.5°	600.6	525.9	413.1	345.1	320.7
65°	536.7	462.0	356.0	289.4	274.5
67.5°	472.9	396.8	293.5	243.2	226.9
70°	410.4	337.0	241.9	194.3	179.4
72.5°	347.9	275.8	191.6	154.9	150.8
75°	284.0	218.8	144.0	130.4	127.7
77.5°	225.6	165.8	112.8	104.6	101.9
80°	169.8	114.1	85.6	81.5	78.8
82.5°	116.9	70.7	61.1	57.1	57.1
85°	72.0	42.1	38.0	35.3	35.3
87.5°	32.6	17.7	17.7	16.3	14.9
90°	1.0	10.9	23.8	27.8	29.8
92.5°	22.8	16.9	25.8	32.8	33.7
95°	60.5	19.8	30.8	37.7	37.7
97.5°	110.2	82.4	31.8	39.7	40.7
100°	167.7	187.6	32.8	40.7	41.7
102.5°	233.2	246.1	73.4	40.7	42.7
105°	295.7	306.7	217.3	41.7	43.7
107.5°	362.2	371.2	386.1	233.2	103.2
110°	428.7	436.7	447.6	414.8	272.9



TEST NUMBER: P1010776

CATALOG NUMBER: S123RDIP-B1000D1025UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	492.2	499.2	510.1	519.0	517.1
115°	554.8	560.7	569.7	579.6	583.5
117.5°	616.3	623.2	628.2	636.1	637.1
120°	672.9	681.8	684.8	692.7	692.7
122.5°	730.4	737.4	741.3	746.3	747.3
125°	782.0	790.0	793.9	795.9	797.9
127.5°	833.6	841.6	846.5	849.5	847.5
130°	881.3	889.2	893.2	897.2	895.2
132.5°	926.9	934.9	937.8	941.8	938.8
135°	973.6	979.5	983.5	986.5	983.5
137.5°	1013.3	1021.2	1023.2	1028.2	1026.2
140°	1053.0	1058.9	1061.9	1065.9	1063.9
142.5°	1089.7	1095.6	1098.6	1101.6	1098.6
145°	1123.4	1130.4	1132.4	1134.3	1134.3
147.5°	1156.2	1161.1	1163.1	1165.1	1160.2
150°	1186.0	1188.9	1190.9	1192.9	1189.9
152.5°	1212.7	1213.7	1214.7	1218.7	1213.7
155°	1237.6	1235.6	1236.6	1241.5	1235.6
157.5°	1257.4	1257.4	1256.4	1262.4	1254.4
160°	1275.3	1274.3	1273.3	1279.2	1272.3
162.5°	1292.1	1289.2	1288.2	1295.1	1289.2
165°	1305.0	1302.1	1301.1	1309.0	1302.1
167.5°	1316.0	1312.0	1312.0	1319.9	1312.0
170°	1324.9	1320.9	1320.9	1328.9	1320.9
172.5°	1330.8	1325.9	1326.9	1334.8	1325.9
175°	1335.8	1330.8	1331.8	1338.8	1330.8
177.5°	1337.8	1332.8	1333.8	1341.8	1331.8
180°	1335.8	1335.8	1335.8	1335.8	1335.8

(END OF REPORT)