

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010491

Luminaire Tested: S123DIP-B1165D1195UB2750-4F0-XX-W2A-D_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010491
REPORT IS A COMBINATION OF REPORTS P989395 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B1165D1195UB2750-4F0-XX-W2A-D_3500K
Description: Define 3 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9669.0 lumens
Efficiency: N/A
Efficacy: 100.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.25 / 1.37
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 96.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010491

CATALOG NUMBER: S123DIP-B1165D1195UB2750-4F0-XX-W2A-D_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1010491

CATALOG NUMBER: S123DIP-B1165D1195UB2750-4F0-XX-W2A-D_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	98	98	98	98	81	81	81	66	66	66	53	53	53
1	96	91	87	83	88	84	80	77	70	67	65	57	55	53	45	44	43
2	87	79	73	67	79	73	67	62	61	56	53	49	46	44	39	37	35
3	79	69	62	55	72	64	57	52	53	48	44	43	40	37	34	32	29
4	72	61	53	47	66	56	49	43	47	41	37	38	34	31	30	28	25
5	66	54	46	40	60	50	43	37	42	36	32	34	30	27	27	24	22
6	61	49	40	34	56	45	37	32	38	32	28	31	27	23	25	22	19
7	56	44	36	30	51	40	33	28	34	28	24	28	24	20	23	19	17
8	52	40	32	26	48	37	30	25	31	25	21	26	21	18	21	17	15
9	48	36	28	23	44	33	27	22	28	23	19	24	19	16	19	16	13
10	45	33	26	21	41	31	24	20	26	21	17	22	18	15	18	15	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15632	15632	15632
5°	15675	15174	15162
10°	15529	14763	14650
15°	15323	14310	14108
20°	15032	13803	13526
25°	14672	13234	12922
30°	14306	12718	12317
35°	13893	12177	11822
40°	13500	11682	11301
45°	13063	11204	10872
50°	12632	10728	10406
55°	12154	10242	9976
60°	11687	9744	9537
65°	11204	9214	9022
70°	10484	8617	8492
75°	9567	7939	7945
80°	8502	7252	7320
85°	7444	6697	6873

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13063 cd/sqm

TEST NUMBER: P1010491

CATALOG NUMBER: S123DIP-B1165D1195UB2750-4F0-XX-W2A-D_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	137.8	1.4
10°-20°	392.8	4.1
20°-30°	587.3	6.1
30°-40°	701.2	7.3
40°-50°	733.7	7.6
50°-60°	688.5	7.1
60°-70°	575.1	5.9
70°-80°	411.2	4.3
80°-90°	247.8	2.6
90°-100°	209.1	2.2
100°-110°	380.6	3.9
110°-120°	731.2	7.6
120°-130°	875.5	9.1
130°-140°	908.6	9.4
140°-150°	835.6	8.6
150°-160°	670.8	6.9
160°-170°	432.9	4.5
170°-180°	149.2	1.5
0°-30°	1117.9	11.6
0°-40°	1819.1	18.8
0°-60°	3241.3	33.5
0°-90°	4475.5	46.3
90°-120°	1320.9	13.7
90°-150°	3940.7	40.8
90°-180°	5194.0	53.7
0°-180°	9669.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1452	1452	1452	1452	1452	
5°	1454	1451	1441	1454	1452	138
15°	1384	1389	1388	1403	1402	390
25°	1250	1266	1270	1291	1291	576
35°	1076	1101	1122	1145	1152	673
45°	880	918	957	987	1000	678
55°	671	723	780	823	835	601
65°	464	525	595	642	658	458
75°	252	326	405	457	476	269
85°	78	157	240	294	310	80
90°	22	111	207	265	283	19
95°	88	102	193	250	266	99
105°	360	411	374	212	228	381
115°	660	686	753	803	820	652
125°	924	933	984	1019	1032	826
135°	1147	1152	1175	1207	1211	883
145°	1322	1328	1330	1346	1352	827
155°	1454	1452	1453	1459	1452	670
165°	1533	1530	1529	1538	1530	433
175°	1570	1564	1565	1573	1564	149
180°	1570	1570	1570	1570	1570	

TEST NUMBER: P1010491

CATALOG NUMBER: S123DIP-B1165D1195UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1452.3	1452.3	1452.3	1452.3	1452.3
2.5°	1460.3	1455.5	1442.8	1455.5	1453.9
5°	1453.9	1450.8	1441.3	1453.9	1452.3
7.5°	1442.8	1442.8	1433.4	1449.2	1447.6
10°	1427.0	1430.2	1422.3	1438.1	1434.9
12.5°	1408.0	1412.8	1408.0	1422.3	1419.1
15°	1384.3	1389.1	1387.5	1403.3	1401.7
17.5°	1355.8	1365.3	1363.7	1378.0	1374.8
20°	1324.2	1333.7	1336.8	1351.1	1352.7
22.5°	1291.0	1300.5	1305.2	1324.2	1322.6
25°	1249.8	1265.7	1270.4	1291.0	1291.0
27.5°	1210.3	1227.7	1237.2	1254.6	1256.2
30°	1167.6	1188.1	1200.8	1219.8	1219.8
32.5°	1120.1	1143.8	1161.2	1181.8	1186.6
35°	1075.8	1101.1	1121.7	1145.4	1151.7
37.5°	1028.3	1056.8	1080.6	1107.4	1112.2
40°	980.9	1009.4	1041.0	1067.9	1074.2
42.5°	928.7	965.1	998.3	1028.3	1037.8
45°	879.6	917.6	957.2	987.2	999.9
47.5°	827.4	870.1	914.4	947.7	957.2
50°	776.8	821.1	870.1	906.5	917.6
52.5°	723.0	770.5	825.8	863.8	878.0
55°	670.8	723.0	780.0	822.7	835.3
57.5°	620.2	674.0	735.7	778.4	792.6
60°	566.4	623.3	688.2	732.5	749.9
62.5°	515.8	574.3	643.9	688.2	704.0
65°	463.5	525.2	594.9	642.3	658.1
67.5°	411.3	476.2	545.8	598.0	610.7
70°	356.0	424.0	499.9	550.6	566.4
72.5°	305.3	373.4	452.5	504.7	520.5
75°	251.5	325.9	405.0	457.2	476.2
77.5°	205.7	280.0	359.1	414.5	428.7
80°	156.6	234.1	316.4	370.2	386.0
82.5°	113.9	193.0	276.9	330.7	346.5
85°	77.5	156.6	240.5	294.3	310.1
87.5°	47.5	126.6	207.3	261.0	276.9
90°	21.8	110.9	206.8	265.3	283.4
92.5°	45.8	106.8	196.4	256.8	272.2
95°	88.5	102.4	192.7	250.0	265.8
97.5°	145.2	169.6	184.4	241.2	258.2
100°	211.3	285.3	176.1	231.3	248.3
102.5°	286.7	346.2	214.4	220.2	238.4
105°	360.2	410.9	374.1	212.0	228.5
107.5°	436.7	480.4	562.8	425.9	287.4
110°	513.2	551.1	627.2	629.8	475.7

TEST NUMBER: P1010491

CATALOG NUMBER: S123DIP-B1165D1195UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	587.9	618.1	691.2	741.2	753.1
115°	659.7	685.7	753.1	802.8	820.2
117.5°	732.0	752.9	812.5	859.8	873.6
120°	796.9	815.3	871.0	916.7	927.8
122.5°	864.5	875.9	929.6	970.2	982.5
125°	923.6	932.9	983.5	1019.0	1032.4
127.5°	984.2	992.0	1037.4	1072.6	1081.2
130°	1040.2	1048.0	1084.3	1119.0	1126.2
132.5°	1092.3	1101.6	1128.8	1162.0	1169.5
135°	1147.1	1152.5	1174.6	1206.6	1211.0
137.5°	1193.8	1201.5	1214.9	1246.1	1251.6
140°	1238.8	1245.8	1254.0	1282.5	1288.0
142.5°	1282.0	1287.3	1290.8	1314.9	1319.3
145°	1321.6	1328.2	1330.5	1345.5	1351.8
147.5°	1358.5	1364.3	1366.6	1373.7	1374.2
150°	1393.5	1397.0	1399.3	1401.6	1401.3
152.5°	1424.9	1426.1	1427.3	1431.9	1426.1
155°	1454.1	1451.8	1452.9	1458.8	1451.8
157.5°	1477.4	1477.4	1476.3	1483.2	1473.9
160°	1498.4	1497.2	1496.1	1503.1	1494.9
162.5°	1518.2	1514.7	1513.6	1521.7	1514.7
165°	1533.4	1529.9	1528.7	1538.1	1529.9
167.5°	1546.2	1541.6	1541.6	1550.9	1541.6
170°	1556.7	1552.0	1552.0	1561.4	1552.0
172.5°	1563.7	1557.9	1559.0	1568.4	1557.9
175°	1569.5	1563.7	1564.9	1573.0	1563.7
177.5°	1571.9	1566.0	1567.2	1576.5	1564.9
180°	1569.5	1569.5	1569.5	1569.5	1569.5

(END OF REPORT)