

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010796

Luminaire Tested: S123RDIP-B1000D365UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010796
REPORT IS A COMBINATION OF REPORTS P992812 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B1000D365UB2750-4F0-XX-W2A-F_3500K
Description: Define 3 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5251.0 lumens
Efficiency: N/A
Efficacy: 93.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 56.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010796

CATALOG NUMBER: S123RDIP-B1000D365UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1010796

CATALOG NUMBER: S123RDIP-B1000D365UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	112	112	112	112	107	107	107	107	96	96	96	86	86	86	76	76	76	76	76	76
1	103	99	95	92	98	94	91	88	85	82	80	76	74	72	68	67	66	66	66	62
2	94	87	81	76	89	83	77	73	75	71	67	67	64	61	61	58	56	56	56	52
3	86	77	70	64	82	73	67	61	66	61	57	60	56	52	54	51	48	48	48	45
4	79	68	60	54	75	65	58	52	59	54	49	54	49	45	49	45	42	42	42	39
5	73	61	53	47	69	59	51	46	53	47	43	49	44	40	44	40	37	37	37	34
6	68	55	47	41	64	53	45	40	48	42	37	44	39	35	40	36	33	33	33	30
7	63	50	42	36	59	48	41	35	44	38	33	40	35	31	37	32	29	29	29	27
8	58	46	38	33	55	44	37	32	40	34	30	37	32	28	34	30	26	26	26	24
9	55	42	34	29	52	40	33	28	37	31	27	34	29	25	31	27	24	24	24	22
10	51	39	31	26	49	37	30	26	34	29	24	32	27	23	29	25	22	22	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18034	18034	18034
5°	18063	17396	17349
10°	17922	16742	16411
15°	17688	15933	15385
20°	17384	15054	14239
25°	17069	14140	13153
30°	16664	13168	11868
35°	16249	12214	10698
40°	15859	11177	9406
45°	15356	10163	8244
50°	14804	9081	7042
55°	14231	7922	5939
60°	13683	6734	4821
65°	12974	5514	3763
70°	12086	4170	2690
75°	10803	2823	2130
80°	9218	1962	1494
85°	6916	1058	782

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15356 cd/sqm

TEST NUMBER: P1010796

CATALOG NUMBER: S123RDIP-B1000D365UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.5	3.0
10°-20°	438.1	8.3
20°-30°	630.8	12.0
30°-40°	710.4	13.5
40°-50°	679.5	12.9
50°-60°	556.3	10.6
60°-70°	375.0	7.1
70°-80°	188.1	3.6
80°-90°	50.1	1.0
90°-100°	16.9	0.3
100°-110°	81.9	1.6
110°-120°	200.8	3.8
120°-130°	254.9	4.9
130°-140°	272.3	5.2
140°-150°	254.6	4.8
150°-160°	205.4	3.9
160°-170°	132.5	2.5
170°-180°	45.7	0.9
0°-30°	1226.5	23.4
0°-40°	1936.9	36.9
0°-60°	3172.7	60.4
0°-90°	3786.0	72.1
90°-120°	299.6	5.7
90°-150°	1081.4	20.6
90°-180°	1465.0	27.9
0°-180°	5251.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1675	1675	1675	1675	1675	
5°	1675	1669	1652	1664	1662	159
15°	1598	1583	1545	1538	1529	450
25°	1454	1420	1357	1329	1314	669
35°	1258	1209	1125	1067	1042	788
45°	1034	973	868	791	758	798
55°	785	719	603	524	497	704
65°	537	462	356	289	274	531
75°	284	219	144	130	128	303
85°	72	42	38	35	35	79
90°	0	4	9	10	11	6
95°	22	7	11	14	14	26
105°	106	110	78	15	16	113
115°	200	202	205	208	210	197
125°	281	284	286	286	287	251
135°	350	352	354	355	354	270
145°	404	407	407	408	408	253
155°	445	444	445	447	444	205
165°	470	468	468	471	468	133
175°	481	479	479	482	479	46
180°	481	481	481	481	481	

TEST NUMBER: P1010796

CATALOG NUMBER: S123RDIP-B1000D365UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1675.4	1675.4	1675.4	1675.4	1675.4
2.5°	1682.2	1676.7	1660.4	1675.4	1672.7
5°	1675.4	1668.6	1652.3	1664.5	1661.8
7.5°	1663.2	1656.4	1636.0	1644.1	1640.1
10°	1646.9	1637.3	1612.9	1614.2	1607.4
12.5°	1623.8	1612.9	1581.6	1580.3	1572.1
15°	1597.9	1583.0	1544.9	1538.2	1528.6
17.5°	1566.7	1550.4	1502.8	1489.2	1475.6
20°	1531.4	1509.6	1458.0	1440.3	1424.0
22.5°	1492.0	1466.1	1410.4	1387.3	1372.4
25°	1453.9	1419.9	1357.4	1328.9	1314.0
27.5°	1407.7	1371.0	1303.1	1265.0	1241.9
30°	1360.1	1319.4	1243.3	1197.1	1175.4
32.5°	1312.6	1265.0	1183.5	1131.9	1108.8
35°	1258.2	1209.3	1125.1	1066.7	1042.2
37.5°	1203.9	1150.9	1062.6	997.4	967.5
40°	1152.3	1092.5	996.0	925.3	894.1
42.5°	1093.8	1034.0	933.5	854.7	827.5
45°	1034.0	972.9	868.3	790.8	758.2
47.5°	975.6	907.7	804.4	720.2	691.6
50°	910.4	846.5	736.5	652.2	621.0
52.5°	852.0	781.3	672.6	584.3	557.1
55°	785.4	718.8	603.3	524.5	497.3
57.5°	725.6	653.6	536.7	462.0	438.9
60°	663.1	588.4	475.6	402.2	379.1
62.5°	600.6	525.9	413.1	345.1	320.7
65°	536.7	462.0	356.0	289.4	274.5
67.5°	472.9	396.8	293.5	243.2	226.9
70°	410.4	337.0	241.9	194.3	179.4
72.5°	347.9	275.8	191.6	154.9	150.8
75°	284.0	218.8	144.0	130.4	127.7
77.5°	225.6	165.8	112.8	104.6	101.9
80°	169.8	114.1	85.6	81.5	78.8
82.5°	116.9	70.7	61.1	57.1	57.1
85°	72.0	42.1	38.0	35.3	35.3
87.5°	32.6	17.7	17.7	16.3	14.9
90°	0.4	3.9	8.6	10.0	10.7
92.5°	8.2	6.1	9.3	11.8	12.1
95°	21.8	7.1	11.1	13.6	13.6
97.5°	39.6	29.6	11.4	14.3	14.6
100°	60.3	67.5	11.8	14.6	15.0
102.5°	83.9	88.5	26.4	14.6	15.4
105°	106.4	110.3	78.2	15.0	15.7
107.5°	130.3	133.5	138.9	83.9	37.1
110°	154.2	157.1	161.0	149.2	98.2

TEST NUMBER: P1010796

CATALOG NUMBER: S123RDIP-B1000D365UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	177.1	179.6	183.5	186.7	186.0
115°	199.6	201.7	204.9	208.5	209.9
117.5°	221.7	224.2	226.0	228.9	229.2
120°	242.1	245.3	246.4	249.2	249.2
122.5°	262.8	265.3	266.7	268.5	268.8
125°	281.3	284.2	285.6	286.3	287.1
127.5°	299.9	302.8	304.5	305.6	304.9
130°	317.0	319.9	321.3	322.8	322.0
132.5°	333.5	336.3	337.4	338.8	337.8
135°	350.2	352.4	353.8	354.9	353.8
137.5°	364.5	367.4	368.1	369.9	369.2
140°	378.8	381.0	382.0	383.5	382.7
142.5°	392.0	394.2	395.2	396.3	395.2
145°	404.2	406.7	407.4	408.1	408.1
147.5°	415.9	417.7	418.4	419.2	417.4
150°	426.7	427.7	428.4	429.2	428.1
152.5°	436.3	436.6	437.0	438.4	436.6
155°	445.2	444.5	444.9	446.6	444.5
157.5°	452.4	452.4	452.0	454.1	451.3
160°	458.8	458.4	458.1	460.2	457.7
162.5°	464.9	463.8	463.4	465.9	463.8
165°	469.5	468.4	468.1	470.9	468.4
167.5°	473.4	472.0	472.0	474.9	472.0
170°	476.6	475.2	475.2	478.1	475.2
172.5°	478.8	477.0	477.4	480.2	477.0
175°	480.6	478.8	479.1	481.6	478.8
177.5°	481.3	479.5	479.8	482.7	479.1
180°	480.6	480.6	480.6	480.6	480.6

(END OF REPORT)