

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010804

Luminaire Tested: S123RDIP-B1000D585UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010804
REPORT IS A COMBINATION OF REPORTS P992850 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B1000D585UB2750-4F0-XX-W2A-F_2700K
Description: Define 3 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6063.0 lumens
Efficiency: N/A
Efficacy: 97.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 62.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010804

CATALOG NUMBER: S123RDIP-B1000D585UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1010804

CATALOG NUMBER: S123RDIP-B1000D585UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	67	67	67
1	101	97	93	89	94	91	87	84	79	77	75	69	67	66	60	58	57	57	57	53
2	92	85	79	74	86	80	74	70	70	66	63	61	58	56	53	51	49	49	49	45
3	84	75	68	62	79	70	64	59	62	57	53	54	51	47	47	44	42	42	42	38
4	77	67	59	53	72	63	56	50	56	50	46	49	44	41	43	39	37	37	37	33
5	71	60	51	45	66	56	49	44	50	44	40	44	39	36	39	35	32	32	32	29
6	66	54	46	40	61	51	43	38	45	39	35	40	35	32	35	31	28	28	28	26
7	61	49	41	35	57	46	39	34	41	35	31	36	32	28	32	28	25	25	25	23
8	57	44	37	31	53	42	35	30	38	32	28	33	29	25	30	26	23	23	23	21
9	53	41	33	28	50	39	32	27	35	29	25	31	26	23	27	24	21	21	21	19
10	49	37	30	25	46	35	29	24	32	26	23	29	24	21	25	22	19	19	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17800	17800	17800
5°	17829	17170	17124
10°	17689	16525	16199
15°	17460	15727	15186
20°	17158	14859	14055
25°	16848	13958	12981
30°	16449	12998	11714
35°	16039	12056	10560
40°	15652	11032	9284
45°	15159	10031	8138
50°	14612	8963	6950
55°	14046	7819	5863
60°	13505	6646	4759
65°	12807	5442	3714
70°	11927	4115	2654
75°	10662	2788	2104
80°	9099	1937	1475
85°	6829	1047	774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15159 cd/sqm

TEST NUMBER: P1010804

CATALOG NUMBER: S123RDIP-B1000D585UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.5	2.6
10°-20°	432.5	7.1
20°-30°	622.7	10.3
30°-40°	701.2	11.6
40°-50°	670.7	11.1
50°-60°	549.1	9.1
60°-70°	370.2	6.1
70°-80°	185.7	3.1
80°-90°	50.1	0.8
90°-100°	26.9	0.4
100°-110°	130.1	2.1
110°-120°	318.7	5.3
120°-130°	404.6	6.7
130°-140°	432.2	7.1
140°-150°	404.2	6.7
150°-160°	326.0	5.4
160°-170°	210.4	3.5
170°-180°	72.5	1.2
0°-30°	1210.6	20.0
0°-40°	1911.8	31.5
0°-60°	3131.6	51.7
0°-90°	3737.5	61.6
90°-120°	475.6	7.8
90°-150°	1716.6	28.3
90°-180°	2325.0	38.3
0°-180°	6063.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1654	1654	1654	1654	1654	
5°	1654	1647	1631	1643	1640	157
15°	1577	1562	1525	1518	1509	444
25°	1435	1402	1340	1312	1297	660
35°	1242	1194	1110	1053	1029	777
45°	1021	960	857	781	748	788
55°	775	710	596	518	491	695
65°	530	456	351	286	271	524
75°	280	216	142	129	126	299
85°	71	42	38	35	35	78
90°	1	6	14	16	17	6
95°	35	11	18	22	22	41
105°	169	175	124	24	25	179
115°	317	320	325	331	333	313
125°	447	451	453	454	456	399
135°	556	559	562	563	562	428
145°	642	646	647	648	648	402
155°	707	706	706	709	706	326
165°	745	744	743	748	744	211
175°	763	760	760	764	760	73
180°	763	763	763	763	763	

TEST NUMBER: P1010804

CATALOG NUMBER: S123RDIP-B1000D585UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1653.7	1653.7	1653.7	1653.7	1653.7
2.5°	1660.4	1655.0	1638.9	1653.7	1651.0
5°	1653.7	1647.0	1630.9	1643.0	1640.3
7.5°	1641.6	1634.9	1614.8	1622.9	1618.8
10°	1625.5	1616.1	1592.0	1593.3	1586.6
12.5°	1602.7	1592.0	1561.2	1559.8	1551.8
15°	1577.3	1562.5	1524.9	1518.2	1508.8
17.5°	1546.4	1530.3	1483.4	1470.0	1456.5
20°	1511.5	1490.1	1439.1	1421.7	1405.6
22.5°	1472.6	1447.2	1392.2	1369.4	1354.6
25°	1435.1	1401.6	1339.9	1311.7	1296.9
27.5°	1389.5	1353.3	1286.2	1248.7	1225.9
30°	1342.5	1302.3	1227.2	1181.6	1160.1
32.5°	1295.6	1248.7	1168.2	1117.2	1094.4
35°	1242.0	1193.7	1110.5	1052.8	1028.7
37.5°	1188.3	1136.0	1048.8	984.4	954.9
40°	1137.3	1078.3	983.1	913.4	882.5
42.5°	1079.7	1020.7	921.4	843.6	816.8
45°	1020.7	960.3	857.0	780.6	748.4
47.5°	963.0	895.9	794.0	710.8	682.7
50°	898.6	835.6	726.9	643.8	612.9
52.5°	840.9	771.2	663.9	576.7	549.9
55°	775.2	709.5	595.5	517.7	490.9
57.5°	716.2	645.1	529.8	456.0	433.2
60°	654.5	580.7	469.4	397.0	374.2
62.5°	592.8	519.0	407.7	340.7	316.5
65°	529.8	456.0	351.4	285.7	270.9
67.5°	466.7	391.6	289.7	240.1	224.0
70°	405.0	332.6	238.7	191.8	177.0
72.5°	343.3	272.3	189.1	152.9	148.9
75°	280.3	215.9	142.2	128.8	126.1
77.5°	222.6	163.6	111.3	103.3	100.6
80°	167.6	112.7	84.5	80.5	77.8
82.5°	115.3	69.7	60.4	56.3	56.3
85°	71.1	41.6	37.6	34.9	34.9
87.5°	32.2	17.4	17.4	16.1	14.8
90°	0.6	6.2	13.6	15.9	17.0
92.5°	13.0	9.6	14.7	18.7	19.3
95°	34.6	11.3	17.6	21.5	21.5
97.5°	62.9	47.0	18.1	22.7	23.2
100°	95.8	107.1	18.7	23.2	23.8
102.5°	133.2	140.5	41.9	23.2	24.4
105°	168.9	175.1	124.1	23.8	24.9
107.5°	206.9	212.0	220.5	133.2	58.9
110°	244.8	249.4	255.6	236.9	155.8



TEST NUMBER: P1010804

CATALOG NUMBER: S123RDIP-B1000D585UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	281.1	285.1	291.3	296.4	295.3
115°	316.8	320.2	325.3	331.0	333.2
117.5°	351.9	355.9	358.7	363.3	363.8
120°	384.2	389.3	391.0	395.6	395.6
122.5°	417.1	421.1	423.3	426.2	426.7
125°	446.6	451.1	453.4	454.5	455.6
127.5°	476.0	480.6	483.4	485.1	484.0
130°	503.2	507.8	510.0	512.3	511.2
132.5°	529.3	533.9	535.6	537.8	536.1
135°	556.0	559.4	561.6	563.3	561.6
137.5°	578.6	583.2	584.3	587.1	586.0
140°	601.3	604.7	606.4	608.7	607.5
142.5°	622.3	625.7	627.4	629.1	627.4
145°	641.5	645.5	646.6	647.8	647.8
147.5°	660.2	663.1	664.2	665.3	662.5
150°	677.2	678.9	680.1	681.2	679.5
152.5°	692.5	693.1	693.7	695.9	693.1
155°	706.7	705.6	706.1	709.0	705.6
157.5°	718.0	718.0	717.5	720.9	716.3
160°	728.2	727.7	727.1	730.5	726.5
162.5°	737.9	736.2	735.6	739.6	736.2
165°	745.2	743.5	743.0	747.5	743.5
167.5°	751.5	749.2	749.2	753.7	749.2
170°	756.6	754.3	754.3	758.8	754.3
172.5°	760.0	757.1	757.7	762.2	757.1
175°	762.8	760.0	760.5	764.5	760.0
177.5°	763.9	761.1	761.7	766.2	760.5
180°	762.8	762.8	762.8	762.8	762.8

(END OF REPORT)