

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010806

Luminaire Tested: S123RDIP-B1000D585UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010806
REPORT IS A COMBINATION OF REPORTS P992852 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B1000D585UB2750-4F0-XX-W2A-F_3500K
Description: Define 3 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6142.0 lumens
Efficiency: N/A
Efficacy: 98.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 62.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010806

CATALOG NUMBER: S123RDIP-B1000D585UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1010806

CATALOG NUMBER: S123RDIP-B1000D585UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	67	67	67
1	101	97	93	89	94	91	87	84	79	77	75	69	67	66	60	58	57	57	57	53
2	92	85	79	74	86	80	74	70	70	66	63	61	58	56	53	51	49	49	49	45
3	84	75	68	62	79	70	64	59	62	57	53	54	51	47	47	44	42	42	42	38
4	77	67	59	53	72	63	56	50	56	50	46	49	44	41	43	39	37	37	37	33
5	71	60	51	45	66	56	49	44	50	44	40	44	39	36	39	35	32	32	32	29
6	66	54	46	40	61	51	43	38	45	39	35	40	35	32	35	31	28	28	28	26
7	61	49	41	35	57	46	39	34	41	35	31	36	32	28	32	28	25	25	25	23
8	57	44	37	31	53	42	35	30	38	32	28	33	29	25	30	26	23	23	23	21
9	53	41	33	28	50	39	32	27	35	29	25	31	26	23	27	24	21	21	21	19
10	49	37	30	25	46	35	29	24	32	26	23	29	24	21	25	22	19	19	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18034	18034	18034
5°	18063	17396	17349
10°	17922	16742	16411
15°	17688	15933	15385
20°	17384	15054	14239
25°	17069	14140	13153
30°	16664	13168	11868
35°	16249	12214	10698
40°	15859	11177	9406
45°	15356	10163	8244
50°	14804	9081	7042
55°	14231	7922	5939
60°	13683	6734	4821
65°	12974	5514	3763
70°	12086	4170	2690
75°	10803	2823	2130
80°	9218	1962	1494
85°	6916	1058	782

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15356 cd/sqm

TEST NUMBER: P1010806

CATALOG NUMBER: S123RDIP-B1000D585UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.5	2.6
10°-20°	438.1	7.1
20°-30°	630.8	10.3
30°-40°	710.4	11.6
40°-50°	679.5	11.1
50°-60°	556.3	9.1
60°-70°	375.0	6.1
70°-80°	188.1	3.1
80°-90°	50.7	0.8
90°-100°	27.2	0.4
100°-110°	131.7	2.1
110°-120°	322.8	5.3
120°-130°	409.8	6.7
130°-140°	437.8	7.1
140°-150°	409.4	6.7
150°-160°	330.2	5.4
160°-170°	213.1	3.5
170°-180°	73.4	1.2
0°-30°	1226.5	20.0
0°-40°	1936.9	31.5
0°-60°	3172.7	51.7
0°-90°	3786.6	61.7
90°-120°	481.8	7.8
90°-150°	1738.7	28.3
90°-180°	2355.0	38.3
0°-180°	6142.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1675	1675	1675	1675	1675	
5°	1675	1669	1652	1664	1662	159
15°	1598	1583	1545	1538	1529	450
25°	1454	1420	1357	1329	1314	669
35°	1258	1209	1125	1067	1042	788
45°	1034	973	868	791	758	798
55°	785	719	603	524	497	704
65°	537	462	356	289	274	531
75°	284	219	144	130	128	303
85°	72	42	38	35	35	79
90°	1	6	14	16	17	6
95°	35	12	18	22	22	42
105°	171	177	126	24	25	181
115°	321	324	330	335	338	317
125°	452	457	459	460	462	404
135°	563	567	569	571	569	434
145°	650	654	655	656	656	407
155°	716	715	715	718	715	330
165°	755	753	752	757	753	213
175°	773	770	770	774	770	74
180°	773	773	773	773	773	

TEST NUMBER: P1010806

CATALOG NUMBER: S123RDIP-B1000D585UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1675.4	1675.4	1675.4	1675.4	1675.4
2.5°	1682.2	1676.7	1660.4	1675.4	1672.7
5°	1675.4	1668.6	1652.3	1664.5	1661.8
7.5°	1663.2	1656.4	1636.0	1644.1	1640.1
10°	1646.9	1637.3	1612.9	1614.2	1607.4
12.5°	1623.8	1612.9	1581.6	1580.3	1572.1
15°	1597.9	1583.0	1544.9	1538.2	1528.6
17.5°	1566.7	1550.4	1502.8	1489.2	1475.6
20°	1531.4	1509.6	1458.0	1440.3	1424.0
22.5°	1492.0	1466.1	1410.4	1387.3	1372.4
25°	1453.9	1419.9	1357.4	1328.9	1314.0
27.5°	1407.7	1371.0	1303.1	1265.0	1241.9
30°	1360.1	1319.4	1243.3	1197.1	1175.4
32.5°	1312.6	1265.0	1183.5	1131.9	1108.8
35°	1258.2	1209.3	1125.1	1066.7	1042.2
37.5°	1203.9	1150.9	1062.6	997.4	967.5
40°	1152.3	1092.5	996.0	925.3	894.1
42.5°	1093.8	1034.0	933.5	854.7	827.5
45°	1034.0	972.9	868.3	790.8	758.2
47.5°	975.6	907.7	804.4	720.2	691.6
50°	910.4	846.5	736.5	652.2	621.0
52.5°	852.0	781.3	672.6	584.3	557.1
55°	785.4	718.8	603.3	524.5	497.3
57.5°	725.6	653.6	536.7	462.0	438.9
60°	663.1	588.4	475.6	402.2	379.1
62.5°	600.6	525.9	413.1	345.1	320.7
65°	536.7	462.0	356.0	289.4	274.5
67.5°	472.9	396.8	293.5	243.2	226.9
70°	410.4	337.0	241.9	194.3	179.4
72.5°	347.9	275.8	191.6	154.9	150.8
75°	284.0	218.8	144.0	130.4	127.7
77.5°	225.6	165.8	112.8	104.6	101.9
80°	169.8	114.1	85.6	81.5	78.8
82.5°	116.9	70.7	61.1	57.1	57.1
85°	72.0	42.1	38.0	35.3	35.3
87.5°	32.6	17.7	17.7	16.3	14.9
90°	0.6	6.3	13.8	16.1	17.2
92.5°	13.2	9.8	14.9	18.9	19.5
95°	35.0	11.5	17.8	21.8	21.8
97.5°	63.7	47.6	18.4	23.0	23.5
100°	97.0	108.5	18.9	23.5	24.1
102.5°	134.9	142.4	42.5	23.5	24.7
105°	171.1	177.4	125.7	24.1	25.3
107.5°	209.5	214.7	223.3	134.9	59.7
110°	248.0	252.6	258.9	239.9	157.9

TEST NUMBER: P1010806

CATALOG NUMBER: S123RDIP-B1000D585UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	284.7	288.7	295.0	300.2	299.1
115°	320.9	324.3	329.5	335.2	337.5
117.5°	356.5	360.5	363.4	368.0	368.5
120°	389.2	394.4	396.1	400.7	400.7
122.5°	422.5	426.5	428.8	431.7	432.2
125°	452.3	456.9	459.2	460.4	461.5
127.5°	482.2	486.8	489.6	491.4	490.2
130°	509.7	514.3	516.6	518.9	517.8
132.5°	536.1	540.7	542.5	544.8	543.0
135°	563.1	566.6	568.9	570.6	568.9
137.5°	586.1	590.7	591.8	594.7	593.5
140°	609.0	612.5	614.2	616.5	615.4
142.5°	630.3	633.7	635.4	637.2	635.4
145°	649.8	653.8	655.0	656.1	656.1
147.5°	668.7	671.6	672.8	673.9	671.0
150°	686.0	687.7	688.8	690.0	688.3
152.5°	701.5	702.0	702.6	704.9	702.0
155°	715.8	714.7	715.2	718.1	714.7
157.5°	727.3	727.3	726.7	730.2	725.6
160°	737.6	737.0	736.5	739.9	735.9
162.5°	747.4	745.7	745.1	749.1	745.7
165°	754.8	753.1	752.5	757.1	753.1
167.5°	761.2	758.9	758.9	763.5	758.9
170°	766.3	764.0	764.0	768.6	764.0
172.5°	769.8	766.9	767.5	772.1	766.9
175°	772.6	769.8	770.3	774.4	769.8
177.5°	773.8	770.9	771.5	776.1	770.3
180°	772.6	772.6	772.6	772.6	772.6

(END OF REPORT)