

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010521

Luminaire Tested: S123DIP-B1165D585UB2750-4F0-XX-W2A-D_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010521
REPORT IS A COMBINATION OF REPORTS P989515 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B1165D585UB2750-4F0-XX-W2A-D_3500K
Description: Define 3 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7238.0 lumens
Efficiency: N/A
Efficacy: 94.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.25 / 1.37
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 76.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010521

CATALOG NUMBER: S123DIP-B1165D585UB2750-4F0-XX-W2A-D_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1010521

CATALOG NUMBER: S123DIP-B1165D585UB2750-4F0-XX-W2A-D_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67
1	99	94	90	86	93	88	84	81	77	74	71	67	64	62	57	56	54
2	90	82	75	69	84	76	70	65	67	62	58	58	54	51	50	47	44
3	82	71	63	57	76	67	60	54	58	53	48	51	46	43	44	40	37
4	74	63	54	48	69	59	51	45	52	46	41	45	40	36	39	35	32
5	68	56	47	41	64	53	45	39	46	40	35	40	35	31	35	31	28
6	63	50	42	35	59	47	39	34	42	35	30	36	31	27	31	27	24
7	58	45	37	31	54	43	35	30	38	31	27	33	28	24	29	25	21
8	54	41	33	27	50	39	31	26	34	28	24	30	25	21	26	22	19
9	50	37	30	24	47	35	28	23	31	25	21	28	23	19	24	20	17
10	47	34	27	22	44	33	26	21	29	23	19	26	21	17	23	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15632	15632	15632
5°	15675	15174	15162
10°	15529	14763	14650
15°	15323	14310	14108
20°	15032	13803	13526
25°	14672	13234	12922
30°	14306	12718	12317
35°	13893	12177	11822
40°	13500	11682	11301
45°	13063	11204	10872
50°	12632	10728	10406
55°	12154	10242	9976
60°	11687	9744	9537
65°	11204	9214	9022
70°	10484	8617	8492
75°	9567	7939	7945
80°	8502	7252	7320
85°	7444	6697	6873

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13063 cd/sqm

TEST NUMBER: P1010521

CATALOG NUMBER: S123DIP-B1165D585UB2750-4F0-XX-W2A-D_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	137.8	1.9
10°-20°	392.8	5.4
20°-30°	587.3	8.1
30°-40°	701.2	9.7
40°-50°	733.7	10.1
50°-60°	688.5	9.5
60°-70°	575.1	7.9
70°-80°	411.2	5.7
80°-90°	246.2	3.4
90°-100°	181.0	2.5
100°-110°	244.8	3.4
110°-120°	398.3	5.5
120°-130°	452.8	6.3
130°-140°	457.1	6.3
140°-150°	413.4	5.7
150°-160°	330.2	4.6
160°-170°	213.1	2.9
170°-180°	73.4	1.0
0°-30°	1117.9	15.4
0°-40°	1819.1	25.1
0°-60°	3241.3	44.8
0°-90°	4473.9	61.8
90°-120°	824.0	11.4
90°-150°	2147.4	29.7
90°-180°	2764.0	38.2
0°-180°	7238.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1452	1452	1452	1452	1452	
5°	1454	1451	1441	1454	1452	138
15°	1384	1389	1388	1403	1402	390
25°	1250	1266	1270	1291	1291	576
35°	1076	1101	1122	1145	1152	673
45°	880	918	957	987	1000	678
55°	671	723	780	823	835	601
65°	464	525	595	642	658	458
75°	252	326	405	457	476	269
85°	78	157	240	294	310	80
90°	21	104	193	249	266	17
95°	52	91	174	228	243	55
105°	184	228	244	187	202	194
115°	329	351	413	457	472	325
125°	457	462	510	544	556	409
135°	566	568	588	618	624	436
145°	651	654	655	669	675	407
155°	716	715	715	718	715	330
165°	755	753	752	757	753	213
175°	773	770	770	774	770	74
180°	773	773	773	773	773	

TEST NUMBER: P1010521

CATALOG NUMBER: S123DIP-B1165D585UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1452.3	1452.3	1452.3	1452.3	1452.3
2.5°	1460.3	1455.5	1442.8	1455.5	1453.9
5°	1453.9	1450.8	1441.3	1453.9	1452.3
7.5°	1442.8	1442.8	1433.4	1449.2	1447.6
10°	1427.0	1430.2	1422.3	1438.1	1434.9
12.5°	1408.0	1412.8	1408.0	1422.3	1419.1
15°	1384.3	1389.1	1387.5	1403.3	1401.7
17.5°	1355.8	1365.3	1363.7	1378.0	1374.8
20°	1324.2	1333.7	1336.8	1351.1	1352.7
22.5°	1291.0	1300.5	1305.2	1324.2	1322.6
25°	1249.8	1265.7	1270.4	1291.0	1291.0
27.5°	1210.3	1227.7	1237.2	1254.6	1256.2
30°	1167.6	1188.1	1200.8	1219.8	1219.8
32.5°	1120.1	1143.8	1161.2	1181.8	1186.6
35°	1075.8	1101.1	1121.7	1145.4	1151.7
37.5°	1028.3	1056.8	1080.6	1107.4	1112.2
40°	980.9	1009.4	1041.0	1067.9	1074.2
42.5°	928.7	965.1	998.3	1028.3	1037.8
45°	879.6	917.6	957.2	987.2	999.9
47.5°	827.4	870.1	914.4	947.7	957.2
50°	776.8	821.1	870.1	906.5	917.6
52.5°	723.0	770.5	825.8	863.8	878.0
55°	670.8	723.0	780.0	822.7	835.3
57.5°	620.2	674.0	735.7	778.4	792.6
60°	566.4	623.3	688.2	732.5	749.9
62.5°	515.8	574.3	643.9	688.2	704.0
65°	463.5	525.2	594.9	642.3	658.1
67.5°	411.3	476.2	545.8	598.0	610.7
70°	356.0	424.0	499.9	550.6	566.4
72.5°	305.3	373.4	452.5	504.7	520.5
75°	251.5	325.9	405.0	457.2	476.2
77.5°	205.7	280.0	359.1	414.5	428.7
80°	156.6	234.1	316.4	370.2	386.0
82.5°	113.9	193.0	276.9	330.7	346.5
85°	77.5	156.6	240.5	294.3	310.1
87.5°	47.5	126.6	207.3	261.0	276.9
90°	21.2	104.4	192.6	248.7	265.6
92.5°	32.2	96.8	181.0	237.2	252.1
95°	52.4	90.6	174.4	227.5	243.3
97.5°	79.5	120.4	165.5	217.6	233.9
100°	111.2	173.4	156.5	207.0	223.4
102.5°	147.6	199.4	170.6	195.9	213.0
105°	183.8	228.0	244.4	187.1	202.5
107.5°	220.6	259.0	332.5	286.8	225.8
110°	257.5	290.6	360.2	382.3	312.9



TEST NUMBER: P1010521

CATALOG NUMBER: S123DIP-B1165D585UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	294.2	320.3	386.8	431.5	444.7
115°	328.8	351.2	413.3	457.0	472.0
117.5°	364.4	381.1	437.8	480.3	493.5
120°	395.5	408.6	462.5	503.5	514.6
122.5°	428.8	436.0	487.3	525.0	536.6
125°	457.0	461.6	509.8	544.2	556.4
127.5°	486.9	490.0	532.3	565.8	575.6
130°	514.4	517.5	551.4	583.8	592.2
132.5°	539.3	543.9	569.4	600.2	609.4
135°	566.3	568.2	587.9	618.1	624.3
137.5°	589.3	592.3	604.5	632.7	639.4
140°	610.6	614.1	620.5	646.6	653.4
142.5°	631.9	633.7	635.4	657.8	663.9
145°	651.4	653.8	655.0	668.8	675.1
147.5°	668.7	671.6	672.8	678.6	682.1
150°	686.0	687.7	688.8	690.0	691.5
152.5°	701.5	702.0	702.6	704.9	702.0
155°	715.8	714.7	715.2	718.1	714.7
157.5°	727.3	727.3	726.7	730.2	725.6
160°	737.6	737.0	736.5	739.9	735.9
162.5°	747.4	745.7	745.1	749.1	745.7
165°	754.8	753.1	752.5	757.1	753.1
167.5°	761.2	758.9	758.9	763.5	758.9
170°	766.3	764.0	764.0	768.6	764.0
172.5°	769.8	766.9	767.5	772.1	766.9
175°	772.6	769.8	770.3	774.4	769.8
177.5°	773.8	770.9	771.5	776.1	770.3
180°	772.6	772.6	772.6	772.6	772.6

(END OF REPORT)