

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010535

Luminaire Tested: S123DIP-B1165D805UB2750-4F0-XX-W2A-D_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010535
REPORT IS A COMBINATION OF REPORTS P989574 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B1165D805UB2750-4F0-XX-W2A-D_3000K
Description: Define 3 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7995.0 lumens
Efficiency: N/A
Efficacy: 97.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.25 / 1.37
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 82.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010535

CATALOG NUMBER: S123DIP-B1165D805UB2750-4F0-XX-W2A-D_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010535

CATALOG NUMBER: S123DIP-B1165D805UB2750-4F0-XX-W2A-D_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	73	73	73	61	61	61
1	98	93	89	85	91	86	83	79	74	71	69	63	61	59	52	51	49
2	89	81	74	68	82	75	69	64	64	60	56	54	51	48	45	43	41
3	81	70	63	56	74	66	59	53	56	51	47	48	44	40	40	37	34
4	74	62	54	47	68	58	50	45	50	44	39	42	38	34	35	32	29
5	67	55	47	40	62	52	44	38	44	38	34	38	33	29	32	28	25
6	62	49	41	35	57	46	39	33	40	34	29	34	29	26	29	25	22
7	57	45	36	31	53	42	34	29	36	30	26	31	26	23	26	22	20
8	53	40	32	27	49	38	31	26	33	27	23	28	24	20	24	20	17
9	50	37	29	24	46	35	28	23	30	24	20	26	21	18	22	18	16
10	46	34	26	21	43	32	25	20	28	22	18	24	20	16	21	17	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15566	15566	15566
5°	15608	15109	15097
10°	15462	14700	14588
15°	15258	14248	14048
20°	14967	13744	13467
25°	14610	13176	12866
30°	14243	12663	12263
35°	13834	12125	11772
40°	13442	11631	11252
45°	13007	11155	10825
50°	12578	10683	10361
55°	12102	10197	9933
60°	11636	9701	9496
65°	11159	9174	8984
70°	10437	8581	8455
75°	9529	7906	7911
80°	8469	7223	7290
85°	7415	6667	6844

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13007 cd/sqm

TEST NUMBER: P1010535

CATALOG NUMBER: S123DIP-B1165D805UB2750-4F0-XX-W2A-D_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	137.2	1.7
10°-20°	391.1	4.9
20°-30°	584.8	7.3
30°-40°	698.2	8.7
40°-50°	730.6	9.1
50°-60°	685.6	8.6
60°-70°	572.6	7.2
70°-80°	409.5	5.1
80°-90°	245.7	3.1
90°-100°	189.4	2.4
100°-110°	287.7	3.6
110°-120°	504.5	6.3
120°-130°	587.9	7.4
130°-140°	601.5	7.5
140°-150°	548.5	6.9
150°-160°	439.2	5.5
160°-170°	283.4	3.5
170°-180°	97.7	1.2
0°-30°	1113.0	13.9
0°-40°	1811.3	22.7
0°-60°	3227.4	40.4
0°-90°	4455.2	55.7
90°-120°	981.6	12.3
90°-150°	2719.6	34.0
90°-180°	3540.0	44.3
0°-180°	7995.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1446	1446	1446	1446	1446	
5°	1448	1444	1435	1448	1446	137
15°	1378	1383	1382	1397	1396	388
25°	1244	1260	1265	1285	1285	574
35°	1071	1096	1117	1140	1147	670
45°	876	914	953	983	996	675
55°	668	720	777	819	832	598
65°	462	523	592	640	655	456
75°	250	324	403	455	474	268
85°	77	156	239	293	309	79
90°	21	106	196	253	270	17
95°	64	94	180	234	250	69
105°	240	286	285	194	210	254
115°	435	458	522	567	583	430
125°	606	612	661	696	708	542
135°	752	755	776	806	812	579
145°	866	870	871	885	892	542
155°	952	951	951	955	951	439
165°	1004	1002	1001	1007	1002	284
175°	1028	1024	1025	1030	1024	98
180°	1028	1028	1028	1028	1028	

TEST NUMBER: P1010535

CATALOG NUMBER: S123DIP-B1165D805UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1446.1	1446.1	1446.1	1446.1	1446.1
2.5°	1454.0	1449.2	1436.6	1449.2	1447.7
5°	1447.7	1444.5	1435.1	1447.7	1446.1
7.5°	1436.6	1436.6	1427.2	1442.9	1441.4
10°	1420.9	1424.0	1416.2	1431.9	1428.8
12.5°	1402.0	1406.7	1402.0	1416.2	1413.0
15°	1378.4	1383.1	1381.5	1397.3	1395.7
17.5°	1350.0	1359.5	1357.9	1372.1	1368.9
20°	1318.5	1327.9	1331.1	1345.3	1346.8
22.5°	1285.4	1294.9	1299.6	1318.5	1316.9
25°	1244.5	1260.2	1264.9	1285.4	1285.4
27.5°	1205.1	1222.4	1231.9	1249.2	1250.8
30°	1162.5	1183.0	1195.6	1214.5	1214.5
32.5°	1115.3	1138.9	1156.2	1176.7	1181.4
35°	1071.2	1096.4	1116.9	1140.5	1146.8
37.5°	1023.9	1052.3	1075.9	1102.7	1107.4
40°	976.7	1005.0	1036.5	1063.3	1069.6
42.5°	924.7	960.9	994.0	1023.9	1033.4
45°	875.8	913.7	953.0	983.0	995.6
47.5°	823.9	866.4	910.5	943.6	953.0
50°	773.5	817.6	866.4	902.6	913.7
52.5°	719.9	767.2	822.3	860.1	874.3
55°	667.9	719.9	776.6	819.1	831.7
57.5°	617.5	671.1	732.5	775.0	789.2
60°	563.9	620.7	685.2	729.3	746.7
62.5°	513.5	571.8	641.1	685.2	701.0
65°	461.6	523.0	592.3	639.6	655.3
67.5°	409.6	474.2	543.5	595.4	608.1
70°	354.4	422.2	497.8	548.2	563.9
72.5°	304.0	371.8	450.5	502.5	518.3
75°	250.5	324.5	403.3	455.3	474.2
77.5°	204.8	278.8	357.6	412.7	426.9
80°	156.0	233.1	315.1	368.6	384.4
82.5°	113.4	192.2	275.7	329.2	345.0
85°	77.2	156.0	239.4	293.0	308.8
87.5°	47.3	126.0	206.4	259.9	275.7
90°	21.3	106.1	196.3	253.0	270.2
92.5°	36.5	99.6	185.3	242.6	257.6
95°	63.9	94.1	179.7	233.8	249.5
97.5°	100.5	135.9	170.9	224.3	240.8
100°	143.2	208.9	162.2	214.0	230.6
102.5°	192.0	246.0	184.1	203.0	220.3
105°	240.1	286.3	285.3	194.4	210.0
107.5°	289.7	329.6	405.7	330.6	244.8
110°	339.3	373.7	445.1	460.9	364.4

TEST NUMBER: P1010535

CATALOG NUMBER: S123DIP-B1165D805UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	388.2	415.5	483.8	530.0	542.7
115°	434.7	458.2	521.7	567.2	582.8
117.5°	482.0	500.0	557.3	601.2	614.6
120°	524.0	538.7	593.0	635.3	646.3
122.5°	568.2	576.8	628.6	667.1	678.9
125°	606.3	612.4	661.2	695.8	708.4
127.5°	646.0	650.6	693.8	727.6	737.1
130°	682.7	687.3	721.9	754.8	762.7
132.5°	716.3	722.4	748.3	779.7	788.5
135°	752.2	755.2	775.5	806.2	811.7
137.5°	782.7	787.2	799.8	828.8	835.2
140°	811.7	816.3	823.2	849.9	856.3
142.5°	839.9	842.9	845.2	868.0	873.6
145°	865.9	869.6	871.2	885.3	891.6
147.5°	889.5	893.3	894.8	901.1	903.5
150°	912.4	914.7	916.2	917.7	918.6
152.5°	933.0	933.8	934.5	937.6	933.8
155°	952.1	950.6	951.3	955.1	950.6
157.5°	967.4	967.4	966.6	971.2	965.1
160°	981.1	980.3	979.6	984.2	978.8
162.5°	994.1	991.8	991.0	996.4	991.8
165°	1004.0	1001.7	1001.0	1007.1	1001.7
167.5°	1012.4	1009.3	1009.3	1015.5	1009.3
170°	1019.3	1016.2	1016.2	1022.3	1016.2
172.5°	1023.9	1020.0	1020.8	1026.9	1020.0
175°	1027.7	1023.9	1024.6	1030.0	1023.9
177.5°	1029.2	1025.4	1026.1	1032.3	1024.6
180°	1027.7	1027.7	1027.7	1027.7	1027.7

(END OF REPORT)