

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010536

Luminaire Tested: S123DIP-B1165D805UB2750-4F0-XX-W2A-D_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010536
REPORT IS A COMBINATION OF REPORTS P989575 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B1165D805UB2750-4F0-XX-W2A-D_3500K
Description: Define 3 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8030.0 lumens
Efficiency: N/A
Efficacy: 97.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.25 / 1.37
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 82.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010536

CATALOG NUMBER: S123DIP-B1165D805UB2750-4F0-XX-W2A-D_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1010536

CATALOG NUMBER: S123DIP-B1165D805UB2750-4F0-XX-W2A-D_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	73	73	73	61	61	61
1	98	93	89	85	91	86	83	79	74	71	69	63	61	59	52	51	49
2	89	81	74	68	82	75	69	64	64	60	56	54	51	48	45	43	41
3	81	70	63	56	74	66	59	53	56	51	47	48	44	40	40	37	34
4	74	62	54	47	68	58	50	45	50	44	39	42	38	34	35	32	29
5	67	55	47	40	62	52	44	38	44	38	34	38	33	29	32	28	25
6	62	49	41	35	57	46	39	33	40	34	29	34	29	26	29	25	22
7	57	45	36	31	53	42	34	29	36	30	26	31	26	23	26	22	20
8	53	40	32	27	49	38	31	26	33	27	23	28	24	20	24	20	17
9	50	37	29	24	46	35	28	23	30	24	20	26	21	18	22	18	16
10	46	34	26	21	43	32	25	20	28	22	18	24	20	16	21	17	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15632	15632	15632
5°	15675	15174	15162
10°	15529	14763	14650
15°	15323	14310	14108
20°	15032	13803	13526
25°	14672	13234	12922
30°	14306	12718	12317
35°	13893	12177	11822
40°	13500	11682	11301
45°	13063	11204	10872
50°	12632	10728	10406
55°	12154	10242	9976
60°	11687	9744	9537
65°	11204	9214	9022
70°	10484	8617	8492
75°	9567	7939	7945
80°	8502	7252	7320
85°	7444	6697	6873

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13063 cd/sqm

TEST NUMBER: P1010536

CATALOG NUMBER: S123DIP-B1165D805UB2750-4F0-XX-W2A-D_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	137.8	1.7
10°-20°	392.8	4.9
20°-30°	587.3	7.3
30°-40°	701.2	8.7
40°-50°	733.7	9.1
50°-60°	688.5	8.6
60°-70°	575.1	7.2
70°-80°	411.2	5.1
80°-90°	246.8	3.1
90°-100°	190.1	2.4
100°-110°	289.0	3.6
110°-120°	506.8	6.3
120°-130°	590.5	7.4
130°-140°	604.2	7.5
140°-150°	551.0	6.9
150°-160°	441.2	5.5
160°-170°	284.7	3.5
170°-180°	98.1	1.2
0°-30°	1117.9	13.9
0°-40°	1819.1	22.7
0°-60°	3241.3	40.4
0°-90°	4474.4	55.7
90°-120°	985.9	12.3
90°-150°	2731.6	34.0
90°-180°	3556.0	44.3
0°-180°	8030.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1452	1452	1452	1452	1452	
5°	1454	1451	1441	1454	1452	138
15°	1384	1389	1388	1403	1402	390
25°	1250	1266	1270	1291	1291	576
35°	1076	1101	1122	1145	1152	673
45°	880	918	957	987	1000	678
55°	671	723	780	823	835	601
65°	464	525	595	642	658	458
75°	252	326	405	457	476	269
85°	78	157	240	294	310	80
90°	21	106	197	254	271	17
95°	64	94	180	235	251	69
105°	241	288	287	195	211	255
115°	437	460	524	570	585	432
125°	609	615	664	699	712	545
135°	756	758	779	810	815	582
145°	870	874	875	889	896	544
155°	956	955	956	959	955	441
165°	1008	1006	1005	1012	1006	285
175°	1032	1028	1029	1035	1028	98
180°	1032	1032	1032	1032	1032	

TEST NUMBER: P1010536

CATALOG NUMBER: S123DIP-B1165D805UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1452.3	1452.3	1452.3	1452.3	1452.3
2.5°	1460.3	1455.5	1442.8	1455.5	1453.9
5°	1453.9	1450.8	1441.3	1453.9	1452.3
7.5°	1442.8	1442.8	1433.4	1449.2	1447.6
10°	1427.0	1430.2	1422.3	1438.1	1434.9
12.5°	1408.0	1412.8	1408.0	1422.3	1419.1
15°	1384.3	1389.1	1387.5	1403.3	1401.7
17.5°	1355.8	1365.3	1363.7	1378.0	1374.8
20°	1324.2	1333.7	1336.8	1351.1	1352.7
22.5°	1291.0	1300.5	1305.2	1324.2	1322.6
25°	1249.8	1265.7	1270.4	1291.0	1291.0
27.5°	1210.3	1227.7	1237.2	1254.6	1256.2
30°	1167.6	1188.1	1200.8	1219.8	1219.8
32.5°	1120.1	1143.8	1161.2	1181.8	1186.6
35°	1075.8	1101.1	1121.7	1145.4	1151.7
37.5°	1028.3	1056.8	1080.6	1107.4	1112.2
40°	980.9	1009.4	1041.0	1067.9	1074.2
42.5°	928.7	965.1	998.3	1028.3	1037.8
45°	879.6	917.6	957.2	987.2	999.9
47.5°	827.4	870.1	914.4	947.7	957.2
50°	776.8	821.1	870.1	906.5	917.6
52.5°	723.0	770.5	825.8	863.8	878.0
55°	670.8	723.0	780.0	822.7	835.3
57.5°	620.2	674.0	735.7	778.4	792.6
60°	566.4	623.3	688.2	732.5	749.9
62.5°	515.8	574.3	643.9	688.2	704.0
65°	463.5	525.2	594.9	642.3	658.1
67.5°	411.3	476.2	545.8	598.0	610.7
70°	356.0	424.0	499.9	550.6	566.4
72.5°	305.3	373.4	452.5	504.7	520.5
75°	251.5	325.9	405.0	457.2	476.2
77.5°	205.7	280.0	359.1	414.5	428.7
80°	156.6	234.1	316.4	370.2	386.0
82.5°	113.9	193.0	276.9	330.7	346.5
85°	77.5	156.6	240.5	294.3	310.1
87.5°	47.5	126.6	207.3	261.0	276.9
90°	21.4	106.5	197.2	254.1	271.4
92.5°	36.6	100.0	186.0	243.6	258.7
95°	64.2	94.4	180.4	234.8	250.6
97.5°	100.9	136.5	171.6	225.3	241.8
100°	143.8	209.8	162.9	214.9	231.5
102.5°	192.9	247.2	184.9	203.8	221.3
105°	241.2	287.6	286.7	195.2	210.9
107.5°	291.0	331.1	407.5	332.1	245.9
110°	340.8	375.4	447.2	463.0	365.9



TEST NUMBER: P1010536

CATALOG NUMBER: S123DIP-B1165D805UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	389.9	417.4	486.0	532.4	545.2
115°	436.6	460.2	524.0	569.7	585.4
117.5°	484.2	502.2	559.9	603.9	617.4
120°	526.3	541.1	595.6	638.1	649.2
122.5°	570.7	579.3	631.4	670.0	681.9
125°	609.0	615.2	664.1	698.9	711.5
127.5°	648.9	653.5	696.9	730.9	740.3
130°	685.7	690.4	725.0	758.2	766.2
132.5°	719.5	725.6	751.6	783.2	791.9
135°	755.5	758.5	779.0	809.8	815.4
137.5°	786.2	790.8	803.4	832.5	838.9
140°	815.3	819.9	826.9	853.8	860.1
142.5°	843.7	846.7	849.0	871.9	877.5
145°	869.7	873.5	875.0	889.3	895.6
147.5°	893.5	897.3	898.8	905.1	907.6
150°	916.5	918.8	920.3	921.8	922.7
152.5°	937.2	937.9	938.7	941.8	937.9
155°	956.3	954.8	955.6	959.4	954.8
157.5°	971.7	971.7	970.9	975.5	969.4
160°	985.5	984.7	983.9	988.5	983.2
162.5°	998.5	996.2	995.5	1000.8	996.2
165°	1008.5	1006.2	1005.4	1011.6	1006.2
167.5°	1016.9	1013.9	1013.9	1020.0	1013.9
170°	1023.8	1020.8	1020.8	1026.9	1020.8
172.5°	1028.4	1024.6	1025.4	1031.5	1024.6
175°	1032.3	1028.4	1029.2	1034.6	1028.4
177.5°	1033.8	1030.0	1030.7	1036.9	1029.2
180°	1032.3	1032.3	1032.3	1032.3	1032.3

(END OF REPORT)