

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010854

Luminaire Tested: S123RDIP-B1165D585UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010854
REPORT IS A COMBINATION OF REPORTS P993050 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B1165D585UB2750-4F0-XX-W2A-F_2700K
Description: Define 3 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6678.0 lumens
Efficiency: N/A
Efficacy: 87.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 76.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010854

CATALOG NUMBER: S123RDIP-B1165D585UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1010854

CATALOG NUMBER: S123RDIP-B1165D585UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	111	111	111	111	104	104	104	104	92	92	92	80	80	80	70	70	70	65		
1	102	97	94	90	95	92	88	85	81	79	76	72	70	68	63	61	60	56		
2	93	86	79	74	87	81	75	71	72	68	64	63	60	57	56	53	51	47		
3	85	76	68	62	80	71	65	60	64	59	54	56	52	49	50	47	44	41		
4	78	67	59	53	73	64	57	51	57	51	47	51	46	42	45	41	38	35		
5	72	60	52	46	67	57	50	44	51	45	41	46	41	37	40	37	34	31		
6	66	54	46	40	62	51	44	39	46	40	36	41	36	33	37	33	30	27		
7	62	49	41	36	58	47	39	34	42	36	32	38	33	29	34	30	27	24		
8	57	45	37	32	54	43	36	31	39	33	28	35	30	26	31	27	24	22		
9	53	41	34	28	50	39	32	27	35	30	26	32	27	24	29	25	22	20		
10	50	38	31	26	47	36	29	25	33	27	23	30	25	22	27	23	20	18		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	20730	20730	20730
5°	20764	19997	19943
10°	20601	19245	18866
15°	20334	18316	17686
20°	19983	17305	16368
25°	19621	16255	15119
30°	19156	15137	13642
35°	18679	14040	12298
40°	18230	12848	10813
45°	17654	11683	9477
50°	17017	10438	8094
55°	16358	9106	6828
60°	15727	7740	5542
65°	14915	6338	4325
70°	13891	4792	3092
75°	12420	3246	2449
80°	10597	2255	1718
85°	7953	1217	900

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17654 cd/sqm

TEST NUMBER: P1010854

CATALOG NUMBER: S123RDIP-B1165D585UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	181.0	2.7
10°-20°	503.7	7.5
20°-30°	725.2	10.9
30°-40°	816.6	12.2
40°-50°	781.2	11.7
50°-60°	639.4	9.6
60°-70°	431.1	6.5
70°-80°	216.2	3.2
80°-90°	58.1	0.9
90°-100°	26.9	0.4
100°-110°	130.1	1.9
110°-120°	318.7	4.8
120°-130°	404.6	6.1
130°-140°	432.2	6.5
140°-150°	404.2	6.1
150°-160°	326.0	4.9
160°-170°	210.4	3.2
170°-180°	72.5	1.1
0°-30°	1409.9	21.1
0°-40°	2226.5	33.3
0°-60°	3647.1	54.6
0°-90°	4352.5	65.2
90°-120°	475.6	7.1
90°-150°	1716.6	25.7
90°-180°	2325.0	34.8
0°-180°	6678.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1926	1926	1926	1926	1926	
5°	1926	1918	1899	1913	1910	183
15°	1837	1820	1776	1768	1757	518
25°	1671	1632	1560	1528	1510	769
35°	1446	1390	1293	1226	1198	905
45°	1189	1118	998	909	872	917
55°	903	826	694	603	572	810
65°	617	531	409	333	316	611
75°	326	252	166	150	147	348
85°	83	48	44	41	41	91
90°	1	6	14	16	17	7
95°	35	11	18	22	22	41
105°	169	175	124	24	25	179
115°	317	320	325	331	333	313
125°	447	451	453	454	456	399
135°	556	559	562	563	562	428
145°	642	646	647	648	648	402
155°	707	706	706	709	706	326
165°	745	744	743	748	744	211
175°	763	760	760	764	760	73
180°	763	763	763	763	763	

TEST NUMBER: P1010854

CATALOG NUMBER: S123RDIP-B1165D585UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1925.9	1925.9	1925.9	1925.9	1925.9
2.5°	1933.7	1927.5	1908.7	1925.9	1922.8
5°	1925.9	1918.1	1899.4	1913.4	1910.3
7.5°	1911.9	1904.1	1880.6	1890.0	1885.3
10°	1893.1	1882.2	1854.1	1855.6	1847.8
12.5°	1866.6	1854.1	1818.1	1816.6	1807.2
15°	1836.9	1819.7	1776.0	1768.2	1757.2
17.5°	1801.0	1782.2	1727.6	1711.9	1696.3
20°	1760.4	1735.4	1676.0	1655.7	1637.0
22.5°	1715.1	1685.4	1621.3	1594.8	1577.6
25°	1671.3	1632.3	1560.4	1527.6	1510.4
27.5°	1618.2	1576.0	1497.9	1454.2	1427.7
30°	1563.5	1516.7	1429.2	1376.1	1351.1
32.5°	1508.9	1454.2	1360.5	1301.1	1274.6
35°	1446.4	1390.2	1293.3	1226.2	1198.0
37.5°	1383.9	1323.0	1221.5	1146.5	1112.1
40°	1324.6	1255.8	1144.9	1063.7	1027.8
42.5°	1257.4	1188.7	1073.1	982.5	951.2
45°	1188.7	1118.4	998.1	909.1	871.6
47.5°	1121.5	1043.4	924.7	827.8	795.0
50°	1046.5	973.1	846.6	749.8	713.8
52.5°	979.4	898.1	773.2	671.7	640.4
55°	902.8	826.3	693.5	602.9	571.7
57.5°	834.1	751.3	617.0	531.1	504.5
60°	762.2	676.3	546.7	462.3	435.8
62.5°	690.4	604.5	474.8	396.7	368.6
65°	617.0	531.1	409.2	332.7	315.5
67.5°	543.6	456.1	337.4	279.6	260.9
70°	471.7	387.4	278.0	223.4	206.2
72.5°	399.9	317.1	220.2	178.1	173.4
75°	326.5	251.5	165.6	150.0	146.8
77.5°	259.3	190.6	129.6	120.3	117.1
80°	195.2	131.2	98.4	93.7	90.6
82.5°	134.3	81.2	70.3	65.6	65.6
85°	82.8	48.4	43.7	40.6	40.6
87.5°	37.5	20.3	20.3	18.7	17.2
90°	0.6	6.2	13.6	15.9	17.0
92.5°	13.0	9.6	14.7	18.7	19.3
95°	34.6	11.3	17.6	21.5	21.5
97.5°	62.9	47.0	18.1	22.7	23.2
100°	95.8	107.1	18.7	23.2	23.8
102.5°	133.2	140.5	41.9	23.2	24.4
105°	168.9	175.1	124.1	23.8	24.9
107.5°	206.9	212.0	220.5	133.2	58.9
110°	244.8	249.4	255.6	236.9	155.8

TEST NUMBER: P1010854

CATALOG NUMBER: S123RDIP-B1165D585UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	281.1	285.1	291.3	296.4	295.3
115°	316.8	320.2	325.3	331.0	333.2
117.5°	351.9	355.9	358.7	363.3	363.8
120°	384.2	389.3	391.0	395.6	395.6
122.5°	417.1	421.1	423.3	426.2	426.7
125°	446.6	451.1	453.4	454.5	455.6
127.5°	476.0	480.6	483.4	485.1	484.0
130°	503.2	507.8	510.0	512.3	511.2
132.5°	529.3	533.9	535.6	537.8	536.1
135°	556.0	559.4	561.6	563.3	561.6
137.5°	578.6	583.2	584.3	587.1	586.0
140°	601.3	604.7	606.4	608.7	607.5
142.5°	622.3	625.7	627.4	629.1	627.4
145°	641.5	645.5	646.6	647.8	647.8
147.5°	660.2	663.1	664.2	665.3	662.5
150°	677.2	678.9	680.1	681.2	679.5
152.5°	692.5	693.1	693.7	695.9	693.1
155°	706.7	705.6	706.1	709.0	705.6
157.5°	718.0	718.0	717.5	720.9	716.3
160°	728.2	727.7	727.1	730.5	726.5
162.5°	737.9	736.2	735.6	739.6	736.2
165°	745.2	743.5	743.0	747.5	743.5
167.5°	751.5	749.2	749.2	753.7	749.2
170°	756.6	754.3	754.3	758.8	754.3
172.5°	760.0	757.1	757.7	762.2	757.1
175°	762.8	760.0	760.5	764.5	760.0
177.5°	763.9	761.1	761.7	766.2	760.5
180°	762.8	762.8	762.8	762.8	762.8

(END OF REPORT)