

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010855

Luminaire Tested: S123RDIP-B1165D585UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010855
REPORT IS A COMBINATION OF REPORTS P993051 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B1165D585UB2750-4F0-XX-W2A-F_3000K
Description: Define 3 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6735.0 lumens
Efficiency: N/A
Efficacy: 87.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 76.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010855

CATALOG NUMBER: S123RDIP-B1165D585UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010855

CATALOG NUMBER: S123RDIP-B1165D585UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	111	111	111	111	104	104	104	104	92	92	92	80	80	80	70	70	70	65		
1	102	97	94	90	95	92	88	85	81	79	76	72	70	68	63	61	60	56		
2	93	86	79	74	87	81	75	71	72	68	64	63	60	57	56	53	51	47		
3	85	76	68	62	80	71	65	60	64	59	54	56	52	49	50	47	44	41		
4	78	67	59	53	73	64	57	51	57	51	47	51	46	42	45	41	38	35		
5	72	60	52	46	67	57	50	44	51	45	41	46	41	37	40	37	34	31		
6	66	54	46	40	62	51	44	39	46	40	36	41	36	33	37	33	30	27		
7	62	49	41	36	58	47	39	34	42	36	32	38	33	29	34	30	27	24		
8	57	45	37	32	54	43	36	31	39	33	28	35	30	26	31	27	24	22		
9	53	41	34	28	50	39	32	27	35	30	26	32	27	24	29	25	22	20		
10	50	38	31	26	47	36	29	25	33	27	23	30	25	22	27	23	20	18		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	20907	20907	20907
5°	20941	20167	20112
10°	20776	19408	19026
15°	20506	18472	17837
20°	20152	17453	16507
25°	19787	16393	15248
30°	19319	15266	13759
35°	18838	14159	12402
40°	18384	12958	10904
45°	17804	11782	9558
50°	17162	10527	8164
55°	16498	9184	6885
60°	15862	7805	5589
65°	15041	6392	4362
70°	14009	4834	3117
75°	12523	3274	2471
80°	10690	2274	1733
85°	8021	1228	909

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17804 cd/sqm

TEST NUMBER: P1010855

CATALOG NUMBER: S123RDIP-B1165D585UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	182.6	2.7
10°-20°	507.9	7.5
20°-30°	731.3	10.9
30°-40°	823.6	12.2
40°-50°	787.8	11.7
50°-60°	644.9	9.6
60°-70°	434.8	6.5
70°-80°	218.1	3.2
80°-90°	58.6	0.9
90°-100°	27.1	0.4
100°-110°	131.2	1.9
110°-120°	321.4	4.8
120°-130°	408.1	6.1
130°-140°	435.9	6.5
140°-150°	407.6	6.1
150°-160°	328.8	4.9
160°-170°	212.2	3.2
170°-180°	73.1	1.1
0°-30°	1421.8	21.1
0°-40°	2245.4	33.3
0°-60°	3678.1	54.6
0°-90°	4389.6	65.2
90°-120°	479.7	7.1
90°-150°	1731.3	25.7
90°-180°	2345.0	34.8
0°-180°	6735.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1942	1942	1942	1942	1942	
5°	1942	1934	1916	1930	1926	184
15°	1852	1835	1791	1783	1772	522
25°	1686	1646	1574	1541	1523	775
35°	1459	1402	1304	1237	1208	913
45°	1199	1128	1007	917	879	925
55°	910	833	699	608	576	817
65°	622	536	413	336	318	616
75°	329	254	167	151	148	351
85°	84	49	44	41	41	91
90°	1	6	14	16	17	7
95°	35	11	18	22	22	42
105°	170	177	125	24	25	181
115°	320	323	328	334	336	316
125°	450	455	457	458	460	402
135°	561	564	566	568	566	432
145°	647	651	652	653	653	405
155°	713	712	712	715	712	328
165°	752	750	749	754	750	212
175°	769	766	767	771	766	73
180°	769	769	769	769	769	

TEST NUMBER: P1010855

CATALOG NUMBER: S123RDIP-B1165D585UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1942.3	1942.3	1942.3	1942.3	1942.3
2.5°	1950.2	1943.9	1925.0	1942.3	1939.1
5°	1942.3	1934.4	1915.5	1929.7	1926.5
7.5°	1928.1	1920.2	1896.6	1906.1	1901.3
10°	1909.2	1898.2	1869.8	1871.4	1863.5
12.5°	1882.4	1869.8	1833.6	1832.0	1822.6
15°	1852.5	1835.2	1791.1	1783.2	1772.2
17.5°	1816.3	1797.4	1742.2	1726.5	1710.7
20°	1775.3	1750.1	1690.3	1669.8	1650.9
22.5°	1729.6	1699.7	1635.1	1608.3	1591.0
25°	1685.5	1646.2	1573.7	1540.6	1523.3
27.5°	1632.0	1589.4	1510.7	1466.6	1439.8
30°	1576.8	1529.6	1441.4	1387.8	1362.6
32.5°	1521.7	1466.6	1372.1	1312.2	1285.4
35°	1458.7	1402.0	1304.3	1236.6	1208.2
37.5°	1395.7	1334.2	1231.9	1156.2	1121.6
40°	1335.8	1266.5	1154.7	1072.8	1036.5
42.5°	1268.1	1198.8	1082.2	990.8	959.3
45°	1198.8	1127.9	1006.6	916.8	879.0
47.5°	1131.0	1052.3	932.6	834.9	801.8
50°	1055.4	981.4	853.8	756.1	719.9
52.5°	987.7	905.8	779.8	677.4	645.9
55°	910.5	833.3	699.4	608.1	576.5
57.5°	841.2	757.7	622.2	535.6	508.8
60°	768.7	682.1	551.3	466.3	439.5
62.5°	696.3	609.6	478.9	400.1	371.8
65°	622.2	535.6	412.7	335.5	318.2
67.5°	548.2	460.0	340.3	282.0	263.1
70°	475.7	390.7	280.4	225.3	207.9
72.5°	403.3	319.8	222.1	179.6	174.9
75°	329.2	253.6	167.0	151.2	148.1
77.5°	261.5	192.2	130.7	121.3	118.1
80°	196.9	132.3	99.2	94.5	91.4
82.5°	135.5	81.9	70.9	66.2	66.2
85°	83.5	48.8	44.1	41.0	41.0
87.5°	37.8	20.5	20.5	18.9	17.3
90°	0.6	6.3	13.7	16.0	17.1
92.5°	13.1	9.7	14.9	18.9	19.4
95°	34.9	11.4	17.7	21.7	21.7
97.5°	63.4	47.4	18.3	22.9	23.4
100°	96.6	108.0	18.9	23.4	24.0
102.5°	134.3	141.8	42.3	23.4	24.6
105°	170.3	176.6	125.2	24.0	25.2
107.5°	208.6	213.8	222.3	134.3	59.4
110°	246.9	251.5	257.8	238.9	157.2

TEST NUMBER: P1010855

CATALOG NUMBER: S123RDIP-B1165D585UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	283.5	287.5	293.8	298.9	297.8
115°	319.5	322.9	328.1	333.8	336.1
117.5°	355.0	359.0	361.8	366.4	367.0
120°	387.5	392.7	394.4	399.0	399.0
122.5°	420.7	424.7	427.0	429.8	430.4
125°	450.4	455.0	457.3	458.4	459.6
127.5°	480.1	484.7	487.6	489.3	488.1
130°	507.6	512.1	514.4	516.7	515.6
132.5°	533.9	538.4	540.2	542.4	540.7
135°	560.7	564.2	566.4	568.2	566.4
137.5°	583.6	588.2	589.3	592.2	591.0
140°	606.5	609.9	611.6	613.9	612.7
142.5°	627.6	631.0	632.8	634.5	632.8
145°	647.0	651.0	652.2	653.3	653.3
147.5°	665.9	668.8	669.9	671.0	668.2
150°	683.1	684.8	685.9	687.1	685.3
152.5°	698.5	699.1	699.6	701.9	699.1
155°	712.8	711.6	712.2	715.1	711.6
157.5°	724.2	724.2	723.6	727.1	722.5
160°	734.5	733.9	733.4	736.8	732.8
162.5°	744.2	742.5	741.9	745.9	742.5
165°	751.6	749.9	749.4	753.9	749.9
167.5°	757.9	755.6	755.6	760.2	755.6
170°	763.1	760.8	760.8	765.4	760.8
172.5°	766.5	763.6	764.2	768.8	763.6
175°	769.4	766.5	767.1	771.1	766.5
177.5°	770.5	767.6	768.2	772.8	767.1
180°	769.4	769.4	769.4	769.4	769.4

(END OF REPORT)