

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010565

Luminaire Tested: S123DIP-B340D1195UB2750-4F0-XX-W2A-D_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010565
REPORT IS A COMBINATION OF REPORTS P989694 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B340D1195UB2750-4F0-XX-W2A-D_3000K
Description: Define 3 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6166.0 lumens
Efficiency: N/A
Efficacy: 128.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.25 / 1.37
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 48
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010565

CATALOG NUMBER: S123DIP-B340D1195UB2750-4F0-XX-W2A-D_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010565

CATALOG NUMBER: S123DIP-B340D1195UB2750-4F0-XX-W2A-D_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	100	100	100	100	89	89	89	89	67	67	67	47	47	47	29	29	29	21		
1	91	86	83	79	80	77	73	70	58	56	54	41	40	38	25	24	24	17		
2	82	75	69	64	73	67	62	57	50	47	44	36	34	32	22	21	20	14		
3	75	66	59	53	66	58	52	48	44	40	37	31	29	27	19	18	17	11		
4	68	58	50	45	60	52	45	40	39	35	31	28	25	23	17	15	14	10		
5	63	51	44	38	55	46	39	34	35	30	27	25	22	19	15	14	12	8		
6	58	46	38	33	51	41	34	29	31	26	23	22	19	17	14	12	11	7		
7	53	41	34	28	47	37	30	25	28	23	20	20	17	15	13	11	9	6		
8	49	37	30	25	43	33	27	22	25	21	18	18	15	13	11	10	8	6		
9	46	34	27	22	40	30	24	20	23	19	16	17	14	11	11	9	7	5		
10	42	31	24	19	37	28	21	17	21	17	14	15	12	10	10	8	7	5		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4481	4481	4481
5°	4493	4349	4346
10°	4451	4232	4199
15°	4392	4102	4044
20°	4308	3957	3877
25°	4205	3793	3704
30°	4101	3646	3530
35°	3981	3490	3389
40°	3869	3349	3239
45°	3744	3211	3116
50°	3620	3075	2982
55°	3484	2936	2859
60°	3349	2793	2733
65°	3213	2641	2586
70°	3004	2470	2433
75°	2743	2276	2277
80°	2438	2079	2098
85°	2132	1919	1970

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3744 cd/sqm

TEST NUMBER: P1010565

CATALOG NUMBER: S123DIP-B340D1195UB2750-4F0-XX-W2A-D_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.5	0.6
10°-20°	112.6	1.8
20°-30°	168.3	2.7
30°-40°	201.0	3.3
40°-50°	210.3	3.4
50°-60°	197.3	3.2
60°-70°	164.8	2.7
70°-80°	117.9	1.9
80°-90°	73.3	1.2
90°-100°	99.2	1.6
100°-110°	298.8	4.8
110°-120°	674.5	10.9
120°-130°	841.2	13.6
130°-140°	890.9	14.4
140°-150°	829.1	13.4
150°-160°	667.8	10.8
160°-170°	431.0	7.0
170°-180°	148.5	2.4
0°-30°	320.4	5.2
0°-40°	521.4	8.5
0°-60°	929.0	15.1
0°-90°	1285.0	20.8
90°-120°	1072.5	17.4
90°-150°	3633.7	58.9
90°-180°	4881.0	79.2
0°-180°	6166.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	416	416	416	416	416	
5°	417	416	413	417	416	40
15°	397	398	398	402	402	112
25°	358	363	364	370	370	165
35°	308	316	322	328	330	193
45°	252	263	274	283	287	194
55°	192	207	224	236	239	172
65°	133	150	170	184	189	131
75°	72	93	116	131	136	77
85°	22	45	69	84	89	23
90°	7	41	79	99	106	8
95°	76	46	81	103	108	88
105°	350	373	288	96	102	370
115°	651	664	690	713	721	643
125°	916	926	943	955	961	819
135°	1140	1146	1156	1168	1166	878
145°	1315	1322	1325	1331	1332	823
155°	1448	1445	1447	1452	1445	667
165°	1527	1523	1522	1531	1523	431
175°	1563	1557	1558	1566	1557	149
180°	1563	1563	1563	1563	1563	

TEST NUMBER: P1010565

CATALOG NUMBER: S123DIP-B340D1195UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	416.3	416.3	416.3	416.3	416.3
2.5°	418.5	417.2	413.6	417.2	416.7
5°	416.7	415.8	413.1	416.7	416.3
7.5°	413.6	413.6	410.8	415.4	414.9
10°	409.0	409.9	407.7	412.2	411.3
12.5°	403.6	404.9	403.6	407.7	406.7
15°	396.8	398.1	397.7	402.2	401.8
17.5°	388.6	391.3	390.9	395.0	394.1
20°	379.5	382.3	383.2	387.3	387.7
22.5°	370.0	372.7	374.1	379.5	379.1
25°	358.2	362.8	364.1	370.0	370.0
27.5°	346.9	351.9	354.6	359.6	360.0
30°	334.7	340.5	344.2	349.6	349.6
32.5°	321.0	327.8	332.8	338.7	340.1
35°	308.3	315.6	321.5	328.3	330.1
37.5°	294.7	302.9	309.7	317.4	318.8
40°	281.1	289.3	298.4	306.1	307.9
42.5°	266.2	276.6	286.1	294.7	297.5
45°	252.1	263.0	274.3	283.0	286.6
47.5°	237.2	249.4	262.1	271.6	274.3
50°	222.6	235.3	249.4	259.8	263.0
52.5°	207.2	220.8	236.7	247.6	251.7
55°	192.3	207.2	223.6	235.8	239.4
57.5°	177.8	193.2	210.9	223.1	227.2
60°	162.3	178.7	197.3	209.9	214.9
62.5°	147.8	164.6	184.6	197.3	201.8
65°	132.9	150.5	170.5	184.1	188.6
67.5°	117.9	136.5	156.4	171.4	175.0
70°	102.0	121.5	143.3	157.8	162.3
72.5°	87.5	107.0	129.7	144.7	149.2
75°	72.1	93.4	116.1	131.0	136.5
77.5°	58.9	80.3	102.9	118.8	122.9
80°	44.9	67.1	90.7	106.1	110.6
82.5°	32.6	55.3	79.4	94.8	99.3
85°	22.2	44.9	68.9	84.3	88.9
87.5°	13.6	36.3	59.4	74.8	79.4
90°	7.1	40.9	79.1	99.2	106.0
92.5°	32.1	44.6	77.8	100.9	106.2
95°	75.8	45.9	80.9	103.0	107.6
97.5°	133.4	117.3	79.4	102.2	107.9
100°	200.3	238.0	77.8	100.2	105.9
102.5°	276.4	304.2	122.6	97.0	103.9
105°	349.6	373.2	288.3	95.5	101.9
107.5°	427.0	446.9	482.9	316.3	168.3
110°	504.2	521.7	552.6	526.1	363.7

TEST NUMBER: P1010565

CATALOG NUMBER: S123DIP-B340D1195UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	578.5	593.1	623.0	644.8	646.6
115°	651.3	663.6	690.4	712.9	721.1
117.5°	723.3	735.0	756.2	776.4	781.1
120°	788.9	801.7	820.1	839.9	843.0
122.5°	856.3	865.3	884.0	899.8	904.1
125°	916.2	925.5	943.3	955.1	960.6
127.5°	976.6	985.4	1002.5	1015.1	1016.0
130°	1032.3	1041.1	1054.9	1068.1	1068.5
132.5°	1085.2	1094.5	1104.8	1117.7	1117.3
135°	1139.8	1146.4	1155.9	1167.6	1166.4
137.5°	1186.2	1195.1	1200.6	1213.7	1213.6
140°	1232.3	1239.2	1244.0	1255.5	1255.4
142.5°	1275.2	1281.7	1285.2	1294.6	1293.4
145°	1314.7	1322.3	1324.7	1330.6	1332.4
147.5°	1352.5	1358.3	1360.6	1364.4	1360.4
150°	1387.3	1390.8	1393.2	1395.5	1392.9
152.5°	1418.7	1419.9	1421.0	1425.7	1419.9
155°	1447.7	1445.4	1446.6	1452.4	1445.4
157.5°	1470.9	1470.9	1469.8	1476.7	1467.5
160°	1491.8	1490.7	1489.5	1496.5	1488.4
162.5°	1511.6	1508.1	1506.9	1515.1	1508.1
165°	1526.7	1523.2	1522.0	1531.3	1523.2
167.5°	1539.4	1534.8	1534.8	1544.1	1534.8
170°	1549.9	1545.2	1545.2	1554.5	1545.2
172.5°	1556.8	1551.0	1552.2	1561.5	1551.0
175°	1562.7	1556.8	1558.0	1566.1	1556.8
177.5°	1565.0	1559.2	1560.3	1569.6	1558.0
180°	1562.7	1562.7	1562.7	1562.7	1562.7

(END OF REPORT)