

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010875

Luminaire Tested: S123RDIP-B340D1025UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010875
REPORT IS A COMBINATION OF REPORTS P993131 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B340D1025UB2750-4F0-XX-W2A-F_3000K
Description: Define 3 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5320.0 lumens
Efficiency: N/A
Efficacy: 128.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010875

CATALOG NUMBER: S123RDIP-B340D1025UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010875

CATALOG NUMBER: S123RDIP-B340D1025UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	32	32	32
1	92	88	84	81	82	78	75	73	60	58	57	44	43	41	28	28	27
2	84	77	71	66	74	69	64	60	53	50	47	39	37	35	25	24	23
3	77	68	61	55	68	60	55	50	47	43	40	34	32	30	22	21	20
4	70	60	52	47	62	54	47	42	42	37	34	30	28	25	20	19	17
5	64	53	46	40	57	48	41	36	37	33	29	27	24	22	18	16	15
6	59	48	40	34	52	43	36	31	33	29	25	25	22	19	17	15	13
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	12
8	50	39	31	26	45	35	28	24	27	23	19	20	17	15	14	12	11
9	47	35	28	23	42	32	26	21	25	21	17	19	16	13	13	11	10
10	44	32	25	21	39	29	23	19	23	19	16	17	14	12	12	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6018	6018	6018
5°	6028	5804	5789
10°	5980	5586	5477
15°	5902	5316	5134
20°	5801	5023	4752
25°	5695	4719	4388
30°	5561	4394	3960
35°	5423	4075	3570
40°	5292	3729	3138
45°	5124	3391	2751
50°	4940	3029	2350
55°	4749	2643	1981
60°	4566	2247	1609
65°	4329	1840	1256
70°	4032	1391	897
75°	3606	943	711
80°	3078	656	499
85°	2305	354	262

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5124 cd/sqm

TEST NUMBER: P1010875

CATALOG NUMBER: S123RDIP-B340D1025UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.6	1.0
10°-20°	146.2	2.7
20°-30°	210.5	4.0
30°-40°	237.1	4.5
40°-50°	226.7	4.3
50°-60°	185.6	3.5
60°-70°	125.1	2.4
70°-80°	62.8	1.2
80°-90°	19.1	0.4
90°-100°	46.9	0.9
100°-110°	226.7	4.3
110°-120°	555.6	10.4
120°-130°	705.4	13.3
130°-140°	753.5	14.2
140°-150°	704.6	13.2
150°-160°	568.4	10.7
160°-170°	366.8	6.9
170°-180°	126.4	2.4
0°-30°	409.2	7.7
0°-40°	646.3	12.1
0°-60°	1058.7	19.9
0°-90°	1265.6	23.8
90°-120°	829.3	15.6
90°-150°	2992.8	56.3
90°-180°	4054.0	76.2
0°-180°	5320.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	559	559	559	559	559	
5°	559	557	551	555	554	53
15°	533	528	516	513	510	150
25°	485	474	453	443	438	223
35°	420	404	375	356	348	263
45°	345	325	290	264	253	266
55°	262	240	201	175	166	235
65°	179	154	119	97	92	177
75°	95	73	48	44	43	101
85°	24	14	13	12	12	26
90°	1	11	24	28	30	5
95°	60	20	31	38	38	72
105°	294	305	216	42	44	312
115°	552	558	567	577	581	545
125°	779	786	790	792	794	696
135°	969	975	979	982	979	746
145°	1118	1125	1127	1129	1129	700
155°	1232	1230	1231	1236	1230	568
165°	1299	1296	1295	1303	1296	367
175°	1330	1325	1326	1333	1325	127
180°	1330	1330	1330	1330	1330	

TEST NUMBER: P1010875

CATALOG NUMBER: S123RDIP-B340D1025UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	559.1	559.1	559.1	559.1	559.1
2.5°	561.3	559.5	554.1	559.1	558.1
5°	559.1	556.8	551.3	555.4	554.5
7.5°	555.0	552.7	545.9	548.6	547.3
10°	549.5	546.4	538.2	538.6	536.4
12.5°	541.8	538.2	527.8	527.3	524.6
15°	533.2	528.2	515.5	513.3	510.1
17.5°	522.8	517.3	501.5	496.9	492.4
20°	511.0	503.7	486.5	480.6	475.2
22.5°	497.8	489.2	470.6	462.9	457.9
25°	485.1	473.8	453.0	443.4	438.4
27.5°	469.7	457.5	434.8	422.1	414.4
30°	453.9	440.3	414.9	399.5	392.2
32.5°	438.0	422.1	394.9	377.7	370.0
35°	419.9	403.5	375.4	355.9	347.8
37.5°	401.7	384.0	354.6	332.8	322.8
40°	384.5	364.5	332.3	308.8	298.3
42.5°	365.0	345.0	311.5	285.2	276.1
45°	345.0	324.6	289.7	263.9	253.0
47.5°	325.5	302.9	268.4	240.3	230.8
50°	303.8	282.5	245.7	217.6	207.2
52.5°	284.3	260.7	224.4	195.0	185.9
55°	262.1	239.9	201.3	175.0	165.9
57.5°	242.1	218.1	179.1	154.2	146.5
60°	221.3	196.3	158.7	134.2	126.5
62.5°	200.4	175.5	137.8	115.2	107.0
65°	179.1	154.2	118.8	96.6	91.6
67.5°	157.8	132.4	97.9	81.2	75.7
70°	136.9	112.4	80.7	64.8	59.8
72.5°	116.1	92.0	63.9	51.7	50.3
75°	94.8	73.0	48.1	43.5	42.6
77.5°	75.3	55.3	37.6	34.9	34.0
80°	56.7	38.1	28.6	27.2	26.3
82.5°	39.0	23.6	20.4	19.0	19.0
85°	24.0	14.1	12.7	11.8	11.8
87.5°	10.9	5.9	5.9	5.4	5.0
90°	1.0	10.9	23.7	27.7	29.6
92.5°	22.7	16.8	25.7	32.6	33.6
95°	60.3	19.8	30.6	37.5	37.5
97.5°	109.7	82.0	31.6	39.5	40.5
100°	167.0	186.7	32.6	40.5	41.5
102.5°	232.2	245.0	73.1	40.5	42.5
105°	294.4	305.3	216.4	41.5	43.5
107.5°	360.6	369.5	384.3	232.2	102.8
110°	426.8	434.7	445.6	413.0	271.7

TEST NUMBER: P1010875

CATALOG NUMBER: S123RDIP-B340D1025UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	490.1	497.0	507.9	516.7	514.8
115°	552.3	558.2	567.1	577.0	581.0
117.5°	613.6	620.5	625.4	633.3	634.3
120°	669.9	678.8	681.8	689.7	689.7
122.5°	727.2	734.1	738.1	743.0	744.0
125°	778.6	786.5	790.4	792.4	794.4
127.5°	830.0	837.9	842.8	845.8	843.8
130°	877.4	885.3	889.2	893.2	891.2
132.5°	922.8	930.7	933.7	937.7	934.7
135°	969.3	975.2	979.2	982.1	979.2
137.5°	1008.8	1016.7	1018.7	1023.6	1021.6
140°	1048.3	1054.2	1057.2	1061.2	1059.2
142.5°	1084.9	1090.8	1093.8	1096.7	1093.8
145°	1118.5	1125.4	1127.4	1129.3	1129.3
147.5°	1151.1	1156.0	1158.0	1160.0	1155.0
150°	1180.7	1183.7	1185.7	1187.6	1184.7
152.5°	1207.4	1208.4	1209.4	1213.3	1208.4
155°	1232.1	1230.1	1231.1	1236.0	1230.1
157.5°	1251.9	1251.9	1250.9	1256.8	1248.9
160°	1269.6	1268.7	1267.7	1273.6	1266.7
162.5°	1286.4	1283.5	1282.5	1289.4	1283.5
165°	1299.3	1296.3	1295.3	1303.2	1296.3
167.5°	1310.1	1306.2	1306.2	1314.1	1306.2
170°	1319.0	1315.1	1315.1	1323.0	1315.1
172.5°	1325.0	1320.0	1321.0	1328.9	1320.0
175°	1329.9	1325.0	1326.0	1332.9	1325.0
177.5°	1331.9	1326.9	1327.9	1335.8	1326.0
180°	1329.9	1329.9	1329.9	1329.9	1329.9

(END OF REPORT)