

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010887

Luminaire Tested: S123RDIP-B340D1195UB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010887
REPORT IS A COMBINATION OF REPORTS P993173 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B340D1195UB2750-4F0-XX-W2A-F_4000K
Description: Define 3 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5996.0 lumens
Efficiency: N/A
Efficacy: 124.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 48
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010887

CATALOG NUMBER: S123RDIP-B340D1195UB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010887

CATALOG NUMBER: S123RDIP-B340D1195UB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	100	100	100	100	89	89	89	89	67	67	67	48	48	48	29	29	29	21	21	21
1	91	87	84	80	81	77	74	72	59	57	55	42	41	40	26	26	25	18	18	18
2	83	76	71	66	74	68	63	59	52	49	46	37	35	33	23	22	21	15	15	15
3	76	67	60	55	67	60	54	49	46	42	39	33	30	28	21	19	18	13	13	13
4	69	59	52	46	61	53	47	42	41	36	33	29	26	24	19	17	16	11	11	11
5	64	53	45	39	56	47	41	36	36	32	28	26	23	21	17	15	14	10	10	10
6	59	47	40	34	52	42	36	31	32	28	24	24	21	18	15	13	12	9	9	9
7	54	42	35	30	48	38	31	27	29	25	21	21	18	16	14	12	11	8	8	8
8	50	38	31	26	44	34	28	24	27	22	19	19	16	14	13	11	10	7	7	7
9	46	35	28	23	41	31	25	21	24	20	17	18	15	13	12	10	9	6	6	6
10	43	32	25	20	38	29	23	19	22	18	15	16	13	11	11	9	8	6	6	6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5985	5985	5985
5°	5994	5773	5756
10°	5947	5555	5446
15°	5870	5288	5106
20°	5769	4995	4725
25°	5664	4692	4364
30°	5529	4370	3938
35°	5392	4053	3550
40°	5263	3709	3121
45°	5095	3372	2736
50°	4913	3013	2337
55°	4722	2629	1971
60°	4540	2234	1600
65°	4305	1829	1249
70°	4011	1384	892
75°	3583	937	707
80°	3062	651	497
85°	2296	351	259

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5095 cd/sqm

TEST NUMBER: P1010887

CATALOG NUMBER: S123RDIP-B340D1195UB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.3	0.9
10°-20°	145.4	2.4
20°-30°	209.3	3.5
30°-40°	235.7	3.9
40°-50°	225.5	3.8
50°-60°	184.6	3.1
60°-70°	124.4	2.1
70°-80°	62.4	1.0
80°-90°	19.4	0.3
90°-100°	54.8	0.9
100°-110°	264.9	4.4
110°-120°	649.2	10.8
120°-130°	824.1	13.7
130°-140°	880.4	14.7
140°-150°	823.3	13.7
150°-160°	664.0	11.1
160°-170°	428.5	7.1
170°-180°	147.7	2.5
0°-30°	407.0	6.8
0°-40°	642.7	10.7
0°-60°	1052.8	17.6
0°-90°	1259.1	21.0
90°-120°	968.9	16.2
90°-150°	3496.7	58.3
90°-180°	4737.0	79.0
0°-180°	5996.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	556	556	556	556	556	
5°	556	554	548	552	551	53
15°	530	525	513	510	507	149
25°	482	471	450	441	436	222
35°	418	401	373	354	346	261
45°	343	323	288	262	252	265
55°	261	238	200	174	165	234
65°	178	153	118	96	91	176
75°	94	73	48	43	42	100
85°	24	14	13	12	12	26
90°	1	13	28	32	35	5
95°	70	23	36	44	44	84
105°	344	357	253	48	51	365
115°	645	652	663	674	679	637
125°	910	919	924	926	928	813
135°	1132	1139	1144	1148	1144	872
145°	1307	1315	1317	1320	1320	818
155°	1440	1437	1438	1444	1437	663
165°	1518	1515	1513	1523	1515	429
175°	1554	1548	1549	1557	1548	148
180°	1554	1554	1554	1554	1554	

TEST NUMBER: P1010887

CATALOG NUMBER: S123RDIP-B340D1195UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	556.0	556.0	556.0	556.0	556.0
2.5°	558.2	556.4	551.0	556.0	555.1
5°	556.0	553.7	548.3	552.3	551.4
7.5°	551.9	549.6	542.9	545.6	544.2
10°	546.5	543.3	535.2	535.7	533.4
12.5°	538.8	535.2	524.8	524.4	521.7
15°	530.3	525.3	512.7	510.4	507.3
17.5°	519.9	514.5	498.7	494.2	489.7
20°	508.2	500.9	483.8	477.9	472.5
22.5°	495.1	486.5	468.0	460.4	455.4
25°	482.5	471.2	450.4	441.0	436.0
27.5°	467.1	455.0	432.4	419.8	412.1
30°	451.3	437.8	412.6	397.2	390.0
32.5°	435.6	419.8	392.7	375.6	367.9
35°	417.5	401.3	373.3	354.0	345.8
37.5°	399.5	381.9	352.6	331.0	321.0
40°	382.4	362.5	330.5	307.1	296.7
42.5°	363.0	343.1	309.8	283.6	274.6
45°	343.1	322.8	288.1	262.4	251.6
47.5°	323.7	301.2	266.9	239.0	229.5
50°	302.1	280.9	244.4	216.4	206.1
52.5°	282.7	259.3	223.2	193.9	184.9
55°	260.6	238.5	200.2	174.0	165.0
57.5°	240.8	216.9	178.1	153.3	145.6
60°	220.0	195.2	157.8	133.5	125.8
62.5°	199.3	174.5	137.1	114.5	106.4
65°	178.1	153.3	118.1	96.0	91.1
67.5°	156.9	131.7	97.4	80.7	75.3
70°	136.2	111.8	80.3	64.5	59.5
72.5°	115.4	91.5	63.6	51.4	50.0
75°	94.2	72.6	47.8	43.3	42.4
77.5°	74.8	55.0	37.4	34.7	33.8
80°	56.4	37.9	28.4	27.1	26.2
82.5°	38.8	23.4	20.3	18.9	18.9
85°	23.9	14.0	12.6	11.7	11.7
87.5°	10.8	5.9	5.9	5.4	5.0
90°	1.2	12.7	27.7	32.3	34.6
92.5°	26.6	19.6	30.0	38.1	39.2
95°	70.4	23.1	35.8	43.9	43.9
97.5°	128.1	95.8	36.9	46.2	47.3
100°	195.1	218.2	38.1	47.3	48.5
102.5°	271.3	286.3	85.4	47.3	49.6
105°	344.0	356.7	252.8	48.5	50.8
107.5°	421.4	431.7	449.1	271.3	120.1
110°	498.7	507.9	520.6	482.5	317.5

TEST NUMBER: P1010887

CATALOG NUMBER: S123RDIP-B340D1195UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	572.6	580.7	593.4	603.7	601.4
115°	645.3	652.2	662.6	674.2	678.8
117.5°	716.9	725.0	730.7	740.0	741.1
120°	782.7	793.1	796.5	805.8	805.8
122.5°	849.6	857.7	862.3	868.1	869.3
125°	909.7	918.9	923.5	925.8	928.1
127.5°	969.7	978.9	984.7	988.2	985.8
130°	1025.1	1034.3	1038.9	1043.6	1041.3
132.5°	1078.2	1087.4	1090.9	1095.5	1092.0
135°	1132.5	1139.4	1144.0	1147.5	1144.0
137.5°	1178.6	1187.9	1190.2	1195.9	1193.6
140°	1224.8	1231.7	1235.2	1239.8	1237.5
142.5°	1267.5	1274.4	1277.9	1281.4	1277.9
145°	1306.8	1314.8	1317.2	1319.5	1319.5
147.5°	1344.9	1350.6	1352.9	1355.2	1349.5
150°	1379.5	1383.0	1385.3	1387.6	1384.1
152.5°	1410.7	1411.8	1413.0	1417.6	1411.8
155°	1439.5	1437.2	1438.4	1444.1	1437.2
157.5°	1462.6	1462.6	1461.5	1468.4	1459.1
160°	1483.4	1482.2	1481.1	1488.0	1479.9
162.5°	1503.0	1499.5	1498.4	1506.5	1499.5
165°	1518.0	1514.6	1513.4	1522.6	1514.6
167.5°	1530.7	1526.1	1526.1	1535.3	1526.1
170°	1541.1	1536.5	1536.5	1545.7	1536.5
172.5°	1548.0	1542.3	1543.4	1552.6	1542.3
175°	1553.8	1548.0	1549.2	1557.3	1548.0
177.5°	1556.1	1550.3	1551.5	1560.7	1549.2
180°	1553.8	1553.8	1553.8	1553.8	1553.8

(END OF REPORT)