

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010582

Luminaire Tested: S123DIP-B340D365UB2750-4F0-XX-W2A-D_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010582
REPORT IS A COMBINATION OF REPORTS P989756 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B340D365UB2750-4F0-XX-W2A-D_4000K
Description: Define 3 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2842.0 lumens
Efficiency: N/A
Efficacy: 127.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.25 / 1.37
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 22.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010582

CATALOG NUMBER: S123DIP-B340D365UB2750-4F0-XX-W2A-D_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010582

CATALOG NUMBER: S123DIP-B340D365UB2750-4F0-XX-W2A-D_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51
1	96	91	87	83	87	83	80	76	69	66	64	56	54	52	44	43	42
2	87	79	72	67	79	72	67	62	60	56	52	49	46	43	38	36	34
3	79	69	61	55	72	63	57	51	53	48	44	43	39	36	33	31	29
4	72	61	53	46	66	56	49	43	47	41	37	38	34	31	30	27	25
5	66	54	46	40	60	50	42	37	41	36	32	34	30	26	27	24	21
6	61	48	40	34	55	45	37	32	37	32	27	30	26	23	24	21	19
7	56	44	35	30	51	40	33	28	34	28	24	28	23	20	22	19	16
8	52	39	32	26	47	36	29	25	31	25	21	25	21	18	20	17	15
9	48	36	28	23	44	33	26	22	28	23	19	23	19	16	19	15	13
10	45	33	26	21	41	30	24	20	26	21	17	21	17	14	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4455	4455	4455
5°	4467	4324	4321
10°	4426	4207	4175
15°	4367	4078	4021
20°	4284	3934	3855
25°	4182	3771	3683
30°	4076	3624	3510
35°	3960	3471	3369
40°	3847	3329	3220
45°	3723	3193	3098
50°	3600	3058	2965
55°	3464	2919	2844
60°	3330	2776	2718
65°	3193	2625	2572
70°	2986	2456	2420
75°	2727	2262	2264
80°	2421	2068	2086
85°	2123	1908	1959

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3723 cd/sqm

TEST NUMBER: P1010582

CATALOG NUMBER: S123DIP-B340D365UB2750-4F0-XX-W2A-D_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.3	1.4
10°-20°	111.9	3.9
20°-30°	167.4	5.9
30°-40°	199.8	7.0
40°-50°	209.1	7.4
50°-60°	196.2	6.9
60°-70°	163.9	5.8
70°-80°	117.2	4.1
80°-90°	70.7	2.5
90°-100°	60.6	2.1
100°-110°	113.3	4.0
110°-120°	220.2	7.7
120°-130°	264.6	9.3
130°-140°	275.0	9.7
140°-150°	253.2	8.9
150°-160°	203.3	7.2
160°-170°	131.2	4.6
170°-180°	45.2	1.6
0°-30°	318.6	11.2
0°-40°	518.4	18.2
0°-60°	923.7	32.5
0°-90°	1275.5	44.9
90°-120°	394.1	13.9
90°-150°	1186.9	41.8
90°-180°	1567.0	55.1
0°-180°	2842.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	414	414	414	414	414	
5°	414	413	411	414	414	39
15°	394	396	395	400	400	111
25°	356	361	362	368	368	164
35°	307	314	320	326	328	192
45°	251	262	273	281	285	193
55°	191	206	222	234	238	171
65°	132	150	170	183	188	131
75°	72	93	115	130	136	77
85°	22	45	68	84	88	23
90°	6	32	59	76	81	5
95°	27	30	56	72	76	30
105°	109	124	111	61	66	115
115°	200	207	227	241	246	197
125°	280	283	297	307	311	250
135°	348	349	356	365	366	268
145°	400	402	403	408	409	251
155°	441	440	440	442	440	203
165°	465	464	463	466	464	131
175°	476	474	474	477	474	45
180°	476	476	476	476	476	

TEST NUMBER: P1010582

CATALOG NUMBER: S123DIP-B340D365UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	413.9	413.9	413.9	413.9	413.9
2.5°	416.1	414.8	411.2	414.8	414.3
5°	414.3	413.4	410.7	414.3	413.9
7.5°	411.2	411.2	408.5	413.0	412.5
10°	406.7	407.6	405.3	409.8	408.9
12.5°	401.3	402.6	401.3	405.3	404.4
15°	394.5	395.9	395.4	399.9	399.5
17.5°	386.4	389.1	388.6	392.7	391.8
20°	377.4	380.1	381.0	385.0	385.5
22.5°	367.9	370.6	372.0	377.4	376.9
25°	356.2	360.7	362.0	367.9	367.9
27.5°	344.9	349.9	352.6	357.5	358.0
30°	332.7	338.6	342.2	347.6	347.6
32.5°	319.2	326.0	330.9	336.8	338.1
35°	306.6	313.8	319.7	326.4	328.2
37.5°	293.1	301.2	307.9	315.6	317.0
40°	279.5	287.7	296.7	304.3	306.1
42.5°	264.7	275.0	284.5	293.1	295.8
45°	250.7	261.5	272.8	281.3	284.9
47.5°	235.8	248.0	260.6	270.1	272.8
50°	221.4	234.0	248.0	258.3	261.5
52.5°	206.0	219.6	235.4	246.2	250.2
55°	191.2	206.0	222.3	234.4	238.1
57.5°	176.7	192.1	209.7	221.8	225.9
60°	161.4	177.6	196.1	208.7	213.7
62.5°	147.0	163.7	183.5	196.1	200.6
65°	132.1	149.7	169.5	183.1	187.6
67.5°	117.2	135.7	155.5	170.4	174.0
70°	101.4	120.8	142.5	156.9	161.4
72.5°	87.0	106.4	128.9	143.8	148.3
75°	71.7	92.9	115.4	130.3	135.7
77.5°	58.6	79.8	102.3	118.1	122.2
80°	44.6	66.7	90.2	105.5	110.0
82.5°	32.5	55.0	78.9	94.2	98.7
85°	22.1	44.6	68.5	83.9	88.4
87.5°	13.5	36.1	59.1	74.4	78.9
90°	6.3	31.9	59.4	76.2	81.4
92.5°	13.5	30.8	56.5	73.9	78.3
95°	26.6	29.6	55.6	72.0	76.5
97.5°	43.7	50.0	53.2	69.6	74.5
100°	63.8	85.3	50.9	66.8	71.6
102.5°	86.6	103.8	62.6	63.6	68.9
105°	108.9	123.6	111.2	61.2	66.0
107.5°	132.2	144.8	168.6	126.3	84.1
110°	155.4	166.3	188.3	188.3	141.4

TEST NUMBER: P1010582

CATALOG NUMBER: S123DIP-B340D365UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	178.0	186.7	207.8	222.2	225.6
115°	199.8	207.4	226.7	241.1	246.1
117.5°	221.7	227.8	244.9	258.5	262.5
120°	241.4	246.9	262.7	276.0	279.2
122.5°	261.9	265.3	280.7	292.3	295.9
125°	279.9	282.7	297.1	307.3	311.2
127.5°	298.2	300.6	313.6	323.7	326.1
130°	315.2	317.5	327.9	338.0	339.9
132.5°	331.0	333.8	341.6	351.2	353.2
135°	347.6	349.3	355.6	364.8	366.0
137.5°	361.7	364.1	367.9	376.9	378.5
140°	375.4	377.6	379.9	388.1	389.6
142.5°	388.5	390.1	391.2	398.1	399.3
145°	400.5	402.5	403.2	407.5	409.3
147.5°	411.7	413.5	414.2	416.3	416.3
150°	422.3	423.3	424.1	424.8	424.6
152.5°	431.8	432.2	432.5	433.9	432.2
155°	440.7	440.0	440.3	442.1	440.0
157.5°	447.7	447.7	447.4	449.5	446.7
160°	454.1	453.7	453.4	455.5	453.0
162.5°	460.1	459.0	458.7	461.2	459.0
165°	464.7	463.6	463.3	466.1	463.6
167.5°	468.6	467.2	467.2	470.0	467.2
170°	471.8	470.3	470.3	473.2	470.3
172.5°	473.9	472.1	472.5	475.3	472.1
175°	475.6	473.9	474.2	476.7	473.9
177.5°	476.4	474.6	474.9	477.8	474.2
180°	475.6	475.6	475.6	475.6	475.6

(END OF REPORT)