

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010587

Luminaire Tested: S123DIP-B340D365UB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010587
REPORT IS A COMBINATION OF REPORTS P989761 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B340D365UB2750-4F0-XX-W2A-F_4000K
Description: Define 3 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2816.0 lumens
Efficiency: N/A
Efficacy: 126.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 22.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010587

CATALOG NUMBER: S123DIP-B340D365UB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010587

CATALOG NUMBER: S123DIP-B340D365UB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55			49
1	97	93	89	86	90	86	82	79	72	70	68	60	58	57	48	47	46			41
2	89	81	75	70	81	75	70	65	63	59	56	52	50	47	42	41	39			34
3	81	71	64	58	74	66	60	54	56	51	47	46	43	40	38	35	33			29
4	74	63	55	49	68	58	51	46	50	44	40	41	37	34	34	31	28			25
5	68	56	48	42	62	52	45	40	44	39	34	37	33	30	30	27	25			21
6	62	50	42	36	57	47	40	34	40	34	30	33	29	26	27	24	22			19
7	58	45	38	32	53	42	35	30	36	31	26	30	26	23	25	22	19			17
8	54	41	34	28	49	38	31	27	33	27	23	28	24	20	23	20	17			15
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16			13
10	47	35	27	23	43	32	26	21	28	23	19	24	19	17	20	16	14			12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5646	5646	5646
5°	5659	5450	5442
10°	5610	5266	5212
15°	5531	5074	4961
20°	5442	4861	4713
25°	5326	4637	4446
30°	5200	4404	4166
35°	5066	4167	3888
40°	4928	3917	3615
45°	4775	3674	3329
50°	4620	3403	3043
55°	4421	3121	2752
60°	4216	2809	2443
65°	4022	2472	2121
70°	3746	2100	1745
75°	3344	1662	1355
80°	2888	1169	958
85°	2257	627	479

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4775 cd/sqm

TEST NUMBER: P1010587

CATALOG NUMBER: S123DIP-B340D365UB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.4	1.8
10°-20°	139.6	5.0
20°-30°	206.2	7.3
30°-40°	240.8	8.6
40°-50°	242.1	8.6
50°-60°	212.7	7.6
60°-70°	158.4	5.6
70°-80°	90.1	3.2
80°-90°	26.6	0.9
90°-100°	16.8	0.6
100°-110°	81.1	2.9
110°-120°	198.7	7.1
120°-130°	252.3	9.0
130°-140°	269.5	9.6
140°-150°	252.0	8.9
150°-160°	203.3	7.2
160°-170°	131.2	4.7
170°-180°	45.2	1.6
0°-30°	395.3	14.0
0°-40°	636.1	22.6
0°-60°	1090.8	38.7
0°-90°	1365.9	48.5
90°-120°	296.6	10.5
90°-150°	1070.4	38.0
90°-180°	1450.0	51.5
0°-180°	2816.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	524	524	524	524	524	
5°	525	523	518	522	521	50
15°	500	498	492	496	493	141
25°	454	451	445	446	444	209
35°	392	390	384	381	379	245
45°	322	320	314	308	306	248
55°	244	244	238	233	230	219
65°	166	164	160	156	155	164
75°	88	86	85	82	81	94
85°	24	22	22	22	22	25
90°	0	4	8	10	11	3
95°	22	7	11	13	13	26
105°	105	109	77	15	16	112
115°	198	200	203	206	208	195
125°	278	281	283	283	284	249
135°	347	349	350	351	350	267
145°	400	402	403	404	404	250
155°	441	440	440	442	440	203
165°	465	464	463	466	464	131
175°	476	474	474	477	474	45
180°	476	476	476	476	476	

TEST NUMBER: P1010587

CATALOG NUMBER: S123DIP-B340D365UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	524.5	524.5	524.5	524.5	524.5
2.5°	526.7	524.9	520.0	524.5	524.0
5°	524.9	522.7	517.7	522.2	521.3
7.5°	520.9	518.6	513.7	517.7	517.3
10°	515.5	513.2	507.3	511.4	510.5
12.5°	508.2	506.4	501.0	503.7	503.3
15°	499.7	497.9	492.0	495.6	492.9
17.5°	490.2	488.0	482.1	484.8	483.9
20°	479.4	476.7	470.8	472.6	471.3
22.5°	467.2	464.5	458.6	460.0	458.2
25°	453.7	451.0	445.1	445.6	444.2
27.5°	439.7	437.0	430.7	431.1	429.8
30°	424.4	422.1	415.8	415.8	412.6
32.5°	409.0	405.9	401.4	398.2	396.9
35°	392.3	389.6	383.8	381.1	378.8
37.5°	375.7	372.1	366.2	363.0	361.7
40°	358.1	355.4	349.1	345.4	343.6
42.5°	340.5	337.3	331.0	327.4	325.6
45°	321.5	319.7	313.9	308.5	306.2
47.5°	303.1	300.3	294.9	289.5	287.7
50°	284.1	281.9	276.0	271.0	268.3
52.5°	264.3	262.9	256.6	252.5	249.8
55°	244.0	243.5	237.7	232.7	230.4
57.5°	225.0	223.2	218.7	214.2	211.5
60°	204.3	203.8	198.4	194.4	192.1
62.5°	185.8	184.4	179.0	175.0	173.6
65°	166.4	164.2	159.6	156.0	154.7
67.5°	145.7	143.9	140.3	137.1	135.3
70°	127.2	124.5	121.8	118.6	116.4
72.5°	107.8	106.0	102.8	100.1	99.2
75°	87.9	86.1	84.8	82.5	81.2
77.5°	70.4	69.5	67.6	65.8	65.8
80°	53.2	51.9	51.0	50.5	50.5
82.5°	36.5	36.5	36.5	35.6	35.2
85°	23.5	22.5	22.5	21.6	21.6
87.5°	11.7	10.4	9.9	9.5	9.5
90°	0.4	3.9	8.5	9.9	10.6
92.5°	8.1	6.0	9.2	11.7	12.0
95°	21.6	7.1	11.0	13.4	13.4
97.5°	39.2	29.3	11.3	14.1	14.5
100°	59.7	66.8	11.7	14.5	14.8
102.5°	83.0	87.6	26.1	14.5	15.2
105°	105.3	109.2	77.4	14.8	15.5
107.5°	129.0	132.2	137.5	83.0	36.8
110°	152.7	155.5	159.4	147.7	97.2

TEST NUMBER: P1010587

CATALOG NUMBER: S123DIP-B340D365UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	175.3	177.7	181.6	184.8	184.1
115°	197.5	199.7	202.8	206.4	207.8
117.5°	219.4	221.9	223.7	226.5	226.9
120°	239.6	242.8	243.8	246.7	246.7
122.5°	260.1	262.6	264.0	265.7	266.1
125°	278.5	281.3	282.7	283.4	284.1
127.5°	296.8	299.7	301.4	302.5	301.8
130°	313.8	316.6	318.0	319.5	318.7
132.5°	330.1	332.9	333.9	335.4	334.3
135°	346.7	348.8	350.2	351.3	350.2
137.5°	360.8	363.6	364.3	366.1	365.4
140°	374.9	377.1	378.1	379.5	378.8
142.5°	388.0	390.1	391.2	392.2	391.2
145°	400.0	402.5	403.2	403.9	403.9
147.5°	411.7	413.5	414.2	414.9	413.1
150°	422.3	423.3	424.1	424.8	423.7
152.5°	431.8	432.2	432.5	433.9	432.2
155°	440.7	440.0	440.3	442.1	440.0
157.5°	447.7	447.7	447.4	449.5	446.7
160°	454.1	453.7	453.4	455.5	453.0
162.5°	460.1	459.0	458.7	461.2	459.0
165°	464.7	463.6	463.3	466.1	463.6
167.5°	468.6	467.2	467.2	470.0	467.2
170°	471.8	470.3	470.3	473.2	470.3
172.5°	473.9	472.1	472.5	475.3	472.1
175°	475.6	473.9	474.2	476.7	473.9
177.5°	476.4	474.6	474.9	477.8	474.2
180°	475.6	475.6	475.6	475.6	475.6

(END OF REPORT)