

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010598

Luminaire Tested: S123DIP-B340D585UB2750-4F0-XX-W2A-D_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010598
REPORT IS A COMBINATION OF REPORTS P989817 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B340D585UB2750-4F0-XX-W2A-D_5000K
Description: Define 3 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3602.0 lumens
Efficiency: N/A
Efficacy: 126.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.25 / 1.37
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 28.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010598

CATALOG NUMBER: S123DIP-B340D585UB2750-4F0-XX-W2A-D_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010598

CATALOG NUMBER: S123DIP-B340D585UB2750-4F0-XX-W2A-D_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	103	103	103	103	93	93	93	93	75	75	75	57	57	57	42	42	42			34
1	94	89	85	81	84	80	77	74	64	62	60	49	48	46	36	35	34			27
2	85	77	71	66	76	70	64	60	56	52	49	43	40	38	31	29	28			22
3	77	68	60	54	69	61	55	50	49	44	41	38	34	32	27	25	23			19
4	70	60	52	46	63	54	47	42	43	38	34	33	30	27	24	22	20			16
5	65	53	45	39	58	48	41	36	39	33	29	30	26	23	22	19	17			14
6	59	47	39	33	53	43	36	31	35	29	25	27	23	20	20	17	15			12
7	55	43	35	29	49	39	32	27	31	26	22	24	21	18	18	15	13			10
8	51	38	31	26	46	35	28	24	28	23	20	22	18	16	16	14	12			9
9	47	35	28	23	42	32	25	21	26	21	17	20	17	14	15	13	11			8
10	44	32	25	20	40	29	23	19	24	19	16	19	15	13	14	11	10			8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4311	4311	4311
5°	4322	4184	4181
10°	4282	4071	4040
15°	4225	3946	3890
20°	4146	3807	3730
25°	4047	3649	3563
30°	3945	3507	3397
35°	3832	3358	3260
40°	3723	3222	3116
45°	3603	3089	2998
50°	3483	2959	2869
55°	3352	2824	2752
60°	3223	2687	2630
65°	3089	2540	2488
70°	2892	2377	2342
75°	2640	2190	2191
80°	2345	2001	2020
85°	2056	1846	1895

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3603 cd/sqm

TEST NUMBER: P1010598

CATALOG NUMBER: S123DIP-B340D585UB2750-4F0-XX-W2A-D_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.0	1.1
10°-20°	108.3	3.0
20°-30°	162.0	4.5
30°-40°	193.4	5.4
40°-50°	202.3	5.6
50°-60°	189.9	5.3
60°-70°	158.6	4.4
70°-80°	113.4	3.1
80°-90°	68.9	1.9
90°-100°	68.5	1.9
100°-110°	157.3	4.4
110°-120°	329.8	9.2
120°-130°	404.1	11.2
130°-140°	424.4	11.8
140°-150°	392.9	10.9
150°-160°	316.1	8.8
160°-170°	204.0	5.7
170°-180°	70.3	2.0
0°-30°	308.3	8.6
0°-40°	501.6	13.9
0°-60°	893.8	24.8
0°-90°	1234.8	34.3
90°-120°	555.5	15.4
90°-150°	1776.9	49.3
90°-180°	2367.0	65.7
0°-180°	3602.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	400	400	400	400	400	
5°	401	400	397	401	400	38
15°	382	383	383	387	386	108
25°	345	349	350	356	356	159
35°	297	304	309	316	318	186
45°	243	253	264	272	276	187
55°	185	199	215	227	230	166
65°	128	145	164	177	182	126
75°	69	90	112	126	131	74
85°	21	43	66	81	86	22
90°	6	33	62	80	85	6
95°	38	33	60	78	82	44
105°	167	184	153	68	73	177
115°	309	318	338	354	360	306
125°	434	439	454	464	468	388
135°	540	543	550	559	560	416
145°	622	626	627	632	633	390
155°	685	684	685	687	684	316
165°	722	721	720	725	721	204
175°	740	737	737	741	737	70
180°	740	740	740	740	740	

TEST NUMBER: P1010598

CATALOG NUMBER: S123DIP-B340D585UB2750-4F0-XX-W2A-D_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	400.5	400.5	400.5	400.5	400.5
2.5°	402.7	401.4	397.9	401.4	400.9
5°	400.9	400.1	397.4	400.9	400.5
7.5°	397.9	397.9	395.3	399.6	399.2
10°	393.5	394.4	392.2	396.6	395.7
12.5°	388.3	389.6	388.3	392.2	391.3
15°	381.7	383.1	382.6	387.0	386.5
17.5°	373.9	376.5	376.1	380.0	379.1
20°	365.2	367.8	368.7	372.6	373.0
22.5°	356.0	358.6	359.9	365.2	364.7
25°	344.7	349.0	350.3	356.0	356.0
27.5°	333.8	338.6	341.2	346.0	346.4
30°	322.0	327.6	331.1	336.4	336.4
32.5°	308.9	315.4	320.2	325.9	327.2
35°	296.7	303.6	309.3	315.9	317.6
37.5°	283.6	291.4	298.0	305.4	306.7
40°	270.5	278.3	287.1	294.5	296.2
42.5°	256.1	266.1	275.3	283.6	286.2
45°	242.6	253.0	263.9	272.2	275.7
47.5°	228.2	240.0	252.2	261.3	263.9
50°	214.2	226.4	240.0	250.0	253.0
52.5°	199.4	212.5	227.7	238.2	242.1
55°	185.0	199.4	215.1	226.9	230.4
57.5°	171.0	185.9	202.9	214.6	218.6
60°	156.2	171.9	189.8	202.0	206.8
62.5°	142.2	158.4	177.6	189.8	194.1
65°	127.8	144.8	164.0	177.1	181.5
67.5°	113.4	131.3	150.5	164.9	168.4
70°	98.2	116.9	137.9	151.8	156.2
72.5°	84.2	103.0	124.8	139.2	143.5
75°	69.4	89.9	111.7	126.1	131.3
77.5°	56.7	77.2	99.0	114.3	118.2
80°	43.2	64.6	87.3	102.1	106.5
82.5°	31.4	53.2	76.3	91.2	95.5
85°	21.4	43.2	66.3	81.1	85.5
87.5°	13.1	34.9	57.2	72.0	76.3
90°	6.2	33.0	62.5	79.5	85.0
92.5°	17.8	33.3	60.1	78.3	82.8
95°	38.3	32.8	60.2	77.6	82.0
97.5°	65.4	65.7	58.2	75.7	80.5
100°	96.8	121.7	56.1	73.1	78.1
102.5°	132.6	152.0	76.0	70.1	75.5
105°	167.2	183.8	153.0	68.0	73.1
107.5°	203.6	217.7	243.8	171.0	102.9
110°	240.0	252.2	275.7	269.0	193.9

TEST NUMBER: P1010598

CATALOG NUMBER: S123DIP-B340D585UB2750-4F0-XX-W2A-D_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	275.1	285.1	307.7	323.6	326.4
115°	309.3	317.8	338.5	354.5	360.2
117.5°	343.4	350.7	368.3	383.2	387.2
120°	374.2	381.4	397.4	411.9	414.9
122.5°	406.1	410.8	426.5	438.9	442.5
125°	434.2	438.6	453.5	463.7	467.9
127.5°	462.8	466.8	480.5	490.8	492.8
130°	489.2	493.2	504.1	514.6	516.1
132.5°	514.1	518.5	526.6	536.7	538.1
135°	539.9	542.7	549.7	559.2	559.8
137.5°	561.9	565.8	570.0	579.7	580.8
140°	583.3	586.6	589.6	598.4	599.5
142.5°	603.7	606.6	608.2	615.6	616.1
145°	622.4	625.8	626.9	631.5	633.2
147.5°	640.1	642.8	643.9	646.3	645.4
150°	656.6	658.2	659.3	660.4	659.7
152.5°	671.4	672.0	672.5	674.7	672.0
155°	685.1	684.0	684.6	687.3	684.0
157.5°	696.1	696.1	695.6	698.9	694.5
160°	706.0	705.5	704.9	708.2	704.4
162.5°	715.4	713.7	713.2	717.0	713.7
165°	722.5	720.9	720.3	724.7	720.9
167.5°	728.5	726.3	726.3	730.7	726.3
170°	733.5	731.3	731.3	735.7	731.3
172.5°	736.8	734.0	734.6	739.0	734.0
175°	739.5	736.8	737.3	741.2	736.8
177.5°	740.6	737.9	738.4	742.8	737.3
180°	739.5	739.5	739.5	739.5	739.5

(END OF REPORT)