

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010601

Luminaire Tested: S123DIP-B340D585UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010601
REPORT IS A COMBINATION OF REPORTS P989820 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B340D585UB2750-4F0-XX-W2A-F_3500K
Description: Define 3 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3736.0 lumens
Efficiency: N/A
Efficacy: 131.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 28.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010601

CATALOG NUMBER: S123DIP-B340D585UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1010601

CATALOG NUMBER: S123DIP-B340D585UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44
1	95	91	87	83	86	82	79	76	67	64	62	52	51	49	39	38	37
2	86	79	73	68	78	72	67	62	58	55	51	46	43	41	34	33	31
3	79	69	62	56	71	63	57	52	51	47	43	40	37	35	30	28	27
4	72	61	54	48	65	56	49	44	46	41	37	36	32	30	27	25	23
5	66	55	47	41	59	50	43	38	41	36	32	32	29	26	24	22	20
6	61	49	41	35	55	45	38	33	37	31	27	29	25	22	22	19	17
7	56	44	36	31	51	40	33	29	33	28	24	26	23	20	20	17	15
8	52	40	32	27	47	36	30	25	30	25	21	24	20	18	18	16	14
9	48	36	29	24	44	33	27	22	28	23	19	22	18	16	17	14	12
10	45	33	26	21	41	30	24	20	25	20	17	20	17	14	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5704	5704	5704
5°	5717	5506	5499
10°	5667	5321	5265
15°	5588	5127	5012
20°	5497	4911	4761
25°	5380	4684	4492
30°	5253	4449	4210
35°	5119	4209	3928
40°	4978	3957	3653
45°	4824	3712	3364
50°	4667	3438	3074
55°	4466	3153	2780
60°	4259	2839	2468
65°	4064	2498	2143
70°	3784	2120	1762
75°	3378	1680	1368
80°	2921	1180	967
85°	2276	635	485

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4824 cd/sqm

TEST NUMBER: P1010601

CATALOG NUMBER: S123DIP-B340D585UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.0	1.3
10°-20°	141.0	3.8
20°-30°	208.3	5.6
30°-40°	243.3	6.5
40°-50°	244.6	6.5
50°-60°	214.8	5.8
60°-70°	160.0	4.3
70°-80°	91.1	2.4
80°-90°	27.4	0.7
90°-100°	27.2	0.7
100°-110°	131.7	3.5
110°-120°	322.8	8.6
120°-130°	409.8	11.0
130°-140°	437.8	11.7
140°-150°	409.4	11.0
150°-160°	330.2	8.8
160°-170°	213.1	5.7
170°-180°	73.4	2.0
0°-30°	399.3	10.7
0°-40°	642.6	17.2
0°-60°	1102.0	29.5
0°-90°	1380.5	37.0
90°-120°	481.8	12.9
90°-150°	1738.7	46.5
90°-180°	2355.0	63.0
0°-180°	3736.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	530	530	530	530	530	
5°	530	528	523	528	527	50
15°	505	503	497	501	498	142
25°	458	456	450	450	449	211
35°	396	394	388	385	383	248
45°	325	323	317	312	309	251
55°	246	246	240	235	233	221
65°	168	166	161	158	156	166
75°	89	87	86	83	82	95
85°	24	23	23	22	22	25
90°	1	6	14	16	17	4
95°	35	12	18	22	22	42
105°	171	177	126	24	25	181
115°	321	324	330	335	338	317
125°	452	457	459	460	462	404
135°	563	567	569	571	569	434
145°	650	654	655	656	656	407
155°	716	715	715	718	715	330
165°	755	753	752	757	753	213
175°	773	770	770	774	770	74
180°	773	773	773	773	773	

TEST NUMBER: P1010601

CATALOG NUMBER: S123DIP-B340D585UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	529.9	529.9	529.9	529.9	529.9
2.5°	532.1	530.3	525.3	529.9	529.4
5°	530.3	528.0	523.0	527.6	526.7
7.5°	526.2	523.9	518.9	523.0	522.6
10°	520.8	518.5	512.6	516.7	515.7
12.5°	513.5	511.6	506.2	508.9	508.5
15°	504.8	503.0	497.1	500.7	498.0
17.5°	495.2	493.0	487.0	489.8	488.9
20°	484.3	481.6	475.6	477.5	476.1
22.5°	472.0	469.3	463.3	464.7	462.9
25°	458.3	455.6	449.7	450.1	448.8
27.5°	444.2	441.5	435.1	435.6	434.2
30°	428.7	426.4	420.1	420.1	416.9
32.5°	413.2	410.0	405.5	402.3	400.9
35°	396.4	393.6	387.7	385.0	382.7
37.5°	379.5	375.9	369.9	366.8	365.4
40°	361.7	359.0	352.6	349.0	347.2
42.5°	344.0	340.8	334.4	330.8	328.9
45°	324.8	323.0	317.1	311.6	309.4
47.5°	306.2	303.4	298.0	292.5	290.7
50°	287.0	284.8	278.8	273.8	271.1
52.5°	267.0	265.6	259.2	255.1	252.4
55°	246.5	246.0	240.1	235.1	232.8
57.5°	227.3	225.5	221.0	216.4	213.7
60°	206.4	205.9	200.5	196.4	194.1
62.5°	187.7	186.3	180.9	176.8	175.4
65°	168.1	165.8	161.3	157.6	156.3
67.5°	147.2	145.3	141.7	138.5	136.7
70°	128.5	125.7	123.0	119.8	117.5
72.5°	108.9	107.1	103.9	101.1	100.2
75°	88.8	87.0	85.7	83.4	82.0
77.5°	71.1	70.2	68.3	66.5	66.5
80°	53.8	52.4	51.5	51.0	51.0
82.5°	36.9	36.9	36.9	36.0	35.5
85°	23.7	22.8	22.8	21.9	21.9
87.5°	11.8	10.5	10.0	9.6	9.6
90°	0.6	6.3	13.8	16.1	17.2
92.5°	13.2	9.8	14.9	18.9	19.5
95°	35.0	11.5	17.8	21.8	21.8
97.5°	63.7	47.6	18.4	23.0	23.5
100°	97.0	108.5	18.9	23.5	24.1
102.5°	134.9	142.4	42.5	23.5	24.7
105°	171.1	177.4	125.7	24.1	25.3
107.5°	209.5	214.7	223.3	134.9	59.7
110°	248.0	252.6	258.9	239.9	157.9

TEST NUMBER: P1010601

CATALOG NUMBER: S123DIP-B340D585UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	284.7	288.7	295.0	300.2	299.1
115°	320.9	324.3	329.5	335.2	337.5
117.5°	356.5	360.5	363.4	368.0	368.5
120°	389.2	394.4	396.1	400.7	400.7
122.5°	422.5	426.5	428.8	431.7	432.2
125°	452.3	456.9	459.2	460.4	461.5
127.5°	482.2	486.8	489.6	491.4	490.2
130°	509.7	514.3	516.6	518.9	517.8
132.5°	536.1	540.7	542.5	544.8	543.0
135°	563.1	566.6	568.9	570.6	568.9
137.5°	586.1	590.7	591.8	594.7	593.5
140°	609.0	612.5	614.2	616.5	615.4
142.5°	630.3	633.7	635.4	637.2	635.4
145°	649.8	653.8	655.0	656.1	656.1
147.5°	668.7	671.6	672.8	673.9	671.0
150°	686.0	687.7	688.8	690.0	688.3
152.5°	701.5	702.0	702.6	704.9	702.0
155°	715.8	714.7	715.2	718.1	714.7
157.5°	727.3	727.3	726.7	730.2	725.6
160°	737.6	737.0	736.5	739.9	735.9
162.5°	747.4	745.7	745.1	749.1	745.7
165°	754.8	753.1	752.5	757.1	753.1
167.5°	761.2	758.9	758.9	763.5	758.9
170°	766.3	764.0	764.0	768.6	764.0
172.5°	769.8	766.9	767.5	772.1	766.9
175°	772.6	769.8	770.3	774.4	769.8
177.5°	773.8	770.9	771.5	776.1	770.3
180°	772.6	772.6	772.6	772.6	772.6

(END OF REPORT)