

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010915

Luminaire Tested: S123RDIP-B340D805UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010915
REPORT IS A COMBINATION OF REPORTS P993291 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B340D805UB2750-4F0-XX-W2A-F_3000K
Description: Define 3 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4398.0 lumens
Efficiency: N/A
Efficacy: 129.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 34.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010915

CATALOG NUMBER: S123RDIP-B340D805UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010915

CATALOG NUMBER: S123RDIP-B340D805UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	72	72	72	53	53	53	37	37	37
1	93	89	85	82	83	80	77	74	63	61	59	47	46	45	33	32	31
2	85	78	72	67	76	70	65	61	55	52	49	42	39	38	29	28	27
3	78	69	62	56	69	62	56	51	49	45	41	37	34	32	26	24	23
4	71	61	53	47	63	55	48	43	43	39	35	33	30	27	23	21	20
5	65	54	46	41	58	49	42	37	39	34	30	30	26	24	21	19	17
6	60	48	41	35	54	44	37	32	35	30	26	27	23	21	19	17	15
7	55	44	36	31	49	39	33	28	32	27	23	24	21	18	17	15	14
8	51	39	32	27	46	36	29	25	29	24	21	22	19	16	16	14	12
9	48	36	29	24	43	33	26	22	26	22	18	20	17	15	15	13	11
10	44	33	26	21	40	30	24	20	24	20	16	19	15	13	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6018	6018	6018
5°	6028	5804	5789
10°	5980	5586	5477
15°	5902	5316	5134
20°	5801	5023	4752
25°	5695	4719	4388
30°	5561	4394	3960
35°	5423	4075	3570
40°	5292	3729	3138
45°	5124	3391	2751
50°	4940	3029	2350
55°	4749	2643	1981
60°	4566	2247	1609
65°	4329	1840	1256
70°	4032	1391	897
75°	3606	943	711
80°	3078	656	499
85°	2305	354	262

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5124 cd/sqm

TEST NUMBER: P1010915

CATALOG NUMBER: S123RDIP-B340D805UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.6	1.2
10°-20°	146.2	3.3
20°-30°	210.5	4.8
30°-40°	237.1	5.4
40°-50°	226.7	5.2
50°-60°	185.6	4.2
60°-70°	125.1	2.8
70°-80°	62.8	1.4
80°-90°	18.5	0.4
90°-100°	36.2	0.8
100°-110°	175.2	4.0
110°-120°	429.3	9.8
120°-130°	545.1	12.4
130°-140°	582.3	13.2
140°-150°	544.5	12.4
150°-160°	439.2	10.0
160°-170°	283.4	6.4
170°-180°	97.7	2.2
0°-30°	409.2	9.3
0°-40°	646.3	14.7
0°-60°	1058.7	24.1
0°-90°	1265.0	28.8
90°-120°	640.8	14.6
90°-150°	2312.6	52.6
90°-180°	3133.0	71.2
0°-180°	4398.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	559	559	559	559	559	
5°	559	557	551	555	554	53
15°	533	528	516	513	510	150
25°	485	474	453	443	438	223
35°	420	404	375	356	348	263
45°	345	325	290	264	253	266
55°	262	240	201	175	166	235
65°	179	154	119	97	92	177
75°	95	73	48	44	43	101
85°	24	14	13	12	12	26
90°	1	8	18	21	23	4
95°	47	15	24	29	29	56
105°	228	236	167	32	34	241
115°	427	431	438	446	449	422
125°	602	608	611	612	614	538
135°	749	754	757	759	757	577
145°	864	870	871	873	873	541
155°	952	951	951	955	951	439
165°	1004	1002	1001	1007	1002	284
175°	1028	1024	1025	1030	1024	98
180°	1028	1028	1028	1028	1028	

TEST NUMBER: P1010915

CATALOG NUMBER: S123RDIP-B340D805UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	559.1	559.1	559.1	559.1	559.1
2.5°	561.3	559.5	554.1	559.1	558.1
5°	559.1	556.8	551.3	555.4	554.5
7.5°	555.0	552.7	545.9	548.6	547.3
10°	549.5	546.4	538.2	538.6	536.4
12.5°	541.8	538.2	527.8	527.3	524.6
15°	533.2	528.2	515.5	513.3	510.1
17.5°	522.8	517.3	501.5	496.9	492.4
20°	511.0	503.7	486.5	480.6	475.2
22.5°	497.8	489.2	470.6	462.9	457.9
25°	485.1	473.8	453.0	443.4	438.4
27.5°	469.7	457.5	434.8	422.1	414.4
30°	453.9	440.3	414.9	399.5	392.2
32.5°	438.0	422.1	394.9	377.7	370.0
35°	419.9	403.5	375.4	355.9	347.8
37.5°	401.7	384.0	354.6	332.8	322.8
40°	384.5	364.5	332.3	308.8	298.3
42.5°	365.0	345.0	311.5	285.2	276.1
45°	345.0	324.6	289.7	263.9	253.0
47.5°	325.5	302.9	268.4	240.3	230.8
50°	303.8	282.5	245.7	217.6	207.2
52.5°	284.3	260.7	224.4	195.0	185.9
55°	262.1	239.9	201.3	175.0	165.9
57.5°	242.1	218.1	179.1	154.2	146.5
60°	221.3	196.3	158.7	134.2	126.5
62.5°	200.4	175.5	137.8	115.2	107.0
65°	179.1	154.2	118.8	96.6	91.6
67.5°	157.8	132.4	97.9	81.2	75.7
70°	136.9	112.4	80.7	64.8	59.8
72.5°	116.1	92.0	63.9	51.7	50.3
75°	94.8	73.0	48.1	43.5	42.6
77.5°	75.3	55.3	37.6	34.9	34.0
80°	56.7	38.1	28.6	27.2	26.3
82.5°	39.0	23.6	20.4	19.0	19.0
85°	24.0	14.1	12.7	11.8	11.8
87.5°	10.9	5.9	5.9	5.4	5.0
90°	0.8	8.4	18.3	21.4	22.9
92.5°	17.6	13.0	19.9	25.2	26.0
95°	46.6	15.3	23.7	29.0	29.0
97.5°	84.7	63.4	24.4	30.5	31.3
100°	129.0	144.3	25.2	31.3	32.1
102.5°	179.4	189.3	56.5	31.3	32.8
105°	227.5	235.9	167.2	32.1	33.6
107.5°	278.7	285.5	297.0	179.4	79.4
110°	329.8	335.9	344.3	319.1	210.0

TEST NUMBER: P1010915

CATALOG NUMBER: S123RDIP-B340D805UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	378.7	384.0	392.4	399.3	397.8
115°	426.8	431.4	438.2	445.9	448.9
117.5°	474.1	479.5	483.3	489.4	490.2
120°	517.7	524.5	526.8	532.9	532.9
122.5°	561.9	567.3	570.3	574.2	574.9
125°	601.6	607.7	610.8	612.3	613.9
127.5°	641.3	647.4	651.3	653.6	652.0
130°	678.0	684.1	687.2	690.2	688.7
132.5°	713.1	719.2	721.5	724.6	722.3
135°	749.0	753.6	756.6	758.9	756.6
137.5°	779.5	785.6	787.2	791.0	789.5
140°	810.1	814.7	816.9	820.0	818.5
142.5°	838.3	842.9	845.2	847.5	845.2
145°	864.3	869.6	871.2	872.7	872.7
147.5°	889.5	893.3	894.8	896.4	892.5
150°	912.4	914.7	916.2	917.7	915.4
152.5°	933.0	933.8	934.5	937.6	933.8
155°	952.1	950.6	951.3	955.1	950.6
157.5°	967.4	967.4	966.6	971.2	965.1
160°	981.1	980.3	979.6	984.2	978.8
162.5°	994.1	991.8	991.0	996.4	991.8
165°	1004.0	1001.7	1001.0	1007.1	1001.7
167.5°	1012.4	1009.3	1009.3	1015.5	1009.3
170°	1019.3	1016.2	1016.2	1022.3	1016.2
172.5°	1023.9	1020.0	1020.8	1026.9	1020.0
175°	1027.7	1023.9	1024.6	1030.0	1023.9
177.5°	1029.2	1025.4	1026.1	1032.3	1024.6
180°	1027.7	1027.7	1027.7	1027.7	1027.7

(END OF REPORT)