

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010916

Luminaire Tested: S123RDIP-B340D805UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010916
REPORT IS A COMBINATION OF REPORTS P993292 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B340D805UB2750-4F0-XX-W2A-F_3500K
Description: Define 3 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4418.0 lumens
Efficiency: N/A
Efficacy: 129.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 34.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010916

CATALOG NUMBER: S123RDIP-B340D805UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1010916

CATALOG NUMBER: S123RDIP-B340D805UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	72	72	72	53	53	53	37	37	37
1	93	89	85	82	83	80	77	74	63	61	59	47	46	45	33	32	31
2	85	78	72	67	76	70	65	61	55	52	49	42	39	38	29	28	27
3	78	69	62	56	69	62	56	51	49	45	41	37	34	32	26	24	23
4	71	61	53	47	63	55	48	43	43	39	35	33	30	27	23	21	20
5	65	54	46	41	58	49	42	37	39	34	30	30	26	24	21	19	17
6	60	48	41	35	54	44	37	32	35	30	26	27	23	21	19	17	15
7	55	44	36	31	49	39	33	28	32	27	23	24	21	18	17	15	14
8	51	39	32	27	46	36	29	25	29	24	21	22	19	16	16	14	12
9	48	36	29	24	43	33	26	22	26	22	18	20	17	15	15	13	11
10	44	33	26	21	40	30	24	20	24	20	16	19	15	13	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6046	6046	6046
5°	6056	5833	5817
10°	6008	5613	5502
15°	5930	5342	5158
20°	5828	5047	4774
25°	5723	4741	4409
30°	5587	4415	3979
35°	5449	4095	3587
40°	5316	3747	3154
45°	5149	3407	2764
50°	4963	3044	2361
55°	4771	2656	1991
60°	4587	2257	1616
65°	4349	1849	1261
70°	4052	1398	901
75°	3621	947	714
80°	3089	658	501
85°	2315	356	262

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5149 cd/sqm

TEST NUMBER: P1010916

CATALOG NUMBER: S123RDIP-B340D805UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.8	1.2
10°-20°	146.9	3.3
20°-30°	211.5	4.8
30°-40°	238.2	5.4
40°-50°	227.8	5.2
50°-60°	186.5	4.2
60°-70°	125.7	2.8
70°-80°	63.1	1.4
80°-90°	18.5	0.4
90°-100°	36.4	0.8
100°-110°	176.0	4.0
110°-120°	431.3	9.8
120°-130°	547.5	12.4
130°-140°	584.9	13.2
140°-150°	546.9	12.4
150°-160°	441.1	10.0
160°-170°	284.7	6.4
170°-180°	98.1	2.2
0°-30°	411.2	9.3
0°-40°	649.4	14.7
0°-60°	1063.7	24.1
0°-90°	1271.0	28.8
90°-120°	643.7	14.6
90°-150°	2323.0	52.6
90°-180°	3147.0	71.2
0°-180°	4418.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	562	562	562	562	562	
5°	562	559	554	558	557	53
15°	536	531	518	516	512	151
25°	488	476	455	446	440	224
35°	422	406	377	358	349	264
45°	347	326	291	265	254	268
55°	263	241	202	176	167	236
65°	180	155	119	97	92	178
75°	95	73	48	44	43	101
85°	24	14	13	12	12	26
90°	1	8	18	22	23	4
95°	47	15	24	29	29	56
105°	228	237	168	32	34	242
115°	429	433	440	448	451	423
125°	604	610	614	615	617	540
135°	752	757	760	762	760	579
145°	868	874	875	877	877	544
155°	956	955	956	959	955	441
165°	1008	1006	1005	1012	1006	285
175°	1032	1028	1029	1035	1028	98
180°	1032	1032	1032	1032	1032	

TEST NUMBER: P1010916

CATALOG NUMBER: S123RDIP-B340D805UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	561.7	561.7	561.7	561.7	561.7
2.5°	564.0	562.2	556.7	561.7	560.8
5°	561.7	559.4	554.0	558.1	557.2
7.5°	557.6	555.3	548.5	551.2	549.9
10°	552.1	549.0	540.8	541.2	538.9
12.5°	544.4	540.8	530.3	529.8	527.1
15°	535.7	530.7	518.0	515.7	512.5
17.5°	525.3	519.8	503.9	499.3	494.7
20°	513.4	506.1	488.8	482.9	477.4
22.5°	500.2	491.6	472.9	465.1	460.1
25°	487.5	476.1	455.1	445.5	440.5
27.5°	472.0	459.7	436.9	424.1	416.4
30°	456.0	442.4	416.8	401.4	394.1
32.5°	440.1	424.1	396.8	379.5	371.7
35°	421.9	405.5	377.2	357.6	349.4
37.5°	403.6	385.9	356.3	334.4	324.4
40°	386.3	366.3	333.9	310.2	299.8
42.5°	366.7	346.7	313.0	286.5	277.4
45°	346.7	326.2	291.1	265.1	254.2
47.5°	327.1	304.3	269.7	241.4	231.9
50°	305.2	283.8	246.9	218.7	208.2
52.5°	285.6	261.9	225.5	195.9	186.8
55°	263.3	241.0	202.3	175.8	166.7
57.5°	243.3	219.1	179.9	154.9	147.1
60°	222.3	197.3	159.4	134.8	127.1
62.5°	201.4	176.3	138.5	115.7	107.5
65°	179.9	154.9	119.4	97.0	92.0
67.5°	158.5	133.0	98.4	81.5	76.1
70°	137.6	113.0	81.1	65.1	60.1
72.5°	116.6	92.5	64.2	51.9	50.6
75°	95.2	73.3	48.3	43.7	42.8
77.5°	75.6	55.6	37.8	35.1	34.2
80°	56.9	38.3	28.7	27.3	26.4
82.5°	39.2	23.7	20.5	19.1	19.1
85°	24.1	14.1	12.8	11.8	11.8
87.5°	10.9	5.9	5.9	5.5	5.0
90°	0.8	8.4	18.4	21.5	23.0
92.5°	17.6	13.0	19.9	25.3	26.1
95°	46.8	15.3	23.8	29.1	29.1
97.5°	85.1	63.7	24.5	30.7	31.4
100°	129.6	144.9	25.3	31.4	32.2
102.5°	180.2	190.2	56.8	31.4	33.0
105°	228.5	237.0	168.0	32.2	33.7
107.5°	279.9	286.8	298.3	180.2	79.8
110°	331.3	337.4	345.9	320.6	210.9

TEST NUMBER: P1010916

CATALOG NUMBER: S123RDIP-B340D805UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	380.4	385.8	394.2	401.1	399.6
115°	428.7	433.3	440.2	447.9	450.9
117.5°	476.3	481.6	485.5	491.6	492.4
120°	520.0	526.9	529.2	535.3	535.3
122.5°	564.4	569.8	572.9	576.7	577.5
125°	604.3	610.5	613.5	615.1	616.6
127.5°	644.2	650.3	654.2	656.5	654.9
130°	681.0	687.2	690.2	693.3	691.8
132.5°	716.3	722.4	724.7	727.8	725.5
135°	752.3	756.9	760.0	762.3	760.0
137.5°	783.0	789.2	790.7	794.5	793.0
140°	813.7	818.3	820.6	823.7	822.1
142.5°	842.1	846.7	849.0	851.3	849.0
145°	868.1	873.5	875.0	876.6	876.6
147.5°	893.5	897.3	898.8	900.4	896.5
150°	916.5	918.8	920.3	921.8	919.5
152.5°	937.2	937.9	938.7	941.8	937.9
155°	956.3	954.8	955.6	959.4	954.8
157.5°	971.7	971.7	970.9	975.5	969.4
160°	985.5	984.7	983.9	988.5	983.2
162.5°	998.5	996.2	995.5	1000.8	996.2
165°	1008.5	1006.2	1005.4	1011.6	1006.2
167.5°	1016.9	1013.9	1013.9	1020.0	1013.9
170°	1023.8	1020.8	1020.8	1026.9	1020.8
172.5°	1028.4	1024.6	1025.4	1031.5	1024.6
175°	1032.3	1028.4	1029.2	1034.6	1028.4
177.5°	1033.8	1030.0	1030.7	1036.9	1029.2
180°	1032.3	1032.3	1032.3	1032.3	1032.3

(END OF REPORT)