

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010917

Luminaire Tested: S123RDIP-B340D805UB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010917
REPORT IS A COMBINATION OF REPORTS P993293 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B340D805UB2750-4F0-XX-W2A-F_4000K
Description: Define 3 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4373.0 lumens
Efficiency: N/A
Efficacy: 128.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 34.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010917

CATALOG NUMBER: S123RDIP-B340D805UB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010917

CATALOG NUMBER: S123RDIP-B340D805UB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	72	72	72	53	53	53	37	37	37
1	93	89	85	82	83	80	77	74	63	61	59	47	46	45	33	32	31
2	85	78	72	67	76	70	65	61	55	52	49	42	39	38	29	28	27
3	78	69	62	56	69	62	56	51	49	45	41	37	34	32	26	24	23
4	71	61	53	47	63	55	48	43	43	39	35	33	30	27	23	21	20
5	65	54	46	41	58	49	42	37	39	34	30	30	26	24	21	19	17
6	60	48	41	35	54	44	37	32	35	30	26	27	23	21	19	17	15
7	55	44	36	31	49	39	33	28	32	27	23	24	21	18	17	15	14
8	51	39	32	27	46	36	29	25	29	24	21	22	19	16	16	14	12
9	48	36	29	24	43	33	26	22	26	22	18	20	17	15	15	13	11
10	44	33	26	21	40	30	24	20	24	20	16	19	15	13	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5985	5985	5985
5°	5994	5773	5756
10°	5947	5555	5446
15°	5870	5288	5106
20°	5769	4995	4725
25°	5664	4692	4364
30°	5529	4370	3938
35°	5392	4053	3550
40°	5263	3709	3121
45°	5095	3372	2736
50°	4913	3013	2337
55°	4722	2629	1971
60°	4540	2234	1600
65°	4305	1829	1249
70°	4011	1384	892
75°	3583	937	707
80°	3062	651	497
85°	2296	351	259

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 5095 cd/sqm

TEST NUMBER: P1010917

CATALOG NUMBER: S123RDIP-B340D805UB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.3	1.2
10°-20°	145.4	3.3
20°-30°	209.3	4.8
30°-40°	235.7	5.4
40°-50°	225.5	5.2
50°-60°	184.6	4.2
60°-70°	124.4	2.8
70°-80°	62.4	1.4
80°-90°	18.4	0.4
90°-100°	36.0	0.8
100°-110°	174.2	4.0
110°-120°	426.9	9.8
120°-130°	541.9	12.4
130°-140°	578.9	13.2
140°-150°	541.4	12.4
150°-160°	436.7	10.0
160°-170°	281.8	6.4
170°-180°	97.1	2.2
0°-30°	407.0	9.3
0°-40°	642.7	14.7
0°-60°	1052.8	24.1
0°-90°	1258.0	28.8
90°-120°	637.1	14.6
90°-150°	2299.4	52.6
90°-180°	3115.0	71.2
0°-180°	4373.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	556	556	556	556	556	
5°	556	554	548	552	551	53
15°	530	525	513	510	507	149
25°	482	471	450	441	436	222
35°	418	401	373	354	346	261
45°	343	323	288	262	252	265
55°	261	238	200	174	165	234
65°	178	153	118	96	91	176
75°	94	73	48	43	42	100
85°	24	14	13	12	12	26
90°	1	8	18	21	23	4
95°	46	15	24	29	29	55
105°	226	235	166	32	33	240
115°	424	429	436	443	446	419
125°	598	604	607	609	610	534
135°	745	749	752	755	752	573
145°	859	865	866	868	868	538
155°	947	945	946	950	945	436
165°	998	996	995	1001	996	282
175°	1022	1018	1019	1024	1018	97
180°	1022	1022	1022	1022	1022	

TEST NUMBER: P1010917

CATALOG NUMBER: S123RDIP-B340D805UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	556.0	556.0	556.0	556.0	556.0
2.5°	558.2	556.4	551.0	556.0	555.1
5°	556.0	553.7	548.3	552.3	551.4
7.5°	551.9	549.6	542.9	545.6	544.2
10°	546.5	543.3	535.2	535.7	533.4
12.5°	538.8	535.2	524.8	524.4	521.7
15°	530.3	525.3	512.7	510.4	507.3
17.5°	519.9	514.5	498.7	494.2	489.7
20°	508.2	500.9	483.8	477.9	472.5
22.5°	495.1	486.5	468.0	460.4	455.4
25°	482.5	471.2	450.4	441.0	436.0
27.5°	467.1	455.0	432.4	419.8	412.1
30°	451.3	437.8	412.6	397.2	390.0
32.5°	435.6	419.8	392.7	375.6	367.9
35°	417.5	401.3	373.3	354.0	345.8
37.5°	399.5	381.9	352.6	331.0	321.0
40°	382.4	362.5	330.5	307.1	296.7
42.5°	363.0	343.1	309.8	283.6	274.6
45°	343.1	322.8	288.1	262.4	251.6
47.5°	323.7	301.2	266.9	239.0	229.5
50°	302.1	280.9	244.4	216.4	206.1
52.5°	282.7	259.3	223.2	193.9	184.9
55°	260.6	238.5	200.2	174.0	165.0
57.5°	240.8	216.9	178.1	153.3	145.6
60°	220.0	195.2	157.8	133.5	125.8
62.5°	199.3	174.5	137.1	114.5	106.4
65°	178.1	153.3	118.1	96.0	91.1
67.5°	156.9	131.7	97.4	80.7	75.3
70°	136.2	111.8	80.3	64.5	59.5
72.5°	115.4	91.5	63.6	51.4	50.0
75°	94.2	72.6	47.8	43.3	42.4
77.5°	74.8	55.0	37.4	34.7	33.8
80°	56.4	37.9	28.4	27.1	26.2
82.5°	38.8	23.4	20.3	18.9	18.9
85°	23.9	14.0	12.6	11.7	11.7
87.5°	10.8	5.9	5.9	5.4	5.0
90°	0.8	8.4	18.2	21.3	22.8
92.5°	17.5	12.9	19.7	25.1	25.8
95°	46.3	15.2	23.5	28.8	28.8
97.5°	84.3	63.0	24.3	30.4	31.1
100°	128.3	143.5	25.1	31.1	31.9
102.5°	178.4	188.3	56.2	31.1	32.6
105°	226.2	234.6	166.2	31.9	33.4
107.5°	277.1	283.9	295.3	178.4	78.9
110°	327.9	334.0	342.4	317.3	208.8

TEST NUMBER: P1010917

CATALOG NUMBER: S123RDIP-B340D805UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	376.5	381.8	390.2	397.0	395.5
115°	424.3	428.9	435.7	443.3	446.4
117.5°	471.4	476.7	480.5	486.6	487.4
120°	514.7	521.5	523.8	529.9	529.9
122.5°	558.7	564.0	567.1	570.9	571.6
125°	598.2	604.3	607.3	608.8	610.3
127.5°	637.7	643.7	647.5	649.8	648.3
130°	674.1	680.2	683.2	686.2	684.7
132.5°	709.0	715.1	717.4	720.4	718.1
135°	744.7	749.2	752.3	754.6	752.3
137.5°	775.1	781.1	782.7	786.4	784.9
140°	805.4	810.0	812.3	815.3	813.8
142.5°	833.5	838.1	840.3	842.6	840.3
145°	859.3	864.6	866.2	867.7	867.7
147.5°	884.4	888.2	889.7	891.2	887.4
150°	907.1	909.4	910.9	912.5	910.2
152.5°	927.6	928.4	929.2	932.2	928.4
155°	946.6	945.1	945.9	949.7	945.1
157.5°	961.8	961.8	961.0	965.6	959.5
160°	975.5	974.7	973.9	978.5	973.2
162.5°	988.4	986.1	985.3	990.6	986.1
165°	998.2	996.0	995.2	1001.3	996.0
167.5°	1006.6	1003.6	1003.6	1009.6	1003.6
170°	1013.4	1010.4	1010.4	1016.5	1010.4
172.5°	1018.0	1014.2	1014.9	1021.0	1014.2
175°	1021.8	1018.0	1018.7	1024.0	1018.0
177.5°	1023.3	1019.5	1020.3	1026.3	1018.7
180°	1021.8	1021.8	1021.8	1021.8	1021.8

(END OF REPORT)