

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010609

Luminaire Tested: S123DIP-B340D805UB2750-4F0-XX-W2A-D_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010609
REPORT IS A COMBINATION OF REPORTS P989873 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B340D805UB2750-4F0-XX-W2A-D_2700K
Description: Define 3 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4494.9 lumens
Efficiency: N/A
Efficacy: 131.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.25 / 1.37
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 34.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010609

CATALOG NUMBER: S123DIP-B340D805UB2750-4F0-XX-W2A-D_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1010609

CATALOG NUMBER: S123DIP-B340D805UB2750-4F0-XX-W2A-D_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36
1	92	88	84	80	82	79	75	72	61	59	57	46	44	43	31	30	29
2	84	76	70	65	75	68	63	59	53	50	47	40	37	35	27	25	24
3	76	67	60	54	68	60	54	49	47	43	39	35	32	29	24	22	20
4	70	59	51	45	62	53	46	41	41	37	33	31	28	25	21	19	17
5	64	52	44	38	57	47	40	35	37	32	28	28	24	21	19	17	15
6	59	47	39	33	52	42	35	30	33	28	24	25	21	19	17	15	13
7	54	42	34	29	48	38	31	26	30	25	21	22	19	16	15	13	12
8	50	38	30	25	44	34	28	23	27	22	19	20	17	14	14	12	10
9	46	34	27	22	41	31	25	20	25	20	17	19	15	13	13	11	9
10	43	31	24	20	39	28	22	18	23	18	15	17	14	12	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4442	4442	4442
5°	4455	4312	4308
10°	4413	4196	4164
15°	4355	4066	4009
20°	4272	3923	3844
25°	4170	3760	3672
30°	4065	3614	3500
35°	3948	3460	3360
40°	3836	3319	3212
45°	3713	3184	3089
50°	3589	3049	2956
55°	3454	2910	2835
60°	3320	2769	2710
65°	3184	2617	2564
70°	2980	2450	2412
75°	2720	2256	2257
80°	2416	2061	2080
85°	2113	1902	1953

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3713 cd/sqm

TEST NUMBER: P1010609

CATALOG NUMBER: S123DIP-B340D805UB2750-4F0-XX-W2A-D_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.2	0.9
10°-20°	111.6	2.5
20°-30°	166.9	3.7
30°-40°	199.3	4.4
40°-50°	208.5	4.6
50°-60°	195.6	4.4
60°-70°	163.4	3.6
70°-80°	116.9	2.6
80°-90°	71.6	1.6
90°-100°	79.6	1.8
100°-110°	205.8	4.6
110°-120°	447.1	9.9
120°-130°	552.6	12.3
130°-140°	582.7	13.0
140°-150°	540.9	12.0
150°-160°	435.4	9.7
160°-170°	281.0	6.3
170°-180°	96.8	2.2
0°-30°	317.7	7.1
0°-40°	516.9	11.5
0°-60°	921.1	20.5
0°-90°	1272.9	28.3
90°-120°	732.5	16.3
90°-150°	2408.8	53.6
90°-180°	3222.0	71.7
0°-180°	4494.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	413	413	413	413	413	
5°	413	412	410	413	413	39
15°	393	395	394	399	398	111
25°	355	360	361	367	367	164
35°	306	313	319	326	327	191
45°	250	261	272	280	284	193
55°	191	206	222	234	237	171
65°	132	149	169	182	187	130
75°	72	93	115	130	135	76
85°	22	44	68	84	88	23
90°	7	36	69	87	93	7
95°	51	38	68	87	92	59
105°	229	248	200	78	84	243
115°	425	435	458	477	483	420
125°	598	604	620	631	636	534
135°	743	748	756	766	766	572
145°	857	862	864	869	871	537
155°	944	942	943	947	942	435
165°	995	993	992	998	993	281
175°	1019	1015	1016	1021	1015	97
180°	1019	1019	1019	1019	1019	

TEST NUMBER: P1010609

CATALOG NUMBER: S123DIP-B340D805UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	412.7	412.7	412.7	412.7	412.7
2.5°	414.9	413.6	410.0	413.6	413.2
5°	413.2	412.3	409.6	413.2	412.7
7.5°	410.0	410.0	407.3	411.8	411.4
10°	405.5	406.4	404.2	408.7	407.8
12.5°	400.1	401.5	400.1	404.2	403.3
15°	393.4	394.7	394.3	398.8	398.3
17.5°	385.3	388.0	387.5	391.6	390.7
20°	376.3	379.0	379.9	383.9	384.4
22.5°	366.8	369.5	370.9	376.3	375.8
25°	355.2	359.7	361.0	366.8	366.8
27.5°	343.9	348.9	351.6	356.5	357.0
30°	331.8	337.6	341.2	346.6	346.6
32.5°	318.3	325.0	330.0	335.8	337.2
35°	305.7	312.9	318.7	325.5	327.3
37.5°	292.2	300.3	307.1	314.7	316.0
40°	278.7	286.8	295.8	303.5	305.3
42.5°	263.9	274.2	283.7	292.2	294.9
45°	250.0	260.7	272.0	280.5	284.1
47.5°	235.1	247.3	259.8	269.3	272.0
50°	220.7	233.3	247.3	257.6	260.7
52.5°	205.5	218.9	234.7	245.5	249.5
55°	190.6	205.5	221.6	233.8	237.4
57.5°	176.2	191.5	209.0	221.2	225.2
60°	160.9	177.1	195.6	208.1	213.1
62.5°	146.6	163.2	183.0	195.6	200.1
65°	131.7	149.3	169.0	182.5	187.0
67.5°	116.9	135.3	155.1	169.9	173.5
70°	101.2	120.5	142.1	156.4	160.9
72.5°	86.8	106.1	128.6	143.4	147.9
75°	71.5	92.6	115.1	129.9	135.3
77.5°	58.4	79.6	102.1	117.8	121.8
80°	44.5	66.5	89.9	105.2	109.7
82.5°	32.4	54.8	78.7	94.0	98.5
85°	22.0	44.5	68.3	83.6	88.1
87.5°	13.5	36.0	58.9	74.2	78.7
90°	6.6	36.2	69.0	87.3	93.3
92.5°	22.8	37.6	66.9	87.0	91.8
95°	51.1	37.6	68.0	87.2	91.7
97.5°	88.5	83.5	66.0	85.6	90.8
100°	131.9	161.5	64.1	83.1	88.4
102.5°	181.5	203.9	92.4	80.0	86.0
105°	229.2	248.3	199.5	78.1	83.7
107.5°	279.4	295.7	325.4	221.1	125.9
110°	329.7	343.8	370.2	356.9	252.3

TEST NUMBER: P1010609

CATALOG NUMBER: S123DIP-B340D805UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	378.1	389.7	415.2	433.2	435.8
115°	425.3	435.3	458.3	476.6	483.3
117.5°	472.3	481.1	500.2	517.1	521.4
120°	515.0	524.0	541.2	557.5	560.7
122.5°	558.9	565.1	582.0	595.7	599.7
125°	597.8	603.8	619.9	630.9	635.6
127.5°	637.1	642.8	657.8	669.0	670.7
130°	673.5	679.1	691.1	702.7	703.8
132.5°	707.9	713.9	722.9	734.0	735.0
135°	743.4	747.5	755.5	765.9	765.8
137.5°	773.7	779.3	784.0	795.0	795.7
140°	803.5	808.0	811.7	821.4	822.2
142.5°	831.5	835.6	837.9	846.0	846.0
145°	857.2	862.1	863.7	868.8	870.6
147.5°	881.8	885.6	887.1	889.9	887.9
150°	904.5	906.8	908.3	909.8	908.5
152.5°	925.0	925.7	926.5	929.5	925.7
155°	943.9	942.4	943.1	946.9	942.4
157.5°	959.0	959.0	958.3	962.8	956.8
160°	972.6	971.9	971.1	975.7	970.4
162.5°	985.5	983.2	982.5	987.8	983.2
165°	995.4	993.1	992.3	998.4	993.1
167.5°	1003.7	1000.7	1000.7	1006.7	1000.7
170°	1010.5	1007.5	1007.5	1013.5	1007.5
172.5°	1015.0	1011.3	1012.0	1018.1	1011.3
175°	1018.8	1015.0	1015.8	1021.1	1015.0
177.5°	1020.3	1016.6	1017.3	1023.4	1015.8
180°	1018.8	1018.8	1018.8	1018.8	1018.8

(END OF REPORT)