

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010610

Luminaire Tested: S123DIP-B340D805UB2750-4F0-XX-W2A-D_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010610
REPORT IS A COMBINATION OF REPORTS P989874 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B340D805UB2750-4F0-XX-W2A-D_3000K
Description: Define 3 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4534.0 lumens
Efficiency: N/A
Efficacy: 133.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.25 / 1.37
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 34.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010610

CATALOG NUMBER: S123DIP-B340D805UB2750-4F0-XX-W2A-D_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010610

CATALOG NUMBER: S123DIP-B340D805UB2750-4F0-XX-W2A-D_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36			28
1	92	88	84	80	82	79	75	72	61	59	57	46	44	43	31	30	29			23
2	84	76	70	65	75	68	63	59	53	50	47	40	37	35	27	25	24			18
3	76	67	60	54	68	60	54	49	47	43	39	35	32	29	24	22	20			15
4	70	59	51	45	62	53	46	41	41	37	33	31	28	25	21	19	17			13
5	64	52	44	38	57	47	40	35	37	32	28	28	24	21	19	17	15			11
6	59	47	39	33	52	42	35	30	33	28	24	25	21	19	17	15	13			10
7	54	42	34	29	48	38	31	26	30	25	21	22	19	16	15	13	12			9
8	50	38	30	25	44	34	28	23	27	22	19	20	17	14	14	12	10			8
9	46	34	27	22	41	31	25	20	25	20	17	19	15	13	13	11	9			7
10	43	31	24	20	39	28	22	18	23	18	15	17	14	12	12	10	8			6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4481	4481	4481
5°	4493	4349	4346
10°	4451	4232	4199
15°	4392	4102	4044
20°	4308	3957	3877
25°	4205	3793	3704
30°	4101	3646	3530
35°	3981	3490	3389
40°	3869	3349	3239
45°	3744	3211	3116
50°	3620	3075	2982
55°	3484	2936	2859
60°	3349	2793	2733
65°	3213	2641	2586
70°	3004	2470	2433
75°	2743	2276	2277
80°	2438	2079	2098
85°	2132	1919	1970

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3744 cd/sqm

TEST NUMBER: P1010610

CATALOG NUMBER: S123DIP-B340D805UB2750-4F0-XX-W2A-D_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.5	0.9
10°-20°	112.6	2.5
20°-30°	168.3	3.7
30°-40°	201.0	4.4
40°-50°	210.3	4.6
50°-60°	197.3	4.4
60°-70°	164.8	3.6
70°-80°	117.9	2.6
80°-90°	72.2	1.6
90°-100°	80.3	1.8
100°-110°	207.6	4.6
110°-120°	451.0	9.9
120°-130°	557.4	12.3
130°-140°	587.8	13.0
140°-150°	545.7	12.0
150°-160°	439.2	9.7
160°-170°	283.4	6.3
170°-180°	97.7	2.2
0°-30°	320.4	7.1
0°-40°	521.4	11.5
0°-60°	929.0	20.5
0°-90°	1283.9	28.3
90°-120°	738.9	16.3
90°-150°	2429.8	53.6
90°-180°	3250.0	71.7
0°-180°	4534.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	416	416	416	416	416	
5°	417	416	413	417	416	40
15°	397	398	398	402	402	112
25°	358	363	364	370	370	165
35°	308	316	322	328	330	193
45°	252	263	274	283	287	194
55°	192	207	224	236	239	172
65°	133	150	170	184	189	131
75°	72	93	116	131	136	77
85°	22	45	69	84	89	23
90°	7	36	70	88	94	7
95°	52	38	69	88	92	60
105°	231	250	201	79	84	245
115°	429	439	462	481	487	424
125°	603	609	625	636	641	539
135°	750	754	762	772	772	577
145°	865	870	871	876	878	541
155°	952	951	951	955	951	439
165°	1004	1002	1001	1007	1002	284
175°	1028	1024	1025	1030	1024	98
180°	1028	1028	1028	1028	1028	

TEST NUMBER: P1010610

CATALOG NUMBER: S123DIP-B340D805UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	416.3	416.3	416.3	416.3	416.3
2.5°	418.5	417.2	413.6	417.2	416.7
5°	416.7	415.8	413.1	416.7	416.3
7.5°	413.6	413.6	410.8	415.4	414.9
10°	409.0	409.9	407.7	412.2	411.3
12.5°	403.6	404.9	403.6	407.7	406.7
15°	396.8	398.1	397.7	402.2	401.8
17.5°	388.6	391.3	390.9	395.0	394.1
20°	379.5	382.3	383.2	387.3	387.7
22.5°	370.0	372.7	374.1	379.5	379.1
25°	358.2	362.8	364.1	370.0	370.0
27.5°	346.9	351.9	354.6	359.6	360.0
30°	334.7	340.5	344.2	349.6	349.6
32.5°	321.0	327.8	332.8	338.7	340.1
35°	308.3	315.6	321.5	328.3	330.1
37.5°	294.7	302.9	309.7	317.4	318.8
40°	281.1	289.3	298.4	306.1	307.9
42.5°	266.2	276.6	286.1	294.7	297.5
45°	252.1	263.0	274.3	283.0	286.6
47.5°	237.2	249.4	262.1	271.6	274.3
50°	222.6	235.3	249.4	259.8	263.0
52.5°	207.2	220.8	236.7	247.6	251.7
55°	192.3	207.2	223.6	235.8	239.4
57.5°	177.8	193.2	210.9	223.1	227.2
60°	162.3	178.7	197.3	209.9	214.9
62.5°	147.8	164.6	184.6	197.3	201.8
65°	132.9	150.5	170.5	184.1	188.6
67.5°	117.9	136.5	156.4	171.4	175.0
70°	102.0	121.5	143.3	157.8	162.3
72.5°	87.5	107.0	129.7	144.7	149.2
75°	72.1	93.4	116.1	131.0	136.5
77.5°	58.9	80.3	102.9	118.8	122.9
80°	44.9	67.1	90.7	106.1	110.6
82.5°	32.6	55.3	79.4	94.8	99.3
85°	22.2	44.9	68.9	84.3	88.9
87.5°	13.6	36.3	59.4	74.8	79.4
90°	6.7	36.5	69.5	88.1	94.1
92.5°	23.0	37.9	67.5	87.8	92.7
95°	51.6	38.0	68.6	87.9	92.5
97.5°	89.2	84.3	66.6	86.3	91.6
100°	133.1	162.9	64.7	83.9	89.2
102.5°	183.0	205.6	93.2	80.7	86.8
105°	231.1	250.4	201.2	78.8	84.4
107.5°	281.9	298.2	328.3	222.9	127.0
110°	332.5	346.8	373.3	359.9	254.4

TEST NUMBER: P1010610

CATALOG NUMBER: S123DIP-B340D805UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	381.4	393.1	418.7	436.9	439.5
115°	429.1	439.1	462.2	480.8	487.4
117.5°	476.4	485.4	504.6	521.6	526.0
120°	519.5	528.6	545.8	562.4	565.5
122.5°	563.7	570.0	587.1	601.0	604.8
125°	603.0	609.1	625.3	636.3	641.1
127.5°	642.7	648.3	663.5	674.9	676.5
130°	679.4	685.0	697.2	708.8	710.0
132.5°	714.0	720.1	729.2	740.5	741.3
135°	749.9	754.1	762.0	772.5	772.5
137.5°	780.4	786.1	790.8	801.9	802.7
140°	810.6	815.2	818.7	828.6	829.4
142.5°	838.8	842.9	845.2	853.4	853.4
145°	864.8	869.6	871.2	876.3	878.1
147.5°	889.5	893.3	894.8	897.8	895.7
150°	912.4	914.7	916.2	917.7	916.3
152.5°	933.0	933.8	934.5	937.6	933.8
155°	952.1	950.6	951.3	955.1	950.6
157.5°	967.4	967.4	966.6	971.2	965.1
160°	981.1	980.3	979.6	984.2	978.8
162.5°	994.1	991.8	991.0	996.4	991.8
165°	1004.0	1001.7	1001.0	1007.1	1001.7
167.5°	1012.4	1009.3	1009.3	1015.5	1009.3
170°	1019.3	1016.2	1016.2	1022.3	1016.2
172.5°	1023.9	1020.0	1020.8	1026.9	1020.0
175°	1027.7	1023.9	1024.6	1030.0	1023.9
177.5°	1029.2	1025.4	1026.1	1032.3	1024.6
180°	1027.7	1027.7	1027.7	1027.7	1027.7

(END OF REPORT)