

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010926

Luminaire Tested: S123RDIP-B560D1025UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010926
REPORT IS A COMBINATION OF REPORTS P993332 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B560D1025UB2750-4F0-XX-W2A-F_3500K
Description: Define 3 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6209.0 lumens
Efficiency: N/A
Efficacy: 118.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 52.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010926

CATALOG NUMBER: S123RDIP-B560D1025UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1010926

CATALOG NUMBER: S123RDIP-B560D1025UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	75	75	75	58	58	58	42	42	42
1	95	90	87	83	85	82	79	76	66	64	62	51	50	48	37	36	36
2	86	79	73	68	78	72	67	63	58	54	51	45	43	41	33	32	30
3	79	70	63	57	71	63	57	52	51	47	43	40	37	35	29	28	26
4	72	62	54	48	65	56	50	45	45	41	37	36	32	30	26	24	23
5	66	55	47	41	60	50	43	38	41	36	32	32	29	26	24	22	20
6	61	49	42	36	55	45	38	33	37	32	28	29	25	23	22	19	18
7	56	44	37	31	51	41	34	29	33	28	25	26	23	20	20	17	16
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	16	14
9	49	37	30	25	44	34	27	23	28	23	19	22	19	16	17	14	13
10	45	34	27	22	41	31	25	20	25	21	17	20	17	14	16	13	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10168	10168	10168
5°	10184	9808	9781
10°	10104	9440	9253
15°	9972	8983	8675
20°	9801	8487	8028
25°	9623	7972	7415
30°	9396	7425	6691
35°	9161	6886	6032
40°	8940	6301	5303
45°	8658	5730	4648
50°	8347	5119	3970
55°	8023	4466	3349
60°	7715	3796	2718
65°	7315	3108	2122
70°	6814	2351	1516
75°	6090	1592	1201
80°	5201	1107	842
85°	3900	599	441

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8658 cd/sqm

TEST NUMBER: P1010926

CATALOG NUMBER: S123RDIP-B560D1025UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.8	1.4
10°-20°	247.0	4.0
20°-30°	355.7	5.7
30°-40°	400.5	6.5
40°-50°	383.1	6.2
50°-60°	313.6	5.1
60°-70°	211.5	3.4
70°-80°	106.1	1.7
80°-90°	30.4	0.5
90°-100°	47.1	0.8
100°-110°	227.8	3.7
110°-120°	558.1	9.0
120°-130°	708.5	11.4
130°-140°	756.9	12.2
140°-150°	707.8	11.4
150°-160°	570.9	9.2
160°-170°	368.4	5.9
170°-180°	127.0	2.0
0°-30°	691.5	11.1
0°-40°	1092.0	17.6
0°-60°	1788.8	28.8
0°-90°	2136.7	34.4
90°-120°	833.0	13.4
90°-150°	3006.1	48.4
90°-180°	4072.0	65.6
0°-180°	6209.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	945	945	945	945	945	
5°	945	941	932	938	937	90
15°	901	892	871	867	862	254
25°	820	801	765	749	741	377
35°	709	682	634	601	588	444
45°	583	548	490	446	428	450
55°	443	405	340	296	280	397
65°	303	260	201	163	155	299
75°	160	123	81	74	72	171
85°	41	24	22	20	20	44
90°	1	11	24	28	30	6
95°	60	20	31	38	38	72
105°	296	307	217	42	44	314
115°	555	561	570	580	584	548
125°	782	790	794	796	798	699
135°	974	980	984	986	984	750
145°	1123	1130	1132	1134	1134	703
155°	1238	1236	1237	1242	1236	570
165°	1305	1302	1301	1309	1302	369
175°	1336	1331	1332	1339	1331	127
180°	1336	1336	1336	1336	1336	

TEST NUMBER: P1010926

CATALOG NUMBER: S123RDIP-B560D1025UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	944.6	944.6	944.6	944.6	944.6
2.5°	948.4	945.4	936.2	944.6	943.1
5°	944.6	940.8	931.6	938.5	936.9
7.5°	937.7	933.9	922.4	927.0	924.7
10°	928.5	923.1	909.4	910.1	906.3
12.5°	915.5	909.4	891.7	891.0	886.4
15°	900.9	892.5	871.0	867.2	861.9
17.5°	883.3	874.1	847.3	839.6	832.0
20°	863.4	851.1	822.0	812.1	802.9
22.5°	841.2	826.6	795.2	782.2	773.8
25°	819.7	800.6	765.3	749.2	740.8
27.5°	793.7	773.0	734.7	713.2	700.2
30°	766.9	743.9	701.0	674.9	662.7
32.5°	740.0	713.2	667.3	638.2	625.1
35°	709.4	681.8	634.3	601.4	587.6
37.5°	678.8	648.9	599.1	562.3	545.5
40°	649.6	615.9	561.5	521.7	504.1
42.5°	616.7	583.0	526.3	481.9	466.6
45°	583.0	548.5	489.5	445.9	427.5
47.5°	550.1	511.7	453.5	406.0	389.9
50°	513.3	477.3	415.2	367.7	350.1
52.5°	480.3	440.5	379.2	329.4	314.1
55°	442.8	405.3	340.1	295.7	280.4
57.5°	409.1	368.5	302.6	260.5	247.4
60°	373.9	331.7	268.1	226.8	213.7
62.5°	338.6	296.5	232.9	194.6	180.8
65°	302.6	260.5	200.7	163.2	154.8
67.5°	266.6	223.7	165.5	137.1	127.9
70°	231.4	190.0	136.4	109.6	101.1
72.5°	196.1	155.5	108.0	87.3	85.0
75°	160.1	123.3	81.2	73.5	72.0
77.5°	127.2	93.5	63.6	59.0	57.5
80°	95.8	64.4	48.3	46.0	44.4
82.5°	65.9	39.8	34.5	32.2	32.2
85°	40.6	23.7	21.5	19.9	19.9
87.5°	18.4	10.0	10.0	9.2	8.4
90°	1.0	10.9	23.8	27.8	29.8
92.5°	22.8	16.9	25.8	32.8	33.7
95°	60.5	19.8	30.8	37.7	37.7
97.5°	110.2	82.4	31.8	39.7	40.7
100°	167.7	187.6	32.8	40.7	41.7
102.5°	233.2	246.1	73.4	40.7	42.7
105°	295.7	306.7	217.3	41.7	43.7
107.5°	362.2	371.2	386.1	233.2	103.2
110°	428.7	436.7	447.6	414.8	272.9

TEST NUMBER: P1010926

CATALOG NUMBER: S123RDIP-B560D1025UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	492.2	499.2	510.1	519.0	517.1
115°	554.8	560.7	569.7	579.6	583.5
117.5°	616.3	623.2	628.2	636.1	637.1
120°	672.9	681.8	684.8	692.7	692.7
122.5°	730.4	737.4	741.3	746.3	747.3
125°	782.0	790.0	793.9	795.9	797.9
127.5°	833.6	841.6	846.5	849.5	847.5
130°	881.3	889.2	893.2	897.2	895.2
132.5°	926.9	934.9	937.8	941.8	938.8
135°	973.6	979.5	983.5	986.5	983.5
137.5°	1013.3	1021.2	1023.2	1028.2	1026.2
140°	1053.0	1058.9	1061.9	1065.9	1063.9
142.5°	1089.7	1095.6	1098.6	1101.6	1098.6
145°	1123.4	1130.4	1132.4	1134.3	1134.3
147.5°	1156.2	1161.1	1163.1	1165.1	1160.2
150°	1186.0	1188.9	1190.9	1192.9	1189.9
152.5°	1212.7	1213.7	1214.7	1218.7	1213.7
155°	1237.6	1235.6	1236.6	1241.5	1235.6
157.5°	1257.4	1257.4	1256.4	1262.4	1254.4
160°	1275.3	1274.3	1273.3	1279.2	1272.3
162.5°	1292.1	1289.2	1288.2	1295.1	1289.2
165°	1305.0	1302.1	1301.1	1309.0	1302.1
167.5°	1316.0	1312.0	1312.0	1319.9	1312.0
170°	1324.9	1320.9	1320.9	1328.9	1320.9
172.5°	1330.8	1325.9	1326.9	1334.8	1325.9
175°	1335.8	1330.8	1331.8	1338.8	1330.8
177.5°	1337.8	1332.8	1333.8	1341.8	1331.8
180°	1335.8	1335.8	1335.8	1335.8	1335.8

(END OF REPORT)