

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010934

Luminaire Tested: S123RDIP-B560D1195UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010934
REPORT IS A COMBINATION OF REPORTS P993370 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B560D1195UB2750-4F0-XX-W2A-F_2700K
Description: Define 3 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6833.0 lumens
Efficiency: N/A
Efficacy: 115.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 59
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010934

CATALOG NUMBER: S123RDIP-B560D1195UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1010934

CATALOG NUMBER: S123RDIP-B560D1195UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39	39	39	31
1	94	90	86	83	84	81	78	75	64	62	60	49	47	46	34	34	33	33	33	26
2	85	78	73	68	77	71	66	62	56	53	50	43	41	39	30	29	28	28	28	22
3	78	69	62	57	70	62	56	52	50	46	42	38	35	33	27	25	24	24	24	19
4	71	61	54	48	64	55	49	44	44	40	36	34	31	28	24	22	21	21	21	17
5	65	54	47	41	59	49	43	38	40	35	31	30	27	25	22	20	18	18	18	15
6	60	49	41	35	54	44	37	33	36	31	27	28	24	21	20	18	16	16	16	13
7	56	44	36	31	50	40	33	29	32	27	24	25	22	19	18	16	14	14	14	11
8	52	40	32	27	46	36	30	25	29	24	21	23	19	17	17	15	13	13	13	10
9	48	36	29	24	43	33	27	22	27	22	19	21	18	15	16	13	12	12	12	9
10	45	33	26	22	40	30	24	20	25	20	17	19	16	14	14	12	11	11	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10038	10038	10038
5°	10055	9684	9658
10°	9977	9319	9136
15°	9846	8869	8564
20°	9677	8380	7926
25°	9501	7871	7321
30°	9277	7330	6607
35°	9045	6799	5956
40°	8827	6221	5236
45°	8548	5657	4590
50°	8241	5055	3920
55°	7922	4409	3306
60°	7616	3748	2683
65°	7223	3070	2095
70°	6726	2320	1496
75°	6014	1572	1186
80°	5130	1093	833
85°	3852	590	437

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8548 cd/sqm

TEST NUMBER: P1010934

CATALOG NUMBER: S123RDIP-B560D1195UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.7	1.3
10°-20°	243.9	3.6
20°-30°	351.2	5.1
30°-40°	395.5	5.8
40°-50°	378.3	5.5
50°-60°	309.7	4.5
60°-70°	208.8	3.1
70°-80°	104.7	1.5
80°-90°	30.5	0.4
90°-100°	54.6	0.8
100°-110°	264.1	3.9
110°-120°	647.3	9.5
120°-130°	821.7	12.0
130°-140°	877.8	12.8
140°-150°	820.8	12.0
150°-160°	662.1	9.7
160°-170°	427.3	6.3
170°-180°	147.2	2.2
0°-30°	682.7	10.0
0°-40°	1078.2	15.8
0°-60°	1766.1	25.8
0°-90°	2110.1	30.9
90°-120°	966.0	14.1
90°-150°	3486.3	51.0
90°-180°	4723.0	69.1
0°-180°	6833.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	933	933	933	933	933	
5°	933	929	920	927	925	88
15°	890	881	860	856	851	251
25°	809	790	756	740	731	372
35°	700	673	626	594	580	438
45°	576	542	483	440	422	444
55°	437	400	336	292	277	392
65°	299	257	198	161	153	296
75°	158	122	80	73	71	168
85°	40	23	21	20	20	44
90°	1	13	28	32	34	6
95°	70	23	36	44	44	84
105°	343	356	252	48	51	364
115°	643	650	661	672	677	635
125°	907	916	921	923	925	810
135°	1129	1136	1141	1144	1141	869
145°	1303	1311	1313	1316	1316	816
155°	1435	1433	1434	1440	1433	661
165°	1514	1510	1509	1518	1510	428
175°	1549	1544	1545	1553	1544	147
180°	1549	1549	1549	1549	1549	

TEST NUMBER: P1010934

CATALOG NUMBER: S123RDIP-B560D1195UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	932.6	932.6	932.6	932.6	932.6
2.5°	936.4	933.4	924.3	932.6	931.1
5°	932.6	928.9	919.8	926.6	925.1
7.5°	925.8	922.1	910.7	915.2	913.0
10°	916.8	911.5	897.8	898.6	894.8
12.5°	903.9	897.8	880.4	879.7	875.2
15°	889.5	881.2	860.0	856.2	850.9
17.5°	872.1	863.1	836.6	829.0	821.4
20°	852.5	840.4	811.6	801.8	792.7
22.5°	830.5	816.2	785.1	772.3	764.0
25°	809.3	790.4	755.6	739.8	731.4
27.5°	783.6	763.2	725.4	704.2	691.3
30°	757.2	734.5	692.1	666.4	654.3
32.5°	730.7	704.2	658.8	630.1	617.2
35°	700.4	673.2	626.3	593.8	580.2
37.5°	670.2	640.7	591.5	555.2	538.6
40°	641.4	608.1	554.4	515.1	497.7
42.5°	608.9	575.6	519.6	475.8	460.6
45°	575.6	541.6	483.3	440.2	422.1
47.5°	543.1	505.3	447.8	400.9	385.0
50°	506.8	471.2	410.0	363.1	345.7
52.5°	474.3	434.9	374.4	325.3	310.1
55°	437.2	400.1	335.8	292.0	276.8
57.5°	403.9	363.8	298.8	257.2	244.3
60°	369.1	327.5	264.7	223.9	211.0
62.5°	334.3	292.7	229.9	192.1	178.5
65°	298.8	257.2	198.2	161.1	152.8
67.5°	263.2	220.9	163.4	135.4	126.3
70°	228.4	187.6	134.6	108.2	99.8
72.5°	193.6	153.5	106.7	86.2	84.0
75°	158.1	121.8	80.2	72.6	71.1
77.5°	125.6	92.3	62.8	58.2	56.7
80°	94.5	63.5	47.7	45.4	43.9
82.5°	65.1	39.3	34.0	31.8	31.8
85°	40.1	23.4	21.2	19.7	19.7
87.5°	18.2	9.8	9.8	9.1	8.3
90°	1.2	12.7	27.6	32.2	34.5
92.5°	26.5	19.6	29.9	38.0	39.1
95°	70.2	23.0	35.7	43.7	43.7
97.5°	127.8	95.5	36.8	46.0	47.2
100°	194.5	217.5	38.0	47.2	48.3
102.5°	270.5	285.4	85.2	47.2	49.5
105°	343.0	355.7	252.1	48.3	50.6
107.5°	420.1	430.5	447.7	270.5	119.7
110°	497.2	506.4	519.1	481.1	316.5

TEST NUMBER: P1010934

CATALOG NUMBER: S123RDIP-B560D1195UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	570.9	578.9	591.6	602.0	599.7
115°	643.4	650.3	660.7	672.2	676.8
117.5°	714.8	722.8	728.6	737.8	738.9
120°	780.4	790.7	794.2	803.4	803.4
122.5°	847.1	855.2	859.8	865.5	866.7
125°	907.0	916.2	920.8	923.1	925.4
127.5°	966.8	976.0	981.8	985.2	982.9
130°	1022.1	1031.3	1035.9	1040.5	1038.2
132.5°	1075.0	1084.2	1087.7	1092.3	1088.8
135°	1129.1	1136.0	1140.6	1144.1	1140.6
137.5°	1175.1	1184.4	1186.7	1192.4	1190.1
140°	1221.2	1228.1	1231.5	1236.1	1233.8
142.5°	1263.8	1270.7	1274.1	1277.6	1274.1
145°	1302.9	1311.0	1313.3	1315.6	1315.6
147.5°	1340.9	1346.6	1348.9	1351.2	1345.5
150°	1375.4	1378.9	1381.2	1383.5	1380.0
152.5°	1406.5	1407.6	1408.8	1413.4	1407.6
155°	1435.3	1433.0	1434.1	1439.9	1433.0
157.5°	1458.3	1458.3	1457.1	1464.0	1454.8
160°	1479.0	1477.9	1476.7	1483.6	1475.6
162.5°	1498.6	1495.1	1494.0	1502.0	1495.1
165°	1513.5	1510.1	1508.9	1518.1	1510.1
167.5°	1526.2	1521.6	1521.6	1530.8	1521.6
170°	1536.6	1531.9	1531.9	1541.2	1531.9
172.5°	1543.5	1537.7	1538.9	1548.1	1537.7
175°	1549.2	1543.5	1544.6	1552.7	1543.5
177.5°	1551.5	1545.8	1546.9	1556.1	1544.6
180°	1549.2	1549.2	1549.2	1549.2	1549.2

(END OF REPORT)