

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010612

Luminaire Tested: S123DIP-B340D805UB2750-4F0-XX-W2A-D_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010612
REPORT IS A COMBINATION OF REPORTS P989876 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B340D805UB2750-4F0-XX-W2A-D_4000K
Description: Define 3 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4508.0 lumens
Efficiency: N/A
Efficacy: 132.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.25 / 1.37
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 34.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010612

CATALOG NUMBER: S123DIP-B340D805UB2750-4F0-XX-W2A-D_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010612

CATALOG NUMBER: S123DIP-B340D805UB2750-4F0-XX-W2A-D_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	28		
1	92	88	84	80	82	79	75	72	61	59	57	46	44	43	31	30	29	23		
2	84	76	70	65	75	68	63	59	53	50	47	40	37	35	27	25	24	18		
3	76	67	60	54	68	60	54	49	47	43	39	35	32	29	24	22	20	15		
4	70	59	51	45	62	53	46	41	41	37	33	31	28	25	21	19	17	13		
5	64	52	44	38	57	47	40	35	37	32	28	28	24	21	19	17	15	11		
6	59	47	39	33	52	42	35	30	33	28	24	25	21	19	17	15	13	10		
7	54	42	34	29	48	38	31	26	30	25	21	22	19	16	15	13	12	9		
8	50	38	30	25	44	34	28	23	27	22	19	20	17	14	14	12	10	8		
9	46	34	27	22	41	31	25	20	25	20	17	19	15	13	13	11	9	7		
10	43	31	24	20	39	28	22	18	23	18	15	17	14	12	12	10	8	6		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4455	4455	4455
5°	4467	4324	4321
10°	4426	4207	4175
15°	4367	4078	4021
20°	4284	3934	3855
25°	4182	3771	3683
30°	4076	3624	3510
35°	3960	3471	3369
40°	3847	3329	3220
45°	3723	3193	3098
50°	3600	3058	2965
55°	3464	2919	2844
60°	3330	2776	2718
65°	3193	2625	2572
70°	2986	2456	2420
75°	2727	2262	2264
80°	2421	2068	2086
85°	2123	1908	1959

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3723 cd/sqm

TEST NUMBER: P1010612

CATALOG NUMBER: S123DIP-B340D805UB2750-4F0-XX-W2A-D_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.3	0.9
10°-20°	111.9	2.5
20°-30°	167.4	3.7
30°-40°	199.8	4.4
40°-50°	209.1	4.6
50°-60°	196.2	4.4
60°-70°	163.9	3.6
70°-80°	117.2	2.6
80°-90°	71.8	1.6
90°-100°	79.8	1.8
100°-110°	206.4	4.6
110°-120°	448.4	9.9
120°-130°	554.2	12.3
130°-140°	584.5	13.0
140°-150°	542.5	12.0
150°-160°	436.7	9.7
160°-170°	281.8	6.3
170°-180°	97.1	2.2
0°-30°	318.6	7.1
0°-40°	518.4	11.5
0°-60°	923.7	20.5
0°-90°	1276.6	28.3
90°-120°	734.7	16.3
90°-150°	2415.9	53.6
90°-180°	3231.0	71.7
0°-180°	4508.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	414	414	414	414	414	
5°	414	413	411	414	414	39
15°	394	396	395	400	400	111
25°	356	361	362	368	368	164
35°	307	314	320	326	328	192
45°	251	262	273	281	285	193
55°	191	206	222	234	238	171
65°	132	150	170	183	188	131
75°	72	93	115	130	136	77
85°	22	45	68	84	88	23
90°	7	36	69	88	94	7
95°	51	38	68	87	92	59
105°	230	249	200	78	84	244
115°	427	437	460	478	485	421
125°	600	606	622	633	637	536
135°	746	750	758	768	768	574
145°	860	865	866	871	873	538
155°	947	945	946	950	945	436
165°	998	996	995	1001	996	282
175°	1022	1018	1019	1024	1018	97
180°	1022	1022	1022	1022	1022	

TEST NUMBER: P1010612

CATALOG NUMBER: S123DIP-B340D805UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	413.9	413.9	413.9	413.9	413.9
2.5°	416.1	414.8	411.2	414.8	414.3
5°	414.3	413.4	410.7	414.3	413.9
7.5°	411.2	411.2	408.5	413.0	412.5
10°	406.7	407.6	405.3	409.8	408.9
12.5°	401.3	402.6	401.3	405.3	404.4
15°	394.5	395.9	395.4	399.9	399.5
17.5°	386.4	389.1	388.6	392.7	391.8
20°	377.4	380.1	381.0	385.0	385.5
22.5°	367.9	370.6	372.0	377.4	376.9
25°	356.2	360.7	362.0	367.9	367.9
27.5°	344.9	349.9	352.6	357.5	358.0
30°	332.7	338.6	342.2	347.6	347.6
32.5°	319.2	326.0	330.9	336.8	338.1
35°	306.6	313.8	319.7	326.4	328.2
37.5°	293.1	301.2	307.9	315.6	317.0
40°	279.5	287.7	296.7	304.3	306.1
42.5°	264.7	275.0	284.5	293.1	295.8
45°	250.7	261.5	272.8	281.3	284.9
47.5°	235.8	248.0	260.6	270.1	272.8
50°	221.4	234.0	248.0	258.3	261.5
52.5°	206.0	219.6	235.4	246.2	250.2
55°	191.2	206.0	222.3	234.4	238.1
57.5°	176.7	192.1	209.7	221.8	225.9
60°	161.4	177.6	196.1	208.7	213.7
62.5°	147.0	163.7	183.5	196.1	200.6
65°	132.1	149.7	169.5	183.1	187.6
67.5°	117.2	135.7	155.5	170.4	174.0
70°	101.4	120.8	142.5	156.9	161.4
72.5°	87.0	106.4	128.9	143.8	148.3
75°	71.7	92.9	115.4	130.3	135.7
77.5°	58.6	79.8	102.3	118.1	122.2
80°	44.6	66.7	90.2	105.5	110.0
82.5°	32.5	55.0	78.9	94.2	98.7
85°	22.1	44.6	68.5	83.9	88.4
87.5°	13.5	36.1	59.1	74.4	78.9
90°	6.7	36.4	69.1	87.6	93.6
92.5°	22.9	37.7	67.0	87.3	92.1
95°	51.3	37.7	68.1	87.4	91.9
97.5°	88.8	83.7	66.2	85.9	91.1
100°	132.4	162.0	64.3	83.4	88.7
102.5°	182.0	204.5	92.7	80.2	86.3
105°	229.8	249.0	200.0	78.3	83.9
107.5°	280.3	296.5	326.4	221.7	126.2
110°	330.6	344.8	371.3	357.9	253.0

TEST NUMBER: P1010612

CATALOG NUMBER: S123DIP-B340D805UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	379.2	390.8	416.4	434.4	437.0
115°	426.6	436.6	459.6	478.0	484.7
117.5°	473.7	482.6	501.7	518.6	523.0
120°	516.5	525.6	542.7	559.2	562.4
122.5°	560.5	566.7	583.8	597.5	601.4
125°	599.6	605.7	621.7	632.7	637.4
127.5°	639.1	644.6	659.7	671.0	672.6
130°	675.5	681.1	693.1	704.7	705.9
132.5°	709.9	716.0	725.1	736.2	737.0
135°	745.6	749.7	757.7	768.1	768.1
137.5°	776.0	781.6	786.3	797.2	798.0
140°	805.9	810.5	814.1	823.9	824.6
142.5°	834.0	838.1	840.3	848.5	848.4
145°	859.8	864.6	866.2	871.3	873.1
147.5°	884.4	888.2	889.7	892.6	890.6
150°	907.1	909.4	910.9	912.5	911.1
152.5°	927.6	928.4	929.2	932.2	928.4
155°	946.6	945.1	945.9	949.7	945.1
157.5°	961.8	961.8	961.0	965.6	959.5
160°	975.5	974.7	973.9	978.5	973.2
162.5°	988.4	986.1	985.3	990.6	986.1
165°	998.2	996.0	995.2	1001.3	996.0
167.5°	1006.6	1003.6	1003.6	1009.6	1003.6
170°	1013.4	1010.4	1010.4	1016.5	1010.4
172.5°	1018.0	1014.2	1014.9	1021.0	1014.2
175°	1021.8	1018.0	1018.7	1024.0	1018.0
177.5°	1023.3	1019.5	1020.3	1026.3	1018.7
180°	1021.8	1021.8	1021.8	1021.8	1021.8

(END OF REPORT)