

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010616

Luminaire Tested: S123DIP-B340D805UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010616
REPORT IS A COMBINATION OF REPORTS P989880 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B340D805UB2750-4F0-XX-W2A-F_3500K
Description: Define 3 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4528.0 lumens
Efficiency: N/A
Efficacy: 132.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 34.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010616

CATALOG NUMBER: S123DIP-B340D805UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1010616

CATALOG NUMBER: S123DIP-B340D805UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	38	38	38
1	93	89	85	82	84	80	77	74	63	61	59	48	47	45	34	33	32
2	85	78	72	67	76	70	65	61	55	52	49	42	40	38	30	28	27
3	77	68	61	56	69	62	56	51	49	45	41	37	34	32	26	24	23
4	71	60	53	47	63	54	48	43	43	39	35	33	30	27	23	21	20
5	65	54	46	40	58	48	42	37	39	34	30	30	26	23	21	19	17
6	60	48	40	34	53	43	37	32	35	30	26	27	23	20	19	17	15
7	55	43	35	30	49	39	32	28	31	26	23	24	21	18	17	15	13
8	51	39	32	26	46	35	29	24	29	24	20	22	19	16	16	14	12
9	47	36	28	23	42	32	26	22	26	21	18	20	17	14	15	12	11
10	44	32	25	21	40	30	23	19	24	19	16	19	15	13	14	11	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5704	5704	5704
5°	5717	5506	5499
10°	5667	5321	5265
15°	5588	5127	5012
20°	5497	4911	4761
25°	5380	4684	4492
30°	5253	4449	4210
35°	5119	4209	3928
40°	4978	3957	3653
45°	4824	3712	3364
50°	4667	3438	3074
55°	4466	3153	2780
60°	4259	2839	2468
65°	4064	2498	2143
70°	3784	2120	1762
75°	3378	1680	1368
80°	2921	1180	967
85°	2276	635	485

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4824 cd/sqm

TEST NUMBER: P1010616

CATALOG NUMBER: S123DIP-B340D805UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.0	1.1
10°-20°	141.0	3.1
20°-30°	208.3	4.6
30°-40°	243.3	5.4
40°-50°	244.6	5.4
50°-60°	214.8	4.7
60°-70°	160.0	3.5
70°-80°	91.1	2.0
80°-90°	28.0	0.6
90°-100°	36.4	0.8
100°-110°	176.0	3.9
110°-120°	431.3	9.5
120°-130°	547.5	12.1
130°-140°	584.9	12.9
140°-150°	546.9	12.1
150°-160°	441.1	9.7
160°-170°	284.7	6.3
170°-180°	98.1	2.2
0°-30°	399.3	8.8
0°-40°	642.6	14.2
0°-60°	1102.0	24.3
0°-90°	1381.1	30.5
90°-120°	643.7	14.2
90°-150°	2323.0	51.3
90°-180°	3147.0	69.5
0°-180°	4528.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	530	530	530	530	530	
5°	530	528	523	528	527	50
15°	505	503	497	501	498	142
25°	458	456	450	450	449	211
35°	396	394	388	385	383	248
45°	325	323	317	312	309	251
55°	246	246	240	235	233	221
65°	168	166	161	158	156	166
75°	89	87	86	83	82	95
85°	24	23	23	22	22	25
90°	1	8	18	22	23	4
95°	47	15	24	29	29	56
105°	228	237	168	32	34	242
115°	429	433	440	448	451	423
125°	604	610	614	615	617	540
135°	752	757	760	762	760	579
145°	868	874	875	877	877	544
155°	956	955	956	959	955	441
165°	1008	1006	1005	1012	1006	285
175°	1032	1028	1029	1035	1028	98
180°	1032	1032	1032	1032	1032	

TEST NUMBER: P1010616

CATALOG NUMBER: S123DIP-B340D805UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	529.9	529.9	529.9	529.9	529.9
2.5°	532.1	530.3	525.3	529.9	529.4
5°	530.3	528.0	523.0	527.6	526.7
7.5°	526.2	523.9	518.9	523.0	522.6
10°	520.8	518.5	512.6	516.7	515.7
12.5°	513.5	511.6	506.2	508.9	508.5
15°	504.8	503.0	497.1	500.7	498.0
17.5°	495.2	493.0	487.0	489.8	488.9
20°	484.3	481.6	475.6	477.5	476.1
22.5°	472.0	469.3	463.3	464.7	462.9
25°	458.3	455.6	449.7	450.1	448.8
27.5°	444.2	441.5	435.1	435.6	434.2
30°	428.7	426.4	420.1	420.1	416.9
32.5°	413.2	410.0	405.5	402.3	400.9
35°	396.4	393.6	387.7	385.0	382.7
37.5°	379.5	375.9	369.9	366.8	365.4
40°	361.7	359.0	352.6	349.0	347.2
42.5°	344.0	340.8	334.4	330.8	328.9
45°	324.8	323.0	317.1	311.6	309.4
47.5°	306.2	303.4	298.0	292.5	290.7
50°	287.0	284.8	278.8	273.8	271.1
52.5°	267.0	265.6	259.2	255.1	252.4
55°	246.5	246.0	240.1	235.1	232.8
57.5°	227.3	225.5	221.0	216.4	213.7
60°	206.4	205.9	200.5	196.4	194.1
62.5°	187.7	186.3	180.9	176.8	175.4
65°	168.1	165.8	161.3	157.6	156.3
67.5°	147.2	145.3	141.7	138.5	136.7
70°	128.5	125.7	123.0	119.8	117.5
72.5°	108.9	107.1	103.9	101.1	100.2
75°	88.8	87.0	85.7	83.4	82.0
77.5°	71.1	70.2	68.3	66.5	66.5
80°	53.8	52.4	51.5	51.0	51.0
82.5°	36.9	36.9	36.9	36.0	35.5
85°	23.7	22.8	22.8	21.9	21.9
87.5°	11.8	10.5	10.0	9.6	9.6
90°	0.8	8.4	18.4	21.5	23.0
92.5°	17.6	13.0	19.9	25.3	26.1
95°	46.8	15.3	23.8	29.1	29.1
97.5°	85.1	63.7	24.5	30.7	31.4
100°	129.6	144.9	25.3	31.4	32.2
102.5°	180.2	190.2	56.8	31.4	33.0
105°	228.5	237.0	168.0	32.2	33.7
107.5°	279.9	286.8	298.3	180.2	79.8
110°	331.3	337.4	345.9	320.6	210.9

TEST NUMBER: P1010616

CATALOG NUMBER: S123DIP-B340D805UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	380.4	385.8	394.2	401.1	399.6
115°	428.7	433.3	440.2	447.9	450.9
117.5°	476.3	481.6	485.5	491.6	492.4
120°	520.0	526.9	529.2	535.3	535.3
122.5°	564.4	569.8	572.9	576.7	577.5
125°	604.3	610.5	613.5	615.1	616.6
127.5°	644.2	650.3	654.2	656.5	654.9
130°	681.0	687.2	690.2	693.3	691.8
132.5°	716.3	722.4	724.7	727.8	725.5
135°	752.3	756.9	760.0	762.3	760.0
137.5°	783.0	789.2	790.7	794.5	793.0
140°	813.7	818.3	820.6	823.7	822.1
142.5°	842.1	846.7	849.0	851.3	849.0
145°	868.1	873.5	875.0	876.6	876.6
147.5°	893.5	897.3	898.8	900.4	896.5
150°	916.5	918.8	920.3	921.8	919.5
152.5°	937.2	937.9	938.7	941.8	937.9
155°	956.3	954.8	955.6	959.4	954.8
157.5°	971.7	971.7	970.9	975.5	969.4
160°	985.5	984.7	983.9	988.5	983.2
162.5°	998.5	996.2	995.5	1000.8	996.2
165°	1008.5	1006.2	1005.4	1011.6	1006.2
167.5°	1016.9	1013.9	1013.9	1020.0	1013.9
170°	1023.8	1020.8	1020.8	1026.9	1020.8
172.5°	1028.4	1024.6	1025.4	1031.5	1024.6
175°	1032.3	1028.4	1029.2	1034.6	1028.4
177.5°	1033.8	1030.0	1030.7	1036.9	1029.2
180°	1032.3	1032.3	1032.3	1032.3	1032.3

(END OF REPORT)