

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010624

Luminaire Tested: S123DIP-B560D1025UB2750-4F0-XX-W2A-D_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010624
REPORT IS A COMBINATION OF REPORTS P989933 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B560D1025UB2750-4F0-XX-W2A-D_2700K
Description: Define 3 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6356.0 lumens
Efficiency: N/A
Efficacy: 121.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.25 / 1.37
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 52.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010624

CATALOG NUMBER: S123DIP-B560D1025UB2750-4F0-XX-W2A-D_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1010624

CATALOG NUMBER: S123DIP-B560D1025UB2750-4F0-XX-W2A-D_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41			34
1	93	89	85	81	84	80	77	74	64	62	59	49	47	46	35	34	33			27
2	85	77	71	66	76	70	64	60	56	52	49	43	40	38	31	29	27			22
3	77	68	60	54	69	61	55	50	49	44	40	37	34	32	27	25	23			18
4	70	60	52	46	63	54	47	42	43	38	34	33	30	27	24	22	20			15
5	64	53	45	39	58	48	41	36	38	33	29	30	26	23	21	19	17			13
6	59	47	39	33	53	43	36	31	34	29	25	27	23	20	19	17	15			12
7	55	42	35	29	49	39	32	27	31	26	22	24	20	18	18	15	13			10
8	51	38	31	26	45	35	28	23	28	23	20	22	18	16	16	14	12			9
9	47	35	28	23	42	32	25	21	26	21	17	20	17	14	15	12	10			8
10	44	32	25	20	39	29	23	19	24	19	15	19	15	12	14	11	9			7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7472	7472	7472
5°	7492	7253	7247
10°	7423	7056	7003
15°	7325	6840	6743
20°	7184	6598	6464
25°	7013	6325	6177
30°	6838	6078	5887
35°	6641	5820	5651
40°	6452	5584	5402
45°	6243	5355	5196
50°	6038	5128	4974
55°	5809	4895	4769
60°	5586	4657	4558
65°	5357	4403	4313
70°	5009	4120	4059
75°	4572	3795	3797
80°	4066	3466	3499
85°	3564	3200	3285

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6243 cd/sqm

TEST NUMBER: P1010624

CATALOG NUMBER: S123DIP-B560D1025UB2750-4F0-XX-W2A-D_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.9	1.0
10°-20°	187.7	3.0
20°-30°	280.7	4.4
30°-40°	335.2	5.3
40°-50°	350.7	5.5
50°-60°	329.1	5.2
60°-70°	274.9	4.3
70°-80°	196.5	3.1
80°-90°	119.6	1.9
90°-100°	120.0	1.9
100°-110°	278.9	4.4
110°-120°	587.1	9.2
120°-130°	720.0	11.3
130°-140°	756.4	11.9
140°-150°	700.7	11.0
150°-160°	563.6	8.9
160°-170°	363.7	5.7
170°-180°	125.3	2.0
0°-30°	534.3	8.4
0°-40°	869.5	13.7
0°-60°	1549.3	24.4
0°-90°	2140.3	33.7
90°-120°	985.9	15.5
90°-150°	3163.1	49.8
90°-180°	4216.0	66.3
0°-180°	6356.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	694	694	694	694	694	
5°	695	693	689	695	694	66
15°	662	664	663	671	670	186
25°	597	605	607	617	617	275
35°	514	526	536	548	550	322
45°	420	439	458	472	478	324
55°	321	346	373	393	399	287
65°	222	251	284	307	315	219
75°	120	156	194	218	228	128
85°	37	75	115	141	148	38
90°	11	58	109	139	148	10
95°	68	57	105	136	143	78
105°	298	327	271	119	128	316
115°	552	566	602	630	640	545
125°	774	782	808	826	833	692
135°	963	968	980	997	997	741
145°	1110	1116	1118	1126	1129	695
155°	1222	1220	1221	1226	1220	563
165°	1288	1286	1284	1292	1286	364
175°	1319	1314	1315	1322	1314	126
180°	1319	1319	1319	1319	1319	

TEST NUMBER: P1010624

CATALOG NUMBER: S123DIP-B560D1025UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	694.2	694.2	694.2	694.2	694.2
2.5°	698.0	695.7	689.6	695.7	694.9
5°	694.9	693.4	688.9	694.9	694.2
7.5°	689.6	689.6	685.1	692.7	691.9
10°	682.1	683.6	679.8	687.4	685.9
12.5°	673.0	675.3	673.0	679.8	678.3
15°	661.7	663.9	663.2	670.7	670.0
17.5°	648.1	652.6	651.8	658.6	657.1
20°	632.9	637.5	639.0	645.8	646.5
22.5°	617.1	621.6	623.9	632.9	632.2
25°	597.4	605.0	607.2	617.1	617.1
27.5°	578.5	586.8	591.3	599.7	600.4
30°	558.1	567.9	573.9	583.0	583.0
32.5°	535.4	546.7	555.0	564.9	567.1
35°	514.2	526.3	536.1	547.5	550.5
37.5°	491.5	505.1	516.5	529.3	531.6
40°	468.8	482.4	497.6	510.4	513.5
42.5°	443.9	461.3	477.2	491.5	496.1
45°	420.4	438.6	457.5	471.9	477.9
47.5°	395.5	415.9	437.1	453.0	457.5
50°	371.3	392.5	415.9	433.3	438.6
52.5°	345.6	368.3	394.7	412.9	419.7
55°	320.6	345.6	372.8	393.2	399.3
57.5°	296.4	322.1	351.6	372.0	378.9
60°	270.7	297.9	328.9	350.1	358.4
62.5°	246.5	274.5	307.8	328.9	336.5
65°	221.6	251.1	284.3	307.0	314.6
67.5°	196.6	227.6	260.9	285.8	291.9
70°	170.1	202.7	239.0	263.2	270.7
72.5°	145.9	178.5	216.3	241.2	248.8
75°	120.2	155.8	193.6	218.5	227.6
77.5°	98.3	133.8	171.7	198.1	204.9
80°	74.9	111.9	151.2	176.9	184.5
82.5°	54.4	92.3	132.3	158.0	165.6
85°	37.1	74.9	114.9	140.7	148.2
87.5°	22.7	60.5	99.1	124.8	132.3
90°	10.8	57.7	108.9	138.6	148.1
92.5°	31.6	58.3	104.9	136.7	144.5
95°	68.1	57.4	105.3	135.5	143.1
97.5°	116.4	116.1	101.7	132.2	140.8
100°	172.4	216.2	98.1	127.9	136.5
102.5°	236.2	270.2	133.8	122.6	132.1
105°	298.0	326.9	271.3	119.1	127.8
107.5°	362.9	387.6	433.3	302.8	181.3
110°	427.8	449.2	490.3	477.6	343.5

TEST NUMBER: P1010624

CATALOG NUMBER: S123DIP-B560D1025UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	490.5	507.9	547.5	575.2	580.1
115°	551.5	566.5	602.5	630.4	640.4
117.5°	612.2	625.1	655.7	681.7	688.7
120°	667.3	679.9	707.8	733.1	738.3
122.5°	724.1	732.5	759.9	781.4	787.7
125°	774.4	782.2	808.0	825.9	833.1
127.5°	825.3	832.3	856.1	874.2	877.5
130°	872.3	879.4	898.4	916.7	919.2
132.5°	916.6	924.4	938.8	956.3	958.7
135°	962.7	967.8	980.0	996.6	997.4
137.5°	1001.8	1009.0	1016.1	1033.1	1035.0
140°	1040.3	1046.2	1051.3	1066.7	1068.4
142.5°	1076.6	1081.7	1084.6	1097.3	1098.2
145°	1109.9	1116.0	1117.9	1125.9	1129.0
147.5°	1141.4	1146.3	1148.3	1152.5	1150.6
150°	1170.8	1173.8	1175.7	1177.7	1176.2
152.5°	1197.3	1198.3	1199.2	1203.2	1198.3
155°	1221.8	1219.8	1220.8	1225.7	1219.8
157.5°	1241.4	1241.4	1240.4	1246.3	1238.4
160°	1259.0	1258.0	1257.0	1262.9	1256.1
162.5°	1275.7	1272.7	1271.7	1278.6	1272.7
165°	1288.4	1285.5	1284.5	1292.3	1285.5
167.5°	1299.2	1295.3	1295.3	1303.1	1295.3
170°	1308.0	1304.1	1304.1	1311.9	1304.1
172.5°	1313.9	1309.0	1309.9	1317.8	1309.0
175°	1318.8	1313.9	1314.8	1321.7	1313.9
177.5°	1320.7	1315.8	1316.8	1324.6	1314.8
180°	1318.8	1318.8	1318.8	1318.8	1318.8

(END OF REPORT)