

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010938

Luminaire Tested: S123RDIP-B560D1195UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010938
REPORT IS A COMBINATION OF REPORTS P993374 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B560D1195UB2750-4F0-XX-W2A-F_5000K
Description: Define 3 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6627.0 lumens
Efficiency: N/A
Efficacy: 112.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 59
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010938

CATALOG NUMBER: S123RDIP-B560D1195UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010938

CATALOG NUMBER: S123RDIP-B560D1195UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39	39	39	31
1	94	90	86	83	84	81	78	75	64	62	60	49	47	46	34	34	33	33	33	26
2	85	78	73	68	77	71	66	62	56	53	50	43	41	39	30	29	28	28	28	22
3	78	69	62	57	70	62	56	52	50	46	42	38	35	33	27	25	24	24	24	19
4	71	61	54	48	64	55	49	44	44	40	36	34	31	28	24	22	21	21	21	17
5	65	54	47	41	59	49	43	38	40	35	31	30	27	25	22	20	18	18	18	15
6	60	49	41	35	54	44	37	33	36	31	27	28	24	21	20	18	16	16	16	13
7	56	44	36	31	50	40	33	29	32	27	24	25	22	19	18	16	14	14	14	11
8	52	40	32	27	46	36	30	25	29	24	21	23	19	17	17	15	13	13	13	10
9	48	36	29	24	43	33	27	22	27	22	19	21	18	15	16	13	12	12	12	9
10	45	33	26	22	40	30	24	20	25	20	17	19	16	14	14	12	11	11	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9734	9734	9734
5°	9750	9389	9364
10°	9673	9037	8858
15°	9547	8600	8305
20°	9383	8126	7685
25°	9213	7632	7099
30°	8996	7108	6406
35°	8771	6593	5774
40°	8559	6033	5077
45°	8288	5486	4450
50°	7991	4901	3801
55°	7681	4275	3206
60°	7385	3634	2602
65°	7003	2977	2032
70°	6523	2250	1451
75°	5831	1523	1149
80°	4978	1059	806
85°	3737	571	423

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8288 cd/sqm

TEST NUMBER: P1010938

CATALOG NUMBER: S123RDIP-B560D1195UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.0	1.3
10°-20°	236.5	3.6
20°-30°	340.5	5.1
30°-40°	383.4	5.8
40°-50°	366.8	5.5
50°-60°	300.2	4.5
60°-70°	202.4	3.1
70°-80°	101.5	1.5
80°-90°	29.5	0.4
90°-100°	53.0	0.8
100°-110°	256.2	3.9
110°-120°	627.8	9.5
120°-130°	797.0	12.0
130°-140°	851.4	12.8
140°-150°	796.2	12.0
150°-160°	642.2	9.7
160°-170°	414.4	6.3
170°-180°	142.8	2.2
0°-30°	662.0	10.0
0°-40°	1045.4	15.8
0°-60°	1712.5	25.8
0°-90°	2046.0	30.9
90°-120°	937.0	14.1
90°-150°	3381.6	51.0
90°-180°	4581.0	69.1
0°-180°	6627.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	904	904	904	904	904	
5°	904	901	892	898	897	86
15°	862	854	834	830	825	243
25°	785	766	733	717	709	361
35°	679	653	607	576	562	425
45°	558	525	469	427	409	431
55°	424	388	326	283	268	380
65°	290	249	192	156	148	287
75°	153	118	78	70	69	163
85°	39	23	20	19	19	43
90°	1	12	27	31	34	6
95°	68	22	35	42	42	81
105°	333	345	244	47	49	353
115°	624	631	641	652	656	616
125°	880	889	893	895	898	786
135°	1095	1102	1106	1110	1106	843
145°	1264	1272	1274	1276	1276	791
155°	1392	1390	1391	1397	1390	641
165°	1468	1465	1464	1472	1465	415
175°	1503	1497	1498	1506	1497	143
180°	1503	1503	1503	1503	1503	

TEST NUMBER: P1010938

CATALOG NUMBER: S123RDIP-B560D1195UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	904.3	904.3	904.3	904.3	904.3
2.5°	908.0	905.0	896.2	904.3	902.8
5°	904.3	900.6	891.8	898.4	897.0
7.5°	897.7	894.0	883.0	887.4	885.2
10°	888.9	883.8	870.6	871.3	867.6
12.5°	876.4	870.6	853.7	853.0	848.6
15°	862.5	854.4	833.9	830.2	825.1
17.5°	845.6	836.8	811.2	803.8	796.5
20°	826.6	814.8	787.0	777.4	768.6
22.5°	805.3	791.4	761.3	748.8	740.8
25°	784.8	766.4	732.7	717.3	709.2
27.5°	759.8	740.0	703.4	682.8	670.3
30°	734.2	712.2	671.1	646.1	634.4
32.5°	708.5	682.8	638.8	610.9	598.5
35°	679.2	652.7	607.3	575.7	562.5
37.5°	649.8	621.2	573.5	538.3	522.2
40°	621.9	589.7	537.6	499.5	482.6
42.5°	590.4	558.1	503.9	461.3	446.7
45°	558.1	525.1	468.7	426.9	409.3
47.5°	526.6	489.9	434.2	388.7	373.3
50°	491.4	456.9	397.5	352.0	335.2
52.5°	459.9	421.7	363.0	315.4	300.7
55°	423.9	388.0	325.6	283.1	268.4
57.5°	391.6	352.8	289.7	249.4	236.9
60°	357.9	317.6	256.7	217.1	204.6
62.5°	324.2	283.8	223.0	186.3	173.1
65°	289.7	249.4	192.2	156.2	148.2
67.5°	255.2	214.2	158.4	131.3	122.5
70°	221.5	181.9	130.5	104.9	96.8
72.5°	187.8	148.9	103.4	83.6	81.4
75°	153.3	118.1	77.7	70.4	68.9
77.5°	121.7	89.5	60.9	56.5	55.0
80°	91.7	61.6	46.2	44.0	42.5
82.5°	63.1	38.1	33.0	30.8	30.8
85°	38.9	22.7	20.5	19.1	19.1
87.5°	17.6	9.5	9.5	8.8	8.1
90°	1.1	12.3	26.8	31.3	33.5
92.5°	25.7	19.0	29.0	36.8	38.0
95°	68.1	22.3	34.6	42.4	42.4
97.5°	123.9	92.7	35.7	44.7	45.8
100°	188.7	211.0	36.8	45.8	46.9
102.5°	262.4	276.9	82.6	45.8	48.0
105°	332.7	345.0	244.5	46.9	49.1
107.5°	407.5	417.5	434.3	262.4	116.1
110°	482.3	491.2	503.5	466.7	307.0

TEST NUMBER: P1010938

CATALOG NUMBER: S123RDIP-B560D1195UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	553.7	561.5	573.8	583.9	581.6
115°	624.1	630.8	640.8	652.0	656.4
117.5°	693.3	701.1	706.7	715.6	716.7
120°	756.9	767.0	770.3	779.2	779.2
122.5°	821.7	829.5	833.9	839.5	840.6
125°	879.7	888.6	893.1	895.3	897.6
127.5°	937.8	946.7	952.3	955.6	953.4
130°	991.4	1000.3	1004.8	1009.2	1007.0
132.5°	1042.7	1051.6	1055.0	1059.5	1056.1
135°	1095.2	1101.9	1106.3	1109.7	1106.3
137.5°	1139.8	1148.8	1151.0	1156.6	1154.3
140°	1184.5	1191.2	1194.5	1199.0	1196.8
142.5°	1225.8	1232.5	1235.8	1239.2	1235.8
145°	1263.8	1271.6	1273.8	1276.0	1276.0
147.5°	1300.6	1306.2	1308.4	1310.6	1305.1
150°	1334.1	1337.4	1339.7	1341.9	1338.6
152.5°	1364.2	1365.3	1366.5	1370.9	1365.3
155°	1392.1	1389.9	1391.0	1396.6	1389.9
157.5°	1414.5	1414.5	1413.4	1420.1	1411.1
160°	1434.6	1433.4	1432.3	1439.0	1431.2
162.5°	1453.5	1450.2	1449.1	1456.9	1450.2
165°	1468.1	1464.7	1463.6	1472.5	1464.7
167.5°	1480.3	1475.9	1475.9	1484.8	1475.9
170°	1490.4	1485.9	1485.9	1494.8	1485.9
172.5°	1497.1	1491.5	1492.6	1501.5	1491.5
175°	1502.7	1497.1	1498.2	1506.0	1497.1
177.5°	1504.9	1499.3	1500.4	1509.4	1498.2
180°	1502.7	1502.7	1502.7	1502.7	1502.7

(END OF REPORT)