

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010947

Luminaire Tested: S123RDIP-B560D365UB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010947
REPORT IS A COMBINATION OF REPORTS P993413 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B560D365UB2750-4F0-XX-W2A-F_4000K
Description: Define 3 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3564.0 lumens
Efficiency: N/A
Efficacy: 107.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 33.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010947

CATALOG NUMBER: S123RDIP-B560D365UB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010947

CATALOG NUMBER: S123RDIP-B560D365UB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	89	89	89	76	76	76	65	65	65
1	100	96	92	89	93	90	87	84	78	76	74	68	66	64	58	57	55
2	92	84	78	73	85	79	74	69	69	65	62	60	57	54	51	49	47
3	84	74	67	61	78	70	63	58	61	56	52	53	49	46	46	43	41
4	77	66	58	52	72	62	55	50	55	49	45	48	43	40	41	38	35
5	71	59	51	45	66	56	48	43	49	43	39	43	38	35	37	34	31
6	65	53	45	39	61	50	43	38	44	39	34	39	34	31	34	30	27
7	61	48	40	35	56	46	38	33	40	35	30	36	31	27	31	27	25
8	56	44	36	31	53	42	35	30	37	31	27	33	28	25	29	25	22
9	52	40	33	28	49	38	31	27	34	28	24	30	26	22	26	23	20
10	49	37	30	25	46	35	28	24	31	26	22	28	23	20	25	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10067	10067	10067
5°	10084	9711	9685
10°	10005	9346	9162
15°	9875	8895	8589
20°	9704	8404	7949
25°	9529	7894	7342
30°	9303	7352	6625
35°	9071	6819	5972
40°	8853	6239	5251
45°	8574	5673	4603
50°	8264	5069	3932
55°	7944	4422	3316
60°	7639	3759	2691
65°	7242	3077	2100
70°	6747	2327	1501
75°	6029	1576	1190
80°	5147	1096	834
85°	3861	590	437

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8574 cd/sqm

TEST NUMBER: P1010947

CATALOG NUMBER: S123RDIP-B560D365UB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.9	2.5
10°-20°	244.6	6.9
20°-30°	352.2	9.9
30°-40°	396.6	11.1
40°-50°	379.4	10.6
50°-60°	310.5	8.7
60°-70°	209.4	5.9
70°-80°	105.0	2.9
80°-90°	28.4	0.8
90°-100°	16.8	0.5
100°-110°	81.1	2.3
110°-120°	198.7	5.6
120°-130°	252.3	7.1
130°-140°	269.5	7.6
140°-150°	252.0	7.1
150°-160°	203.3	5.7
160°-170°	131.2	3.7
170°-180°	45.2	1.3
0°-30°	684.7	19.2
0°-40°	1081.3	30.3
0°-60°	1771.2	49.7
0°-90°	2114.0	59.3
90°-120°	296.6	8.3
90°-150°	1070.4	30.0
90°-180°	1450.0	40.7
0°-180°	3564.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	935	935	935	935	935	
5°	935	932	922	929	928	89
15°	892	884	862	859	853	251
25°	812	793	758	742	734	373
35°	702	675	628	596	582	440
45°	577	543	485	442	423	445
55°	438	401	337	293	278	393
65°	300	258	199	162	153	297
75°	158	122	80	73	71	169
85°	40	24	21	20	20	44
90°	0	4	8	10	11	4
95°	22	7	11	13	13	26
105°	105	109	77	15	16	112
115°	198	200	203	206	208	195
125°	278	281	283	283	284	249
135°	347	349	350	351	350	267
145°	400	402	403	404	404	250
155°	441	440	440	442	440	203
165°	465	464	463	466	464	131
175°	476	474	474	477	474	45
180°	476	476	476	476	476	

TEST NUMBER: P1010947

CATALOG NUMBER: S123RDIP-B560D365UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	935.3	935.3	935.3	935.3	935.3
2.5°	939.1	936.1	927.0	935.3	933.8
5°	935.3	931.5	922.4	929.2	927.7
7.5°	928.5	924.7	913.3	917.8	915.6
10°	919.4	914.1	900.4	901.2	897.4
12.5°	906.5	900.4	883.0	882.2	877.6
15°	892.1	883.7	862.5	858.7	853.4
17.5°	874.6	865.5	839.0	831.4	823.8
20°	854.9	842.8	813.9	804.1	795.0
22.5°	832.9	818.5	787.4	774.5	766.1
25°	811.7	792.7	757.8	741.9	733.5
27.5°	785.9	765.4	727.5	706.2	693.3
30°	759.3	736.6	694.1	668.3	656.1
32.5°	732.8	706.2	660.7	631.9	619.0
35°	702.4	675.1	628.1	595.5	581.8
37.5°	672.1	642.5	593.2	556.8	540.1
40°	643.3	609.9	556.0	516.6	499.1
42.5°	610.6	577.3	521.1	477.1	462.0
45°	577.3	543.1	484.7	441.5	423.3
47.5°	544.6	506.7	449.1	402.0	386.1
50°	508.2	472.6	411.1	364.1	346.7
52.5°	475.6	436.2	375.5	326.2	311.0
55°	438.4	401.3	336.8	292.8	277.6
57.5°	405.1	364.9	299.6	257.9	245.0
60°	370.2	328.5	265.5	224.5	211.6
62.5°	335.3	293.6	230.6	192.7	179.0
65°	299.6	257.9	198.7	161.6	153.2
67.5°	264.0	221.5	163.8	135.8	126.7
70°	229.1	188.1	135.0	108.5	100.1
72.5°	194.2	154.0	107.0	86.5	84.2
75°	158.5	122.1	80.4	72.8	71.3
77.5°	125.9	92.5	63.0	58.4	56.9
80°	94.8	63.7	47.8	45.5	44.0
82.5°	65.2	39.4	34.1	31.9	31.9
85°	40.2	23.5	21.2	19.7	19.7
87.5°	18.2	9.9	9.9	9.1	8.3
90°	0.4	3.9	8.5	9.9	10.6
92.5°	8.1	6.0	9.2	11.7	12.0
95°	21.6	7.1	11.0	13.4	13.4
97.5°	39.2	29.3	11.3	14.1	14.5
100°	59.7	66.8	11.7	14.5	14.8
102.5°	83.0	87.6	26.1	14.5	15.2
105°	105.3	109.2	77.4	14.8	15.5
107.5°	129.0	132.2	137.5	83.0	36.8
110°	152.7	155.5	159.4	147.7	97.2



TEST NUMBER: P1010947

CATALOG NUMBER: S123RDIP-B560D365UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	175.3	177.7	181.6	184.8	184.1
115°	197.5	199.7	202.8	206.4	207.8
117.5°	219.4	221.9	223.7	226.5	226.9
120°	239.6	242.8	243.8	246.7	246.7
122.5°	260.1	262.6	264.0	265.7	266.1
125°	278.5	281.3	282.7	283.4	284.1
127.5°	296.8	299.7	301.4	302.5	301.8
130°	313.8	316.6	318.0	319.5	318.7
132.5°	330.1	332.9	333.9	335.4	334.3
135°	346.7	348.8	350.2	351.3	350.2
137.5°	360.8	363.6	364.3	366.1	365.4
140°	374.9	377.1	378.1	379.5	378.8
142.5°	388.0	390.1	391.2	392.2	391.2
145°	400.0	402.5	403.2	403.9	403.9
147.5°	411.7	413.5	414.2	414.9	413.1
150°	422.3	423.3	424.1	424.8	423.7
152.5°	431.8	432.2	432.5	433.9	432.2
155°	440.7	440.0	440.3	442.1	440.0
157.5°	447.7	447.7	447.4	449.5	446.7
160°	454.1	453.7	453.4	455.5	453.0
162.5°	460.1	459.0	458.7	461.2	459.0
165°	464.7	463.6	463.3	466.1	463.6
167.5°	468.6	467.2	467.2	470.0	467.2
170°	471.8	470.3	470.3	473.2	470.3
172.5°	473.9	472.1	472.5	475.3	472.1
175°	475.6	473.9	474.2	476.7	473.9
177.5°	476.4	474.6	474.9	477.8	474.2
180°	475.6	475.6	475.6	475.6	475.6

(END OF REPORT)