

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010629

Luminaire Tested: S123DIP-B560D1025UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010629
REPORT IS A COMBINATION OF REPORTS P989938 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B560D1025UB2750-4F0-XX-W2A-F_2700K
Description: Define 3 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6312.0 lumens
Efficiency: N/A
Efficacy: 120.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 52.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010629

CATALOG NUMBER: S123DIP-B560D1025UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1010629

CATALOG NUMBER: S123DIP-B560D1025UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	104	104	104	104		94	94	94	94		76	76	76		59	59	59		44	44	44
1	95	90	87	83		86	82	79	76		66	64	62		52	50	49		38	37	37
2	86	79	73	68		78	72	67	62		58	54	51		45	43	41		34	32	31
3	79	69	62	56		71	63	57	52		51	47	43		40	37	34		30	28	26
4	72	61	53	48		65	56	49	44		45	40	37		36	32	29		27	24	23
5	66	54	47	41		59	50	43	38		40	35	31		32	28	25		24	22	20
6	61	49	41	35		55	44	38	32		36	31	27		29	25	22		22	19	17
7	56	44	36	31		50	40	33	28		33	28	24		26	22	20		20	17	15
8	52	40	32	27		47	36	30	25		30	25	21		24	20	17		18	16	14
9	48	36	29	24		44	33	27	22		27	22	19		22	18	16		17	14	12
10	45	33	26	21		41	30	24	20		25	20	17		20	17	14		16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9467	9467	9467
5°	9491	9141	9126
10°	9406	8831	8741
15°	9275	8509	8320
20°	9125	8152	7902
25°	8932	7775	7456
30°	8719	7385	6987
35°	8496	6987	6521
40°	8264	6568	6063
45°	8008	6161	5583
50°	7747	5706	5103
55°	7413	5233	4615
60°	7069	4712	4097
65°	6747	4146	3556
70°	6281	3520	2925
75°	5611	2788	2271
80°	4843	1960	1606
85°	3775	1053	805

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8008 cd/sqm

TEST NUMBER: P1010629

CATALOG NUMBER: S123DIP-B560D1025UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	82.9	1.3
10°-20°	234.1	3.7
20°-30°	345.8	5.5
30°-40°	403.8	6.4
40°-50°	406.0	6.4
50°-60°	356.6	5.7
60°-70°	265.6	4.2
70°-80°	151.1	2.4
80°-90°	45.6	0.7
90°-100°	46.5	0.7
100°-110°	224.8	3.6
110°-120°	551.0	8.7
120°-130°	699.5	11.1
130°-140°	747.2	11.8
140°-150°	698.7	11.1
150°-160°	563.6	8.9
160°-170°	363.7	5.8
170°-180°	125.3	2.0
0°-30°	662.8	10.5
0°-40°	1066.7	16.9
0°-60°	1829.3	29.0
0°-90°	2291.7	36.3
90°-120°	822.3	13.0
90°-150°	2967.7	47.0
90°-180°	4020.0	63.7
0°-180°	6312.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	880	880	880	880	880	
5°	880	876	868	876	874	83
15°	838	835	825	831	827	236
25°	761	756	746	747	745	350
35°	658	653	644	639	635	412
45°	539	536	526	517	514	416
55°	409	408	398	390	386	367
65°	279	275	268	262	259	275
75°	148	144	142	138	136	158
85°	39	38	38	36	36	42
90°	1	11	24	27	29	6
95°	60	20	30	37	37	71
105°	292	303	215	41	43	310
115°	548	554	562	572	576	541
125°	772	780	784	786	788	690
135°	961	967	971	974	971	740
145°	1109	1116	1118	1120	1120	694
155°	1222	1220	1221	1226	1220	563
165°	1288	1286	1284	1292	1286	364
175°	1319	1314	1315	1322	1314	126
180°	1319	1319	1319	1319	1319	

TEST NUMBER: P1010629

CATALOG NUMBER: S123DIP-B560D1025UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	879.5	879.5	879.5	879.5	879.5
2.5°	883.3	880.3	872.0	879.5	878.8
5°	880.3	876.5	868.2	875.7	874.2
7.5°	873.5	869.7	861.4	868.2	867.4
10°	864.4	860.6	850.8	857.6	856.1
12.5°	852.3	849.3	840.2	844.7	844.0
15°	837.9	834.9	825.1	831.1	826.6
17.5°	822.0	818.3	808.4	813.0	811.5
20°	803.9	799.4	789.5	792.6	790.3
22.5°	783.5	778.9	769.1	771.4	768.4
25°	760.8	756.3	746.4	747.2	744.9
27.5°	737.3	732.8	722.2	723.0	720.7
30°	711.6	707.9	697.3	697.3	692.0
32.5°	685.9	680.6	673.1	667.8	665.5
35°	657.9	653.4	643.6	639.0	635.3
37.5°	630.0	623.9	614.1	608.8	606.5
40°	600.5	595.9	585.3	579.3	576.3
42.5°	571.0	565.7	555.1	549.0	546.0
45°	539.2	536.2	526.4	517.3	513.5
47.5°	508.2	503.7	494.6	485.5	482.5
50°	476.4	472.7	462.8	454.5	450.0
52.5°	443.2	440.9	430.3	423.5	419.0
55°	409.1	408.4	398.5	390.2	386.4
57.5°	377.4	374.3	366.8	359.2	354.7
60°	342.6	341.8	332.8	325.9	322.2
62.5°	311.6	309.3	300.2	293.4	291.2
65°	279.1	275.3	267.7	261.7	259.4
67.5°	244.3	241.2	235.2	229.9	226.9
70°	213.3	208.7	204.2	198.9	195.1
72.5°	180.7	177.7	172.4	167.9	166.4
75°	147.5	144.4	142.2	138.4	136.1
77.5°	118.0	116.5	113.4	110.4	110.4
80°	89.2	87.0	85.5	84.7	84.7
82.5°	61.3	61.3	61.3	59.7	59.0
85°	39.3	37.8	37.8	36.3	36.3
87.5°	19.7	17.4	16.6	15.9	15.9
90°	1.0	10.8	23.5	27.4	29.4
92.5°	22.5	16.7	25.5	32.3	33.3
95°	59.8	19.6	30.4	37.2	37.2
97.5°	108.8	81.3	31.4	39.2	40.2
100°	165.6	185.2	32.3	40.2	41.2
102.5°	230.2	243.0	72.5	40.2	42.1
105°	292.0	302.7	214.6	41.2	43.1
107.5°	357.6	366.4	381.1	230.2	101.9
110°	423.3	431.1	441.9	409.5	269.4

TEST NUMBER: P1010629

CATALOG NUMBER: S123DIP-B560D1025UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	486.0	492.8	503.6	512.4	510.5
115°	547.7	553.6	562.4	572.2	576.1
117.5°	608.4	615.3	620.2	628.0	629.0
120°	664.3	673.1	676.0	683.9	683.9
122.5°	721.1	728.0	731.9	736.8	737.8
125°	772.1	779.9	783.8	785.8	787.7
127.5°	823.0	830.8	835.7	838.7	836.7
130°	870.0	877.9	881.8	885.7	883.7
132.5°	915.1	922.9	925.9	929.8	926.9
135°	961.2	967.0	970.9	973.9	970.9
137.5°	1000.3	1008.2	1010.1	1015.0	1013.1
140°	1039.5	1045.4	1048.3	1052.3	1050.3
142.5°	1075.8	1081.7	1084.6	1087.5	1084.6
145°	1109.1	1116.0	1117.9	1119.9	1119.9
147.5°	1141.4	1146.3	1148.3	1150.2	1145.3
150°	1170.8	1173.8	1175.7	1177.7	1174.7
152.5°	1197.3	1198.3	1199.2	1203.2	1198.3
155°	1221.8	1219.8	1220.8	1225.7	1219.8
157.5°	1241.4	1241.4	1240.4	1246.3	1238.4
160°	1259.0	1258.0	1257.0	1262.9	1256.1
162.5°	1275.7	1272.7	1271.7	1278.6	1272.7
165°	1288.4	1285.5	1284.5	1292.3	1285.5
167.5°	1299.2	1295.3	1295.3	1303.1	1295.3
170°	1308.0	1304.1	1304.1	1311.9	1304.1
172.5°	1313.9	1309.0	1309.9	1317.8	1309.0
175°	1318.8	1313.9	1314.8	1321.7	1313.9
177.5°	1320.7	1315.8	1316.8	1324.6	1314.8
180°	1318.8	1318.8	1318.8	1318.8	1318.8

(END OF REPORT)