

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010956

Luminaire Tested: S123RDIP-B560D585UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010956
REPORT IS A COMBINATION OF REPORTS P993452 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B560D585UB2750-4F0-XX-W2A-F_3500K
Description: Define 3 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4491.0 lumens
Efficiency: N/A
Efficacy: 114.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 39.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010956

CATALOG NUMBER: S123RDIP-B560D585UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1010956

CATALOG NUMBER: S123RDIP-B560D585UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	48	48	48
1	98	93	90	86	90	86	83	80	72	70	68	60	58	57	48	47	46	41	41	41
2	89	82	76	71	82	76	70	66	64	60	57	53	50	48	43	41	39	35	35	35
3	81	72	65	59	75	67	61	56	56	52	48	47	44	41	38	36	34	30	30	30
4	75	64	56	50	68	59	53	47	50	45	41	42	38	35	34	32	29	26	26	26
5	69	57	49	43	63	53	46	41	45	40	36	38	34	31	31	28	26	22	22	22
6	63	51	43	38	58	48	41	36	41	35	31	34	30	27	28	25	23	20	20	20
7	59	46	39	33	54	43	36	31	37	32	28	31	27	24	26	23	20	18	18	18
8	54	42	35	29	50	39	33	28	34	28	25	29	24	21	24	21	18	16	16	16
9	51	39	31	26	47	36	29	25	31	26	22	26	22	19	22	19	17	14	14	14
10	47	35	28	24	44	33	27	22	29	23	20	24	20	17	20	17	15	13	13	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10168	10168	10168
5°	10184	9808	9781
10°	10104	9440	9253
15°	9972	8983	8675
20°	9801	8487	8028
25°	9623	7972	7415
30°	9396	7425	6691
35°	9161	6886	6032
40°	8940	6301	5303
45°	8658	5730	4648
50°	8347	5119	3970
55°	8023	4466	3349
60°	7715	3796	2718
65°	7315	3108	2122
70°	6814	2351	1516
75°	6090	1592	1201
80°	5201	1107	842
85°	3900	599	441

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8658 cd/sqm

TEST NUMBER: P1010956

CATALOG NUMBER: S123RDIP-B560D585UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.8	2.0
10°-20°	247.0	5.5
20°-30°	355.7	7.9
30°-40°	400.5	8.9
40°-50°	383.1	8.5
50°-60°	313.6	7.0
60°-70°	211.5	4.7
70°-80°	106.1	2.4
80°-90°	29.3	0.7
90°-100°	27.2	0.6
100°-110°	131.7	2.9
110°-120°	322.8	7.2
120°-130°	409.8	9.1
130°-140°	437.8	9.7
140°-150°	409.4	9.1
150°-160°	330.2	7.4
160°-170°	213.1	4.7
170°-180°	73.4	1.6
0°-30°	691.5	15.4
0°-40°	1092.0	24.3
0°-60°	1788.8	39.8
0°-90°	2135.6	47.6
90°-120°	481.8	10.7
90°-150°	1738.7	38.7
90°-180°	2355.0	52.4
0°-180°	4491.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	945	945	945	945	945	
5°	945	941	932	938	937	90
15°	901	892	871	867	862	254
25°	820	801	765	749	741	377
35°	709	682	634	601	588	444
45°	583	548	490	446	428	450
55°	443	405	340	296	280	397
65°	303	260	201	163	155	299
75°	160	123	81	74	72	171
85°	41	24	22	20	20	44
90°	1	6	14	16	17	4
95°	35	12	18	22	22	42
105°	171	177	126	24	25	181
115°	321	324	330	335	338	317
125°	452	457	459	460	462	404
135°	563	567	569	571	569	434
145°	650	654	655	656	656	407
155°	716	715	715	718	715	330
165°	755	753	752	757	753	213
175°	773	770	770	774	770	74
180°	773	773	773	773	773	

TEST NUMBER: P1010956

CATALOG NUMBER: S123RDIP-B560D585UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	944.6	944.6	944.6	944.6	944.6
2.5°	948.4	945.4	936.2	944.6	943.1
5°	944.6	940.8	931.6	938.5	936.9
7.5°	937.7	933.9	922.4	927.0	924.7
10°	928.5	923.1	909.4	910.1	906.3
12.5°	915.5	909.4	891.7	891.0	886.4
15°	900.9	892.5	871.0	867.2	861.9
17.5°	883.3	874.1	847.3	839.6	832.0
20°	863.4	851.1	822.0	812.1	802.9
22.5°	841.2	826.6	795.2	782.2	773.8
25°	819.7	800.6	765.3	749.2	740.8
27.5°	793.7	773.0	734.7	713.2	700.2
30°	766.9	743.9	701.0	674.9	662.7
32.5°	740.0	713.2	667.3	638.2	625.1
35°	709.4	681.8	634.3	601.4	587.6
37.5°	678.8	648.9	599.1	562.3	545.5
40°	649.6	615.9	561.5	521.7	504.1
42.5°	616.7	583.0	526.3	481.9	466.6
45°	583.0	548.5	489.5	445.9	427.5
47.5°	550.1	511.7	453.5	406.0	389.9
50°	513.3	477.3	415.2	367.7	350.1
52.5°	480.3	440.5	379.2	329.4	314.1
55°	442.8	405.3	340.1	295.7	280.4
57.5°	409.1	368.5	302.6	260.5	247.4
60°	373.9	331.7	268.1	226.8	213.7
62.5°	338.6	296.5	232.9	194.6	180.8
65°	302.6	260.5	200.7	163.2	154.8
67.5°	266.6	223.7	165.5	137.1	127.9
70°	231.4	190.0	136.4	109.6	101.1
72.5°	196.1	155.5	108.0	87.3	85.0
75°	160.1	123.3	81.2	73.5	72.0
77.5°	127.2	93.5	63.6	59.0	57.5
80°	95.8	64.4	48.3	46.0	44.4
82.5°	65.9	39.8	34.5	32.2	32.2
85°	40.6	23.7	21.5	19.9	19.9
87.5°	18.4	10.0	10.0	9.2	8.4
90°	0.6	6.3	13.8	16.1	17.2
92.5°	13.2	9.8	14.9	18.9	19.5
95°	35.0	11.5	17.8	21.8	21.8
97.5°	63.7	47.6	18.4	23.0	23.5
100°	97.0	108.5	18.9	23.5	24.1
102.5°	134.9	142.4	42.5	23.5	24.7
105°	171.1	177.4	125.7	24.1	25.3
107.5°	209.5	214.7	223.3	134.9	59.7
110°	248.0	252.6	258.9	239.9	157.9



TEST NUMBER: P1010956

CATALOG NUMBER: S123RDIP-B560D585UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	284.7	288.7	295.0	300.2	299.1
115°	320.9	324.3	329.5	335.2	337.5
117.5°	356.5	360.5	363.4	368.0	368.5
120°	389.2	394.4	396.1	400.7	400.7
122.5°	422.5	426.5	428.8	431.7	432.2
125°	452.3	456.9	459.2	460.4	461.5
127.5°	482.2	486.8	489.6	491.4	490.2
130°	509.7	514.3	516.6	518.9	517.8
132.5°	536.1	540.7	542.5	544.8	543.0
135°	563.1	566.6	568.9	570.6	568.9
137.5°	586.1	590.7	591.8	594.7	593.5
140°	609.0	612.5	614.2	616.5	615.4
142.5°	630.3	633.7	635.4	637.2	635.4
145°	649.8	653.8	655.0	656.1	656.1
147.5°	668.7	671.6	672.8	673.9	671.0
150°	686.0	687.7	688.8	690.0	688.3
152.5°	701.5	702.0	702.6	704.9	702.0
155°	715.8	714.7	715.2	718.1	714.7
157.5°	727.3	727.3	726.7	730.2	725.6
160°	737.6	737.0	736.5	739.9	735.9
162.5°	747.4	745.7	745.1	749.1	745.7
165°	754.8	753.1	752.5	757.1	753.1
167.5°	761.2	758.9	758.9	763.5	758.9
170°	766.3	764.0	764.0	768.6	764.0
172.5°	769.8	766.9	767.5	772.1	766.9
175°	772.6	769.8	770.3	774.4	769.8
177.5°	773.8	770.9	771.5	776.1	770.3
180°	772.6	772.6	772.6	772.6	772.6

(END OF REPORT)