

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010632

Luminaire Tested: S123DIP-B560D1025UB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010632
REPORT IS A COMBINATION OF REPORTS P989941 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B560D1025UB2750-4F0-XX-W2A-F_4000K
Description: Define 3 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6330.0 lumens
Efficiency: N/A
Efficacy: 120.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 52.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010632

CATALOG NUMBER: S123DIP-B560D1025UB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010632

CATALOG NUMBER: S123DIP-B560D1025UB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44
1	95	90	87	83	86	82	79	76	66	64	62	52	50	49	38	37	37
2	86	79	73	68	78	72	67	62	58	54	51	45	43	41	34	32	31
3	79	69	62	56	71	63	57	52	51	47	43	40	37	34	30	28	26
4	72	61	53	48	65	56	49	44	45	40	37	36	32	29	27	24	23
5	66	54	47	41	59	50	43	38	40	35	31	32	28	25	24	22	20
6	61	49	41	35	55	44	38	32	36	31	27	29	25	22	22	19	17
7	56	44	36	31	50	40	33	28	33	28	24	26	22	20	20	17	15
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	16	14
9	48	36	29	24	44	33	27	22	27	22	19	22	18	16	17	14	12
10	45	33	26	21	41	30	24	20	25	20	17	20	17	14	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9496	9496	9496
5°	9520	9168	9155
10°	9435	8858	8767
15°	9304	8535	8345
20°	9154	8177	7926
25°	8959	7799	7479
30°	8746	7408	7008
35°	8523	7008	6541
40°	8289	6588	6081
45°	8033	6180	5601
50°	7771	5723	5118
55°	7436	5250	4629
60°	7090	4726	4109
65°	6766	4159	3567
70°	6299	3530	2934
75°	5626	2795	2277
80°	4859	1964	1612
85°	3785	1055	807

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8033 cd/sqm

TEST NUMBER: P1010632

CATALOG NUMBER: S123DIP-B560D1025UB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.2	1.3
10°-20°	234.8	3.7
20°-30°	346.8	5.5
30°-40°	405.1	6.4
40°-50°	407.2	6.4
50°-60°	357.7	5.7
60°-70°	266.4	4.2
70°-80°	151.6	2.4
80°-90°	45.7	0.7
90°-100°	46.6	0.7
100°-110°	225.5	3.6
110°-120°	552.5	8.7
120°-130°	701.4	11.1
130°-140°	749.3	11.8
140°-150°	700.6	11.1
150°-160°	565.1	8.9
160°-170°	364.7	5.8
170°-180°	125.7	2.0
0°-30°	664.8	10.5
0°-40°	1069.9	16.9
0°-60°	1834.9	29.0
0°-90°	2298.6	36.3
90°-120°	824.6	13.0
90°-150°	2975.8	47.0
90°-180°	4031.0	63.7
0°-180°	6330.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	882	882	882	882	882	
5°	883	879	871	878	877	84
15°	840	838	828	834	829	237
25°	763	759	749	750	747	352
35°	660	655	646	641	637	413
45°	541	538	528	519	515	418
55°	410	410	400	391	388	368
65°	280	276	268	262	260	276
75°	148	145	143	139	136	158
85°	39	38	38	36	36	42
90°	1	11	24	28	30	6
95°	60	20	30	37	37	72
105°	293	304	215	41	43	310
115°	549	555	564	574	578	542
125°	774	782	786	788	790	692
135°	964	970	974	977	974	742
145°	1112	1119	1121	1123	1123	696
155°	1225	1223	1224	1229	1223	564
165°	1292	1289	1288	1296	1289	365
175°	1322	1318	1318	1325	1318	126
180°	1322	1322	1322	1322	1322	

TEST NUMBER: P1010632

CATALOG NUMBER: S123DIP-B560D1025UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	882.2	882.2	882.2	882.2	882.2
2.5°	886.0	883.0	874.6	882.2	881.5
5°	883.0	879.2	870.8	878.4	876.9
7.5°	876.1	872.3	864.0	870.8	870.1
10°	867.0	863.2	853.4	860.2	858.7
12.5°	854.9	851.9	842.8	847.3	846.6
15°	840.5	837.5	827.6	833.7	829.1
17.5°	824.6	820.8	810.9	815.5	813.9
20°	806.4	801.8	791.9	795.0	792.7
22.5°	785.9	781.3	771.5	773.7	770.7
25°	763.1	758.6	748.7	749.5	747.2
27.5°	739.6	735.0	724.4	725.2	722.9
30°	713.8	710.0	699.4	699.4	694.1
32.5°	688.0	682.7	675.1	669.8	667.5
35°	660.0	655.4	645.5	641.0	637.2
37.5°	631.9	625.8	616.0	610.6	608.4
40°	602.3	597.7	587.1	581.1	578.0
42.5°	572.7	567.4	556.8	550.7	547.7
45°	540.9	537.8	528.0	518.9	515.1
47.5°	509.8	505.2	496.1	487.0	484.0
50°	477.9	474.1	464.2	455.9	451.3
52.5°	444.5	442.2	431.6	424.8	420.2
55°	410.4	409.6	399.8	391.4	387.6
57.5°	378.5	375.5	367.9	360.3	355.8
60°	343.6	342.9	333.8	326.9	323.1
62.5°	312.5	310.3	301.1	294.3	292.0
65°	279.9	276.1	268.5	262.5	260.2
67.5°	245.0	242.0	235.9	230.6	227.6
70°	213.9	209.4	204.8	199.5	195.7
72.5°	181.3	178.3	173.0	168.4	166.9
75°	147.9	144.9	142.6	138.8	136.5
77.5°	118.3	116.8	113.8	110.8	110.8
80°	89.5	87.2	85.7	85.0	85.0
82.5°	61.4	61.4	61.4	59.9	59.2
85°	39.4	37.9	37.9	36.4	36.4
87.5°	19.7	17.4	16.7	15.9	15.9
90°	1.0	10.8	23.6	27.5	29.5
92.5°	22.6	16.7	25.5	32.4	33.4
95°	59.9	19.6	30.5	37.3	37.3
97.5°	109.1	81.5	31.4	39.3	40.3
100°	166.0	185.7	32.4	40.3	41.3
102.5°	230.9	243.6	72.7	40.3	42.2
105°	292.8	303.6	215.2	41.3	43.2
107.5°	358.6	367.4	382.2	230.9	102.2
110°	424.4	432.3	443.1	410.7	270.2

TEST NUMBER: P1010632

CATALOG NUMBER: S123DIP-B560D1025UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	487.3	494.2	505.0	513.8	511.9
115°	549.2	555.1	563.9	573.7	577.7
117.5°	610.1	617.0	621.9	629.7	630.7
120°	666.1	674.9	677.9	685.7	685.7
122.5°	723.1	730.0	733.9	738.8	739.8
125°	774.2	782.0	786.0	787.9	789.9
127.5°	825.3	833.1	838.0	841.0	839.0
130°	872.4	880.3	884.2	888.1	886.2
132.5°	917.6	925.5	928.4	932.3	929.4
135°	963.8	969.7	973.6	976.6	973.6
137.5°	1003.1	1010.9	1012.9	1017.8	1015.8
140°	1042.4	1048.3	1051.2	1055.1	1053.2
142.5°	1078.7	1084.6	1087.6	1090.5	1087.6
145°	1112.1	1119.0	1121.0	1122.9	1122.9
147.5°	1144.5	1149.5	1151.4	1153.4	1148.5
150°	1174.0	1177.0	1178.9	1180.9	1178.0
152.5°	1200.5	1201.5	1202.5	1206.4	1201.5
155°	1225.1	1223.1	1224.1	1229.0	1223.1
157.5°	1244.8	1244.8	1243.8	1249.7	1241.8
160°	1262.4	1261.5	1260.5	1266.4	1259.5
162.5°	1279.1	1276.2	1275.2	1282.1	1276.2
165°	1291.9	1289.0	1288.0	1295.8	1289.0
167.5°	1302.7	1298.8	1298.8	1306.7	1298.8
170°	1311.6	1307.6	1307.6	1315.5	1307.6
172.5°	1317.5	1312.5	1313.5	1321.4	1312.5
175°	1322.4	1317.5	1318.4	1325.3	1317.5
177.5°	1324.3	1319.4	1320.4	1328.3	1318.4
180°	1322.4	1322.4	1322.4	1322.4	1322.4

(END OF REPORT)