

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010957

Luminaire Tested: S123RDIP-B560D585UB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010957
REPORT IS A COMBINATION OF REPORTS P993453 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B560D585UB2750-4F0-XX-W2A-F_4000K
Description: Define 3 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4446.0 lumens
Efficiency: N/A
Efficacy: 112.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 39.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010957

CATALOG NUMBER: S123RDIP-B560D585UB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010957

CATALOG NUMBER: S123RDIP-B560D585UB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54
1	98	93	90	86	90	86	83	80	72	70	68	60	58	57	48	47	46
2	89	82	76	71	82	76	70	66	64	60	57	53	50	48	43	41	39
3	81	72	65	59	75	67	61	56	56	52	48	47	44	41	38	36	34
4	75	64	56	50	68	59	53	47	50	45	41	42	38	35	34	32	29
5	69	57	49	43	63	53	46	41	45	40	36	38	34	31	31	28	26
6	63	51	43	38	58	48	41	36	41	35	31	34	30	27	28	25	23
7	59	46	39	33	54	43	36	31	37	32	28	31	27	24	26	23	20
8	54	42	35	29	50	39	33	28	34	28	25	29	24	21	24	21	18
9	51	39	31	26	47	36	29	25	31	26	22	26	22	19	22	19	17
10	47	35	28	24	44	33	27	22	29	23	20	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10067	10067	10067
5°	10084	9711	9685
10°	10005	9346	9162
15°	9875	8895	8589
20°	9704	8404	7949
25°	9529	7894	7342
30°	9303	7352	6625
35°	9071	6819	5972
40°	8853	6239	5251
45°	8574	5673	4603
50°	8264	5069	3932
55°	7944	4422	3316
60°	7639	3759	2691
65°	7242	3077	2100
70°	6747	2327	1501
75°	6029	1576	1190
80°	5147	1096	834
85°	3861	590	437

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 8574 cd/sqm

TEST NUMBER: P1010957

CATALOG NUMBER: S123RDIP-B560D585UB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.9	2.0
10°-20°	244.6	5.5
20°-30°	352.2	7.9
30°-40°	396.6	8.9
40°-50°	379.4	8.5
50°-60°	310.5	7.0
60°-70°	209.4	4.7
70°-80°	105.0	2.4
80°-90°	29.0	0.7
90°-100°	27.0	0.6
100°-110°	130.4	2.9
110°-120°	319.5	7.2
120°-130°	405.6	9.1
130°-140°	433.3	9.7
140°-150°	405.2	9.1
150°-160°	326.8	7.4
160°-170°	210.9	4.7
170°-180°	72.7	1.6
0°-30°	684.7	15.4
0°-40°	1081.3	24.3
0°-60°	1771.2	39.8
0°-90°	2114.5	47.6
90°-120°	476.9	10.7
90°-150°	1721.0	38.7
90°-180°	2331.0	52.4
0°-180°	4446.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	935	935	935	935	935	
5°	935	932	922	929	928	89
15°	892	884	862	859	853	251
25°	812	793	758	742	734	373
35°	702	675	628	596	582	440
45°	577	543	485	442	423	445
55°	438	401	337	293	278	393
65°	300	258	199	162	153	297
75°	158	122	80	73	71	169
85°	40	24	21	20	20	44
90°	1	6	14	16	17	4
95°	35	11	18	22	22	41
105°	169	176	124	24	25	180
115°	318	321	326	332	334	314
125°	448	452	454	456	457	400
135°	557	561	563	565	563	429
145°	643	647	648	649	649	403
155°	708	707	708	711	707	326
165°	747	746	745	749	746	211
175°	765	762	762	766	762	73
180°	765	765	765	765	765	

TEST NUMBER: P1010957

CATALOG NUMBER: S123RDIP-B560D585UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	935.3	935.3	935.3	935.3	935.3
2.5°	939.1	936.1	927.0	935.3	933.8
5°	935.3	931.5	922.4	929.2	927.7
7.5°	928.5	924.7	913.3	917.8	915.6
10°	919.4	914.1	900.4	901.2	897.4
12.5°	906.5	900.4	883.0	882.2	877.6
15°	892.1	883.7	862.5	858.7	853.4
17.5°	874.6	865.5	839.0	831.4	823.8
20°	854.9	842.8	813.9	804.1	795.0
22.5°	832.9	818.5	787.4	774.5	766.1
25°	811.7	792.7	757.8	741.9	733.5
27.5°	785.9	765.4	727.5	706.2	693.3
30°	759.3	736.6	694.1	668.3	656.1
32.5°	732.8	706.2	660.7	631.9	619.0
35°	702.4	675.1	628.1	595.5	581.8
37.5°	672.1	642.5	593.2	556.8	540.1
40°	643.3	609.9	556.0	516.6	499.1
42.5°	610.6	577.3	521.1	477.1	462.0
45°	577.3	543.1	484.7	441.5	423.3
47.5°	544.6	506.7	449.1	402.0	386.1
50°	508.2	472.6	411.1	364.1	346.7
52.5°	475.6	436.2	375.5	326.2	311.0
55°	438.4	401.3	336.8	292.8	277.6
57.5°	405.1	364.9	299.6	257.9	245.0
60°	370.2	328.5	265.5	224.5	211.6
62.5°	335.3	293.6	230.6	192.7	179.0
65°	299.6	257.9	198.7	161.6	153.2
67.5°	264.0	221.5	163.8	135.8	126.7
70°	229.1	188.1	135.0	108.5	100.1
72.5°	194.2	154.0	107.0	86.5	84.2
75°	158.5	122.1	80.4	72.8	71.3
77.5°	125.9	92.5	63.0	58.4	56.9
80°	94.8	63.7	47.8	45.5	44.0
82.5°	65.2	39.4	34.1	31.9	31.9
85°	40.2	23.5	21.2	19.7	19.7
87.5°	18.2	9.9	9.9	9.1	8.3
90°	0.6	6.2	13.6	15.9	17.0
92.5°	13.1	9.7	14.8	18.7	19.3
95°	34.7	11.4	17.6	21.6	21.6
97.5°	63.1	47.2	18.2	22.7	23.3
100°	96.0	107.4	18.7	23.3	23.9
102.5°	133.5	140.9	42.0	23.3	24.4
105°	169.3	175.6	124.4	23.9	25.0
107.5°	207.4	212.5	221.0	133.5	59.1
110°	245.5	250.0	256.2	237.5	156.2

TEST NUMBER: P1010957

CATALOG NUMBER: S123RDIP-B560D585UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	281.8	285.8	292.0	297.2	296.0
115°	317.6	321.0	326.1	331.8	334.1
117.5°	352.8	356.8	359.7	364.2	364.8
120°	385.2	390.3	392.0	396.6	396.6
122.5°	418.2	422.2	424.4	427.3	427.8
125°	447.7	452.3	454.5	455.7	456.8
127.5°	477.3	481.8	484.7	486.4	485.2
130°	504.5	509.1	511.4	513.6	512.5
132.5°	530.7	535.2	536.9	539.2	537.5
135°	557.4	560.8	563.1	564.8	563.1
137.5°	580.1	584.7	585.8	588.6	587.5
140°	602.8	606.2	608.0	610.2	609.1
142.5°	623.9	627.3	629.0	630.7	629.0
145°	643.2	647.2	648.3	649.4	649.4
147.5°	661.9	664.8	665.9	667.0	664.2
150°	679.0	680.7	681.8	683.0	681.2
152.5°	694.3	694.9	695.5	697.7	694.9
155°	708.5	707.4	708.0	710.8	707.4
157.5°	719.9	719.9	719.3	722.7	718.2
160°	730.1	729.5	729.0	732.4	728.4
162.5°	739.8	738.1	737.5	741.5	738.1
165°	747.2	745.5	744.9	749.4	745.5
167.5°	753.4	751.1	751.1	755.7	751.1
170°	758.5	756.2	756.2	760.8	756.2
172.5°	761.9	759.1	759.7	764.2	759.1
175°	764.8	761.9	762.5	766.5	761.9
177.5°	765.9	763.1	763.6	768.2	762.5
180°	764.8	764.8	764.8	764.8	764.8

(END OF REPORT)