

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010644

Luminaire Tested: S123DIP-B560D1195UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010644
REPORT IS A COMBINATION OF REPORTS P989998 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B560D1195UB2750-4F0-XX-W2A-F_2700K
Description: Define 3 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7015.0 lumens
Efficiency: N/A
Efficacy: 118.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 59
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010644

CATALOG NUMBER: S123DIP-B560D1195UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1010644

CATALOG NUMBER: S123DIP-B560D1195UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40
1	94	90	86	82	84	81	78	75	64	62	60	49	48	47	35	35	34
2	85	78	72	67	77	71	66	61	56	53	50	43	41	39	31	30	28
3	78	69	62	56	70	62	56	51	50	45	42	38	35	33	28	26	24
4	71	61	53	47	64	55	48	43	44	39	36	34	31	28	25	23	21
5	65	54	46	40	58	49	42	37	39	34	31	30	27	24	22	20	18
6	60	48	40	35	54	44	37	32	35	30	26	27	24	21	20	18	16
7	55	43	36	30	50	39	33	28	32	27	23	25	21	19	18	16	14
8	51	39	32	27	46	36	29	25	29	24	21	23	19	17	17	14	13
9	48	36	29	24	43	33	26	22	27	22	18	21	17	15	15	13	11
10	44	33	26	21	40	30	24	19	24	20	16	19	16	13	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9467	9467	9467
5°	9491	9141	9126
10°	9406	8831	8741
15°	9275	8509	8320
20°	9125	8152	7902
25°	8932	7775	7456
30°	8719	7385	6987
35°	8496	6987	6521
40°	8264	6568	6063
45°	8008	6161	5583
50°	7747	5706	5103
55°	7413	5233	4615
60°	7069	4712	4097
65°	6747	4146	3556
70°	6281	3520	2925
75°	5611	2788	2271
80°	4843	1960	1606
85°	3775	1053	805

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8008 cd/sqm

TEST NUMBER: P1010644

CATALOG NUMBER: S123DIP-B560D1195UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	82.9	1.2
10°-20°	234.1	3.3
20°-30°	345.8	4.9
30°-40°	403.8	5.8
40°-50°	406.0	5.8
50°-60°	356.6	5.1
60°-70°	265.6	3.8
70°-80°	151.1	2.2
80°-90°	46.1	0.7
90°-100°	54.6	0.8
100°-110°	264.1	3.8
110°-120°	647.3	9.2
120°-130°	821.7	11.7
130°-140°	877.8	12.5
140°-150°	820.8	11.7
150°-160°	662.1	9.4
160°-170°	427.3	6.1
170°-180°	147.2	2.1
0°-30°	662.8	9.4
0°-40°	1066.7	15.2
0°-60°	1829.3	26.1
0°-90°	2292.1	32.7
90°-120°	966.0	13.8
90°-150°	3486.3	49.7
90°-180°	4723.0	67.3
0°-180°	7015.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	880	880	880	880	880	
5°	880	876	868	876	874	83
15°	838	835	825	831	827	236
25°	761	756	746	747	745	350
35°	658	653	644	639	635	412
45°	539	536	526	517	514	416
55°	409	408	398	390	386	367
65°	279	275	268	262	259	275
75°	148	144	142	138	136	158
85°	39	38	38	36	36	42
90°	1	13	28	32	34	7
95°	70	23	36	44	44	84
105°	343	356	252	48	51	364
115°	643	650	661	672	677	635
125°	907	916	921	923	925	810
135°	1129	1136	1141	1144	1141	869
145°	1303	1311	1313	1316	1316	816
155°	1435	1433	1434	1440	1433	661
165°	1514	1510	1509	1518	1510	428
175°	1549	1544	1545	1553	1544	147
180°	1549	1549	1549	1549	1549	

TEST NUMBER: P1010644

CATALOG NUMBER: S123DIP-B560D1195UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	879.5	879.5	879.5	879.5	879.5
2.5°	883.3	880.3	872.0	879.5	878.8
5°	880.3	876.5	868.2	875.7	874.2
7.5°	873.5	869.7	861.4	868.2	867.4
10°	864.4	860.6	850.8	857.6	856.1
12.5°	852.3	849.3	840.2	844.7	844.0
15°	837.9	834.9	825.1	831.1	826.6
17.5°	822.0	818.3	808.4	813.0	811.5
20°	803.9	799.4	789.5	792.6	790.3
22.5°	783.5	778.9	769.1	771.4	768.4
25°	760.8	756.3	746.4	747.2	744.9
27.5°	737.3	732.8	722.2	723.0	720.7
30°	711.6	707.9	697.3	697.3	692.0
32.5°	685.9	680.6	673.1	667.8	665.5
35°	657.9	653.4	643.6	639.0	635.3
37.5°	630.0	623.9	614.1	608.8	606.5
40°	600.5	595.9	585.3	579.3	576.3
42.5°	571.0	565.7	555.1	549.0	546.0
45°	539.2	536.2	526.4	517.3	513.5
47.5°	508.2	503.7	494.6	485.5	482.5
50°	476.4	472.7	462.8	454.5	450.0
52.5°	443.2	440.9	430.3	423.5	419.0
55°	409.1	408.4	398.5	390.2	386.4
57.5°	377.4	374.3	366.8	359.2	354.7
60°	342.6	341.8	332.8	325.9	322.2
62.5°	311.6	309.3	300.2	293.4	291.2
65°	279.1	275.3	267.7	261.7	259.4
67.5°	244.3	241.2	235.2	229.9	226.9
70°	213.3	208.7	204.2	198.9	195.1
72.5°	180.7	177.7	172.4	167.9	166.4
75°	147.5	144.4	142.2	138.4	136.1
77.5°	118.0	116.5	113.4	110.4	110.4
80°	89.2	87.0	85.5	84.7	84.7
82.5°	61.3	61.3	61.3	59.7	59.0
85°	39.3	37.8	37.8	36.3	36.3
87.5°	19.7	17.4	16.6	15.9	15.9
90°	1.2	12.7	27.6	32.2	34.5
92.5°	26.5	19.6	29.9	38.0	39.1
95°	70.2	23.0	35.7	43.7	43.7
97.5°	127.8	95.5	36.8	46.0	47.2
100°	194.5	217.5	38.0	47.2	48.3
102.5°	270.5	285.4	85.2	47.2	49.5
105°	343.0	355.7	252.1	48.3	50.6
107.5°	420.1	430.5	447.7	270.5	119.7
110°	497.2	506.4	519.1	481.1	316.5

TEST NUMBER: P1010644

CATALOG NUMBER: S123DIP-B560D1195UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	570.9	578.9	591.6	602.0	599.7
115°	643.4	650.3	660.7	672.2	676.8
117.5°	714.8	722.8	728.6	737.8	738.9
120°	780.4	790.7	794.2	803.4	803.4
122.5°	847.1	855.2	859.8	865.5	866.7
125°	907.0	916.2	920.8	923.1	925.4
127.5°	966.8	976.0	981.8	985.2	982.9
130°	1022.1	1031.3	1035.9	1040.5	1038.2
132.5°	1075.0	1084.2	1087.7	1092.3	1088.8
135°	1129.1	1136.0	1140.6	1144.1	1140.6
137.5°	1175.1	1184.4	1186.7	1192.4	1190.1
140°	1221.2	1228.1	1231.5	1236.1	1233.8
142.5°	1263.8	1270.7	1274.1	1277.6	1274.1
145°	1302.9	1311.0	1313.3	1315.6	1315.6
147.5°	1340.9	1346.6	1348.9	1351.2	1345.5
150°	1375.4	1378.9	1381.2	1383.5	1380.0
152.5°	1406.5	1407.6	1408.8	1413.4	1407.6
155°	1435.3	1433.0	1434.1	1439.9	1433.0
157.5°	1458.3	1458.3	1457.1	1464.0	1454.8
160°	1479.0	1477.9	1476.7	1483.6	1475.6
162.5°	1498.6	1495.1	1494.0	1502.0	1495.1
165°	1513.5	1510.1	1508.9	1518.1	1510.1
167.5°	1526.2	1521.6	1521.6	1530.8	1521.6
170°	1536.6	1531.9	1531.9	1541.2	1531.9
172.5°	1543.5	1537.7	1538.9	1548.1	1537.7
175°	1549.2	1543.5	1544.6	1552.7	1543.5
177.5°	1551.5	1545.8	1546.9	1556.1	1544.6
180°	1549.2	1549.2	1549.2	1549.2	1549.2

(END OF REPORT)