

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010964

Luminaire Tested: S123RDIP-B560D805UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010964
REPORT IS A COMBINATION OF REPORTS P993490 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B560D805UB2750-4F0-XX-W2A-F_2700K
Description: Define 3 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5215.0 lumens
Efficiency: N/A
Efficacy: 115.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 45.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010964

CATALOG NUMBER: S123RDIP-B560D805UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1010964

CATALOG NUMBER: S123RDIP-B560D805UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	47	47	47
1	96	92	88	85	87	84	81	78	69	67	65	55	53	52	42	41	40
2	88	80	74	70	80	73	68	64	61	57	54	49	46	44	37	36	34
3	80	71	64	58	73	65	59	54	54	49	45	43	40	37	33	31	30
4	73	63	55	49	66	58	51	46	48	43	39	39	35	32	30	28	26
5	67	56	48	42	61	51	45	39	43	38	34	35	31	28	27	25	23
6	62	50	42	37	56	46	39	34	39	33	29	31	28	25	25	22	20
7	57	45	38	32	52	42	35	30	35	30	26	29	25	22	23	20	18
8	53	41	34	28	48	38	31	27	32	27	23	26	22	19	21	18	16
9	49	38	30	25	45	35	28	24	29	24	21	24	20	18	19	16	14
10	46	34	27	23	42	32	26	21	27	22	19	22	19	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10038	10038	10038
5°	10055	9684	9658
10°	9977	9319	9136
15°	9846	8869	8564
20°	9677	8380	7926
25°	9501	7871	7321
30°	9277	7330	6607
35°	9045	6799	5956
40°	8827	6221	5236
45°	8548	5657	4590
50°	8241	5055	3920
55°	7922	4409	3306
60°	7616	3748	2683
65°	7223	3070	2095
70°	6726	2320	1496
75°	6014	1572	1186
80°	5130	1093	833
85°	3852	590	437

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8548 cd/sqm

TEST NUMBER: P1010964

CATALOG NUMBER: S123RDIP-B560D805UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.7	1.7
10°-20°	243.9	4.7
20°-30°	351.2	6.7
30°-40°	395.5	7.6
40°-50°	378.3	7.3
50°-60°	309.7	5.9
60°-70°	208.8	4.0
70°-80°	104.7	2.0
80°-90°	29.4	0.6
90°-100°	35.9	0.7
100°-110°	173.7	3.3
110°-120°	425.7	8.2
120°-130°	540.4	10.4
130°-140°	577.3	11.1
140°-150°	539.8	10.4
150°-160°	435.4	8.3
160°-170°	281.0	5.4
170°-180°	96.8	1.9
0°-30°	682.7	13.1
0°-40°	1078.2	20.7
0°-60°	1766.1	33.9
0°-90°	2109.0	40.4
90°-120°	635.3	12.2
90°-150°	2292.7	44.0
90°-180°	3106.0	59.6
0°-180°	5215.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	933	933	933	933	933	
5°	933	929	920	927	925	88
15°	890	881	860	856	851	251
25°	809	790	756	740	731	372
35°	700	673	626	594	580	438
45°	576	542	483	440	422	444
55°	437	400	336	292	277	392
65°	299	257	198	161	153	296
75°	158	122	80	73	71	168
85°	40	23	21	20	20	44
90°	1	8	18	21	23	5
95°	46	15	24	29	29	55
105°	226	234	166	32	33	239
115°	423	428	434	442	445	418
125°	596	602	606	607	609	533
135°	742	747	750	752	750	572
145°	857	862	864	865	865	536
155°	944	942	943	947	942	435
165°	995	993	992	998	993	281
175°	1019	1015	1016	1021	1015	97
180°	1019	1019	1019	1019	1019	

TEST NUMBER: P1010964

CATALOG NUMBER: S123RDIP-B560D805UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	932.6	932.6	932.6	932.6	932.6
2.5°	936.4	933.4	924.3	932.6	931.1
5°	932.6	928.9	919.8	926.6	925.1
7.5°	925.8	922.1	910.7	915.2	913.0
10°	916.8	911.5	897.8	898.6	894.8
12.5°	903.9	897.8	880.4	879.7	875.2
15°	889.5	881.2	860.0	856.2	850.9
17.5°	872.1	863.1	836.6	829.0	821.4
20°	852.5	840.4	811.6	801.8	792.7
22.5°	830.5	816.2	785.1	772.3	764.0
25°	809.3	790.4	755.6	739.8	731.4
27.5°	783.6	763.2	725.4	704.2	691.3
30°	757.2	734.5	692.1	666.4	654.3
32.5°	730.7	704.2	658.8	630.1	617.2
35°	700.4	673.2	626.3	593.8	580.2
37.5°	670.2	640.7	591.5	555.2	538.6
40°	641.4	608.1	554.4	515.1	497.7
42.5°	608.9	575.6	519.6	475.8	460.6
45°	575.6	541.6	483.3	440.2	422.1
47.5°	543.1	505.3	447.8	400.9	385.0
50°	506.8	471.2	410.0	363.1	345.7
52.5°	474.3	434.9	374.4	325.3	310.1
55°	437.2	400.1	335.8	292.0	276.8
57.5°	403.9	363.8	298.8	257.2	244.3
60°	369.1	327.5	264.7	223.9	211.0
62.5°	334.3	292.7	229.9	192.1	178.5
65°	298.8	257.2	198.2	161.1	152.8
67.5°	263.2	220.9	163.4	135.4	126.3
70°	228.4	187.6	134.6	108.2	99.8
72.5°	193.6	153.5	106.7	86.2	84.0
75°	158.1	121.8	80.2	72.6	71.1
77.5°	125.6	92.3	62.8	58.2	56.7
80°	94.5	63.5	47.7	45.4	43.9
82.5°	65.1	39.3	34.0	31.8	31.8
85°	40.1	23.4	21.2	19.7	19.7
87.5°	18.2	9.8	9.8	9.1	8.3
90°	0.8	8.3	18.2	21.2	22.7
92.5°	17.4	12.9	19.7	25.0	25.7
95°	46.2	15.1	23.5	28.8	28.8
97.5°	84.0	62.8	24.2	30.3	31.0
100°	127.9	143.1	25.0	31.0	31.8
102.5°	177.9	187.7	56.0	31.0	32.5
105°	225.6	233.9	165.8	31.8	33.3
107.5°	276.3	283.1	294.4	177.9	78.7
110°	327.0	333.0	341.4	316.4	208.2

TEST NUMBER: P1010964

CATALOG NUMBER: S123RDIP-B560D805UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	375.4	380.7	389.1	395.9	394.4
115°	423.1	427.7	434.5	442.0	445.1
117.5°	470.1	475.3	479.1	485.2	485.9
120°	513.2	520.0	522.3	528.3	528.3
122.5°	557.1	562.4	565.4	569.2	570.0
125°	596.5	602.5	605.5	607.1	608.6
127.5°	635.8	641.9	645.7	647.9	646.4
130°	672.2	678.2	681.2	684.3	682.7
132.5°	707.0	713.0	715.3	718.3	716.1
135°	742.5	747.1	750.1	752.4	750.1
137.5°	772.8	778.9	780.4	784.2	782.7
140°	803.1	807.6	809.9	812.9	811.4
142.5°	831.1	835.6	837.9	840.2	837.9
145°	856.8	862.1	863.7	865.2	865.2
147.5°	881.8	885.6	887.1	888.6	884.8
150°	904.5	906.8	908.3	909.8	907.6
152.5°	925.0	925.7	926.5	929.5	925.7
155°	943.9	942.4	943.1	946.9	942.4
157.5°	959.0	959.0	958.3	962.8	956.8
160°	972.6	971.9	971.1	975.7	970.4
162.5°	985.5	983.2	982.5	987.8	983.2
165°	995.4	993.1	992.3	998.4	993.1
167.5°	1003.7	1000.7	1000.7	1006.7	1000.7
170°	1010.5	1007.5	1007.5	1013.5	1007.5
172.5°	1015.0	1011.3	1012.0	1018.1	1011.3
175°	1018.8	1015.0	1015.8	1021.1	1015.0
177.5°	1020.3	1016.6	1017.3	1023.4	1015.8
180°	1018.8	1018.8	1018.8	1018.8	1018.8

(END OF REPORT)