

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010965

Luminaire Tested: S123RDIP-B560D805UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010965
REPORT IS A COMBINATION OF REPORTS P993491 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B560D805UB2750-4F0-XX-W2A-F_3000K
Description: Define 3 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5260.0 lumens
Efficiency: N/A
Efficacy: 116.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 45.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010965

CATALOG NUMBER: S123RDIP-B560D805UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010965

CATALOG NUMBER: S123RDIP-B560D805UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	47	47	47			40
1	96	92	88	85	87	84	81	78	69	67	65	55	53	52	42	41	40			35
2	88	80	74	70	80	73	68	64	61	57	54	49	46	44	37	36	34			29
3	80	71	64	58	73	65	59	54	54	49	45	43	40	37	33	31	30			25
4	73	63	55	49	66	58	51	46	48	43	39	39	35	32	30	28	26			22
5	67	56	48	42	61	51	45	39	43	38	34	35	31	28	27	25	23			19
6	62	50	42	37	56	46	39	34	39	33	29	31	28	25	25	22	20			17
7	57	45	38	32	52	42	35	30	35	30	26	29	25	22	23	20	18			15
8	53	41	34	28	48	38	31	27	32	27	23	26	22	19	21	18	16			14
9	49	38	30	25	45	35	28	24	29	24	21	24	20	18	19	16	14			12
10	46	34	27	23	42	32	26	21	27	22	19	22	19	16	18	15	13			11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10125	10125	10125
5°	10141	9766	9740
10°	10061	9399	9214
15°	9930	8946	8638
20°	9759	8451	7994
25°	9583	7939	7384
30°	9356	7393	6663
35°	9123	6857	6006
40°	8903	6275	5281
45°	8621	5706	4629
50°	8311	5098	3953
55°	7989	4447	3335
60°	7682	3780	2706
65°	7284	3096	2113
70°	6785	2341	1510
75°	6063	1586	1196
80°	5179	1103	838
85°	3881	596	439

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8621 cd/sqm

TEST NUMBER: P1010965

CATALOG NUMBER: S123RDIP-B560D805UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.4	1.7
10°-20°	246.0	4.7
20°-30°	354.2	6.7
30°-40°	398.8	7.6
40°-50°	381.5	7.3
50°-60°	312.3	5.9
60°-70°	210.6	4.0
70°-80°	105.6	2.0
80°-90°	29.7	0.6
90°-100°	36.2	0.7
100°-110°	175.2	3.3
110°-120°	429.3	8.2
120°-130°	545.1	10.4
130°-140°	582.3	11.1
140°-150°	544.5	10.4
150°-160°	439.2	8.3
160°-170°	283.4	5.4
170°-180°	97.7	1.9
0°-30°	688.6	13.1
0°-40°	1087.4	20.7
0°-60°	1781.2	33.9
0°-90°	2127.1	40.4
90°-120°	640.8	12.2
90°-150°	2312.6	44.0
90°-180°	3133.0	59.6
0°-180°	5260.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	941	941	941	941	941	
5°	941	937	928	934	933	89
15°	897	889	867	864	858	253
25°	816	797	762	746	738	375
35°	706	679	632	599	585	442
45°	580	546	488	444	426	448
55°	441	404	339	294	279	395
65°	301	259	200	162	154	298
75°	159	123	81	73	72	170
85°	40	24	21	20	20	44
90°	1	8	18	21	23	5
95°	47	15	24	29	29	56
105°	228	236	167	32	34	241
115°	427	431	438	446	449	422
125°	602	608	611	612	614	538
135°	749	754	757	759	757	577
145°	864	870	871	873	873	541
155°	952	951	951	955	951	439
165°	1004	1002	1001	1007	1002	284
175°	1028	1024	1025	1030	1024	98
180°	1028	1028	1028	1028	1028	

TEST NUMBER: P1010965

CATALOG NUMBER: S123RDIP-B560D805UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	940.6	940.6	940.6	940.6	940.6
2.5°	944.4	941.4	932.2	940.6	939.1
5°	940.6	936.8	927.6	934.5	933.0
7.5°	933.7	929.9	918.5	923.1	920.8
10°	924.6	919.2	905.5	906.3	902.5
12.5°	911.6	905.5	888.0	887.2	882.6
15°	897.1	888.7	867.4	863.6	858.2
17.5°	879.6	870.4	843.7	836.1	828.5
20°	859.7	847.5	818.5	808.6	799.5
22.5°	837.6	823.1	791.8	778.9	770.5
25°	816.3	797.2	762.1	746.1	737.7
27.5°	790.3	769.7	731.6	710.2	697.3
30°	763.6	740.7	698.0	672.1	659.9
32.5°	736.9	710.2	664.5	635.5	622.5
35°	706.4	678.9	631.6	598.8	585.1
37.5°	675.9	646.1	596.6	559.9	543.2
40°	646.9	613.3	559.2	519.5	502.0
42.5°	614.1	580.5	524.1	479.8	464.6
45°	580.5	546.2	487.5	444.0	425.7
47.5°	547.7	509.6	451.6	404.3	388.3
50°	511.1	475.3	413.5	366.2	348.6
52.5°	478.3	438.6	377.6	328.0	312.8
55°	440.9	403.6	338.7	294.5	279.2
57.5°	407.4	366.9	301.3	259.4	246.4
60°	372.3	330.3	267.0	225.8	212.8
62.5°	337.2	295.2	231.9	193.8	180.0
65°	301.3	259.4	199.9	162.5	154.1
67.5°	265.5	222.8	164.8	136.6	127.4
70°	230.4	189.2	135.8	109.1	100.7
72.5°	195.3	154.9	107.6	87.0	84.7
75°	159.4	122.8	80.9	73.2	71.7
77.5°	126.6	93.1	63.3	58.7	57.2
80°	95.4	64.1	48.1	45.8	44.2
82.5°	65.6	39.7	34.3	32.0	32.0
85°	40.4	23.6	21.4	19.8	19.8
87.5°	18.3	9.9	9.9	9.2	8.4
90°	0.8	8.4	18.3	21.4	22.9
92.5°	17.6	13.0	19.9	25.2	26.0
95°	46.6	15.3	23.7	29.0	29.0
97.5°	84.7	63.4	24.4	30.5	31.3
100°	129.0	144.3	25.2	31.3	32.1
102.5°	179.4	189.3	56.5	31.3	32.8
105°	227.5	235.9	167.2	32.1	33.6
107.5°	278.7	285.5	297.0	179.4	79.4
110°	329.8	335.9	344.3	319.1	210.0

TEST NUMBER: P1010965

CATALOG NUMBER: S123RDIP-B560D805UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	378.7	384.0	392.4	399.3	397.8
115°	426.8	431.4	438.2	445.9	448.9
117.5°	474.1	479.5	483.3	489.4	490.2
120°	517.7	524.5	526.8	532.9	532.9
122.5°	561.9	567.3	570.3	574.2	574.9
125°	601.6	607.7	610.8	612.3	613.9
127.5°	641.3	647.4	651.3	653.6	652.0
130°	678.0	684.1	687.2	690.2	688.7
132.5°	713.1	719.2	721.5	724.6	722.3
135°	749.0	753.6	756.6	758.9	756.6
137.5°	779.5	785.6	787.2	791.0	789.5
140°	810.1	814.7	816.9	820.0	818.5
142.5°	838.3	842.9	845.2	847.5	845.2
145°	864.3	869.6	871.2	872.7	872.7
147.5°	889.5	893.3	894.8	896.4	892.5
150°	912.4	914.7	916.2	917.7	915.4
152.5°	933.0	933.8	934.5	937.6	933.8
155°	952.1	950.6	951.3	955.1	950.6
157.5°	967.4	967.4	966.6	971.2	965.1
160°	981.1	980.3	979.6	984.2	978.8
162.5°	994.1	991.8	991.0	996.4	991.8
165°	1004.0	1001.7	1001.0	1007.1	1001.7
167.5°	1012.4	1009.3	1009.3	1015.5	1009.3
170°	1019.3	1016.2	1016.2	1022.3	1016.2
172.5°	1023.9	1020.0	1020.8	1026.9	1020.0
175°	1027.7	1023.9	1024.6	1030.0	1023.9
177.5°	1029.2	1025.4	1026.1	1032.3	1024.6
180°	1027.7	1027.7	1027.7	1027.7	1027.7

(END OF REPORT)